


# I<sub>CC</sub> vs V<sub>CC</sub> (High-speed on-chip oscillator mode)

Prepared on Oct. 20, 2006

R5F21258SNFP(Topr=-20 to 85degrees C)    — 85degreesC    — 25degreesC  
R5F21258SDFP(Topr=-40 to 85degrees C)    — -40degreesC  
no division  
XIN clock off  
High-speed on-chip oscillator on fOCO = 20 MHz  
Low-speed on-chip oscillator on = 125 kHz



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.