

# M16C R8C E100 Emulator Software

## V.1.03 Release 01

R20UT0659EJ0100

Rev.1.00

Jun 16, 2011

### Release Notes

---

Thank you for purchasing our product. There are several precautions which need to be taken while using this product. Please also read the precautions on the High-performance Embedded Workshop described in the High-performance Embedded Workshop Release Notes.

#### Contents

1.	MCU Unit and Target MCU .....	2
2.	Contents of Revision from V.1.03 Release 00 .....	4
2.1	Emulator Software Revision Up .....	4
2.2	Problem Fixed .....	4
3.	Contents of Revision from V.1.02 Release 01 .....	5
3.1	Supported MCUs Increased .....	5
3.2	High-performance Embedded Workshop Updated .....	7
3.3	Compatibility with Windows® 7 .....	7
3.4	Real-time OS Aware Debugging Function Enhanced .....	7
3.5	Notification Function of an Access to Address 0 Introduced .....	7
3.6	Warning Function Against Loading Programs onto Reserved Areas Introduced .....	7
3.7	Step-execution Function with an Input to RESET Masked Introduced .....	7
4.	Note .....	8
4.1	Installing the M16C R8C E100 Emulator software .....	8
5.	Real-Time OS Aware Debugging .....	8
6.	Operating Environment .....	9

## 1. MCU Unit and Target MCU

Table 1.1 shows the names of the MCU unit and target MCU for the M16C R8C E100 emulator software.

Table 1.1 MCU Unit and Target MCU

MCU Unit	Target MCU	
	Group Name	MCU Model [*1]
R0E530640MCU00	M16C/64	R5F36406, R5F3640D, R5F3640M
R0E530650MCU00	M16C/64A	R5F364A6, R5F364AE, R5F364AK, R5F364AM
	M16C/65	R5F36506, R5F3650E, R5F3650K, R5F3650M, R5F3650N, R5F3650R, R5F3650T R5F365x6, R5F365xE, R5F365xK, R5F365xM, R5F365xN, R5F365xR, R5F365xT
R0E535M00MCU00	M16C/5L	R5F35Lx0, R5F35Lx3, R5F35Lx6, R5F35LxE
	M16C/5M	R5F35M23, R5F35M33, R5F35M73, R5F35M83, R5F35M16, R5F35M26, R5F35M36, R5F35M66, R5F35M76, R5F35M86, R5F35M1E, R5F35M2E, R5F35M3E, R5F35M6E, R5F35M7E, R5F35M8E, R5F35MB3, R5F35MC3, R5F35ME3, R5F35MF3, R5F35MA6, R5F35MB6, R5F35MC6, R5F35MD6, R5F35ME6, R5F35MF6, R5F35MAE, R5F35MBE, R5F35MCE, R5F35MDE, R5F35MEE, R5F35MFE
	M16C/56	R5F356x0, R5F356x3, R5F356x6, R5F356xE
	M16C/57	R5F35723, R5F35733, R5F35773, R5F35783, R5F35716, R5F35726, R5F35736, R5F35766, R5F35776, R5F35786, R5F3571E, R5F3572E, R5F3573E, R5F3576E, R5F3577E, R5F3578E
R0E521300MCU00	R8C/32A	R5F21321A, R5F21322A, R5F21324A
	R8C/32C	R5F21321C, R5F21322C, R5F21324C
	R8C/32D	R5F21321D, R5F21322D, R5F21324D
	R8C/32G	R5F21324G, R5F21326G
	R8C/32H	R5F21324H, R5F21326H
	R8C/32M	R5F21321M, R5F21322M, R5F21324M
	R8C/33A	R5F21331A, R5F21332A, R5F21334A, R5F21335A, R5F21336A
	R8C/33C	R5F21331C, R5F21332C, R5F21334C, R5F21335C, R5F21336C
	R8C/33D	R5F21331D, R5F21332D, R5F21334D, R5F21335D, R5F21336D
	R8C/33G	R5F21334G, R5F21336G
	R8C/33H	R5F21334H, R5F21336H
	R8C/33M	R5F21331M, R5F21332M, R5F21334M, R5F21335M, R5F21336M
	R8C/34C	R5F21344C, R5F21345C, R5F21346C
	R8C/34E	R5F21346E, R5F21347E, R5F21348E, R5F2134AE, R5F2134CE
	R8C/34F	R5F21346F, R5F21347F, R5F21348F, R5F2134AF, R5F2134CF
	R8C/34G	R5F21346G, R5F21347G, R5F21348G, R5F2134AG, R5F2134CG
	R8C/34H	R5F21346H, R5F21347H, R5F21348H, R5F2134AH, R5F2134CH
	R8C/34M	R5F21344M, R5F21345M, R5F21346M
	R8C/34P	R5F21346P
	R8C/34R	R5F21346R
R8C/34W	R5F21346W, R5F21347W, R5F21348W, R5F2134AW, R5F2134CW	
R8C/34X	R5F21346X, R5F21347X, R5F21348X, R5F2134AX, R5F2134CX	
R8C/34Y	R5F21346Y, R5F21347Y, R5F21348Y, R5F2134AY, R5F2134CY	
R8C/34Z	R5F21346Z, R5F21347Z, R5F21348Z, R5F2134AZ, R5F2134CZ	

MCU Unit	Target MCU	
	Group Name	MCU Model [*1]
R0E521300MCU00	R8C/35A	R5F21354A, R5F21355A, R5F21356A, R5F21357A, R5F21358A, R5F2135AA, R5F2135CA
	R8C/35C	R5F21354C, R5F21355C, R5F21356C, R5F21357C, R5F21358C, R5F2135AC, R5F2135CC
	R8C/35D	R5F21354D, R5F21355D, R5F21356D
	R8C/35M	R5F21354M, R5F21355M, R5F21356M, R5F21357M, R5F21358M, R5F2135AM, R5F2135CM
	R8C/36A	R5F21364A, R5F21365A, R5F21366A, R5F21367A, R5F21368A, R5F2136AA, R5F2136CA
	R8C/36C	R5F21364C, R5F21365C, R5F21366C, R5F21367C, R5F21368C, R5F2136AC, R5F2136CC
	R8C/36E	R5F21368E, R5F2136AE, R5F2136CE
	R8C/36F	R5F21368F, R5F2136AF, R5F2136CF
	R8C/36G	R5F21368G, R5F2136AG, R5F2136CG
	R8C/36H	R5F21368H, R5F2136AH, R5F2136CH
	R8C/36M	R5F2136AM, R5F2136CM, R5F21364M, R5F21365M R5F21366M, R5F21367M, R5F21368M
	R8C/36W	R5F21368W, R5F2136AW, R5F2136CW
	R8C/36X	R5F21368X, R5F2136AX, R5F2136CX
	R8C/36Y	R5F21368Y, R5F2136AY, R5F2136CY
	R8C/36Z	R5F21368Z, R5F2136AZ, R5F2136CZ
	R8C/38A	R5F21386A, R5F21387A, R5F21388A, R5F2138AA, R5F2138CA
	R8C/38C	R5F21386C, R5F21387C, R5F21388C, R5F2138AC, R5F2138CC
	R8C/38E	R5F21388E, R5F2138AE, R5F2138CE
	R8C/38F	R5F21388F, R5F2138AF, R5F2138CF
	R8C/38G	R5F21388G, R5F2138AG, R5F2138CG
	R8C/38H	R5F21388H, R5F2138AH, R5F2138CH
	R8C/38M	R5F2138AM, R5F2138CM, R5F21386M, R5F21387M, R5F21388M
	R8C/38W	R5F21388W, R5F2138AW, R5F2138CW
	R8C/38X	R5F21388X, R5F2138AX, R5F2138CX
	R8C/38Y	R5F21388Y, R5F2138AY, R5F2138CY
	R8C/38Z	R5F21388Z, R5F2138AZ, R5F2138CZ

\*1: This is the MCU selectable from the [Device] drop-down list box in the [Device setting] dialog box.

## 2. Contents of Revision from V.1.03 Release 00

### 2.1 Emulator Software Revision Up

The M16C R8C E100 Emulator Software version has been revised from V.1.03 Release 00 to V.1.03 Release 01.

### 2.2 Problem Fixed

The following known problem has been fixed:

With using the MCU unit for the R8C/3x MCU series--R0E521300MCU00.

For details of the problem, see Renesas Tool News Document No. 110427/tn1 at:

<http://tool-support.renesas.com/eng/toolnews/110427/tn1.htm>

### 3. Contents of Revision from V.1.02 Release 01

Contents of revision from The M16C R8C E100 Emulator Software V.1.02 Release 01 to V.1.03 Release 00 are shown below.

#### 3.1 Supported MCUs Increased

The following MCUs have been added to the support line:

-In the M16C/60 series

- (1) R5F364AK (the M16C/64 group)
- (2) R5F365x6, R5F365xE, R5F365xK, R5F365xM, R5F365xN, R5F365xR, and R5F365xT (the M16C/65 group)

-In the M16C/50 series

- (1) R5F35M23, R5F35M33, R5F35M73, R5F35M83,  
R5F35M16, R5F35M26, R5F35M36, R5F35M66, R5F35M76, R5F35M86,  
R5F35M1E, R5F35M2E, R5F35M3E, R5F35M6E, R5F35M7E, R5F35M8E,  
R5F35MB3, R5F35MC3, R5F35ME3, R5F35MF3,  
R5F35MA6, R5F35MB6, R5F35MC6, R5F35MD6, R5F35ME6, R5F35MF6,  
R5F35MAE, R5F35MBE, R5F35MCE, R5F35MDE, R5F35MEE, and R5F35MFE (the M16C/5M group)
- (2) R5F35723, R5F35733, R5F35773, R5F35783,  
R5F35716, R5F35726, R5F35736, R5F35766, R5F35776, R5F35786,  
R5F3571E, R5F3572E, R5F3573E, R5F3576E, R5F3577E, and R5F3578E (the M16C/57 group)

-In the R8C/3x series

- (1) R5F21321C, R5F21322C, and R5F21324C (the R8C/32C group)
- (2) R5F21321D, R5F21322D, and R5F21324D (the R8C/32D group)
- (3) R5F21321M, R5F21322M, and R5F21324M (the R8C/32M group)
- (4) R5F21324G, and R5F21326G (the R8C/32G group)
- (5) R5F21324H, and R5F21326H (the R8C/32H group)
- (6) R5F21331C, R5F21332C, R5F21334C, R5F21335C, and R5F21336C (the R8C/33C group)
- (7) R5F21331D, R5F21332D, R5F21334D, R5F21335D, and R5F21336D (the R8C/33D group)
- (8) R5F21334G, and R5F21336G (the R8C/33G group)
- (9) R5F21334H, and R5F21336H (the R8C/33H group)
- (10) R5F21331M, R5F21332M, R5F21334M, R5F21335M, and R5F21336M (the R8C/33M group)

- (11) R5F21344C, R5F21345C, and R5F21346C (the R8C/34C group)
- (12) R5F21344M, R5F21345M, and R5F21346M (the R8C/34M group)
- (13) R5F21346P (the R8C/34P C group)
- (14) RR5F21346R (the R8C/34 group)
- (15) R5F21346W, R5F21347W, R5F21348W, R5F2134AW, and R5F2134CW (the R8C/34W group)
- (16) R5F21346X, R5F21347X, R5F21348X, R5F2134AX, and R5F2134CX (the R8C/34X group)
- (17) RR5F21346Y, R5F21347Y, R5F21348Y, R5F2134AY, and R5F2134CY (the R8C/34Y group)
- (18) R5F21346Z, R5F21347Z, R5F21348Z, R5F2134AZ, and R5F2134CZ (the R8C/34Z group)
- (19) R5F21354C, R5F21355C, R5F21356C, R5F21357C, R5F21358C, R5F2135AC, and  
R5F2135CC (the R8C/35C group)
- (20) R5F21354D, R5F21355D, and R5F21356D (the R8C/35D group)
- (21) R5F21354M, R5F21355M, R5F21356M, R5F21357M, R5F21358M, R5F2135AM, and  
R5F2135CM (the R8C/35M group)
- (22) R5F21364C, R5F21365C, R5F21366C, R5F21367C, R5F21368C, R5F2136AC, and  
R5F2136CC (the R8C/36C group)
- (23) R5F2136AM, R5F2136CM, R5F21364M, R5F21365M, R5F21366M, R5F21367M, and  
R5F21368M (the R8C/36M group)
- (24) R5F21368W, R5F2136AW, and R5F2136CW (the R8C/36W group)
- (25) RR5F21368X, R5F2136AX, and R5F2136CX (the R8C/36X group)
- (26) R5F21368Y, R5F2136AY, and R5F2136CY (the R8C/36Y group)
- (27) R5F21368Z, R5F2136AZ, and R5F2136CZ (the R8C/36Z group)
- (28) RR5F21386C, R5F21387C, R5F21388C, R5F2138AC, and R5F2138CC (the R8C/38C group)
- (29) R5F2138AM, R5F2138CM, R5F21386M, R5F21387M, and R5F21388M (the R8C/38M group)
- (30) R5F21388W, R5F2138AW, and R5F2138CW (the R8C/38W group)
- (31) R5F21388X, R5F2138AX, and R5F2138CX (the R8C/38X group)
- (32) R5F21388Y, R5F2138AY, and R5F2138CY (the R8C/38Y group)
- (33) R5F21388Z, R5F2138AZ, and R5F2138CZ (the R8C/38Z group)

### 3.2 High-performance Embedded Workshop Updated

The High-performance Embedded Workshop included in the package have been updated from V.4.05.01 to V.4.08.00.

### 3.3 Compatibility with Windows® 7

The revised product has been made compatible with the 64-bit and the 32-bit editions of Windows(R) 7.

### 3.4 Real-time OS Aware Debugging Function Enhanced

To enhanced the debugging functions for systems using real-time OSes, the following windows have been added:

- OS Trace window
- OS Analyze window

Note that the above windows support the MCUs of the M16C/60 and the M16C/50 series only. They do not support any MCU of the R8C/3x series, so never use these windows in such a case. If used, the windows may not operate properly.

### 3.5 Notification Function of an Access to Address 0 Introduced

If address 00000h or 00001h is read out except when an interrupt is serviced, a warning for notifying this read is displayed in the Extended Monitor window.

### 3.6 Warning Function Against Loading Programs onto Reserved Areas Introduced

If you start loading a program onto any area except ROM, RAM, and external areas, a warning for notifying the illegal operation is displayed in the Output window.

### 3.7 Step-execution Function with an Input to RESET Masked Introduced

Even if the Mask the terminal RESET check box is selected in the Configuration Properties dialog box that appears when the debugger is started, the debugger can perform step execution whenever the RESET signal is in the LOW state.

## 4. Note

### 4.1 Installing the M16C R8C E100 Emulator software

M16C R8C E100 Emulator Software V.1.03 Release 01 contains High-performance Embedded Workshop V.4.08.00.

When M16C R8C E100 Emulator Software V.1.03 Release 01 is installed on the host computer where V.4.07.01 or earlier versions has been installed, the High-performance Embedded Workshop will be updated to V.4.08.00.

## 5. Real-Time OS Aware Debugging

For details of the real-time OS aware debugging, refer to the following page.

<http://www.renesas.com/ecxos>



## 6. Operating Environment

Table 5.1 Operating Environment (Windows® XP)

PC Environment	
PC	IBM PC/AT compatible
OS	Windows® XP 32-bit edition [*2] [*4]
CPU2	Pentium 4 running at 1.6 GHz or more recommended
Interface	USB2.0/USB1.1 [*3]
Memory	1 Gbyte or larger (more than 10 times the file size of the load module) recommended
Hard disk	Installation of the emulator debugger requires free space of 200 Mbytes or larger. Also keep additional free space that is at least twice the memory capacity (four times or larger recommended) for use as swap space.
Display resolution	1024 × 768 or higher recommended

Table 5.2 Operating Environment (Windows Vista® or Windows® 7)

PC Environment	
PC	IBM PC/AT compatible
OS	Windows Vista® 32-bit edition [*2] [*5] Windows 7 32-bit edition/64-bit edition [*2]
CPU	Pentium 4 running at 3 GHz or Core 2 Duo running at 1 GHz or more recommended
Interface	USB2.0/USB1.1 [*3]
Memory	2 Gbyte or larger (more than 10 times the file size of the load module) recommended (32-bit edition) 3 Gbyte or larger (more than 10 times the file size of the load module) recommended (64-bit edition)
Hard disk	Installation of the emulator debugger requires free space of 200 Mbytes or larger. Also keep additional free space that is at least twice the memory capacity (four times or larger recommended) for use as swap space.
Display resolution	1024 × 768 or higher recommended

Notes:

- \*2: Windows and Windows Vista are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. All other company or product names are the property of their respective owners.
- \*3: Operation with all combinations of host machine, USB device and USB hub is not guaranteed for the USB interface.
- \*4: The 64-bit edition of Windows® XP is not supported.
- \*5: The 64-bit edition of Windows Vista® is not supported.

## Notice

- All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.  
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.  
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.  
"Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
- Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.  
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.  
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



### SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

#### Renesas Electronics America Inc.

2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A.  
Tel: +1-408-588-6000, Fax: +1-408-588-6130

#### Renesas Electronics Canada Limited

1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada  
Tel: +1-905-898-5441, Fax: +1-905-898-3220

#### Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.  
Tel: +44-1628-585-100, Fax: +44-1628-585-900

#### Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany  
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

#### Renesas Electronics (China) Co., Ltd.

7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China  
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

#### Renesas Electronics (Shanghai) Co., Ltd.

Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd., Pudong District, Shanghai 200120, China  
Tel: +86-21-5877-1818, Fax: +86-21-6887-7858 / -7898

#### Renesas Electronics Hong Kong Limited

Unit 1601-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong  
Tel: +852-2886-9318, Fax: +852-2886-9022/9044

#### Renesas Electronics Taiwan Co., Ltd.

7F, No. 363 Fu Shing North Road Taipei, Taiwan, R.O.C.  
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

#### Renesas Electronics Singapore Pte. Ltd.

1 HarbourFront Avenue, #06-10, Keppel Bay Tower, Singapore 098632  
Tel: +65-6213-0200, Fax: +65-6278-8001

#### Renesas Electronics Malaysia Sdn.Bhd.

Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia  
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

#### Renesas Electronics Korea Co., Ltd.

11F., Samik Laviel' or Bldg., 720-2 Yeoksam-Dong, Kangnam-Ku, Seoul 135-080, Korea  
Tel: +82-2-558-3737, Fax: +82-2-558-5141