

# QE for Camera[RZ] V1.1.0, QE for Display[RZ] V3.1.0

R20UT4490EJ0100  
Rev.1.00  
Feb 20, 2019

## Release Note

---

Thank you very much for your using the QE for Camera[RZ] V1.0.0. and QE for Display[RZ] V3.1.0.

This release documentation, we have indicated this product installation, restrictions and so on.

## Contents

<b>1. About QE for Camera[RZ], QE for Display[RZ].....</b>	<b>2</b>
<b>1.1 Summary .....</b>	<b>2</b>
<b>1.2 New Functions.....</b>	<b>2</b>
<b>1.3 Supported Environment .....</b>	<b>3</b>
<b>1.4 Supported Microcontroller .....</b>	<b>3</b>
<b>1.5 Supporting Sample Project .....</b>	<b>3</b>
<b>2. Installation and Uninstallation.....</b>	<b>4</b>
<b>2.1 Installing This Product .....</b>	<b>4</b>
<b>2.2 Uninstalling This Product.....</b>	<b>4</b>

# 1. About QE for Camera[RZ], QE for Display[RZ]

## 1.1 Summary

QE for Camera, QE for Display is an assistance tool for applications which operate under the e<sup>2</sup> studio integrated development environment. In development of embedded systems using Video Display Controller 5,6 (VDC5,6) installed in the MCUs of the RZ/A series, this product facilitates easy initial adjustment of the camera and display connection and camera module settings, thus, reducing development time.

For details on QE (Quick and Effective tool solution), refer to the URL below.

<https://www.renesas.com/qe>

QE for Camera[RZ] V1.1.0 and QE for Display[RZ] V3.1.0 are the same plug-in. Therefore, you can install both items by installing either one of the two. Download one of the following packages. The software would be installed in e<sup>2</sup> studio as "Renesas QE for Camera/Display[RZ] V3.1.0".

- ✓ QE for Camera V1.1.0: Development Assistance Tool for Camera  
<https://www.renesas.com/qe-camera>
- ✓ QE for Camera V1.2.0: Development Assistance Tool for Display  
<https://www.renesas.com/qe-display>

Please refer the Help to know the how to use this product.

## 1.2 New Functions

- **Supports RZ/A2M Device** (QE for Camera, QE for Display)



QE supports RZ/A2M device. For projects in which such setting values can be incorporated, see section 1.5 Supporting Sample Projects.

New presets are followings;

- [Camera] RZ/A2M Evaluation Board Kit / Raspberry Pi Camera Module V2
- [Display] HDMI Board (RZ/A2M Evaluation Board Kit) / WXGA 1360\*768

- **Timing adjustment function for MIPI Camera** (QE for Camera)

You can adjust the timing settings easily in the Timing Adjustment(MIPI/VIN) tab on the GUI, making it easy to connect the MIPI Camera.



### 1.3 Supported Environment

Microsoft Windows 7, Windows 8.1, Windows 10

Renesas e<sup>2</sup> studio V7.1.0 (or later)

\* If you are using a version earlier than e<sup>2</sup> studio V 7.1.0, please update to V 7.1.0 or later.

### 1.4 Supported Microcontroller

RZ Family:

— RZ/A series (RZ/A2M, RZ/A1H, RZ/A1L, RZ/A1LU, RZ/A1M, RZ/A1LC)

### 1.5 Supporting Sample Project

You can obtain sample programs that support QE for Camera from the URL below:

- RZ/A2M Group Simple Applications Package (V2.00 or later)  
<https://www.renesas.com/search/keyword-search.html#genre=sampleprogram&q=r01an4494>
- RZ/A1LU Group RZ/A1 Software Package (V2.00 or later)  
<https://www.renesas.com/search/keyword-search.html#genre=sampleprogram&q=r01an4310>
- RZ/A1H Group, RZ/A1M Group, RZ/A1LU Group, RZ/A1L Group, RZ/A1LC Group  
RZ/A1 Framework (V2.00 or later)  
<https://www.renesas.com/search/keyword-search.html#genre=sampleprogram&q=r01an3638>

## 2. Installation and Uninstallation

### 2.1 Installing This Product

Use the following procedure to install this product.

#### ■ Installation

- (1) Activate e<sup>2</sup> studio.
- (2) Click [Help], and then click the [Install New Software...] menu to open the [Install] dialog box.
- (3) Click the [Add...] button to open the [Add Repository] dialog box.
- (4) Click the [Archive...] button, select the installation file (zip file) in the opened file selection dialog box, and then click the [Open] button.
- (5) Click the [OK] button in the [Add Repository] dialog box.
- (6) Expand the [Renesas QE] item shown in the [Install] dialog box, select the [Renesas QE for Camera/Display[RZ]] check box, and then click the [Next>] button.
- (7) Confirm that the installation target is correct, and then click the [Next>] button.  
\* If you don't need to update the modules that are related, check off the [Contact all update sites during install to find required software] checkbox to shorten the installation time.
- (8) After checking the license, select the [I accept the terms of the license agreements] radio button, and then click the [Finish] button.
- (9) When a dialog box for selecting a trusted certificate appears, check the displayed certificate, and then click the [OK] button to continue installation.
- (10) Restart e<sup>2</sup> studio according to the instruction on the screen.
- (11) Start this product from the [Renesas Views] - [Renesas QE] menu of e<sup>2</sup> studio.  
For details about how to use this product, see the [Help] menu of e<sup>2</sup> studio.

### 2.2 Uninstalling This Product

Use the following procedure to uninstall this product.

#### ■ Uninstallation

- (1) Start e<sup>2</sup> studio.
- (2) Select [Help -> Installation Details] to open the [e<sup>2</sup> studio Installation Details] dialog box.
- (3) Select [Renesas QE for Camera/Display[RZ]] displayed on the [Installed Software] tabbed page and click the [Uninstall...] button to open the [Uninstall] dialog box.
- (4) Check the displayed information and click the [Finish] button.
- (5) When prompted to restart e<sup>2</sup> studio, restart it.

# General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

## 1. Precaution against Electrostatic Discharge (ESD)

A strong electrical field, when exposed to a CMOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop the generation of static electricity as much as possible, and quickly dissipate it when it occurs. Environmental control must be adequate. When it is dry, a humidifier should be used. This is recommended to avoid using insulators that can easily build up static electricity. Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work benches and floors must be grounded. The operator must also be grounded using a wrist strap. Semiconductor devices must not be touched with bare hands. Similar precautions must be taken for printed circuit boards with mounted semiconductor devices.

## 2. Processing at power-on

The state of the product is undefined at the time when power is supplied. The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the time when power is supplied. In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the time when power is supplied until the reset process is completed. In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the time when power is supplied until the power reaches the level at which resetting is specified.

## 3. Input of signal during power-off state

Do not input signals or an I/O pull-up power supply while the device is powered off. The current injection that results from input of such a signal or I/O pull-up power supply may cause malfunction and the abnormal current that passes in the device at this time may cause degradation of internal elements. Follow the guideline for input signal during power-off state as described in your product documentation.

## 4. Handling of unused pins

Handle unused pins in accordance with the directions given under handling of unused pins in the manual. The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of the LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible.

## 5. Clock signals

After applying a reset, only release the reset line after the operating clock signal becomes stable. When switching the clock signal during program execution, wait until the target clock signal is stabilized. When the clock signal is generated with an external resonator or from an external oscillator during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Additionally, when switching to a clock signal produced with an external resonator or by an external oscillator while program execution is in progress, wait until the target clock signal is stable.

## 6. Voltage application waveform at input pin

Waveform distortion due to input noise or a reflected wave may cause malfunction. If the input of the CMOS device stays in the area between  $V_{IL}$  (Max.) and  $V_{IH}$  (Min.) due to noise, for example, the device may malfunction. Take care to prevent chattering noise from entering the device when the input level is fixed, and also in the transition period when the input level passes through the area between  $V_{IL}$  (Max.) and  $V_{IH}$  (Min.).

## 7. Prohibition of access to reserved addresses

Access to reserved addresses is prohibited. The reserved addresses are provided for possible future expansion of functions. Do not access these addresses as the correct operation of the LSI is not guaranteed.

## 8. Differences between products

Before changing from one product to another, for example to a product with a different part number, confirm that the change will not lead to problems. The characteristics of a microprocessing unit or microcontroller unit products in the same group but having a different part number might differ in terms of internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

## Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.  
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.  
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.  
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)

## Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,  
Koto-ku, Tokyo 135-0061, Japan  
[www.renesas.com](http://www.renesas.com)

## Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

## Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:  
[www.renesas.com/contact/](http://www.renesas.com/contact/).