ADDODIATION CONNECTING	© Co	terial Compo pyright 2005. IPC, Bannocl ternational and Pan-Americ	kburn, Illinois	. All rights reser	ition with lowe	r level	parts, the	declarat	ion enco	mpasses		erials for whic	f the item is an assembly the manufacturer has is declaration.	
1752-2 1.1	ard	Form Type * Distribute			Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information									
Supplier Information														
Company Name * Company Unique ID				Unique ID Authority			Response Date *			Respons	se Document ID			
IDT Inc.						2008-10-13				opper Wire				
Contact Name *	itle - Contact		Phone - Contact *			Email - Contact *			D		۸ دار	Dannasantation		
CS Phek	Engineer		604-613-2538		csph	csphek@idt.com			Du	iplicate Contact	-> Authorized	Representative		
Authorized Representati	Title - Representative		Phone - Representative *		Email - Representative *			Supplier Comments or URL for Additional Information						
CS Phek		Engineer		604-613-253	38	csph	ek@idt.co	m						
Requester Item Number	r	Mfr Item Number		Mfr Item Nam	Effect	ive Date	Version	Manut	acturing Si	ite Weight *	UOM	Unit Type		
				DCG8 coppe	2008-	-10-13	0 ATP			79.8	mg	Each		
Alternate Recommendation						Alternate		te Item C	e Item Comments		•			
Manufacturing Proces	ss In	formation												
Terminal Plating / Grid Array Material Terminal E			Base Alloy J-STD-020 MSL Rat			ating Peak Process Body Temp			rature Ma	ax Time at Peak Tem	perature Numb	erature Number of Reflow Cycles		
Matte Tin (Sn) - annealed CU Allo			CU Alloy	, 1			260				30 s	econds 3		
Comments					•		•			,				

Save the fields in this form to a file	Export Data	Import fields from a file into this form	rt Data	Clear all of the fields on this form	Reset Form	Lock the fields on this form to prevent changes	Lock Supplier Fields
RoHS Material Co	mposition Declaratio	n				Declaration Type *	Simplified
		nit of 0.1% by mass (1000 PPM) ers (PBDE) and quantity limit of 0					inated Biphenyls (PBB),
ate that Supplier completes t upplier may have relied on ir upplier agrees that, at a mini ritten agreement with respec	his form. Supplier acknowledges formation provided by others in commum, its suppliers have provided	is form concerning RoHS restrictive substanthat Company will rely on this certification in ompleting this form, and that Supplier may no certifications regarding their contributions to ad conditions of that agreement, including an provides in this form.	determining the co ot have independe the part, and those	ompliance of its products with ntly verified such information e certifications are at least as	European Union member state However, in situations where S comprehensive as the certificati	laws that implement the RoHS Dire supplier has not independently verifi on in this paragraph. If the Compar	ctive. Company acknowledges that ed information provided by others, ny and the Supplier enter into a
RoHS Declaration *	1 - Item(s) does not contain Ro	HS restricted substances per the definitio	n above			Supplier Acceptance * Acc	epted
Exemptions: If the dec bove and choose all ap		RoHS restricted substances per th	ne definition abo	ove except for defined	RoHS exemptions, then so	elect the corresponding resp	onse in the RoHS Declaration
Declaration Signa	iture						
nstructions: Compl	ete all of the required fie	lds on all pages of this form. So	elect the "Acc	cepted" on the Suppli	er Acceptance drop-do	wn. This will display the s	gnature area. Digitally sign

Declaration Signature	
Instructions: Complete all of the required fields on all pages of this form.	Select the "

the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

Homogeneous Material Composition Declaration for Electronic Products

Subltem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Line Functions: +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

	Item/SubItem		Homogeneous	Woight	Unit of			Laval	Substance Category			Substance	CAS	Exempt	Waight	Unit of	Tolerance		PPM
	Name		Material	Weight	Measure			Level	Substance Category			Substance	CAS	Exempt	weight	Measure	-	+	PPIVI
+1 -1	DCG8 copper Wire	+M -M	Mold Compound	47.82	mg	+C	-C	Supplier	Filler	+S	-S	Fused Silica	60676-86-0		42.09	mg	0.02	0.02	527,38
	-					+C	-C	Supplier	Binder	+S	-S	Polymeric Resin	Trade Secre		5.5	mg			68,920
						+C	-C	Supplier	Coloring	+S	-S	Carbon Black	1333-86-4		0.24	mg			2,997
		+M -M	Die Attach Adhe	s 0.41	mg	+C	-C	Supplier	Filler	+S	Ş	Silver	7440-22-4		0.29	mg			3,692
						+C	-C	Supplier	Binder	\$	-s	Epoxy Resin	Trade Secre		0.08	mg			1,040
						+C	-C	Supplier	Binder	\$	-s	Metal Oxide	Trade Secre		0.01	mg			156
						+C	-C	Supplier	Binder	\$	Ş	Hardening Agent	Trade Secre		0.01	mg			156
						+C	-C	Supplier	Binder	\$	Ş	Gamma- butyrolactone	96-48-0		0.01	mg			156
		+M -M	Lead Frame	27.13	mg	+C	-C	Supplier	Copper Alloy	+S	Ş	Copper	7440-50-8		26.4	mg			330,84
						+C	-C	Supplier	Copper Alloy	\$	Ş	Iron	7439-89-6		0.57	mg			7,130
						+C	-C	Supplier	Copper Alloy	\$	Ş	Phophorus	7723-14-0		0.004	mg			51
						+C	-C	Supplier	Copper Alloy	+S	-S	Zinc	7440-66-6		0.01	mg			170
						+C	-C	A	Lead/Lead Compound	+S	-s	Lead	7439-92-1		0.01	mg			102
						+C	-C	Supplier	Plating	\$	Ş	Silver	7440-22-4		0.14	mg			1,700
		+M -M	Lead Finish	1.79	mg	+C	-C	Supplier	Metal	+S	-S	Tin	7440-31-5		1.79	mg			22,400
		+M -M	Bond Wire	0.08	mg	+C	-C	Supplier	Wire	+S	-S	Copper	7440-50-8		0.08	mg			1,000
		+M-M	Silicon Chip	2.56	mg	+C	-C	Supplier	Silicon	+S	-S	Silicon	7440-21-3		2.56	mg			32,100