

Application Note

2-Axis Robot Arm Controlled via Analog Joystick

AN-CM-333

Abstract

This application note explains how to build a 2-axis robot arm controlled via an analog joystick using a GreenPAK chip and two servomotors.

This application note comes complete with design files which can be found in the References section.

2-Axis Robot Arm Controlled via Analog Joystick

Contents

Abstract	1
Contents	2
Figures	2
1 Terms and Definitions	3
2 References	3
3 Introduction	4
4 Principle of Operation	4
4.1 Servomotor.....	4
4.2 Analog Joystick	5
5 GreenPAK Design	6
6 Conclusions	11
Revision History	12

Figures

Figure 1. System Block Diagram.....	4
Figure 2. Tower Pro SG90 Servomotor	5
Figure 3. Analog Joystick Module	5
Figure 4. Timing Diagram	7
Figure 5. GreenPAK Design - Matrix 0.....	7
Figure 6. GreenPAK Design - Matrix 1	8
Figure 7. LUT Configuration	9
Figure 8. Circuit Schematic	9
Figure 9. Generating Sawtooth Wave	10
Figure 10. Pin8 (Yellow), Pin9 (Blue), Pin5 (Red), and Pin6 (Green)	10

2-Axis Robot Arm Controlled via Analog Joystick

1 Terms and Definitions

PWM	Pulse-Width Modulation
PGA	Programmable Gain Amplifier
ADC	Analog-to-Digital Converter
MUX	Multiplexer
FSM	Finite State Machine

2 References

For related documents and software, please visit:

[GreenPAK™ Programmable Mixed-signal Products | Renesas](#)

Download our free [GreenPAK Designer](#) software [1] to open the .gp files [2] and view the proposed circuit design. Use the [GreenPAK](#) development tools to freeze the design into your own customized IC in a matter of minutes. Find out more in complete library of application notes [3] featuring design examples as well as explanations of features and blocks within the GreenPAK IC.

- [1] [Go Configure Software Hub](#), Software Download and User Guide
- [2] [AN-CM-333 2-Axis Robot Arm Controlled via Analog Joystic.gp](#), [GreenPAK](#) Design File
- [3] [GreenPAK Application Notes](#), [GreenPAK](#) Application Notes Webpage
- [4] [SLG46620](#), Datasheet

2-Axis Robot Arm Controlled via Analog Joystick

3 Introduction

Robot arms are one of the most widely used robotic applications because they can make movements similar to a human hand. A robot arm could be an independent application or part of a bigger robotic system. Robot arms are mainly used in industry for pick and place applications. They are also found in mobile security cameras and toys.

A robot arm usually consists of several links connected by joints which can rotate. In this project, we will build a robot arm including two joints of rotation, one for the x-axis and the other for the y-axis. These will be controlled by an analog signal from a joystick. The circuit will be designed with the GreenPAK SLG46620 chip, two Tower Pro SG90 servomotors (Figure 2), and an analog joystick (Figure 3). The project does not require a microcontroller, since the GreenPAK chip includes all the elements needed to build a static IC capable of controlling the servomotors independently.

4 Principle of Operation

The GreenPAK chip will carry out all of the system's functions. It receives an analog signal from the x-output of the joystick, which is internally digitized and used as a PWM signal for the servomotor. The input channel is then changed to read from the joystick's y-output, and the process is repeated. The analog signals will be read every 10 ms, alternating between x- and y-outputs. Therefore, each individual signal is read every 20 ms, so the output frequency is 50 Hz. This is suitable for the operation of the servomotor.




Figure 1. System Block Diagram

4.1 Servomotor

Two Tower Pro SG90 servomotors will be used to build the robot arm. The motor needs a PWM signal to control its angle of rotation, which varies from 0° – 180° . When a 0.5 ms pulse width is introduced, the motor rotates to 0° . When the pulse width equals 2.5 ms, the motor rotates to 180° . The pulse width consequently must be between 0.5 – 2.5 ms every 20 ms to get an angle between 0° and 180° .

2-Axis Robot Arm Controlled via Analog Joystick



Figure 2. Tower Pro SG90 Servomotor

4.2 Analog Joystick

Analog joysticks are widely used in robot applications due to their low price and easy connection. The joystick consists of two potentiometers positioned crisscross. It provides three outputs: x, y, and a push button in the middle. The joystick in our application will offer manual control of the servos.

To get a range suiting the GreenPAK's ADC specifications, the joystick will use the chip's VREF rather than connecting an external voltage divider. This will reduce the number of external parts.




Figure 3. Analog Joystick Module

2-Axis Robot Arm Controlled via Analog Joystick

5 GreenPAK Design

The GreenPAK design comprises several parts (Figure 5). An analog MUX receives the signal from two different outputs according to a defined time interval. A pulse generator of 100 Hz gives a pulse every 10 ms. The x-signal is received in the first 10 ms and the y-signal in the next 10 ms.

Pin8 and Pin9 are configured as analog inputs connected to a PGA configured as an analog multiplexer. The signal from Pin16 switches between its two channels. When the signal CH Selector is set HIGH, the reading comes from Pin8, and when it is set LOW, the reading comes from Pin9. After the analog signal is transformed to a digital one, it is read from FSM0. FSM0 gets its input from the output of the ADC block (ADC data). FSM0 is configured as Falling Edge DLY.

delay time = (counter value+1)/clock.
clock = 256/2ms = 128kHz

FSM0's CLK Pin is connected to the CNT5 output via EXT CLK0 to get 128 kHz so that the pulse width of the output is 2 ms when the value of 255 is received from the ADC. The output period of CNT5 therefore is 7.8125 μ s and CNT5 data is 210.

The 2-L0 inverter and CNT6 define the 100 Hz generator, which gives a pulse every 10 ms in order to output the PWM signal to both servomotors every 20 ms. The generator's output triggers CNT9, which is configured to work as Falling Edge DLY with a delay time of 0.5 ms. The CNT9 output triggers FSM0 to output a signal whose width is FSM data + 0.5, which will be between 0.5 and 2.5 ms. This is passed through LUTs to the suitable servo.

CNT0 is used to give a 2.5 ms pulse width every work cycle as the maximum allowed time frame to output the signal to the servomotors (each one in turn) to prevent any errors.

DFF0, 2-L1, 3-L2 are used to control the input channel, where switching is periodically done between channel 1 and 2 of the PGA every 10 ms. Pin6 is externally connected to Pin16, which is linked to PGA's CH Selector pin.

The 4-bit LUT0, 3-bit LUT0, 3-bit LUT1, and 2-L2 form the demultiplexer to pass the PWM signal to the requested servomotor.

2-Axis Robot Arm Controlled via Analog Joystick




Figure 4. Timing Diagram

When the CH Selector signal is HIGH, the reading comes from channel 1 through Pin8 and the modified PWM signal passes to the x-servomotor through Pin4. When the CH Selector is set LOW, the reading comes from channel 2 and the signal is passed to Pin5 and then to the y-servomotor.

The channel is changed with the falling edge of the CNT0 output after 2.5 ms has elapsed from the start of the cycle, to output the pulse with the start of the next cycle (see Figure 4). This provides sufficient time for signal reading and stability.




Figure 5. GreenPAK Design - Matrix 0

2-Axis Robot Arm Controlled via Analog Joystick

To prevent any error in the ADC when the signal is small (less than 40 mV), DCMP0 is used to compare the ADC value with register 0. If the value is smaller than 9, the angle will be regarded as 0° and the output of CNT9 will be directly passed to the requested servomotor.

The joystick is sourced from VREF0 inside the GreenPAK chip so that the signal read by the joystick is within the ADC's operation range. VREF0 is connected to Pin19 where the source selector is set to be ACMP0, which was adjusted to be 1200 mV.

The joystick contains a push button which can be leveraged for additional functionality. A debouncer was constructed using CNT8 and the improved signal is output through Pin20.

Pin12 is configured as a low voltage digital input, because the joystick voltage is 1200 mV.




Figure 6. GreenPAK Design - Matrix 1

2-Axis Robot Arm Controlled via Analog Joystick




Figure 7. LUT Configuration




Figure 8. Circuit Schematic

To test the design, GreenPAK Designer's Signal Wizard was used to apply different signals to the inputs and monitor the outputs.

A video showing the working project is also attached to this file.

2-Axis Robot Arm Controlled via Analog Joystick




Figure 9. Generating Sawtooth Wave




Figure 10. Pin8 (Yellow), Pin9 (Blue), Pin5 (Red), and Pin6 (Green)

2-Axis Robot Arm Controlled via Analog Joystick

6 Conclusions

In this application note, we used a GreenPAK SLG46620 chip to build a circuit controlling a robot arm of two joints, x and y, using two servomotors operated with an analog joystick. The chip was highly efficient for incorporating all of the circuit's important elements within a small space. There was no need for an external microcontroller and few external elements were required.

This design may be expanded to build a robot arm of larger degrees of freedom by connecting more than one chip. Such a system could be applied to many different industrial applications.

2-Axis Robot Arm Controlled via Analog Joystick**Revision History**

Revision	Date	Description
1.0	07-Apr-2022	Initial Version

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.