

RZ/T2M Group

Encoder I/F EnDat sample program

Summary

This document describes the RZ/T2M Encoder I/F EnDat sample program package. To use this sample program, please obtain “RZ/T2M Group Encoder I/F Configuration Library” release package (Rev.1.60 or later).

For EnDat 2.2 communication protocol specifications and encoder specifications (EQN1035), contact HEIDENHAIN GmbH.

Functionality Checked Device

RZ/T2M CPU Board (RTK9RZT2M0C00000BE)

Contents

1. Package Contents	2
1.1 Software	2
1.2 Document	2
2. File Structure	3
3. About EnDat sample program.....	4
3.1 Software Information	4
3.1.2 Memory Size.....	4
3.2 Hardware Information	5
3.2.2 Target board	5
3.3 Procedures on Development Environments.....	6
3.3.1 Preparation before executing the sample program	6
3.3.2 EWARM from IAR Systems.....	6
3.3.3 e ² studio from RENESAS	8
Revision History	10

EnDat is registered trademark of Dr. Johannes Heidenhain GmbH

1. Package Contents

This package contains the following contents.

The Configuration Data included in this package supports up to 2 axes, but the sample program supports only 1 axis; to use it with 2 axes, modify the sample program to support 2 axes.

1.1 Software

Source code

No.	name	Version
1	RZ/T2M EnDat sample program	1.1

Configuration data

No.	name	Version
1	RZ/T2M Encoder I/F Configuration Data (EnDat)	1.0
2	RZ/T2M Encoder I/F PINMUX Data	1.0

1.2 Document

No.	Document name	Version	File name
1	RZ/T2M Group Encoder I/F EnDat sample program Release Note	1.20	(j) r11an0601jj0120-rzt2m.pdf (e) r11an0601ej0120-rzt2m.pdf
2	RZ/T2M Group EnDat sample program Application Note	1.10	(j) r11an0598jj0110-rzt2m-endat.pdf (e) r11an0598ej0110-rzt2m-endat.pdf
3	RZ/T2M Group EnDat 2.2 Interface Application Note	1.00	(j) r01an6409jj0100-rzt2m-endat.pdf (e) r01an6409ej0100-rzt2m-endat.pdf

2. File Structure

The file structure and contents of this package are detailed below.

Top

```

├── r11an0601jj0120-rzt2m.pdf
├── r11an0601ej0120-rzt2m.pdf
└── workspace
    ├── Software
    │   ├── iccarm
    │   │   └── RZ_T2_endat.zip : RZ/T2M EnDat sample program set (IAR)
    │   ├── gcc
    │   │   └── RZ_T2_endat.zip : RZ/T2M EnDat sample program set (e2 studio)
    └── Documents
        ├── r11an0598jj0110-rzt2m-endat.pdf
        ├── r11an0598ej0110-rzt2m-endat.pdf
        ├── r01an6409jj0100-rzt2m-endat.pdf
        └── r01an6409ej0100-rzt2m-endat.pdf

```

The file structure of the RZ_T2_endat.zip is shown below.

Top folder

```

├── configuration.xml           : FSP Configuration data
├── R9A07G075M28GBG.pincfg    : RZ/T2M Pin Configuration data
├── ( Environment File Depending on Build Tool )
├── lib
│   └── ecl
│       ├── Config_Endat22_v1.0.dat : RZ/T2M EnDat 2.2 Configuration data
│       └── RZT2_pinmux_v1.0.bin    : RZ/T2M Encoder I/F Pin Configuration data
└── src
    ├── hal_entry.c             : EnDat sample program
    ├── endat_main.c            : EnDat sample program
    ├── enc_dat.asm             : Encoder I/F Linker setup file (only e2 studio)
    ├── siochar.c               : SCI_UART sample program
    ├── siorw.c                 : SCI_UART sample program
    ├── sio_char.h              : SCI_UART sample program
    └── drv
        └── endat
            ├── iodefendat.h      : EnDat register definition file
            ├── r_endat_rzt2.c    : EnDat driver file
            ├── r_endat_rzt2_config.h : EnDat driver file
            ├── r_endat_rzt2_dat.h : EnDat driver file
            └── r_endat_rzt2_if.h : EnDat driver file

```

3. About EnDat sample program

This section contains information necessary to use the complete set of EnDat sample program.

3.1 Software Information

3.1.1 Base OS

This sample program is OS-independent.

3.1.2 Memory Size

Memory size used by this sample program, EnDat driver, and configuration data is shown in following table. This table does not include memory size used by Encoder I/F Configuration Library, Flexible Software Package, or C language libraries of the compiler.

Items		Memory Size	
		EWARM [kBytes]	e ² studio [kBytes]
EnDat driver	Code	4.3	3.2
	Data (with initial value)	0.0	0.0
	Data (without initial value)	0.1	0.1
	Constant Data	0.1	0.1
EnDat configuration data	Constant Data	108.8	108.8
Sample program	Code	3.0	3.3
	Data (with initial value)	0.0	0.0
	Data (without initial value)	0.4	0.4
	Constant Data	1.3	1.3

3.2 Hardware Information

3.2.1 Device

RZ/T2M

3.2.2 Target board

(1) Board name

RZ/T2M CPU Board (RTK9RZT2M0C00000BE)

(2) Setting of CPU Board

The target board configuration is as follows.

SW4-1: ON

SW4-2: OFF

SW4-3: ON

SW4-4: ON

SW4-5: OFF

SW6-1: OFF

(3) Terminal

The correspondence between the pin used as the encoder I/F and the pin header of the target board is as follows.

Channel	Port name (Function pin name)	Pin header	Input/Output	Description
ENDAT_CH0	TCLK0 (ENCIF4)	CN1 #6	output	Clock output pin
	DE0 (ENCIF3)	CN1 #4	output	Data output enable setting pin
	DATA_DV0 (ENCIF2)	CN1 #3	output	Data output pin
	DATA_RC0 (ENCIF0)	CN1 #1	input	Data input pin
ENDAT_CH1	TCLK1 (ENCIF9)	CN1 #12	output	Clock output pin
	DE1 (ENCIF8)	CN1 #11	output	Data output enable setting pin
	DATA_DV1 (ENCIF7)	CN1 #9	output	Data output pin
	DATA_RC1 (ENCIF5)	CN1 #7	input	Data input pin

3.3 Procedures on Development Environments

3.3.1 Preparation before executing the sample program

This sample program communicates with a PC. The USB connection terminal on the target board is CN16. The terminal software of the host PC is set as shown in the following table.

function	setting
Communication method	Asynchronous Serial transmit/receive
send / receiving order	LSB first
Transfer rate	19200 bps
Character length	8 bits
Stop bit length	1 bit
Parity function	None
Hardware flow control	None

3.3.2 EWARM from IAR Systems

(1) Build environment

IAR Embedded Workbench for ARM v9.32.2

RENESAS RZ/T2 Flexible Software Package v1.3.0

(2) Execution environment ICE

IAR I-jet

(3) Build Procedure for Sample Programs

The build procedure for the sample program is as follows.

- 1 Copy the extracted source files to the desired location.
- 2 Copy the following files from "RZ/T2M Group Encoder I/F Configuration Library" under lib\ec1 in the same folder as the source files. (If the "lib\ec1" folder already exists, overwrite it.) *1
lib\ec1\r_ec1_rzt2_iar.a
lib\ec1\r_ec1_rzt2_if.h
- 3 Activate EWARM.
- 4 Select [File] menu -> [Open Workspace].
- 5 Open the extracted source file RZT2_endat.eww.
- 6 Start the FSP Smart Configurator from the [Tools] menu of the EWARM IDE. *2


Note: 1. Please use Encoder I/F Configuration Library revision 1.50 or later (release package revision 1.60 or later) that corresponds to the EWARM v9.32.2.
2. The following procedure adds the activation of the FSP Smart Configurator to the [Tools] menu of the EWARM IDE. Select [Tools] menu -> [Tool Configuration] in the EWARM IDE. Select the [New] button, specify a table string in each field, and press [OK].

Field	String
Menu text	RZ Smart Configurator
command	\$RASC_EXE_PATH\$
argument	--compiler IAR configuration.xml
Initial directory	\$PROJ_DIR\$

String for the command is variable holding the path of the Smart Configurator execution file, rasc.exe.

You can also start the FSP Smart Configurator directly from the command prompt by specifying the folder where it is installed.

- 7 In the FSP Configuration pane of the Smart Configurator, click Generate Project Content. The rzt, rzt_cfg, rzt_gen, script and .setting folders will be generated.



- 8 When project generation is complete, close the Smart Configurator.
 9 Select [Rebuild ALL] from the [Project] menu of EWARM.
 The file Debug\Exe\RZT2_endat_iar.out is generated.

(4) Sample Program Execution Procedure

After executing the "build procedure", connect the target board and debugger correctly, and perform the following operations.

- 1 Select [Project] menu -> [Download and Execute].
- 2 Select [Debug] menu -> [Execute].

(5) Execution result of the sample program

Run the sample program and enter commands in the terminal software window. For commands, see 4.11.8 console commands in the RZ/T2M Group EnDat Sample Program Application Note.

```
COM4 - Tera Term VT
ファイル(F) 編集(E) 設定(S) コントロール(O) ウィンドウ(W) ヘルプ(H)
EnDat sample program start
endat >pos
pos command
result      : ENDAT_SUCCESS
pos_upper   : 0x00000004
pos_lower   : 0xFE251CF8
add_datum1  : 0x00000000
add_datum2  : 0x00000000
endat >
```

3.3.3 e² studio from RENESAS

(1) Build environment

RENESAS e² studio 2023-07

GNU ARM Embedded Toolchain 12.2.1.arm-12-24

RENESAS RZ/T2 Flexible Software Package v1.3.0


(2) Execution environment ICE

SEGGER J-Link

(3) Build procedure of the sample program


The procedure for building the sample program is as follows.

- 1 Copy the expanded source file to any location.
- 2 Copy the following files in the "RZ/T2M Group Encoder I/F Configuration Library" to lib\ec1 in the same folder as the source file. (If the lib\ec1 folder already exists, overwrite it.) *1
lib\ec1\r_ec1_rzt2_gcc.a
lib\ec1\r_ec1_rzt2_if.h
- 3 After launching e² studio and moving to the workspace, click the [File] menu -> [Import] and select Existing project to workspace and click [Next].
- 4 On the project import screen, select the folder where the sample program was expanded as the root directory.
- 5 Select a project, check Copy Project to Workspace, and click [Finish].
- 6 Double-click the configuration.xml in the Project Explorer pane of e² studio to open it.



Note. 1. Please use Encoder I/F Configuration Library revision 1.50 or later (release package revision 1.60 or later) that corresponds to the GNU ARM Embedded Toolchain 12.2.1.

- 7 Click Generate Project Content in the FSP Configuration pane of e² studio.
The rzt, rzt_cfg, rzt_gen, script and .settings folders are generated.



- 8 Select [Project] menu -> [Build All]
The Debug\RZT2_endat_gcc.elf file is generated.


(4) Execution procedure of the sample program

After executing the "build procedure", connect the target board and debugger correctly, and perform the following operations.

- 1 Select [Run] menu -> [Debug As] -> [Renesas GDB Hardware Debugging].
- 2 Click [Debug] to start downloading to internal RAM.
- 3 Click [Run] menu -> [Resume] to run the sample program.

(5) Execution result of the sample program

Run the sample program and enter commands in the terminal software window. For commands, see 4.11.8 console commands in the RZ/T2M Group EnDat Sample Program Application Note.



Revision History

Rev.	Date	Description	
		Page	Summary
1.00	Jun.28.22	-	First Edition issued.
1.10	May 31.23	1, 4 2, 3	Appended section 3.1.2 for memory size information. Updated the release note version number.
1.20	Sep.29.23	1, 6, 8 1, 5 2, 3 4 5 6 to 9	Append notes for the Encoder I/F Configuration Library revision. Updated the target board name. Updated the source code, documents revisions and the document filenames. Changed the number of storing samples by poscon and elctimer commands. Source code for command selection is corrected. Updated memory size information. Updated description of the CPU board setting. (Description for the SW4-2 is changed. SW6-1 setting is added.) Updated build environment for FSP v1.3.0. Figures are replaced.

General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Precaution against Electrostatic Discharge (ESD)

A strong electrical field, when exposed to a CMOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop the generation of static electricity as much as possible, and quickly dissipate it when it occurs. Environmental control must be adequate. When it is dry, a humidifier should be used. This is recommended to avoid using insulators that can easily build up static electricity. Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work benches and floors must be grounded. The operator must also be grounded using a wrist strap. Semiconductor devices must not be touched with bare hands. Similar precautions must be taken for printed circuit boards with mounted semiconductor devices.

2. Processing at power-on

The state of the product is undefined at the time when power is supplied. The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the time when power is supplied. In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the time when power is supplied until the reset process is completed. In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the time when power is supplied until the power reaches the level at which resetting is specified.

3. Input of signal during power-off state

Do not input signals or an I/O pull-up power supply while the device is powered off. The current injection that results from input of such a signal or I/O pull-up power supply may cause malfunction and the abnormal current that passes in the device at this time may cause degradation of internal elements. Follow the guideline for input signal during power-off state as described in your product documentation.

4. Handling of unused pins

Handle unused pins in accordance with the directions given under handling of unused pins in the manual. The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of the LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible.

5. Clock signals

After applying a reset, only release the reset line after the operating clock signal becomes stable. When switching the clock signal during program execution, wait until the target clock signal is stabilized. When the clock signal is generated with an external resonator or from an external oscillator during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Additionally, when switching to a clock signal produced with an external resonator or by an external oscillator while program execution is in progress, wait until the target clock signal is stable.

6. Voltage application waveform at input pin

Waveform distortion due to input noise or a reflected wave may cause malfunction. If the input of the CMOS device stays in the area between V_{IL} (Max.) and V_{IH} (Min.) due to noise, for example, the device may malfunction. Take care to prevent chattering noise from entering the device when the input level is fixed, and also in the transition period when the input level passes through the area between V_{IL} (Max.) and V_{IH} (Min.).

7. Prohibition of access to reserved addresses

Access to reserved addresses is prohibited. The reserved addresses are provided for possible future expansion of functions. Do not access these addresses as the correct operation of the LSI is not guaranteed.

8. Differences between products

Before changing from one product to another, for example to a product with a different part number, confirm that the change will not lead to problems. The characteristics of a microprocessing unit or microcontroller unit products in the same group but having a different part number might differ in terms of internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.

7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 October 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan

www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:

www.renesas.com/contact/.