

NESG2101M05

NPN SiGe RF Transistor for Medium Output Power Amplification (125 mW)
Flat-Lead 4-Pin Thin-Type Super Minimold (M05)

R09DS0036EJ0300
Rev. 3.00
Jun 20, 2012

FEATURES

- The device is an ideal choice for medium output power, high-gain amplification and low distortion, low noise, high-gain amplification
 - $P_{O(1\text{ dB})} = 21\text{ dBm TYP. @ } V_{CE} = 3.6\text{ V, } I_{Cq} = 10\text{ mA, } f = 2\text{ GHz}$
 - $NF = 0.6\text{ dB TYP., } G_a = 19.0\text{ dB TYP. @ } V_{CE} = 2\text{ V, } I_C = 7\text{ mA, } f = 1\text{ GHz}$
- Maximum stable power gain: $MSG = 17.0\text{ dB TYP. @ } V_{CE} = 3\text{ V, } I_C = 50\text{ mA, } f = 2\text{ GHz}$
- High breakdown voltage technology for SiGe Tr. adopted: V_{CEO} (absolute maximum ratings) = 5.0 V
- Flat-lead 4-pin thin-type super minimold (M05) package

<R>

ORDERING INFORMATION

Part Number	Order Number	Package	Quantity	Supplying Form
NESG2101M05	NESG2101M05-A	Flat-lead 4-pin thin-type super minimold (M05, 2012 PKG) (Pb-Free)	50 pcs (Non reel)	<ul style="list-style-type: none"> • 8 mm wide embossed taping • Pin 3 (Collector), Pin 4 (Emitter) face the perforation side of the tape
NESG2101M05-T1	NESG2101M05-T1-A		3 kpcs/reel	

Remark To order evaluation samples, please contact your nearby sales office.
Unit sample quantity is 50 pcs.

ABSOLUTE MAXIMUM RATINGS ($T_A = +25^\circ\text{C}$)

Parameter	Symbol	Ratings	Unit
Collector to Base Voltage	V_{CBO}	13.0	V
Collector to Emitter Voltage	V_{CEO}	5.0	V
Emitter to Base Voltage	V_{EBO}	1.5	V
Collector Current	I_C	100	mA
Total Power Dissipation	P_{tot} ^{Note}	500	mW
Junction Temperature	T_j	150	$^\circ\text{C}$
Storage Temperature	T_{stg}	-65 to +150	$^\circ\text{C}$

Note: Mounted on $38\text{ cm}^2 \times 0.4\text{ mm}$ (t) polyimide PCB

CAUTION

Observe precautions when handling because these devices are sensitive to electrostatic discharge.

The mark <R> shows major revised points.

The revised points can be easily searched by copying an "<R>" in the PDF file and specifying it in the "Find what:" field.

<R> **ELECTRICAL CHARACTERISTICS (T_A = +25°C)**







Parameter	Symbol	Test Conditions	MIN.	TYP.	MAX.	Unit
DC Characteristics						
Collector Cut-off Current	I _{CBO}	V _{CB} = 5 V, I _E = 0	–	–	100	nA
Emitter Cut-off Current	I _{EBO}	V _{EB} = 1 V, I _C = 0	–	–	100	nA
DC Current Gain	h _{FE} ^{Note 1}	V _{CE} = 2 V, I _C = 5 mA	130	190	260	–
RF Characteristics						
Gain Bandwidth Product	f _T	V _{CE} = 3 V, I _C = 50 mA, f = 2 GHz	14	17	–	GHz
Insertion Power Gain	S _{21e} ²	V _{CE} = 3 V, I _C = 50 mA, f = 2 GHz	11.5	13.5	–	dB
Noise Figure (1)	NF	V _{CE} = 2 V, I _C = 10 mA, f = 2 GHz, Z _S = Z _{Sopt} , Z _L = Z _{Lopt}	–	0.9	1.2	dB
Noise Figure (2)	NF	V _{CE} = 2 V, I _C = 7 mA, f = 1 GHz, Z _S = Z _{Sopt} , Z _L = Z _{Lopt}	–	0.6	–	dB
Associated Gain (1)	G _a	V _{CE} = 2 V, I _C = 10 mA, f = 2 GHz, Z _S = Z _{Sopt} , Z _L = Z _{Lopt}	11.0	13.0	–	dB
Associated Gain (2)	G _a	V _{CE} = 2 V, I _C = 7 mA, f = 1 GHz, Z _S = Z _{Sopt} , Z _L = Z _{Lopt}	–	19.0	–	dB
Reverse Transfer Capacitance	C _{re} ^{Note 2}	V _{CB} = 2 V, I _E = 0, f = 1 MHz	–	0.4	0.5	pF
Maximum Stable Power Gain	MSG ^{Note 3}	V _{CE} = 3 V, I _C = 50 mA, f = 2 GHz	14.5	17.0	–	dB
Gain 1 dB Compression Output Power	P _O (1 dB)	V _{CE} = 3.6 V, I _{Cq} = 10 mA, f = 2 GHz	–	21	–	dBm
Linear Gain	G _L	V _{CE} = 3.6 V, I _{Cq} = 10 mA, f = 2 GHz	–	15	–	dB

- Notes
1. Pulse measurement: PW ≤ 350 μs, Duty Cycle ≤ 2%
 2. Collector to base capacitance when the emitter grounded
 3. $MSG = \left| \frac{S_{21}}{S_{12}} \right|$

h_{FE} CLASSIFICATION


Rank	FB/YFB
Marking	T1J
h _{FE} Value	130 to 260

TYPICAL CHARACTERISTICS ($T_A = +25^\circ\text{C}$, unless otherwise specified)




Remark The graph indicates nominal characteristics.


COLLECTOR CURRENT vs. COLLECTOR TO EMITTER VOLTAGE




DC CURRENT GAIN vs. COLLECTOR CURRENT




DC CURRENT GAIN vs. COLLECTOR CURRENT



DC CURRENT GAIN vs. COLLECTOR CURRENT




DC CURRENT GAIN vs. COLLECTOR CURRENT




Remark The graph indicates nominal characteristics.


GAIN BANDWIDTH PRODUCT vs. COLLECTOR CURRENT




GAIN BANDWIDTH PRODUCT vs. COLLECTOR CURRENT



GAIN BANDWIDTH PRODUCT vs. COLLECTOR CURRENT




GAIN BANDWIDTH PRODUCT vs. COLLECTOR CURRENT




Remark The graph indicates nominal characteristics.


INSERTION POWER GAIN, MAG, MSG vs. FREQUENCY




INSERTION POWER GAIN, MAG, MSG vs. FREQUENCY



INSERTION POWER GAIN, MAG, MSG vs. FREQUENCY




INSERTION POWER GAIN, MAG, MSG vs. FREQUENCY




Remark The graph indicates nominal characteristics.


INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT



INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT




Remark The graph indicates nominal characteristics.


INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT



INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG vs. COLLECTOR CURRENT




Remark The graph indicates nominal characteristics.


OUTPUT POWER, POWER GAIN, COLLECTOR CURRENT, COLLECTOR EFFICIENCY vs. INPUT POWER




OUTPUT POWER, POWER GAIN, COLLECTOR CURRENT, COLLECTOR EFFICIENCY vs. INPUT POWER



OUTPUT POWER, POWER GAIN, COLLECTOR CURRENT, COLLECTOR EFFICIENCY vs. INPUT POWER




OUTPUT POWER, POWER GAIN, COLLECTOR CURRENT, COLLECTOR EFFICIENCY vs. INPUT POWER




Remark The graph indicates nominal characteristics.


NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT




NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT




NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT




NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT



NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT




NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT




Remark The graphs indicate nominal characteristics.


NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT




NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT




NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT




NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT



NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT



NOISE FIGURE, ASSOCIATED GAIN vs. COLLECTOR CURRENT



Remark The graphs indicate nominal characteristics.

<R> **S-PARAMETERS**

S-parameters and noise parameters are provided on our web site in a form (S2P) that enables direct import of the parameters to microwave circuit simulators without the need for keyboard inputs.

Click here to download S-parameters.


[Products] → [RF Devices] → [Device Parameters]

URL <http://www.renesas.com/products/microwave/>

**Not recommend
for new design**

PACKAGE DIMENSIONS

<R> FLAT-LEAD 4-PIN THIN-TYPE SUPER MINIMOLD (M05, 2012 PKG) (UNIT: mm)



PIN CONNENTION

- 1. Base
- 2. Emitter
- 3. Collector
- 4. Emitter

Remark () : Reference value

Not recommended for new design

Revision History	NESG2101M05 Data Sheet
-------------------------	-------------------------------

Rev.	Date	Description	
		Page	Summary
-	Mar 2003	-	Previous No. : PU10190EJ02V0DS
3.00	Jun 20, 2012	p.1	Modification of ORDERING INFORMATION
		p.2	Modification of ELECTRICAL CHARACTERISTICS
			Modification of h_{FE} CLASSIFICATION
		p.12	Modification of S-PARAMETERS
p.13	Modification of PACKAGE DIMENSIONS		

Not recommend
for new design

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.
Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.
 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A.
Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited
1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada
Tel: +1-905-898-5441, Fax: +1-905-898-3220

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-65030, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd., Pudong District, Shanghai 200120, China
Tel: +86-21-5877-1818, Fax: +86-21-6887-7858 / -7898

Renesas Electronics Hong Kong Limited
Unit 1601-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2886-9318, Fax: +852 2886-9022/9044

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei, Taiwan
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
1 HarbourFront Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: +65-6213-0200, Fax: +65-6278-9001

Renesas Electronics Malaysia Sdn.Bhd.
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics Korea Co., Ltd.
11F., Samik Laved' or Bldg., 720-2 Yeoksam-Dong, Kangnam-Ku, Seoul 135-080, Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5141