



VOICE USER INTERFACE SOLUTION

Easy-to-use Reference Design with RA Family

The new Renesas easy-to-use hardware platform for Voice User Interface (VUI) solutions is based on the high-performance RA family of 32-bit MCUs. The new reference platform is used for all VUI partner-enabled solutions within the Renesas Ready Partner Network and demonstrates how easy it is to control your system with a simple voice command interface without extensive coding experience or in-house expertise.

The reference kit enables local voice recognition without a network connection, and allows you to quickly start building an enhanced VUI in minutes that recognizes your own voice commands to trigger the corresponding operation.

Hardware Features

- RA Arm[®] Cortex[®]-M23 & -M33 MCU
- Up to two digital microphones and two analog microphones
- External QSPI flash to store voice samples and library data
- Communication interfaces:
 - Pmod type-2A / 3A / 6A
 - USB type-C and micro-B
 - On board J-link Seggar debugger / programmer



Block Diagram

Software Features

- Cyberon DSpotter
 - Provides DNN based pre-trained voice model
 - User creates command by text input
 - Support for Online & Offline test options
 - Analyze recognition score
 - Tune performance real-time
 - Real-time tool to observe input voice waveform



Target Applications

- Edge applications enabling endpoint voice user interface independent from network / cloud / edge connections
 - IoT Devices
 - Home Appliances
 - Wearable / Hearable Devices

VOICE USER INTERFACE SOLUTION

Benefits

- Local voice trigger and command recognition
 Endpoint capable, no need of network connection
- Robust noise reduction | High-accuracy performance | Very small footprint
 - Small footprint (Flash: 55K/90KB/155KB + 32B*Xc, RAM:18KB/21KB/24KB+128B*Xc)
- Supports multiple languages | Arm® Trust Zone for security
 - Separation of recognition engine and command model, switching commands dynamically

44+ Languages Supported

- Enables command customization, performance tuning, testing
 - Quick command customization / optimization by model adaptation with only a small amount of speech data
- Voice Activity Detection (VAD) and audio playback
 - Reduces power consumption, provides snooze mode, enables voice response function



Ordering Information

Part Number	Description
TW001-VUIA6E1POCZ	RA6E1 Voice reference kit with multi-language support
TW001-VUIA4E1POCZ	RA4E1 Voice reference kit with command recognition
TW001-VUIA2L1P0CZ	RA2L1 Voice reference kit with low MHz consumption

Get more details and request a kit at: renesas.com/voice-recognition



Corporate Headquarters TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

Document No.: R12PF0025EU0200

Trademarks Arm⁶ and Cortex⁶ are registered trademarks of Arm Limited. Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

© 2022 Renesas Electronics Corporation. All rights reserved.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit: www.renesas.com/contact/