



Integrated Device Technology

# VPS-1848 Virtual Channel Serial RapidIO® Gen2 Switch

POWER MANAGEMENT | ANALOG & RF | INTERFACE & CONNECTIVITY | CLOCKS & TIMING | MEMORY & LOGIC | TOUCH & USER INTERFACE | VIDEO & DISPLAY | AUDIO

## FEATURES


- Designed to the Serial RapidIO 2.1 Specification
- 48 lanes, with up to 12x4, 18x2, or 18x1 port configurations
- Full-duplex 240 Gbps non-blocking bandwidth
- Virtual Channel Features
  - VC0 supports standard S-RIO 1.3 priorities and CRF
  - Minimum bandwidth reservation guarantees for each of VC0, VC1, and VC5 ensure throughput and deterministic latency
  - VC1 and VC5 support Continuous Transmission mode for real-time data transport
  - Buffers allocated to VC0 when VC1 and VC5 are disabled
  - Support for 64 outstanding packets for VC1 and VC5
  - “VC Migration Mode” allows for Gen 1 endpoints to communicate using VC1 and VC5
- Carrier-grade, high performance SerDes
  - 1.25, 2.5, 3.125, 5.0, or 6.25 Gbaud
  - Long reach 100 cm with 2 connectors
  - Transmit drive strength and pre-emphasis
  - Receive equalization with DFE
  - On-die scope
- Up to 40% power-per-gigabit savings vs. RapidIO 1.3 Switches
- Dynamic ingress and egress buffer management improves performance over RapidIO 1.3 switches
  - Better per-port throughput
  - Better system-level traffic engineering
- 40 multicast groups per port
- Cut-through and store-and-forward modes
- Cut-through latency of 100 ns
- RapidIO Error Management Extension support
- Error log captures sequence of errors
- Packet mirror, trace, filter per port
- Receiver- and transmitter-based flow control
- Per-port reset provides robust hot swap support
- Multicast Event Control Symbol (MECS) generation input pin
- Industrial and Commercial temperature grades
- 29 x 29 mm FCBGA

## BENEFITS VS OTHER INTERCONNECT PROTOCOLS

- Design highest performance backplane in the industry with 20 Gbps data rate per link
- Lowest power per payload bit
- Ecosystem support for four levels of priority plus critical request flow, providing up to eight classes of traffic
- RapidIO standard supports arbitrary system topology with true peer-to-peer networking
- Twice the performance per link compared to 10-Gb Ethernet
- RapidIO messaging support for transfers of 4-KB messages in hardware

## TARGET APPLICATIONS

- Wireless: Baseband cards and backplanes in LTE/WiMAX/WCDMA/TD-SCDMA
- Defense and aerospace: RADAR, SONAR and navigations systems
- Medical imaging: CT scanners, MRIs
- Video: Teleconferencing and Head End
- Industrial control systems



## Device Overview

The VPS-1848 is a virtual channel enabled RapidIO switch. Using the VPS-1848, any physical link can be further subdivided into multiple virtual links or “virtual channels” as described by the RapidIO 2.1 specification. Using Virtual Channels (VC’s), OEMs can design systems where the bandwidth utilization between switch-to-switch links is optimized for various classes of traffic. The use of Virtual Channels improves overall S-RIO network traffic management, improving end application performance.

In addition to the above, the VPS-1848 supports all RapidIO features available in the pin-compatible CPS-1848 including a full, non-blocking bandwidth of 240 Gbps for up to 18 ports. The device uses a 5th generation switch fabric, building upon IDT’s Gen 1 switching architecture. This new switch uses patent-pending features to minimize latency, ensure scheduling fairness, and provide superior multicast throughput. The VPS-1848’s 6.25 Gbaud SerDes is ideal for backplanes yet can run even lower power for local connectivity. This performance is realized over twice the transmission channel distance and three orders of magnitude improvement in bit error ratio (BER) compared to the very capable Gen1 standard.

IDT’s Gen2 switches connect the Serial RapidIO ecosystem, including full backward compatibility to RapidIO 1.3 systems and components. The Serial RapidIO ecosystem enables carrier-grade reliable, fault tolerant systems with four standard traffic priority levels for quality of service. It also offers best-in-class messaging and atomic transaction support with protocol throughput efficiencies superior to other leading embedded interconnect protocols.

## Applications

IDT’s Gen2 switches, in tandem with other Serial RapidIO endpoints, enable next-generation compute density and power efficiencies. This significantly increases channel capacity for 3G to 4G wireless infrastructure, media gateways, video conferencing, and defense and medical imaging systems. Full peer-to-peer networking makes systems of arbitrary topology possible. The VPS-1848 further improves system performance by using VC’s to optimize the usage of available bandwidth on any physical RapidIO 2.1 link between IDT switches.

## VPS-1848 BENEFITS FOR WIRELESS

- Carrier-grade reliable packet transport with virtual-channel features for optimized traffic management and S-RIO network bandwidth utilization
- VCO supports traditional S-RIO 1.3 priorities and CRF
- VC1 and VC5 support both Reliable Transmission (RT) and Continuous Transmission mode (CT). CT mode is ideal for real-time support of video and voice traffic
- Internal packet buffer flexibility means that internal switch memory can be reallocated to VCO when VC1 and VC5 is not used, ensuring optimum network throughput

## VPS-1848 BENEFITS FOR DEFENSE AND AEROSPACE

- Virtual Channel capability on switch-to-switch links improves performance of multi-switch cluster in an OpenVPX 24x4 port switch card
- VITA 41, OpenVPX, and ATCA fabric mappings enable rapid development of modular, standards-based systems
- RapidIO-standard, true peer-to-peer networking allows scaling of arbitrary topology and simplifies hot swap software implementation
- Per-port filter feature allows blocking errant packets or malicious attack (for example, denial of service, system memory reads and writes)

## VPS-1848 BENEFITS FOR VIDEO AND IMAGING

- Continuous Transmission mode in VC1 and VC5 are ideal for real-time video and voice as packets can be dropped if necessary to guarantee latency
- 40 multicast masks per port provides strong support for broadcasting or multicasting a given data stream to multiple endpoints executing unique transforms, scaling, and CODECs
- IDT-proprietary "retransmit mimic" feature improves real-time support for latency sensitive lossy data transfers


## SOFTWARE AND HARDWARE ECOSYSTEM

- Serial RapidIO Development Platform Gen2 (SRDP2)
- RapidFET JTAG edition software support
- Serial RapidIO Gen2 Endpoint Intellectual Property for ASIC, CPU, DSP, and FPGAs
- Numerous partner RapidIO-enabled AMCs
- RapidIO Linux support
- Power Calculator tool
- HSPICE and IBIS models


Discover what IDT know-how can do for you:

[www.IDT.com/go/SRIOGen2](http://www.IDT.com/go/SRIOGen2)


## Wireless Application



## Military OpenVPX Application



## Imaging Application



DISCLAIMER Integrated Device Technology, Inc. (IDT) and its subsidiaries reserve the right to modify the products and/or specifications described herein at any time and at IDT's sole discretion. All information in this document, including descriptions of product features and performance, is subject to change without notice. Performance specifications and the operating parameters of the described products are determined in the independent state and are not guaranteed to perform the same way when installed in customer products. The information contained herein is provided without representation or warranty of any kind, whether express or implied, including, but not limited to, the suitability of IDT's products for any particular purpose, an implied warranty of merchantability, or non-infringement of the intellectual property rights of others. This document is presented only as a guide and does not convey any license under intellectual property rights of IDT or any third parties. IDT's products are not intended for use in life support systems or similar devices where the failure or malfunction of an IDT product can be reasonably expected to significantly affect the health or safety of users. Anyone using an IDT product in such a manner does so at their own risk, absent an express, written agreement by IDT.

Integrated Device Technology, IDT and the IDT logo are registered trademarks of IDT. Other trademarks and service marks used herein, including protected names, logos and designs, are the property of IDT or their respective third party owners. © Copyright 2011. All rights reserved.