

Introduction

In an integrated circuit, the individual transistors must be isolated from each other for correct circuit operation. In most IC processes, this is done by using reverse biased PN junctions and the technology is referred to as Junction Isolation (JI). The degree of isolation is limited by collector-substrate leakage currents and voltage modulated collector-substrate capacitance. An ideal isolation technology would not have leakage and capacitive coupling between devices.

Intersil uses a Silicon On Insulator (SOI) bipolar process, which differs radically from conventional bipolar JI processes in that the individual transistors are electrically isolated from their neighbors by a layer of glass. With the Intersil SOI process, a layer of glass (SiO_2) surrounds the transistors on all four sides and the bottom. This totally isolates the individual transistors and provides essentially ideal isolation.

Silicon On Insulator (SOI) is a way of building monolithic integrated circuits, which have performance that rivals a multi-chip hybrid.

Intersil SOI Process

Intersil uses SOI to make both NPN transistors and PNP transistors in a high frequency vertical structure as shown in [Figure 1](#). There are two collector, two base and two emitter diffusions. Therefore, each transistor type can be optimized without compromising its complement. In analog circuit design, both NPN and PNP transistors are in the signal path. Thus the slower of the two transistors determines the overall circuit speed limitations. Most JI processes use lateral structure PNP transistors, which have speed characteristics (f_t) that are 50 to 100 times slower than the NPNs. Thus most JI processes are 50 to 100 times slower than Intersil's SOI process.

SOI also has the capability of operating at a given high frequency with lower power consumption than conventional bipolar processes of similar geometry due to the reduced collector-substrate capacitance. These stray capacitances require extra supply current to charge them, supply current that is otherwise unnecessary in the circuit. Collector to substrate capacitances in SOI are about one-tenth of those in JI.

SOI is an isolation technique and as such is a process technology platform, which may be used as a starting point in more esoteric process development. Intersil's advanced SOI process today uses implanted resistors, MOS capacitors and Schottky diodes in addition to high performance, totally implanted complementary transistors. Other elements may be added such as BiFETs and thin film resistors. CMOS or even combined CMOS and bipolar (BiCMOS) can be implemented on SOI. In all cases, the SOI lends its superb isolation, low leakage and high-speed characteristics to the process.

Intersil's patented SOI technology has been improved substantially from the original process. Performance and device density have been increased resulting in costs equaling that of standard JI. Intersil's latest process has NPN and PNP f_t 's of 4GHz at 40V, 2 micron CMOS and very low defect density.

SOI Benefits

Speed

Speed is improved in SOI integrated circuits for two reasons. First, since the collector substrate capacitance is smaller than JI by a factor of 10, the slew rate of an internal node can be 10 times as fast as the same node in JI, using the same amount of current. Second, it is very difficult to build fast vertical PNP transistors with JI, so most JI circuits settle for using a lateral PNP transistor somewhere in the signal path. With SOI, fully isolated fast vertical PNP and NPN transistors can be made on the same chip and therefore performance need not be compromised by a slow transistor.

Temperature Performance

All junctions have leakage currents directly impacted by temperature. Higher temperatures create higher leakages. Many integrated circuits stop working if stray leakages between adjacent transistors are too high. Thus at high temperatures, these ICs cease working. With SOI, the high temperature leakages between adjacent transistors do not exist and the circuit can continue to work at high temperatures. Applications such as oil wells, where the temperatures may reach +200 °C, are prime examples where SOI is necessary for its temperature characteristics.

Radiation Hardness

The same leakages affected by temperature are also affected by radiation. The radiation may be from either a nuclear event or from deep space radiation. Because the SOI glass layer is unaffected by radiation, the performance of SOI circuits in the presence of radiation makes SOI the mandatory technology for many military applications.

Freedom From Latch-up

Many JI devices are prone to latch-up. That is, under some external conditions the circuit will become stuck in a particular internal condition and will not function properly until the power is removed. Sometimes the circuit will self destruct due to latch-up. A key factor in this latch-up is the participation of the isolation junction in the circuitry that creates a parasitic SCR (Silicon Controlled Rectifier). In SOI, since there is no isolation junction, there can be no latch-up.

Intersil SOI Advantages Over JI

- Speed
 - Fast (vertical) PNP and NPNs
 - Lower Collector to substrate capacitance
 - Collector to substrate capacitance not modulated by collector voltage
- No Possibility of Circuit Latch-up via Parasitic SCRs
 - No parasitic devices with SOI
- Operates in High Temperature and Radiation Environments
 - Leakage currents are blocked by SOI walls
- High Voltage Operation
 - Device to device breakdown >2000V
- Mixed Technologies on Same Chip
 - Bipolar transistors, diffused resistors and MOS can be done on the same monolithic chip




FIGURE 1. COMPLIMENTARY SOI PROCESS

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
 6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
 7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
 11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338