

DA9281 Unused Pin Configuration

This application note describes the recommended configuration for unused pins in applications that use the DA9281 power management IC.

Contents

Contents1

Tables.....1

1. Terms and Definitions2

2. References.....2

3. Introduction2

4. DA9281 Functional Blocks.....2

5. Conclusion3

Revision History4

Tables

Table 1: Pin Type Definition.....2

Table 2: Pin Description.....2

1. Terms and Definitions

CH<x>	Channel <x>
DDR	Double data rate
LDO	Low drop out (regulator)
OC	Over-current protection
OVP	Over-voltage protection
PGND	Power ground
PMIC	Power management integrated circuit
SW	Switching
UVP	Under-voltage protection
VTT	Termination voltage regulator

2. References

[1] DA9281_Datasheet, Renesas Electronics.

Note 1 References are for the latest published version, unless otherwise indicated.

3. Introduction

DA9281 is an eight-channel power management integrated circuit (PMIC) with four buck regulators, three LDOs and one voltage buffer to support DDR VTT termination

Key functions for power applications, such as soft-start, selectable preset output voltage, flexible power-up and power-down sequences are provided on chip and are programmable via the I²C interface with non-volatile memory defaults.

All eight channels have an output discharge function and protections features such as over-current protection (OCP), over voltage protection (OVP), and under voltage protection (UVP).

4. DA9281 Functional Blocks

The following tables describe the recommended configurations for unused pins. "Mandatory" means that the pin is used in all applications.

Table 1: Pin Type Definition

Pin Type	Description	Pin Type	Description
DI	Digital input	AI	Analog input
DO	Digital output	AIO	Analog input/output
DIO	Digital input/output	PWR	Power
DIOD	Digital input/output open drain	GND	Ground

Table 2: Pin Description

Pin #	Pin Name	Type (Table 1)	Description	If Unused
1,2	VIN3	PWR	Input voltage for CH3 buck converter	Connect to GND (cap not required)
3	VOUT3	AI	Output voltage feedback of CH3 buck converter	Connect to GND
4,5	VIN8	PWR	Input voltage for CH8 LDO	Connect to GND (cap not required)
6,7	VOUT8	AO	Output voltage of CH8 LDO	Leave floating (cap not required)
8	PGND	GND	Power ground	Mandatory

Pin #	Pin Name	Type (Table 1)	Description	If Unused
9,10	LX2	AO	SW node of CH2 buck converter	Leave floating (L and Cout not required)
11,12	VIN2	PWR	Input voltage for CH2 buck converter	Connect to GND (cap not required)
13	VOUT2	AI	Output voltage feedback of CH2 buck converter	Connect to GND
14	VOUT6	AO	Output voltage of CH6 LDO	Leave floating (cap not required)
15	VIN6	PWR	Input voltage for CH6 LDO	Connect to GND (cap not required)
16	VIN7	PWR	Input voltage for CH7 LDO	Connect to GND (cap not required)
17	VOUT7	AO	Output voltage of CH7 LDO	Leave floating (cap not required)
18	VOUT5_FB	AI	Output voltage feedback of CH5 regulator	Connect to GND
19	VOUT5	AO	Output voltage of CH5 regulator	Leave floating (cap not required)
20	VIN5	PWR	Input voltage for CH5 regulator	Connect to GND (cap not required)
21	VOUT4	AI	Output voltage feedback of CH4 buck converter	Connect to GND
22,23	VIN4	PWR	Input voltage for CH4 buck converter	Connect to GND (cap not required)
24,25	LX4	AO	SW node of CH4 buck converter	Leave floating (L and Cout not required)
26	PGND	GND	Power ground	Mandatory
27-30	LX1	AO	SW node of CH1 buck converter	Leave floating (L and Cout not required)
31,32	VIN1	PWR	Input voltage for CH1 buck converter	Connect to GND (cap not required)
33	VOUT1	AI	Output voltage feedback of CH1 buck converter	Connect to GND
34	EN	DI	Enable pin	Mandatory
35	SCL	DI	Two-wire I ² C clock	Mandatory - though can be connected to GND if I ² C control/monitoring is not required
36	SDA	DIO	Two-wire I ² C data input/output	Mandatory - though can be connected to GND if I ² C control/monitoring is not required
37	AGND	GND	Quiet analog ground	Mandatory
38	AVCC	PWR	Quiet analog supply	Mandatory
39,40	LX3	AO	SW node of CH3 buck converter	Leave floating (L and Cout not required)
Paddle	PGND	GND	Common ground for all channels	Mandatory

5. Conclusion

Adherence to the recommendations of this document helps minimize spurious application issues such as noise and increased current consumption and may avoid device damage due to incorrectly biased pins. For further information please consult your Renesas Electronics [local sales representative](#).

Revision History

Revision	Date	Description
1.0	Nov 26, 2024	First version.

Status Definitions

Status	Definition
DRAFT	The content of this document is under review and subject to formal approval, which may result in modifications or additions.
APPROVED or unmarked	The content of this document has been approved for publication.

RoHS Compliance

Renesas Electronics' suppliers certify that its products are in compliance with the requirements of Directive 2011/65/EU of the European Parliament on the restriction of the use of certain hazardous substances in electrical and electronic equipment. RoHS certificates from our suppliers are available on request.

Important Notice and Disclaimer

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

© 2024 Renesas Electronics Corporation. All rights reserved.

(Rev.1.0 Mar 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
<https://www.renesas.com/contact/>

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation.
All trademarks and registered trademarks are the property of their respective owners.