




TOP VIEW




SIDE VIEW




BOTTOM VIEW



SIDE VIEW



Detail A  
(Rotated 90° CW)



RECOMMENDED LAND PATTERN  
(PCB Top View, SMD Design)

| Reference | Dimension in mm |           |      |
|-----------|-----------------|-----------|------|
| Symbol    | Min             | Nom       | Max  |
| D         | 4.80            | 4.90      | 5.00 |
| E         | 3.80            | 3.90      | 4.00 |
| A2        | 1.30            | 1.40      | 1.50 |
| HD        | -               | -         | -    |
| HE        | 5.80            | 6.00      | 6.20 |
| D1        | -               | -         | -    |
| E1        | -               | -         | -    |
| A         | -               | -         | 1.75 |
| A1        | 0.10            | -         | 0.23 |
| bp        | 0.39            | -         | 0.47 |
| c         | 0.20            | -         | 0.24 |
| θ         | 0.00            | -         | 8.00 |
| e         | 1.27 BSC        |           |      |
| y         | -               | -         | 0.08 |
| LP        | 0.50            | 0.65      | 0.80 |
| L1        | -               | 1.05 REF. | -    |

NOTES:

- JEDEC compatible.
- All dimensions are in mm and angles are in degrees.
- Use  $\pm 0.05$  mm for the non-toleranced dimensions.
- Foot length is measured at gauge plane 0.25 mm above seating plane.