



32-BIT MCU FAMILY


RENESAS RA4T1 GROUP

RA4 Series 100MHz Arm® Cortex®-M33 Motor Control Microcontroller

The RA4T1 is based on the 100 MHz Arm® Cortex®-M33 core with TrustZone®.

The RA4T1 group offers optimized peripheral functions for motor control and inverter control with small 32-pin QFN and LQFP package options. These satisfy the needs of high-performance, cost-sensitive and space-constrained applications.

The RA4T1 integrates a wide range of communication interfaces including CAN FD, I3C, SCI and SPI covering all the connectivity needs of a wide range of motor control and consumer applications.




Target Applications

- Vacuum cleaner
- Washing machine
- Refrigerator
- IH cooker
- Fan
- Pump
- Thermal printer
- Power tools

Key Features

- 100MHz Arm® Cortex®-M33 with TrustZone®
- 128KB - 256KB Flash memory and 40KB SRAM
- 4KB Data Flash to store data as in EEPROM
- Scalable from 32-pin to 64-pin packages
- PWM timer
- 12-bit ADC
- Programmable gain amp
- High speed comparator
- 12-bit DAC
- Trigonometric Function Unit
- CAN FD
- I3C, SCI, SPI

Block Diagram




RENESAS RA4T1 GROUP

Software Package

The Renesas Flexible Software Package (FSP) is designed to provide easy-to-use, scalable, high-quality software for embedded system designs using the Renesas RA family. The FSP is based on an open software ecosystem of production-ready drivers, supporting Azure® RTOS, FreeRTOS™ or bare-metal programming. It also includes a selection of other middleware stacks, providing great flexibility for migrating code from older systems or developing new applications from scratch.

Tools and Support

The e² studio IDE provides support with intuitive configurators and intelligent code generation to make programming and debugging easier and faster.



IDE	Renesas e²studio	Keil MDK	IAR EWARM
Compiler	• GCC • Arm Compiler • IAR Arm Compiler	• Arm Compiler	• IAR Arm Compiler
Debug Probe	• Renesas E2/E2 Lite • SEGGER J-Link	• SEGGER J-Link • Keil ULINK (limited support)	• IAR I-Jet (limited support) • SEGGER J-Link
Production Programmer	• Renesas PG-FP6 • SEGGER J-Flash • Partner solutions		

Evaluation Kit

- MCK-RA4T1 Renesas Flexible Motor Control Kit for RA4T1 MCU Group
- Includes CPU board, inverter board, PMSM motor, and accessories
- Documentation and more information: renesas.com/mck-ra4t1
- Orderable part number: **RTK0EMA430S00020BJ**



- MCB-RA4T1 CPU Board for RA4T1 MCU Group
- On-board debugging using SEGGER J-Link®
- Documentation and more information: renesas.com/mcb-ra4t1
- Orderable part number: **RTK0EMA430C00000BJ**



Ordering References

Flash RAM DataFlash	256KB	R7FA4T1BB3CNH	R7FA4T1BB3CFJ	R7FA4T1BB3CNE	R7FA4T1BB3CFL	R7FA4T1BB3CFM
	40KB					
	4KB					
	128KB	R7FA4T1B93CNH	R7FA4T1B93CFJ	R7FA4T1B93CNE	R7FA4T1B93CFL	R7FA4T1B93CFM
Pin Count	40KB					
	4KB					
	4KB					
	4KB					
Package	QFN	QFN	QFN	QFN	QFN	QFN
Size (body)	5x5mm	7x7mm	7x7mm	7x7mm	7x7mm	10x10mm
Pitch	0.5mm	0.8mm	0.5mm	0.5mm	0.5mm	0.5mm
Operating Temperature	-40 to +105°C	-40 to +105°C	-40 to +105°C	-40 to +105°C	-40 to +105°C	-40 to +105°C

For more details, please visit: renesas.com/ra4t1



renesas.com

Corporate Headquarters
TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Document No.: R01PF0236EU0100

Trademarks
Arm® and Cortex® are registered trademarks of Arm Limited. Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information
For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/

© 2023 Renesas Electronics Corporation. All rights reserved.