


Analog input current vs AVcc (AN0-AN11)

Prepared on Oct. 20, 2006

R5F21258SNFP(Topr=-20 to 85degrees C)
R5F21258SDFP(Topr=-40 to 85degrees C)
Topr=25 degrees C
AVcc-Vss: 0.1uF Vref-Vss: 0.1uF
ANIN-Vss: 0.1uF
AVcc=Vref
Xin=10MHz ϕ_{AD} =5MHz
sample and hold=on Repeat mode

— Analog input=0V
— Analog input=AVCC



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.