

RS-232 Transmitter/Receivers Provide High Speed and 15KV ESD Protection

AN9799
Rev 2.00
November 21, 2005

Introduction

The Intersil family of high-speed, 15kV ESD-protected devices (HIN202E - HIN241E) offers the user unparalleled performance in RS-232 communication. The devices feature high speed (230kbits/s) ISDN-compatible operation together with exceptional $\pm 15\text{kV}$ ESD protection and offer a wide variety of RS-232 transmitter/receiver combinations to suit various applications.

The HIN202E - HIN241E interface circuits meet all EIA RS-232E and V.28 specifications and are ideally suited to those applications where $\pm 12\text{V}$ supplies are not available. The devices require a single 5V supply and incorporate on-chip charge pumps and converter circuitry which derive the $\pm 10\text{V}$ levels. In addition, the HIN203E, HIN205E, HIN233E and HIN235E require no external capacitors and are particularly suited for those applications where board space is critical. The HIN205E, HIN206E, HIN211E, HIN213E, HIN235E, HIN236E and HIN241E feature a low power shutdown mode and TTL three-state outputs. The typical current draw in the low power shutdown mode is $1\mu\text{A}$. The HIN213E also provides two active receivers in shutdown mode allowing for easy "wake-up" capability.

The family of HIN202E - HIN241E devices are designed to be used in modems, printers, terminals, desktops, laptops, notebooks, bar code scanners, portable instrumentation and any system requiring RS-232 communication. Portable, battery-powered, or handheld devices are inherently susceptible to electrical stress such as ESD. Their I/O ports conduct ESD noise which may likely zap a system unusable. ESD-protected RS-232 serial ports in this equipment eliminate the need for additional external protection in most applications.

Evolution

With the "never ending" trend of shrinking technologies, submicron CMOS processes, higher pin count devices, higher operating frequencies and lower supply voltages, the importance of robust ESD protection becomes even more critical. With the smaller geometry devices comes reduced gate oxide thickness, shallow junctions, and higher resistive connections. These factors make these new devices inherently more susceptible to ESD damage, compromising the products reliability and performance.

EOS/ESD

ESD (Electrostatic Discharge) which is a subset of EOS (Electrical Overstress), has become increasingly important and of major concern to the electronics industry as a whole and of particular importance to organizations such as EOS/ESD Association which has attempted to standardize this phenomena. Many manufacturers, realizing the significance of EOS/ESD, specify ESD protection limits when purchasing components. Virtually all electronic components can be damaged due to EOS/ESD and the costs associated with this damage has been estimated to be in the billions of dollars, industry-wide. Compounding these costs are the additional costs associated with the customer perception of the product's diminished quality and reliability.

To define EOS, or Electrical Overstress, it is typically generated by power supplies or test equipment and generally lasts from milliseconds to seconds and often results in a catastrophic failure. From an IC level, indications of an EOS event are blown metal lines, molten damage, and often, thermal damage. ESD or Electrostatic Discharge on the other hand is a subset of EOS. ESD events are typically characterized by much less power dissipation (limited energy), events last for much shorter periods, in the range of nanoseconds to milliseconds, and may result in catastrophic failures but frequently result in performance degradation or latent failures. Also, the cumulative effect of repeated exposure can lead to complete failure. Typical indications of ESD damage are gate oxide breakdown, junction spiking, or input leakage failures. ESD events typically occur with device handling by automated handlers or assembly. The fundamental mechanism of ESD is called "tribocharging". Tribocharging occurs when different materials come in contact with one another and then separate, such as the sole of a person's shoe as they walk across a carpet, or when an IC rubs against a rail on an automatic handler. The magnitude of the charge generated is dependent upon many factors such as type of materials, speed at which they rub together, and the relative humidity of the environment.

The extent to which a device can tolerate ESD is measured in kV. The actual definitions of an ESD failures varies among different vendors, some requiring complete functional failure of the device. Intersil defines an ESD failure in the strictest sense. After ESD "zapping" of the device it is subject to full production testing and any part failing to meet any of the DC parametric, AC propagation, or functional testing to the data sheet specifications, is rejected. Maintaining this strict level of testing assures the user the most reliable devices possible.

ESD Testing

There are several test methods currently in use for ESD testing. These methods are:

- Human Body Model (HBM)
- Machine Model (MM)
- Charge Device Model (CDM)
- International Electromechanical Commission (IEC61000-4-2 previously IEC801-X series)

The Human Body Model (HBM) essentially charges a 100pF capacitor in increasing voltages in steps of 100V (100V, 200V, 300V, etc.) and then discharges the capacitor through a 1500Ω resistor into the device pin. (Figure 1). This model simulates that of a human finger contacting a device pin. Specifications that apply to HBM testing are MIL-STD-883, ESD Association Standard EOS/ESD-S5.1-1993 and JEDEC's Test method A114A.




FIGURE 1.

The next, Machine Model (MM), is similar to the HBM. The MM charges a 200pF capacitor in increasing voltages in steps of 100V and then discharges the capacitor directly into the device pin. This model simulates a worst case HBM or that of a charged metallic object contacting a device pin. (Figure 2) Specifications that apply to the MM are ESD Association Standard EOS/ESD-DS5.2-1992 and JEDEC's Test method A115A and EIAJ's IC-121-1988 test Method 20.




FIGURE 2.

The Charged Device Model (CDM) directly charges the device pin to increasing voltage levels through a 300MΩ or 1GΩ resistor then discharges the pin, to ground, through 1Ω resistor. (Figure 3) This model simulates a device pin acquiring a static charge and then touching ground. This scenario has been observed on lead trimming assemblies where the IC devices run along a rail, developing a static charge, and then contacts a metal stop at the

bottom. Standards that apply to the CDM are the ESD Association Standard EOS/ESD-DS5.3-1993 and JEDEC's Test method C101.




FIGURE 3.

Next is the International Electromechanical Commission Human Body Model (IEC61000-4-2). The IEC61000 is actually a system level specification but some customers have been applying this standard to individual IC's. The IEC61000-4-2 again simulates that of a human finger. Two modes are specified within the test. The Contact Mode and the Air Discharge Mode. As its name implies, the contact mode simulates actual contact made to device pin, whereas in the air discharge mode, after charging, the device pin is approached with a probe until arc occurs. With the air discharge mode, the results are influenced by humidity, temperature, barometric pressure and closure rate of probe.

The IEC standard is being applied to all systems and equipment entering the market of the European Union (EU). OEMs are playing it safe by using ESD-protected components inside their systems although the standard is not directed to individual integrated circuits (IC's). Whole systems are awarded the "CE" mark once they conform to the EU directive on electromagnetic compatibility.

Benefits of HIN202E - HIN241E

The HIN202E - HIN241E series of devices offer the following levels of ESD protection:

- Human Body Model T_{OUT} , R_{IN} $\pm 15kV$
- IEC61000-4-2 Contact Discharge T_{OUT} , R_{IN} $\pm 8kV$
- IEC61000-4-2 Air Gap T_{OUT} , R_{IN} $\pm 15kV$
- Human Body Model T_{IN} , R_{OUT} $\pm 2kV$

Simply touching or plugging in a cable can result in an ESD strike. Since the device I/O pins are most susceptible to an ESD strike (the pins that route off the board) T_{OUT} and R_{IN} are all protected to $\pm 15kV$ HBM.

In addition to the robust ESD and inherent latch-up protection provided by the HIN202E - HIN241E devices, is the high data rate capability. The guaranteed data rate of 230kbits/s far exceeds the RS-232 requirement of 19.2kbits/s. These features together with the variety of transmitter/receiver combinations, low power shutdown, three-state mode, active receivers in shutdown, single 5V supply, 0.1μF or no capacitor versions and a variety of package options provide the user a total solution for their RS-232 needs.

SUMMARY OF ESD PROTECTION LEVELS OF VARIOUS RS-232 INTERFACE FAMILIES

	HBM	IEC61000-4-2 CONTACT DISCHARGE	IEC61000-4-2 AIR GAP
Intersil HIN202E-HIN241E	±15kv	±8kV	±15kV
Sipex SP200-SP213	±10kV	-	-
Maxim MAX202E-MAX213E	±15kv	±8kV	±15kV
Linear Technology LT1130A/LT1140A Series	±10kV	-	-
Maxim MAX202E-MAX213E	±15kv	±8kV	±15kV

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
 6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
 7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
 11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338