

RENESAS SEMICONDUCTOR RELIABILITY REPORT

GROUP : RX65N
DEVICE : R5F565NXXX
APPLICATION : Consumer / Industry

Quality Assurance Div.
Renesas Electronics Corporation

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
 5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
 6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
 7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
 8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
 9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
 12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
 13. This document shall not be reproduced or duplicated in any form or disclosed to any third party, in whole or in part, without prior written consent of Renesas Electronics.
 14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-2 October 2020)

Table. Reliability test results (QFP)

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

*1) With preconditioning per JESD22-A113, MSL 3

•It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

Table. Reliability test results (BGA)

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-55 °C to 125 °C , 500 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

*1) With preconditioning per JESD22-A113, MSL 3

•It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

Table. Reliability test results (LGA)

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-55 °C to 125 °C , 500 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

*1) With preconditioning per JESD22-A113, MSL 3

•It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

The failure rate of the device in an actual use condition can be estimated by the below procedure.

•Equation for the failure rate estimation (λ)

$$\lambda = \lambda_b \times \pi T \text{ (FIT)}$$

①Unique failure rate (λ_b)

$$\lambda_b = 0.08 \text{ FIT}$$

Unique failure rate at $T_a=55^\circ\text{C}$ using 60 % confidence level.

②Temperature term (πT)

$$\pi T = \exp\{11600 \times E_a \times (1/(273+55) - 1/(273+T_a))\}$$

E_a : Activation energy (eV)

T_a : Ambient temperature ($^\circ\text{C}$)

πT simplified chart as $E_a=0.7 \text{ eV}$

T_a ($^\circ\text{C}$)	40	50	55	60	65	70	75	80	85	90	100	110
πT	0.31	0.68	1	1.45	2.08	2.95	4.15	5.77	7.96	10.88	19.82	34.99

•MTTF (Mean Time To Failure)

$$MTTF = 1/\lambda$$

Reference about Renesas package code

Package type		Package code *1
Lead type plastic package	QFP	PxQP
Non-lead type plastic package	QFN	PxQN
Grid array type plastic package	BGA	PxBG
	LGA	PxLG

*1. First four digit

Table. Product list

No	Group	Product part number	Package code	No	Group	Product part number	Package code
1	RX65N	R5F565NCDDBG	PLBG0176G*	51	RX65N	R5F565N4BDFP	PLQP0100K*
2	RX65N	R5F565NCDGBG	PLBG0176G*	52	RX65N	R5F565N4BGFP	PLQP0100K*
3	RX65N	R5F565NCHDBG	PLBG0176G*	53	RX65N	R5F565N4EDFP	PLQP0100K*
4	RX65N	R5F565NCHGBG	PLBG0176G*	54	RX65N	R5F565N4EGFP	PLQP0100K*
5	RX65N	R5F565NEDDBG	PLBG0176G*	55	RX65N	R5F565N4FDFP	PLQP0100K*
6	RX65N	R5F565NEDGBG	PLBG0176G*	56	RX65N	R5F565N4FGFP	PLQP0100K*
7	RX65N	R5F565NEHDBG	PLBG0176G*	57	RX65N	R5F565N7ADFP	PLQP0100K*
8	RX65N	R5F565NEHGBG	PLBG0176G*	58	RX65N	R5F565N7AGFP	PLQP0100K*
9	RX65N	R5F565N4ADFB	PLQP0144K*	59	RX65N	R5F565N7BDFP	PLQP0100K*
10	RX65N	R5F565N4AGFB	PLQP0144K*	60	RX65N	R5F565N7BGFP	PLQP0100K*
11	RX65N	R5F565N4BDFB	PLQP0144K*	61	RX65N	R5F565N7EDFP	PLQP0100K*
12	RX65N	R5F565N4BGFB	PLQP0144K*	62	RX65N	R5F565N7EGFP	PLQP0100K*
13	RX65N	R5F565N4EDFB	PLQP0144K*	63	RX65N	R5F565N7FDFP	PLQP0100K*
14	RX65N	R5F565N4EGFB	PLQP0144K*	64	RX65N	R5F565N7FGFP	PLQP0100K*
15	RX65N	R5F565N4FDFB	PLQP0144K*	65	RX65N	R5F565N9ADFP	PLQP0100K*
16	RX65N	R5F565N4FGFB	PLQP0144K*	66	RX65N	R5F565N9AGFP	PLQP0100K*
17	RX65N	R5F565N7ADFB	PLQP0144K*	67	RX65N	R5F565N9BDFP	PLQP0100K*
18	RX65N	R5F565N7AGFB	PLQP0144K*	68	RX65N	R5F565N9BGFP	PLQP0100K*
19	RX65N	R5F565N7BDFB	PLQP0144K*	69	RX65N	R5F565N9EDFP	PLQP0100K*
20	RX65N	R5F565N7BGFB	PLQP0144K*	70	RX65N	R5F565N9EGFP	PLQP0100K*
21	RX65N	R5F565N7EDFB	PLQP0144K*	71	RX65N	R5F565N9FDFP	PLQP0100K*
22	RX65N	R5F565N7EGFB	PLQP0144K*	72	RX65N	R5F565N9FGFP	PLQP0100K*
23	RX65N	R5F565N7FDFB	PLQP0144K*	73	RX65N	R5F565NCDDFP	PLQP0100K*
24	RX65N	R5F565N7FGFB	PLQP0144K*	74	RX65N	R5F565NCDGFP	PLQP0100K*
25	RX65N	R5F565N9ADFB	PLQP0144K*	75	RX65N	R5F565NCHDFP	PLQP0100K*
26	RX65N	R5F565N9AGFB	PLQP0144K*	76	RX65N	R5F565NCHGFP	PLQP0100K*
27	RX65N	R5F565N9BDFB	PLQP0144K*	77	RX65N	R5F565NEDDFP	PLQP0100K*
28	RX65N	R5F565N9BGFB	PLQP0144K*	78	RX65N	R5F565NEDGFP	PLQP0100K*
29	RX65N	R5F565N9EDFB	PLQP0144K*	79	RX65N	R5F565NEHDFP	PLQP0100K*
30	RX65N	R5F565N9EGFB	PLQP0144K*	80	RX65N	R5F565NEHGFP	PLQP0100K*
31	RX65N	R5F565N9FDFB	PLQP0144K*	81	RX65N	R5F565NCDDLCL	PTLG0177K*
32	RX65N	R5F565N9FGFB	PLQP0144K*	82	RX65N	R5F565NCDGLCL	PTLG0177K*
33	RX65N	R5F565NCDDFB	PLQP0144K*	83	RX65N	R5F565NCHDLCL	PTLG0177K*
34	RX65N	R5F565NCDGFB	PLQP0144K*	84	RX65N	R5F565NCHGLCL	PTLG0177K*
35	RX65N	R5F565NCHDFB	PLQP0144K*	85	RX65N	R5F565NEDDLCL	PTLG0177K*
36	RX65N	R5F565NCHGFB	PLQP0144K*	86	RX65N	R5F565NEDGLCL	PTLG0177K*
37	RX65N	R5F565NEDDFB	PLQP0144K*	87	RX65N	R5F565NEHDLCL	PTLG0177K*
38	RX65N	R5F565NEDGFB	PLQP0144K*	88	RX65N	R5F565NEHGLCL	PTLG0177K*
39	RX65N	R5F565NEHDFB	PLQP0144K*	89	RX65N	R5F565N4ADLJ	PTLG0100J*
40	RX65N	R5F565NEHGFB	PLQP0144K*	90	RX65N	R5F565N4AGLJ	PTLG0100J*
41	RX65N	R5F565NCDDFC	PLQP0176K*	91	RX65N	R5F565N4BDLJ	PTLG0100J*
42	RX65N	R5F565NCDGFC	PLQP0176K*	92	RX65N	R5F565N4BGLJ	PTLG0100J*
43	RX65N	R5F565NCHDFC	PLQP0176K*	93	RX65N	R5F565N4EDLJ	PTLG0100J*
44	RX65N	R5F565NCHGFC	PLQP0176K*	94	RX65N	R5F565N4EGLJ	PTLG0100J*
45	RX65N	R5F565NEDDFC	PLQP0176K*	95	RX65N	R5F565N4FDLJ	PTLG0100J*
46	RX65N	R5F565NEDGFC	PLQP0176K*	96	RX65N	R5F565N4FGLJ	PTLG0100J*
47	RX65N	R5F565NEHDFC	PLQP0176K*	97	RX65N	R5F565N7ADLJ	PTLG0100J*
48	RX65N	R5F565NEHGFC	PLQP0176K*	98	RX65N	R5F565N7AGLJ	PTLG0100J*
49	RX65N	R5F565N4ADFP	PLQP0100K*	99	RX65N	R5F565N7BDLJ	PTLG0100J*
50	RX65N	R5F565N4AGFP	PLQP0100K*	100	RX65N	R5F565N7BGLJ	PTLG0100J*

Table. Product list

MCR-22-0317

No	Group	Product part number	Package code	No	Group	Product part number	Package code
101	RX65N	R5F565N7EDLJ	PTLG0100J*	161			
102	RX65N	R5F565N7EGLJ	PTLG0100J*	162			
103	RX65N	R5F565N7FDLJ	PTLG0100J*	163			
104	RX65N	R5F565N7FGLJ	PTLG0100J*	164			
105	RX65N	R5F565N9ADLJ	PTLG0100J*	165			
106	RX65N	R5F565N9AGLJ	PTLG0100J*	166			
107	RX65N	R5F565N9BDLJ	PTLG0100J*	167			
108	RX65N	R5F565N9BGLJ	PTLG0100J*	168			
109	RX65N	R5F565N9EDLJ	PTLG0100J*	169			
110	RX65N	R5F565N9EGLJ	PTLG0100J*	170			
111	RX65N	R5F565N9FDLJ	PTLG0100J*	171			
112	RX65N	R5F565N9FGLJ	PTLG0100J*	172			
113	RX65N	R5F565NCDLJ	PTLG0100J*	173			
114	RX65N	R5F565NCDGLJ	PTLG0100J*	174			
115	RX65N	R5F565NCHDLJ	PTLG0100J*	175			
116	RX65N	R5F565NCHGLJ	PTLG0100J*	176			
117	RX65N	R5F565NEDDLJ	PTLG0100J*	177			
118	RX65N	R5F565NEDGLJ	PTLG0100J*	178			
119	RX65N	R5F565NEHDLJ	PTLG0100J*	179			
120	RX65N	R5F565NEHGLJ	PTLG0100J*	180			
121	RX65N	R5F565N4ADLK	PTLG0145K*	181			
122	RX65N	R5F565N4AGLK	PTLG0145K*	182			
123	RX65N	R5F565N4BDLK	PTLG0145K*	183			
124	RX65N	R5F565N4BGLK	PTLG0145K*	184			
125	RX65N	R5F565N4EDLK	PTLG0145K*	185			
126	RX65N	R5F565N4EGLK	PTLG0145K*	186			
127	RX65N	R5F565N4FDLK	PTLG0145K*	187			
128	RX65N	R5F565N4FGLK	PTLG0145K*	188			
129	RX65N	R5F565N7ADLK	PTLG0145K*	189			
130	RX65N	R5F565N7AGLK	PTLG0145K*	190			
131	RX65N	R5F565N7BDLK	PTLG0145K*	191			
132	RX65N	R5F565N7BGLK	PTLG0145K*	192			
133	RX65N	R5F565N7EDLK	PTLG0145K*	193			
134	RX65N	R5F565N7EGLK	PTLG0145K*	194			
135	RX65N	R5F565N7FDLK	PTLG0145K*	195			
136	RX65N	R5F565N7FGLK	PTLG0145K*	196			
137	RX65N	R5F565N9ADLK	PTLG0145K*	197			
138	RX65N	R5F565N9AGLK	PTLG0145K*	198			
139	RX65N	R5F565N9BDLK	PTLG0145K*	199			
140	RX65N	R5F565N9BGLK	PTLG0145K*	200			
141	RX65N	R5F565N9EDLK	PTLG0145K*	201			
142	RX65N	R5F565N9EGLK	PTLG0145K*	202			
143	RX65N	R5F565N9FDLK	PTLG0145K*	203			
144	RX65N	R5F565N9FGLK	PTLG0145K*	204			
145	RX65N	R5F565NCDLJ	PTLG0145K*	205			
146	RX65N	R5F565NCDGLK	PTLG0145K*	206			
147	RX65N	R5F565NCHDLK	PTLG0145K*	207			
148	RX65N	R5F565NCHGLK	PTLG0145K*	208			
149	RX65N	R5F565NEDDLK	PTLG0145K*	209			
150	RX65N	R5F565NEDGLK	PTLG0145K*	210			
151	RX65N	R5F565NEHDLK	PTLG0145K*	211			
152	RX65N	R5F565NEHGLK	PTLG0145K*	212			
153				213			
154				214			
155				215			
156				216			
157				217			
158				218			
159				219			
160				220			