

# R8C/35A Group

Timer RA (Pulse Output Mode)

REJ05B1285-0100 Rev.1.00 July 23, 2010

#### 1. Abstract

This document describes a method and an application example for timer RA pulse output mode in the R8C/35A Group.

#### 2. Introduction

The application example described in this document applies to the following microcomputer (MCU) and parameters:

• MCU: R8C/35A Group

• XIN clock frequency: 20 MHz

This application note can be used with other R8C Family MCUs which have the same special function registers (SFRs) as the above group. Check the manual for any modifications to functions. Careful evaluation is recommended before using the program described in this application note.

# 3. Application Example

### 3.1 Program Outline

Use the prescaler register (TRAPRE) and timer RA register (TRA) to count count source f8. Use the TRA register underflow signal to generate an inverted waveform from pins TRAIO and TRAO every millisecond. Settings

- TRAPRE = 249, TRA = 9
- Select the 20 MHz XIN clock as the system clock.

Calculation formula for setting time

```
1 ms = (1 \div f8) \times (TRAPRE + 1) \times (TRA + 1)
= \{1 \div (20 \text{ MHz} \div 8)\} \times 250 \times 10
= (4 \times 10^{-7})\text{s} \times 2500
```

Figure 3.1 shows a Block Diagram and Figure 3.2 shows a Timing Diagram.




Figure 3.1 Block Diagram




Figure 3.2 Timing Diagram

### 3.2 Memory

Table 3.1 Memory

Memory	Size	Remarks
ROM	98 bytes	In the rej05b1285_src.c module
RAM	0 bytes	
Maximum user stack	10 bytes	
Maximum interrupt stack	0 bytes	

Memory size varies depending on the C compiler version and compile options.

The above applies to the following conditions:

C compiler: M16C/60,30,20,10,Tiny,R8C/Tiny Series Compiler V.5.44 Release 00

Compile option: -D\_\_UARTO\_\_ -c -finfo -dir "\$(CONFIGDIR)" -R8CE

### 4. Software

This section shows the initial setting procedures and values to set the example described in section **3. Application Example**. Refer to the latest **R8C/35A Group hardware user's manual** for details on individual registers.


The  $\times$  in the register's Setting Value represents bits not used in this application, blank spaces represent bits that do not change, and the dash represents reserved bits or bits that have nothing assigned.

#### 4.1 Function Tables

Declaration	void timer_ra_init(void)					
Outline	Initial setting of time	r RA associated SFRs				
Argument	Argument name		Meaning			
Argument	None		_			
Variable (global)	Variable name		Contents			
variable (global)	None		_			
Returned value	Туре	Value	Meaning			
Neturned value	None	_	_			
Function	Perform initial setting of timer RA associated SFRs.					

### 4.2 Main Function

#### • Flowchart



- Register settings
  - (1) Enable writing to registers CM0, CM1, CM3, OCD, FRA0, FRA1, FRA2, and FRA3.

### Protect Register (PRCR)

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value	_	_	_	_	Х	Х	Х	1

Bit	Symbol	Bit Name	Function	R/W
b0	PRC0	Protect bit 0	Enables writing to registers CM0, CM1, CM3, OCD, FRA0, FRA1, FRA2, and FRA3.  1: Write enabled	R/W

(2) Select the XIN-XOUT pin.

### System Clock Control Register 1 (CM1)

Bit	b7	b6	b5	b4	b3	b2	b1	b0	
Setting Value	Х	Х	_	Х	1	Х	Х	Х	

Bit	Symbol	Bit Name	Function	R/W
b3	CM13	Port/XIN-XOUT switch bit	1: XIN-XOUT pin	R/W

(3) Oscillate the XIN clock.

### System Clock Control Register 0 (CM0)

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value		Х	0	Х	Х	Х	_	_

Bit	Symbol	Bit Name	Function	R/W
b5	CM05	XIN clock (XIN-XOUT) stop bit	0: XIN clock oscillates	R/W

- (4) Wait until oscillation stabilizes.
- (5) Select the XIN clock.

# Oscillation Stop Detection Register (OCD)

Bit	b7	b6	b5	b4	b3	b2	b1	b0	
Setting Value		_	_	_		0	Х	Х	1

Bit	Symbol	Bit Name	Function	R/W
b2	OCD2	System clock select bit	0: XIN clock selected	R/W

(6) Select the XIN clock as the system clock.

### System Clock Control Register 0 (CM0)

Bit	b7	b6	b5	b4	b3	b2	b1	b0	
Setting Value	0	Х		Х	Х	Х	_	_	l

Bit	Symbol	Bit Name	Function	R/W
b7	CM07	XIN, XCIN clock select bit	0: XIN clock	R/W

(7) Disable writing to registers CM0, CM1, CM3, OCD, FRA0, FRA1, FRA2, and FRA3.


# Protect Register (PRCR)

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value	_	_	_	_	Х	Х	Х	0

Bit	Symbol	Bit Name	Function	R/W
b0	PRC0	Protect bit 0	Enables writing to registers CM0, CM1, CM3, OCD, FRA0, FRA1, FRA2, and FRA3.  0: Write disabled	R/W

# 4.3 Initial Setting of Timer RA Associated SFRs

#### • Flowchart



- Register settings
  - (1) Stop the timer RA count.

### Timer RA Control Register (TRACR)

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value	_	_	Х	Х	_	Х		0

Bit	Symbol	Bit Name	Function	R/W
b0	TSTART	Timer RA count start bit	0: Count stops	R/W

(2) Wait until the timer RA count stops.

# Timer RA Control Register (TRACR)

Bit	Symbol	Bit Name	Function	R/W
b1	TCSTF	Timer RA count status flag	Count stops     During count	R

(3) Disable the timer RA interrupt.

### Interrupt Control Register (TRAIC)

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value	_	_	_	_	0	0	0	0

Bit	Symbol	Bit Name	Function	R/W		
b0	ILVL0			R/W		
b1	ILVL1	Interrupt priority level select	2 b1 b0 0 0 0: Level 0 (interrupt disabled)			
b2	ILVL2					
b3	IR	Interrupt request bit	0: No interrupt requested	R/W		

(4) Set the timer pin select register.

### Timer RA Pin Select Register (TRASR)

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value	_	-		0	0	_	0	1

Bit	Symbol	Bit Name	Function	R/W	
b0	TRAIOSEL0	TD (10 min a alant hit	b1 b0	R/W	
b1	TRAIOSEL1	TIVAIO piii select bit	0 1: P1_7 assigned		
b3	TRAOSEL0	TRAO pin select bit	b4 b3	R/W	
b4	TRAOSEL1	TIVAO piir select bit	0 0: P3_7 assigned	R/W	

(5) Set the timer RA prescaler register to F9h.

# Timer RA Prescaler Register (TRAPRE)

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value	1	1	1	1	1	0	0	1

Ī	Bit	Function	Setting Range	R/W
ĺ	b7-b0	Counts an internal count source	00h to FFh	R/W

(6) Set timer RA register to 09h.

# Timer RA Register (TRA)

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value	0	0	0	0	1	0	0	1

Bit	Function	Setting Range	R/W
b7-b0	Counts on underflow of TRAPRE register	00h to FFh	R/W

(7) Set the timer RA I/O control register.

### Timer RA I/O Control Register (TRAIOC) [in Pulse Output Mode]

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value	0	0	0	0	0	1	0	0

Bit	Symbol	Bit Name	Function	R/W		
b0	TEDGSEL	TRAIO polarity switch bit	0: TRAIO output starts at "H"	R/W		
b1	TOPCR	TRAIO output control bit	0: TRAIO output	R/W		
b2	TOENA	TRAO output enable bit	1: TRAO output (inverted TRAIO output from P3_7)	R/W		
b3	TIOSEL	Hardware LIN function select bit	Set to 0.	R/W		
b4	TIPF0	TRAIO input filter select bit		R/W		
b5	TIPF1	TIVAIO IIIput IIItel Select bit	Set to 0 in pulse output mode.	R/W		
b6	TIOGT0	TRAIO event input control bit	— Get to 6 in pulse output mode.			
b7	TIOGT1	Tro to event input control bit		R/W		

(8) Set the timer RA mode register.

# Timer RA Mode Register (TRAMR)

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value	0	0	0	1	_	0	0	1

Bit	Symbol	Bit Name	Function	R/W	
b0	TMOD0			R/W	
b1	TMOD1	Timer RA operating mode select bit	0 0 1: Pulse output mode	R/W	
b2	TMOD2		·		
b4	TCK0			R/W	
b5	TCK1	Timer RA count source select bit	b6 b5 b4 0 0 1: f8	R/W	
b6	TCK2			R/W	
b7	TCKCUT	Timer RA count source cutoff bit	0: Provides count source	R/W	

(9) Start the timer RA count.

### Timer RA Control Register (TRACR)

Bit	b7	b6	b5	b4	b3	b2	b1	b0
Setting Value	1		Х	Х	1	Х		1

	Bit	Symbol	Bit Name	Function	R/W
I	b0	TSTART	Timer RA count start bit	1: Count starts	R/W

(10) Wait until the timer RA count starts.

# Timer RA Control Register (TRACR)

Bit	Symbol	Bit Name	Function	R/W
b1	TCSTF	Limer RA count status flag	0: Count stops 1: During count	R

# 5. Sample Program

A sample program can be downloaded from the Renesas Electronics website.

To download, click "Application Notes" in the left-hand side menu of the R8C Family page.

### 6. Reference Documents

R8C/35A Group User's Manual: Hardware Rev.0.40

The latest version can be downloaded from the Renesas Electronics website.

Technical Update/Technical News

The latest information can be downloaded from the Renesas Electronics website.

# **Website and Support**

Renesas Electronics website http://www.renesas.com/

Inquiries

http://www.renesas.com/inquiry

Pavisian History	R8C/35A Group
Revision History	Timer RA (Pulse Output Mode)

Rev. Date	Date		Description
ixev.	Date	Page	Summary
1.00	July 23, 2010	_	First edition issued

All trademarks and registered trademarks are the property of their respective owners.

### General Precautions in the Handling of MPU/MCU Products

The following usage notes are applicable to all MPU/MCU products from Renesas. For detailed usage notes on the products covered by this manual, refer to the relevant sections of the manual. If the descriptions under General Precautions in the Handling of MPU/MCU Products and in the body of the manual differ from each other, the description in the body of the manual takes precedence.

#### 1. Handling of Unused Pins

Handle unused pins in accord with the directions given under Handling of Unused Pins in the manual.

The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.

#### 2. Processing at Power-on

The state of the product is undefined at the moment when power is supplied.

The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.

In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed.

In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.

#### 3. Prohibition of Access to Reserved Addresses

Access to reserved addresses is prohibited.

 The reserved addresses are provided for the possible future expansion of functions. Do not access these addresses; the correct operation of LSI is not guaranteed if they are accessed.

#### 4. Clock Signals

After applying a reset, only release the reset line after the operating clock signal has become stable. When switching the clock signal during program execution, wait until the target clock signal has stabilized.

— When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.

#### 5. Differences between Products

Before changing from one product to another, i.e. to one with a different part number, confirm that the change will not lead to problems.

— The characteristics of MPU/MCU in the same group but having different part numbers may differ because of the differences in internal memory capacity and layout pattern. When changing to products of different part numbers, implement a system-evaluation test for each of the products.

#### Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- 2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc
  - Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools personal electronic equipment; and industrial robots.
  - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - "Specific": Aircraft: aerospace equipment: submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries. (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics



#### SALES OFFICES

Renesas Electronics Corporation

http://www.renesas.com

Refer to "http://www.renesas.com/" for the latest and detailed information

Renesas Electronics America Inc. 2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A. Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited 1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada Tel: +1-905-898-5441, Fax: +1-905-898-3220

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH Arcadiastrasse 10, 40472 Düsseldorf, Germany Tel: +49-211-65030, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd., Pudong District, Shanghai 200120, China Tel: +86-21-5877-1818, Fax: +86-21-6887-7858 / -7898

Limites State United Programs From Limited Unit 1601-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong Tet: +952-2866-9318, Fax: +852-2866-9022/9044

Renesas Electronics Taiwan Co., Ltd. 7F, No. 363 Fu Shing North Road Taipei, Taiwar Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd.

1 harbourFront Avenue, #06-10, keppel Bay Tower, Singapore 098632
Tel: +65-627-80-3000, Fax: +65-6278-8001
Renesas Electronics Malaysia Sdn.Bhd. Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics Korea Co., Ltd. 11F., Samik Lavied' or Bldg., 720-2 Yeoksam-Dong, Kangnam-Ku, Seoul 135-080, Korea Tel: 482-2-588-3737, Fax: 482-2-558-5141

© 2010 Renesas Electronics Corporation. All rights reserved.