

RX210 Group

Differences Between Chip Versions B and C

R01AN1624EJ0100 Rev. 1.00 Aug. 1, 2013

Abstract

This document confirms the differences between chip versions B and C in the RX210 Group.

Products

RX210 Group

Contents

1.	RX210	Chip Version B and C Products	3
2.	Differe	nces of Specifications Between Chip Versions B and C	4
	2.1 Fu	nctions Added in Chip Version B	5
	2.1.1	Operating Power Control Modes	5
	2.1.2	PLL Power Control Register (PLLPCR)	6
	2.1.3	16-Bit Timer Pulse Unit (TPU)	6
	2.1.4	Serial Communications Interface (SCIc)	6
	2.2 Fui	nctions Improved in Chip Version B	7
	2.2.1	Maximum Operating Frequency of Low-Speed Operating Mode 1	7
	2.2.2	Communication Rate of the RSPI	
	2.3 Fui	nction Changed in Chip Version B	7
	2.3.1	Software Cut 0 Bits (SOFTCUT[2:0])	7
3	Refere	nce Documents	8

1. RX210 Chip Version B and C Products

Chip version C has products only with less than or equal to 100 pins, and 512 KB or 384 KB ROM. Chip version B covers all RX210 Group products except chip version C products.

Table 1.1 lists the RX210 Group Chip Version B and C Products. In the table, B indicates chip version B and C indicates chip version C.

Table 1.1 RX210 Group Chip Version B and C Products

	Number of Pins				
ROM/RAM	48 pins	64 pins	80 pins	100 pins	144 and 145 pins
1 MB/96 KB	_	_	_	B ⁽¹⁾	B ⁽²⁾
768 KB/96 KB	_	_	_	B ⁽¹⁾	B ⁽²⁾
512 KB/64 KB	_	С	С	С	B ⁽²⁾
384 KB/64 KB	_	С	С	С	B ⁽²⁾
256 KB/32 KB	В	В	В	В	B ⁽²⁾
128 KB/16 KB	В	В	В	В	B ⁽²⁾
96 KB/16 KB	В	В	_	_	_
64 KB/12 KB	В	В	_	_	_

Notes:

- 1. Bit rate of the RSPI can be set to a maximum of 16 Mbps.
- 2. Bit rate of the RSPI can be set to a maximum of 16 Mbps, TPU is on-chip, and all 12 channels of SCIc can be used.

2. Differences of Specifications Between Chip Versions B and C

Chip version B has the same functions as chip version C. Furthermore chip version B has additional and improved functions. The same software can be used for functions common to these two chip versions.

Table 2.1 lists the Additional, Improved, and Changed Functions in Chip Version B. Figure 2.1 shows the Software Compatibility Between Chip Versions B and C.

Table 2.1 Additional, Improved, and Changed Functions in Chip Version B

No.	Addition/Improvement		Description	Reference
1	Operating power control mode	Addition	Added middle-speed operating mode 2A and 2B.	<u>2.1.1</u>
2	PLL power control register	Addition	Added the register to turn on and off the PLL power supply.	<u>2.1.2</u>
3	16-bit timer pulse unit (TPU)	Addition	Added the 16-bit timer pulse unit (only for products with 144 pins or more).	<u>2.1.3</u>
4	Serial communications interface (SCIc)	Addition	Added 6 channels. All 12 channels can be used (only for products with 144 pins or more).	<u>2.1.4</u>
5	Low-speed operating mode 1	Improvement	Improved the maximum frequency.	<u>2.2.1</u>
6	Serial peripheral interface (RSPI)	Improvement	Improved the maximum bit rate from 8.0 Mbps to16.0 Mbps (only for chip version B products with 768 KB or more of the flash memory, or with 144 pins or more).	2.2.2
7	Specification of the software cut 0 bits (SOFTCUT[2:0])	Specification changed	No control function provided for supplying power to the flash memory when in software standby mode.	2.3.1




Figure 2.1 Software Compatibility Between Chip Versions B and C

2.1 Functions Added in Chip Version B

2.1.1 Operating Power Control Modes

Middle-speed operating modes 2A and 2B are added in chip version B.

Middle-speed operating mode 2A can reduce power consumption and is more suitable for low-speed operation than middle-speed operating mode 1A or 1B. If operating in middle-speed operating mode 1A, 1B, and 2A under the same operating conditions (frequency and voltage), middle-speed operating mode 2A can reduce the power consumption the most.

Middle-speed operating mode 2B is based on middle-speed operating mode 2A and can reduce power consumption when programming/erasing the flash memory in the low-speed and low power voltage operating range.

When reading the flash memory in middle-speed operating mode 2B, the operating frequency and operating voltage ranges are the same as these in middle-speed operating mode 2A.

Figure 2.2 shows the Operating Frequency and Operating Voltage Ranges in Middle-Speed Operating Mode 2A and Figure 2.3 shows the Operating Frequency and Operating Voltage Ranges in Middle-Speed Operating Mode 2B.




Figure 2.2 Operating Frequency and Operating Voltage Ranges in Middle-Speed Operating Mode 2A




Figure 2.3 Operating Frequency and Operating Voltage Ranges in Middle-Speed Operating Mode 2B

2.1.2 PLL Power Control Register (PLLPCR)

The PLL power control register (PLLPCR) is only available in chip version B. With this register, when PLL is not used, the PLL power supply can be turned off to reduce power consumption.

2.1.3 16-Bit Timer Pulse Unit (TPU)

The TPU consists of six 16-bit timers and is the peripheral function which is implemented only in chip version B products with more than or equal to 144 pins.

2.1.4 Serial Communications Interface (SCIc)

Chip version B products with more than or equal to 144 pins can use all 12 channels (SCI0 to SCI11) of SCIc.

Table 2.2 shows the Available SCIc Channels for Each Pin Package.

Table 2.2 Available SCIc Channels for Each Pin Package

	Package				
Channel	48 pins	64 pins	80 pins	100 pins	144 and 145 pins
SCI0	N/A	N/A	Available	Available	Available
SCI1	Available	Available	Available	Available	Available
SCI2	N/A	N/A	N/A	N/A	Available
SCI3	N/A	N/A	N/A	N/A	Available
SCI4	N/A	N/A	N/A	N/A	Available
SCI5	Available	Available	Available	Available	Available
SCI6	Available	Available	Available	Available	Available
SCI7	N/A	N/A	N/A	N/A	Available
SCI8	Available	Available	Available	Available	Available
SCI9	N/A	Available	Available	Available	Available
SCI10	N/A	N/A	N/A	N/A	Available
SCI11	N/A	N/A	N/A	N/A	Available

2.2 Functions Improved in Chip Version B

2.2.1 Maximum Operating Frequency of Low-Speed Operating Mode 1

The operating frequency ranges of clocks in low-speed operating mode 1 are improved in chip version B.

Table 2.3 lists the comparison of low-speed operating mode 1 between chip versions B and C.

Table 2.3 Comparison of Low-Speed Operating Mode 1 (VCC = 2.7 to 5.5 V)

	Maximum Operating Frequency				
Voltage	ICLK, FCLK, PCLKB, PCLKD, and BCLK when reading the flash memory				
Chip version B Chip v		Chip version C			
VCC = 2.7 to 5.5 V	8 MHz				
VCC = 1.8 to 2.7 V	4 MHz	1 MHz			
VCC = 1.62 to 1.8 V	2 MHz				

2.2.2 Communication Rate of the RSPI

The maximum bit rate is 16.0 Mbps in chip version B products with 768 KB or more of the flash memory, or with more than or equal to 144 pins. For other products, the maximum bit rate is 8 Mbps.

2.3 Function Changed in Chip Version B

2.3.1 Software Cut 0 Bits (SOFTCUT[2:0])

The SOFTCUT[2:0] bits are used to control the following during software standby mode:

- POR low power consumption function
- Power supply to HOCO
- Power supply to the flash memory

With chip version B, power supply to the flash memory does not need to be controlled and the same software can be used as chip version C.

3. Reference Documents

User's Manual: Hardware

RX210 Group User's Manual: Hardware Rev.1.40 (R01UH0037EJ)

The latest version can be downloaded from the Renesas Electronics website.

Technical Update/Technical News

The latest information can be downloaded from the Renesas Electronics website.

Website and Support

Renesas Electronics website

http://www.renesas.com

Inquiries

http://www.renesas.com/contact/

REVISION HISTORY	RX210 Group Application Note		
	Differences Between Chip Versions B and C		

Rev.	Date	Description			
Rev.	Date	Page Summary			
1.00	Aug. 1, 2013	_	First edition issued		

All trademarks and registered trademarks are the property of their respective owners.

General Precautions in the Handling of MPU/MCU Products

The following usage notes are applicable to all MPU/MCU products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Handling of Unused Pins

Handle unused pins in accord with the directions given under Handling of Unused Pins in the manual.

The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.

2. Processing at Power-on

The state of the product is undefined at the moment when power is supplied.

- The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.
 In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed. In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.
- 3. Prohibition of Access to Reserved Addresses

Access to reserved addresses is prohibited.

The reserved addresses are provided for the possible future expansion of functions. Do not access
these addresses; the correct operation of LSI is not guaranteed if they are accessed.

4. Clock Signals

After applying a reset, only release the reset line after the operating clock signal has become stable. When switching the clock signal during program execution, wait until the target clock signal has stabilized.

— When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.

5. Differences between Products

Before changing from one product to another, i.e. to a product with a different part number, confirm that the change will not lead to problems.

The characteristics of an MPU or MCU in the same group but having a different part number may differ in terms of the internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

Notice

- 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein
- 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or
- You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product
- 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.

Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics

- 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
- Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations
- 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics
- 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics



SALES OFFICES

Renesas Electronics Corporation

http://www.renesas.com

Refer to "http://www.renesas.com/" for the latest and detailed information

Renesas Electronics America Inc. 2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A. Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited 1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada Tel: +1-905-898-5441, Fax: +1-905-898-3220

Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH Arcadiastrasse 10, 40472 Düsseldorf, Germany Tel: +49-211-65030, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd. Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd., Pudong District, Shanghai 200120, China Tel: +86-Z1-5877-1818, Fax: +86-Z1-6887-7858 / -7898

Renesas Electronics Hong Kong Limited
Unit 1601-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2886-9318, Fax: +852 2886-9022/9044

Renesas Electronics Taiwan Co., Ltd. 13F, No. 363, Fu Shing North Road, Taipei, Taiwan Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd. 80 Bendemeer Road, Unit #d6-02 Hyflux Innovation Centre Singapore 339949 Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics Korea Co., Ltd. 11F., Samik Lavied' or Bldg., 720-2 Yeoksam-Dong, Kangnam-Ku, Seoul 135-080, Korea Tel: +82-2-558-3737, Fax: +82-2-558-5141