



SYMBOLS	MIN.	NOM.	MAX.
A	—	—	1.75
A1	0.10	—	0.25
A2	1.25	—	—
b	0.31	—	0.51
D	4.80	4.90	5.00
H _E	5.80	6.00	6.20
E	3.80	3.90	4.00
e	1.27 BSC		
ccc	0.10		
L _P	0.40	—	1.27
L	(1.00)		
θ°	5°	—	15°
θ ₁ °	0°	—	8°
h	0.25	—	0.50
b	0.31	—	0.51
b1	0.28	—	0.48
c	0.10	—	0.25
c1	0.10	—	0.25

UNIT : MM

NOTES:

1. JEDEC compatible.
2. All dimensions are in mm and angles are in degrees.
3. Use ±0.05 mm for the non-toleranced dimensions.
4. Foot length is measured at gauge plane 0.25 mm above seating plane.