

# RENESAS SEMICONDUCTOR RELIABILITY REPORT

GROUP : RL78/G14  
DEVICE : R5F104XXX  
APPLICATION : Consumer / Industry

Quality Assurance Div.  
Renesas Electronics Corporation

## Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
  2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
  3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
  4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
  5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
  6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.  
 "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.  
 "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.  
 Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
  7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
  8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
  9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
  10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
  11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
  12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document .
  13. This document shall not be reproduced or duplicated in any form or disclosed to any third party, in whole or in part, without prior written consent of Renesas Electronics.
  14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-2 October 2020)

**Table. Reliability test results (QFP)**

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

\*1) With preconditioning per JESD22-A113, MSL 3

•It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

**Table. Reliability test results (QFN)**

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

\*1) With preconditioning per JESD22-A113, MSL 3

•It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

**Table. Reliability test results (SOP)**

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

\*1) With preconditioning per JESD22-A113, MSL 3

•It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

**Table. Reliability test results (BGA)**

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-55 °C to 125 °C , 500 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

\*1) With preconditioning per JESD22-A113, MSL 3

·It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

**Table. Reliability test results (LGA)**

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-55 °C to 125 °C , 500 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

\*1) With preconditioning per JESD22-A113, MSL 3

·It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

The failure rate of the device in an actual use condition can be estimated by the below procedure.

**•Equation for the failure rate estimation ( $\lambda$ )**

$$\lambda = \lambda_b \times \pi T \text{ (FIT)}$$

① Unique failure rate ( $\lambda_b$ )

$$\lambda_b = 3.8 \text{ FIT}$$

Unique failure rate at  $T_a = 55 \text{ }^\circ\text{C}$  using 60 % confidence level.

② Temperature term ( $\pi T$ )

$$\pi T = \exp\{11600 \times E_a \times (1/(273+55) - 1/(273+T_a))\}$$

$E_a$  : Activation energy (eV)

$T_a$  : Ambient temperature ( $^\circ\text{C}$ )

$\pi T$ simplified chart as $E_a = 0.7 \text{ eV}$												
$T_a$ ( $^\circ\text{C}$ )	40	50	55	60	65	70	75	80	85	90	100	110
$\pi T$	0.31	0.68	1	1.45	2.08	2.95	4.15	5.77	7.96	10.88	19.82	34.99

**•MTTF ( Mean Time To Failure )**

$$MTTF = 1/\lambda$$



## Reference about Renesas package code

Package type	Package code *1	
Lead type plastic package	QFP	PxQP
	SOP	PxSP
Non-lead type plastic package	QFN	PxQN
Grid array type plastic package	BGA	PxBG
	LGA	PxLG

\*1. First four digit

Table. Product list

No	Group	Product part number	Package code	No	Group	Product part number	Package code
1	RL78/G14	R5F104AAASP	PLSP0030J*	51	RL78/G14	R5F104BGDFP	PLQP0032G*
2	RL78/G14	R5F104AADSP	PLSP0030J*	52	RL78/G14	R5F104BGDNA	PWQN0032K*
3	RL78/G14	R5F104AAGSP	PLSP0030J*	53	RL78/G14	R5F104BGGFP	PLQP0032G*
4	RL78/G14	R5F104ACASP	PLSP0030J*	54	RL78/G14	R5F104BGGNA	PWQN0032K*
5	RL78/G14	R5F104ACDSP	PLSP0030J*	55	RL78/G14	R5F104CAALA	PWLG0036K*
6	RL78/G14	R5F104ACGSP	PLSP0030J*	56	RL78/G14	R5F104CADLA	PWLG0036K*
7	RL78/G14	R5F104ADASP	PLSP0030J*	57	RL78/G14	R5F104CAGLA	PWLG0036K*
8	RL78/G14	R5F104ADDSP	PLSP0030J*	58	RL78/G14	R5F104CCALA	PWLG0036K*
9	RL78/G14	R5F104ADGSP	PLSP0030J*	59	RL78/G14	R5F104CCDLA	PWLG0036K*
10	RL78/G14	R5F104AEASP	PLSP0030J*	60	RL78/G14	R5F104CCGLA	PWLG0036K*
11	RL78/G14	R5F104AEDSP	PLSP0030J*	61	RL78/G14	R5F104CDALA	PWLG0036K*
12	RL78/G14	R5F104AEGSP	PLSP0030J*	62	RL78/G14	R5F104CDDLA	PWLG0036K*
13	RL78/G14	R5F104AFASP	PLSP0030J*	63	RL78/G14	R5F104CDGLA	PWLG0036K*
14	RL78/G14	R5F104AFDSP	PLSP0030J*	64	RL78/G14	R5F104CEALA	PWLG0036K*
15	RL78/G14	R5F104AFGSP	PLSP0030J*	65	RL78/G14	R5F104CEDLA	PWLG0036K*
16	RL78/G14	R5F104AGASP	PLSP0030J*	66	RL78/G14	R5F104CEGLA	PWLG0036K*
17	RL78/G14	R5F104AGDSP	PLSP0030J*	67	RL78/G14	R5F104CFALA	PWLG0036K*
18	RL78/G14	R5F104AGGSP	PLSP0030J*	68	RL78/G14	R5F104CFGLA	PWLG0036K*
19	RL78/G14	R5F104BAAFP	PLQP0032G*	69	RL78/G14	R5F104CGALA	PWLG0036K*
20	RL78/G14	R5F104BAANA	PWQN0032K*	70	RL78/G14	R5F104CGDLA	PWLG0036K*
21	RL78/G14	R5F104BADFP	PLQP0032G*	71	RL78/G14	R5F104CGGLA	PWLG0036K*
22	RL78/G14	R5F104BADNA	PWQN0032K*	72	RL78/G14	R5F104EAANA	PWQN0040K*
23	RL78/G14	R5F104BAGFP	PLQP0032G*	73	RL78/G14	R5F104EADNA	PWQN0040K*
24	RL78/G14	R5F104BAGNA	PWQN0032K*	74	RL78/G14	R5F104EAGNA	PWQN0040K*
25	RL78/G14	R5F104BCAFP	PLQP0032G*	75	RL78/G14	R5F104ECANA	PWQN0040K*
26	RL78/G14	R5F104BCANA	PWQN0032K*	76	RL78/G14	R5F104ECDNA	PWQN0040K*
27	RL78/G14	R5F104BCDFP	PLQP0032G*	77	RL78/G14	R5F104ECGNA	PWQN0040K*
28	RL78/G14	R5F104BCDNA	PWQN0032K*	78	RL78/G14	R5F104EDANA	PWQN0040K*
29	RL78/G14	R5F104BCGFP	PLQP0032G*	79	RL78/G14	R5F104EDDNA	PWQN0040K*
30	RL78/G14	R5F104BCGNA	PWQN0032K*	80	RL78/G14	R5F104EDGNA	PWQN0040K*
31	RL78/G14	R5F104BDAFP	PLQP0032G*	81	RL78/G14	R5F104EEANA	PWQN0040K*
32	RL78/G14	R5F104BDANA	PWQN0032K*	82	RL78/G14	R5F104EEDNA	PWQN0040K*
33	RL78/G14	R5F104BDDFP	PLQP0032G*	83	RL78/G14	R5F104EEGNA	PWQN0040K*
34	RL78/G14	R5F104BDDNA	PWQN0032K*	84	RL78/G14	R5F104EFANA	PWQN0040K*
35	RL78/G14	R5F104BDGFP	PLQP0032G*	85	RL78/G14	R5F104EFDNA	PWQN0040K*
36	RL78/G14	R5F104BDGNA	PWQN0032K*	86	RL78/G14	R5F104EFGNA	PWQN0040K*
37	RL78/G14	R5F104BEAFP	PLQP0032G*	87	RL78/G14	R5F104EGANA	PWQN0040K*
38	RL78/G14	R5F104BEANA	PWQN0032K*	88	RL78/G14	R5F104EGDNA	PWQN0040K*
39	RL78/G14	R5F104BEDFP	PLQP0032G*	89	RL78/G14	R5F104EGGNA	PWQN0040K*
40	RL78/G14	R5F104BEDNA	PWQN0032K*	90	RL78/G14	R5F104EHANA	PWQN0040K*
41	RL78/G14	R5F104BEGFP	PLQP0032G*	91	RL78/G14	R5F104EHDNA	PWQN0040K*
42	RL78/G14	R5F104BEGNA	PWQN0032K*	92	RL78/G14	R5F104EHGNA	PWQN0040K*
43	RL78/G14	R5F104BFAFP	PLQP0032G*	93	RL78/G14	R5F104FAAFP	PLQP0044G*
44	RL78/G14	R5F104BFANA	PWQN0032K*	94	RL78/G14	R5F104FADFP	PLQP0044G*
45	RL78/G14	R5F104BFDFP	PLQP0032G*	95	RL78/G14	R5F104FAGFP	PLQP0044G*
46	RL78/G14	R5F104BFDNA	PWQN0032K*	96	RL78/G14	R5F104FCAFP	PLQP0044G*
47	RL78/G14	R5F104BFGFP	PLQP0032G*	97	RL78/G14	R5F104FCDFP	PLQP0044G*
48	RL78/G14	R5F104BFGNA	PWQN0032K*	98	RL78/G14	R5F104FCGFP	PLQP0044G*
49	RL78/G14	R5F104BGAFP	PLQP0032G*	99	RL78/G14	R5F104FDAFP	PLQP0044G*
50	RL78/G14	R5F104BGANA	PWQN0032K*	100	RL78/G14	R5F104FDDFP	PLQP0044G*

Table. Product list

MCR-22-0500

No	Group	Product part number	Package code	No	Group	Product part number	Package code
101	RL78/G14	R5F104FDGFP	PLQP0044G*	161	RL78/G14	R5F104LDGLA	PWLG0064K*
102	RL78/G14	R5F104FEAFP	PLQP0044G*	162	RL78/G14	R5F104LEAFA	PLQP0064J*
103	RL78/G14	R5F104FEDFP	PLQP0044G*	163	RL78/G14	R5F104LEAFB	PLQP0064K*
104	RL78/G14	R5F104FEGFP	PLQP0044G*	164	RL78/G14	R5F104LEAFP	PLQP0064G*
105	RL78/G14	R5F104FFAFP	PLQP0044G*	165	RL78/G14	R5F104LEALA	PWLG0064K*
106	RL78/G14	R5F104FFDFP	PLQP0044G*	166	RL78/G14	R5F104LEDFA	PLQP0064J*
107	RL78/G14	R5F104FFGFP	PLQP0044G*	167	RL78/G14	R5F104LEDFB	PLQP0064K*
108	RL78/G14	R5F104FGAFP	PLQP0044G*	168	RL78/G14	R5F104LEDFP	PLQP0064G*
109	RL78/G14	R5F104FGDFP	PLQP0044G*	169	RL78/G14	R5F104LEDLA	PWLG0064K*
110	RL78/G14	R5F104FGGFP	PLQP0044G*	170	RL78/G14	R5F104LEGFA	PLQP0064J*
111	RL78/G14	R5F104FHAFP	PLQP0044G*	171	RL78/G14	R5F104LEGFB	PLQP0064K*
112	RL78/G14	R5F104FHDFP	PLQP0044G*	172	RL78/G14	R5F104LEGFP	PLQP0064G*
113	RL78/G14	R5F104FHGFP	PLQP0044G*	173	RL78/G14	R5F104LEGLA	PWLG0064K*
114	RL78/G14	R5F104FJAFP	PLQP0044G*	174	RL78/G14	R5F104LFABG	PVBG0064L*
115	RL78/G14	R5F104FJDFP	PLQP0044G*	175	RL78/G14	R5F104LFAFA	PLQP0064J*
116	RL78/G14	R5F104FJGFP	PLQP0044G*	176	RL78/G14	R5F104LFAFB	PLQP0064K*
117	RL78/G14	R5F104JCAFA	PLQP0052J*	177	RL78/G14	R5F104LFAFP	PLQP0064G*
118	RL78/G14	R5F104JCDFA	PLQP0052J*	178	RL78/G14	R5F104LFALA	PWLG0064K*
119	RL78/G14	R5F104JCGFA	PLQP0052J*	179	RL78/G14	R5F104LFANA	PWQN0064K*
120	RL78/G14	R5F104JDAFA	PLQP0052J*	180	RL78/G14	R5F104LFDFA	PLQP0064J*
121	RL78/G14	R5F104JDDFA	PLQP0052J*	181	RL78/G14	R5F104LDFDB	PLQP0064K*
122	RL78/G14	R5F104JDGFA	PLQP0052J*	182	RL78/G14	R5F104LDFDP	PLQP0064G*
123	RL78/G14	R5F104JEAFB	PLQP0052J*	183	RL78/G14	R5F104LFDNA	PWQN0064K*
124	RL78/G14	R5F104JEDFA	PLQP0052J*	184	RL78/G14	R5F104LFGBG	PVBG0064L*
125	RL78/G14	R5F104JEGFA	PLQP0052J*	185	RL78/G14	R5F104LFGFA	PLQP0064J*
126	RL78/G14	R5F104JFAFA	PLQP0052J*	186	RL78/G14	R5F104LFGFB	PLQP0064K*
127	RL78/G14	R5F104JFDFA	PLQP0052J*	187	RL78/G14	R5F104LFGFP	PLQP0064G*
128	RL78/G14	R5F104JGFA	PLQP0052J*	188	RL78/G14	R5F104LFGLA	PWLG0064K*
129	RL78/G14	R5F104JGAFA	PLQP0052J*	189	RL78/G14	R5F104LFGNA	PWQN0064K*
130	RL78/G14	R5F104JGDFA	PLQP0052J*	190	RL78/G14	R5F104LGABG	PVBG0064L*
131	RL78/G14	R5F104JGGFA	PLQP0052J*	191	RL78/G14	R5F104LGAFA	PLQP0064J*
132	RL78/G14	R5F104JHAFA	PLQP0052J*	192	RL78/G14	R5F104LGAFB	PLQP0064K*
133	RL78/G14	R5F104JHDFB	PLQP0052J*	193	RL78/G14	R5F104LGAFP	PLQP0064G*
134	RL78/G14	R5F104JHGFA	PLQP0052J*	194	RL78/G14	R5F104LGALA	PWLG0064K*
135	RL78/G14	R5F104JJAFA	PLQP0052J*	195	RL78/G14	R5F104LGANA	PWQN0064K*
136	RL78/G14	R5F104JJDFA	PLQP0052J*	196	RL78/G14	R5F104LGDFA	PLQP0064J*
137	RL78/G14	R5F104JJGFA	PLQP0052J*	197	RL78/G14	R5F104LGDDB	PLQP0064K*
138	RL78/G14	R5F104LCAFA	PLQP0064J*	198	RL78/G14	R5F104LGDFP	PLQP0064G*
139	RL78/G14	R5F104LCAFB	PLQP0064K*	199	RL78/G14	R5F104LGDNA	PWQN0064K*
140	RL78/G14	R5F104LCAFP	PLQP0064G*	200	RL78/G14	R5F104LGGBG	PVBG0064L*
141	RL78/G14	R5F104LCALA	PWLG0064K*	201	RL78/G14	R5F104LGGFA	PLQP0064J*
142	RL78/G14	R5F104LCDFA	PLQP0064J*	202	RL78/G14	R5F104LGGFB	PLQP0064K*
143	RL78/G14	R5F104LCDFB	PLQP0064K*	203	RL78/G14	R5F104LGGFP	PLQP0064G*
144	RL78/G14	R5F104LCDFP	PLQP0064G*	204	RL78/G14	R5F104LGGLA	PWLG0064K*
145	RL78/G14	R5F104LCDLA	PWLG0064K*	205	RL78/G14	R5F104LGGNA	PWQN0064K*
146	RL78/G14	R5F104LCGFA	PLQP0064J*	206	RL78/G14	R5F104LHABG	PVBG0064L*
147	RL78/G14	R5F104LCGFB	PLQP0064K*	207	RL78/G14	R5F104LHAFA	PLQP0064J*
148	RL78/G14	R5F104LCGFP	PLQP0064G*	208	RL78/G14	R5F104LHAFB	PLQP0064K*
149	RL78/G14	R5F104LCGLA	PWLG0064K*	209	RL78/G14	R5F104LHAFP	PLQP0064G*
150	RL78/G14	R5F104LDAFA	PLQP0064J*	210	RL78/G14	R5F104LHALA	PWLG0064K*
151	RL78/G14	R5F104LDAFB	PLQP0064K*	211	RL78/G14	R5F104LHANA	PWQN0064K*
152	RL78/G14	R5F104LDAFP	PLQP0064G*	212	RL78/G14	R5F104LHDFA	PLQP0064J*
153	RL78/G14	R5F104LDALA	PWLG0064K*	213	RL78/G14	R5F104LHDFB	PLQP0064K*
154	RL78/G14	R5F104LDDFA	PLQP0064J*	214	RL78/G14	R5F104LHDFP	PLQP0064G*
155	RL78/G14	R5F104LDDFB	PLQP0064K*	215	RL78/G14	R5F104LHDNA	PWQN0064K*
156	RL78/G14	R5F104LDDFP	PLQP0064G*	216	RL78/G14	R5F104LHGBG	PVBG0064L*
157	RL78/G14	R5F104LDDLA	PWLG0064K*	217	RL78/G14	R5F104LHGFA	PLQP0064J*
158	RL78/G14	R5F104LDGFA	PLQP0064J*	218	RL78/G14	R5F104LHGFB	PLQP0064K*
159	RL78/G14	R5F104LDGFB	PLQP0064K*	219	RL78/G14	R5F104LHGFP	PLQP0064G*
160	RL78/G14	R5F104LDGFP	PLQP0064G*	220	RL78/G14	R5F104LHGLA	PWLG0064K*

Table. Product list

MCR-22-0500

No	Group	Product part number	Package code	No	Group	Product part number	Package code
221	RL78/G14	R5F104LHGNA	PWQN0064K*	281	RL78/G14	R5F104MLGFB	PLQP0080K*
222	RL78/G14	R5F104LJABG	PVBG0064L*	282	RL78/G14	R5F104PFAFA	PLQP0100J*
223	RL78/G14	R5F104LJAFA	PLQP0064J*	283	RL78/G14	R5F104PFAFB	PLQP0100K*
224	RL78/G14	R5F104LJAFB	PLQP0064K*	284	RL78/G14	R5F104PFDFFA	PLQP0100J*
225	RL78/G14	R5F104LJAFF	PLQP0064G*	285	RL78/G14	R5F104PFDFB	PLQP0100K*
226	RL78/G14	R5F104LJALA	PWLG0064K*	286	RL78/G14	R5F104PFGFA	PLQP0100J*
227	RL78/G14	R5F104LJANA	PWQN0064K*	287	RL78/G14	R5F104PFGFB	PLQP0100K*
228	RL78/G14	R5F104LJDFA	PLQP0064J*	288	RL78/G14	R5F104PGAFA	PLQP0100J*
229	RL78/G14	R5F104LJDFF	PLQP0064K*	289	RL78/G14	R5F104PGAFF	PLQP0100K*
230	RL78/G14	R5F104LJDFF	PLQP0064G*	290	RL78/G14	R5F104PGDFA	PLQP0100J*
231	RL78/G14	R5F104LJDNA	PWQN0064K*	291	RL78/G14	R5F104PGDFB	PLQP0100K*
232	RL78/G14	R5F104LJGBG	PVBG0064L*	292	RL78/G14	R5F104PGGFA	PLQP0100J*
233	RL78/G14	R5F104LJGFA	PLQP0064J*	293	RL78/G14	R5F104PGGFB	PLQP0100K*
234	RL78/G14	R5F104LJGFB	PLQP0064K*	294	RL78/G14	R5F104PHAFA	PLQP0100J*
235	RL78/G14	R5F104LJGFF	PLQP0064G*	295	RL78/G14	R5F104PHAFB	PLQP0100K*
236	RL78/G14	R5F104LJGLA	PWLG0064K*	296	RL78/G14	R5F104PHDFA	PLQP0100J*
237	RL78/G14	R5F104LJGNA	PWQN0064K*	297	RL78/G14	R5F104PHDFB	PLQP0100K*
238	RL78/G14	R5F104LKAFB	PLQP0064J*	298	RL78/G14	R5F104PHGFA	PLQP0100J*
239	RL78/G14	R5F104LKAFB	PLQP0064K*	299	RL78/G14	R5F104PHGFB	PLQP0100K*
240	RL78/G14	R5F104LKALA	PWLG0064K*	300	RL78/G14	R5F104PJAFB	PLQP0100J*
241	RL78/G14	R5F104LKGFA	PLQP0064J*	301	RL78/G14	R5F104PJAFB	PLQP0100K*
242	RL78/G14	R5F104LKGFB	PLQP0064K*	302	RL78/G14	R5F104PJDFB	PLQP0100J*
243	RL78/G14	R5F104LKGLA	PWLG0064K*	303	RL78/G14	R5F104PJDFB	PLQP0100K*
244	RL78/G14	R5F104LLAFA	PLQP0064J*	304	RL78/G14	R5F104PJGFA	PLQP0100J*
245	RL78/G14	R5F104LLAFB	PLQP0064K*	305	RL78/G14	R5F104PJGFB	PLQP0100K*
246	RL78/G14	R5F104LLALA	PWLG0064K*	306	RL78/G14	R5F104PKAFA	PLQP0100J*
247	RL78/G14	R5F104LLGFA	PLQP0064J*	307	RL78/G14	R5F104PKAFB	PLQP0100K*
248	RL78/G14	R5F104LLGFB	PLQP0064K*	308	RL78/G14	R5F104PKGFA	PLQP0100J*
249	RL78/G14	R5F104LLGLA	PWLG0064K*	309	RL78/G14	R5F104PKGFB	PLQP0100K*
250	RL78/G14	R5F104MFAFA	PLQP0080J*	310	RL78/G14	R5F104PLAFA	PLQP0100J*
251	RL78/G14	R5F104MFAFB	PLQP0080K*	311	RL78/G14	R5F104PLAFB	PLQP0100K*
252	RL78/G14	R5F104MFDFA	PLQP0080J*	312	RL78/G14	R5F104PLGFA	PLQP0100J*
253	RL78/G14	R5F104MFDFF	PLQP0080K*	313	RL78/G14	R5F104PLGFB	PLQP0100K*
254	RL78/G14	R5F104MFGFA	PLQP0080J*	314	RL78/G14	R5F104GAAFB	PLQP0048K*
255	RL78/G14	R5F104MFGFB	PLQP0080K*	315	RL78/G14	R5F104GAANA	PWQN0048K*
256	RL78/G14	R5F104MGFA	PLQP0080J*	316	RL78/G14	R5F104GADFB	PLQP0048K*
257	RL78/G14	R5F104MGAFB	PLQP0080K*	317	RL78/G14	R5F104GADNA	PWQN0048K*
258	RL78/G14	R5F104MGDFA	PLQP0080J*	318	RL78/G14	R5F104GAGFB	PLQP0048K*
259	RL78/G14	R5F104MGDFB	PLQP0080K*	319	RL78/G14	R5F104GAGNA	PWQN0048K*
260	RL78/G14	R5F104MGGFA	PLQP0080J*	320	RL78/G14	R5F104GCAFB	PLQP0048K*
261	RL78/G14	R5F104MGGFB	PLQP0080K*	321	RL78/G14	R5F104GCANA	PWQN0048K*
262	RL78/G14	R5F104MHAFB	PLQP0080J*	322	RL78/G14	R5F104GCDFF	PLQP0048K*
263	RL78/G14	R5F104MHAFB	PLQP0080K*	323	RL78/G14	R5F104GCDNA	PWQN0048K*
264	RL78/G14	R5F104MHDFA	PLQP0080J*	324	RL78/G14	R5F104GCGFB	PLQP0048K*
265	RL78/G14	R5F104MHDFF	PLQP0080K*	325	RL78/G14	R5F104GCGNA	PWQN0048K*
266	RL78/G14	R5F104MHGFA	PLQP0080J*	326	RL78/G14	R5F104GDFAFB	PLQP0048K*
267	RL78/G14	R5F104MHGFB	PLQP0080K*	327	RL78/G14	R5F104GDANA	PWQN0048K*
268	RL78/G14	R5F104MJAFB	PLQP0080J*	328	RL78/G14	R5F104GDDFF	PLQP0048K*
269	RL78/G14	R5F104MJAFB	PLQP0080K*	329	RL78/G14	R5F104GDDNA	PWQN0048K*
270	RL78/G14	R5F104MJDFB	PLQP0080J*	330	RL78/G14	R5F104GDGFB	PLQP0048K*
271	RL78/G14	R5F104MJDFB	PLQP0080K*	331	RL78/G14	R5F104GDGNA	PWQN0048K*
272	RL78/G14	R5F104MJGFA	PLQP0080J*	332	RL78/G14	R5F104GEAFB	PLQP0048K*
273	RL78/G14	R5F104MJGFB	PLQP0080K*	333	RL78/G14	R5F104GEANA	PWQN0048K*
274	RL78/G14	R5F104MKAFB	PLQP0080J*	334	RL78/G14	R5F104GEDFB	PLQP0048K*
275	RL78/G14	R5F104MKAFB	PLQP0080K*	335	RL78/G14	R5F104GEDNA	PWQN0048K*
276	RL78/G14	R5F104MKGFA	PLQP0080J*	336	RL78/G14	R5F104GEGFB	PLQP0048K*
277	RL78/G14	R5F104MKGFB	PLQP0080K*	337	RL78/G14	R5F104GEGNA	PWQN0048K*
278	RL78/G14	R5F104MLAFA	PLQP0080J*	338	RL78/G14	R5F104GFAFB	PLQP0048K*
279	RL78/G14	R5F104MLAFB	PLQP0080K*	339	RL78/G14	R5F104GFANA	PWQN0048K*
280	RL78/G14	R5F104MLGFA	PLQP0080J*	340	RL78/G14	R5F104GFDFB	PLQP0048K*

Table. Product list

MCR-22-0500

No	Group	Product part number	Package code	No	Group	Product part number	Package code
341	RL78/G14	R5F104GFDNA	PWQN0048K*	401			
342	RL78/G14	R5F104GFGFB	PLQP0048K*	402			
343	RL78/G14	R5F104GFGNA	PWQN0048K*	403			
344	RL78/G14	R5F104GGAFB	PLQP0048K*	404			
345	RL78/G14	R5F104GGANA	PWQN0048K*	405			
346	RL78/G14	R5F104GGDFB	PLQP0048K*	406			
347	RL78/G14	R5F104GGDNA	PWQN0048K*	407			
348	RL78/G14	R5F104GGGFB	PLQP0048K*	408			
349	RL78/G14	R5F104GGGNA	PWQN0048K*	409			
350	RL78/G14	R5F104GHAFB	PLQP0048K*	410			
351	RL78/G14	R5F104GHANA	PWQN0048K*	411			
352	RL78/G14	R5F104GHDFB	PLQP0048K*	412			
353	RL78/G14	R5F104GHDNA	PWQN0048K*	413			
354	RL78/G14	R5F104GHGFB	PLQP0048K*	414			
355	RL78/G14	R5F104GHGNA	PWQN0048K*	415			
356	RL78/G14	R5F104GJAFB	PLQP0048K*	416			
357	RL78/G14	R5F104GJANA	PWQN0048K*	417			
358	RL78/G14	R5F104GJDFB	PLQP0048K*	418			
359	RL78/G14	R5F104GJDNA	PWQN0048K*	419			
360	RL78/G14	R5F104GJGFB	PLQP0048K*	420			
361	RL78/G14	R5F104GJGNA	PWQN0048K*	421			
362	RL78/G14	R5F104GKAFB	PLQP0048K*	422			
363	RL78/G14	R5F104GKANA	PWQN0048K*	423			
364	RL78/G14	R5F104GKGF B	PLQP0048K*	424			
365	RL78/G14	R5F104GKGNA	PWQN0048K*	425			
366	RL78/G14	R5F104GLAFB	PLQP0048K*	426			
367	RL78/G14	R5F104GLANA	PWQN0048K*	427			
368	RL78/G14	R5F104GLGFB	PLQP0048K*	428			
369	RL78/G14	R5F104GLGNA	PWQN0048K*	429			
370				430			
371				431			
372				432			
373				433			
374				434			
375				435			
376				436			
377				437			
378				438			
379				439			
380				440			
381				441			
382				442			
383				443			
384				444			
385				445			
386				446			
387				447			
388				448			
389				449			
390				450			
391				451			
392				452			
393				453			
394				454			
395				455			
396				456			
397				457			
398				458			
399				459			
400				460			