

RENESAS TOOL NEWS on April 16, 2007: 070416/tn2

A Note on Using High-performance Embedded Workshop V.4.02.00 --With Typing the Default Directory Name of a New Workspace--

Please take note of the following problem in using High-performance Embedded Workshop V.4.02.00:

- With typing the default directory name of a new workspace
-

1. Description

If a build is performed without saving manually after include files are edited in the Editor window of High-performance Embedded Workshop (Include files are saved automatically when the build is performed.), the source file that includes the edited include files may be left out of the objects of the build.

2. Conditions

This problem occurs if either of the following conditions is satisfied:

(1) You have typed the default directory name of a new workspace into its text box such a way that it is different from the one presented by Windows Explorer in upper- and lower-case letters. (That is, directory names are case sensitive.)

(2) You have typed the default directory name of a new workspace into its text box in the Workspace tab of the Options dialog box* such a way that it is different from the one presented by Windows Explorer in upper- and lower-case letters.

* To open this dialog box, open the Setup menu and select the Options command.

3. Workaround

Select the default directory name of a new workspace out of the list in the Choose Directory dialog box. This dialog box is opened by clicking the Browse button. Or, type its name into its text box such a way that it is the same as the one presented by Windows Explorer in upper- and lower-case letters.

4. Schedule of Fixing the Problem

We plan to fix this problem in the next release of the product.

[Disclaimer]

The past news contents have been based on information at the time of publication. Now changed or invalid information may be included. The URLs in the Tool News also may be subject to change or become invalid without prior notice.

© 2010-2016 Renesas Electronics Corporation. All rights reserved.