

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

M16C/62

Using the M16C/62 Timers in Timer Mode

1.0 Abstract

The following article describes how to use timers A and B as basic timers, referred to as Timer Mode. Timers are useful for updating multiplexed display, scanning inputs, real time clocks, hardware watchdogs, etc.

2.0 Introduction

The M16C/62 is a 16-bit MCU, based on the M16C CPU core, with features including 10-bit A/D, D/A, UARTS, timers, DMA, etc., and up to 256KB of user flash. The MCU has 11 timers. The timers are separated into two categories by functionality, 5 Timer A's and 6 Timer B's. All 11 timers can operate in Timer Mode.

Timer A has the following additional modes of operation:

- Event Counter Mode
- PWM Mode
- One-Shot Mode

Timer B has the following additional modes of operation:

- Event Counter Mode
- Pulse Width Measurement Mode

Figure 1 illustrates the operation of timer A and Figure 2 illustrates Timer B. Note that there are some differences between the two timers but both operate similarly in Timer Mode. The remainder of this document will focus on setting up timer A0 in Timer Mode.




Figure 1 Block Diagram of Timer A




Figure 2 Block Diagram of Timer B

3.0 Timer Mode Description

In Timer Mode, the counter register counts down using the selected clock source until the counter underflows (0000 to FFFFh). At this point, the timer interrupt request bit is set and the contents of the reload register are loaded back into the counter and countdown continues. An interrupt will be accepted when all of the following conditions are met:

- interrupt enable flag (I flag) = "1"
- interrupt request bit = "1"
- interrupt priority level > IPL (Processor Interrupt Priority Level)

If at any time during countdown the count start flag is cleared, counting is suspended until set. Figure 3 illustrates this.




Figure 3 Operation Timing of Timer Mode

4.0 Configuring Timer Mode

To configure a timer for Timer Mode:

1. Load the Timer Ai register, TAI (which also loads the reload register) with the count source.
2. Load the Timer Mode register, TAIMR:
 - Select timer mode: bits TMOD0, TMOD1 = 0.
 - Select the clock source (f1, f/8, f/32, or fc/32): bits TCK0, TCK1.
3. Load the Timer Interrupt Control register (TAiC) with an interrupt priority level (ILVL) value of at least 1 if interrupts are desired.
4. Ensure interrupts are enabled (I flag set).
5. Set the 'start count' flag bit, TAiS in the Count Start Flag register, TABSR.

It is not necessary to perform these steps in the order listed, but the count register should be loaded before the 'start count' flag is set. Also, the priority level should not be modified when there is a possibility of an interrupt occurring.

The required registers are shown in Figure 4 through Figure 7.

Symbol	Address	When reset
TA0	0387 ₁₆ , 0386 ₁₆	Indeterminate
TA1	0389 ₁₆ , 0388 ₁₆	Indeterminate
TA2	038B ₁₆ , 038A ₁₆	Indeterminate
TA3	038D ₁₆ , 038C ₁₆	Indeterminate
TA4	038F ₁₆ , 038E ₁₆	Indeterminate

Function	Values that can be set	R	W
• Timer mode Counts an internal count source	0000 ₁₆ to FFFF ₁₆	O	O
• Event counter mode Counts pulses from an external source or timer overflow	0000 ₁₆ to FFFF ₁₆	O	O
• One-shot timer mode Counts a one-shot width	0000 ₁₆ to FFFF ₁₆	X	O
• Pulse width modulation mode (16-bit PWM) Functions as a 16-bit pulse width modulator	0000 ₁₆ to FFFF ₁₆	X	O
• Pulse width modulation mode (8-bit PWM) timer low-order address functions as an 8-bit prescaler and high-order address functions as an 8-bit pulse width modulator	00 ₁₆ to FE ₁₆ (Both high-order and low-order addresses)	X	O

Note: Read and write data in 16-bit units

Figure 4 Timer Ai Register




Figure 5 Timer Ai Mode Register




Figure 6 Count Start Flag Register




Figure 7 Timer Interrupt Control Register

5.0 Reference

Renesas Technology Corporation Semiconductor Home Page

<http://www.renesas.com>

E-mail Support

support_apl@renesas.com

Data Sheets

- M16C/62 datasheets, 62aeds.pdf

User's Manual

- M16C/62 User's Manual, 62eum.pdf
- M16C/60 and M16C/20 C Language Programming Manual, 6020EC.pdf
- Application Note: Writing Interrupt Handlers in C for the M16C
- NC30 Ver. 4.0 User's Manual, NC30UE.PDF

6.0 Software Code

Following is a simple program written for Renesas' NC30 compiler to illustrate how to set up a timer mode on timer A0. This program runs on the MSV1632/62 Starter Kit Board and flashes the green LED (LED4) at a 1Hz rate.

To become familiar with the timer, try changing the flash rate, the clock source, or even switch to a different timer (e.g., TA1, TB0, etc.).

```

/*****
*
*   File Name: timer_mode.c
*
*   Content: Example program using Timer A0 in "Timer Mode" .This program
*           is written for the Timer Mode application note.  This program
*           works with the MSV1632/62 starter kit board and flashes the
*           red LED (LED2) connected to p7_2.
*
*   Compiled with NC30 ver. 3.20.00.
*
*   All timing based on 16 Mhz Xtal
*
*   Copyright, 2003 Renesas Technology Corporation, Inc.
*=====
*   $Log:$
*=====*/
#include "sfr62.h"

#define TIME_CONFIG 0x40 /* 01000000 value to load into Timer Ai mode register
        |||||_  TMOD0,TMOD1: TIMER MODE SELECTED
        |||||_  MR0:          NO PULSE OUTPUT
        ||||_  MR1,MR2:      GATE FUNCTION NOT SELECTED
        ||_    MR3:          SET TO 0 IN TIMER MODE
        ||_    TCK0,TCK1:    F DIVIDED BY 8 SELECTED */

#define CNTR_IPL 0x03 // TA0 interrupt priority level
#define LED p7_2

int time_cnt;
int count; //Global count value, incremented every second

//prototypes
void init(void);

#pragma INTERRUPT /B TimerA0Int
void TimerA0Int(void);

```

```

/*****
Name:      TimerA0Int()
Parameters: none
Returns:  nothing
Description: Timer A0 Interrupt Service Routine. Interrupts every 5 msec,
            toggles LED every second, and increments global 'count'
*****/

void TimerA0Int(void)
{
    if ((time_cnt += 5) > (1000))    // = 1 second
    { LED ^= 1;                      // toggle LED
      count++;                       // counts the number of seconds since the last
                                    // reset
      time_cnt = 0;
    }
}

/*****
Name:      main()
Parameters: none
Returns:  nothing
Description: initializes variables and LED port. Then does nothing but
            wait for TA0 interrupts.
*****/

void main (void)
{
    time_cnt = 0;
    count = 0;
    pd7_2 = 1;
    init();
    while (1);    //LED flashing is interrupt driven
}

/*****
Name:  init()
Parameters: none
Returns:  nothing
Description: Timer TA0 setup for 5msec interrupts.
*****/

void init()
{
    ta0 = 10000; // 16meg xtal, divide by 8, times 10,000 counts-> 5msec interrupts.
}

```

/* the following procedure for writing an Interrupt Priority Level follows that as described in the M16C data sheets under 'Interrupts' */

```

_asm (" fclr i") ; // turn off interrupts before modifying IPL
ta0ic |= CNTR_IPL; // Interrupt Control register for Timer A0
// use read-modify-write instruction to clear IPL
// (disable Timer A0 interrupts)
ta0mr = TIME_CONFIG; // Timer A0 mode register set to pulse output mode
_asm (" fset i");

ta0s = 1; // Count Start Flag register bit0, for Timer A0
// start counting!
}

```

In order for this program to run properly, timer A0's interrupt vector needs to point to the function. The interrupt vector table is near the end of the startup file "sect30.inc". Insert the function label "_TimerA0Int" into the interrupt vector table at vector 21 as shown below.

```

;*****
;
; NC30 C Compiler for M16C/62
;
; Copyright,2003 Renesas Technology Corporation, Inc.
; All Rights Reserved.
;
; Modified for use on MSV1632 Starter Kit.
; sect30.inc : section definition file
; This program is applicable when using KD30 and the ROM Monitor.
;*****
:
:
:

.lword dummy_int ; A-D(for user) (vector 14)
.lword dummy_int ; uart2 transmit(for user) (vector 15)
.lword dummy_int ; uart2 receive(for user) (vector 16)
.lword dummy_int ; uart0 transmit(for user) (vector 17)
.lword dummy_int ; uart0 receive(for user) (vector 18)
.lword 0ff900h ; uart1 transmit(for user) (vector 19)
.lword 0fff900h ; uart1 receive(for user) (vector 20)

```

```
.glob      _TimerA0Int
.lword    _TimerA0Int      ; timer A0 (for user) (vector 21)
.lword    dummy_int       ; timer A1 (for user) (vector 22)
.lword    dummy_int       ; timer A2 (for user) (vector 23)
.lword    dummy_int       ; timer A3 (for user) (vector 24)
.lword    dummy_int       ; timer A4 (for user) (vector 25)
.lword    dummy_int       ; timer B0 (for user) (vector 26)
.lword    dummy_int       ; timer B1 (for user) (vector 27)
.lword    dummy_int       ; timer B2 (for user) (vector 28)
.lword    dummy_int       ; int0  (for user) (vector 29)
.lword    dummy_int       ; int1  (for user) (vector 30)
.lword    dummy_int       ; int2  (for user) (vector 31)
          :
          :
          :
```

Keep safety first in your circuit designs!

- Renesas Technology Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corporation product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corporation or a third party.
- Renesas Technology Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corporation assumes no responsibility for any damage, liability, or other loss arising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corporation by various means, including the Renesas Technology Corporation Semiconductor home page (<http://www.renesas.com>).
- When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- Renesas Technology Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- The prior written approval of Renesas Technology Corporation is necessary to reprint or reproduce in whole or in part these materials.
- If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- Please contact Renesas Technology Corporation for further details on these materials or the products contained therein.