

NX8349TB

LASER DIODE

R08DS0001EJ0100 Rev.1.00 Jul 26, 2010

1 310 nm AlGainAs MQW-DFB LASER DIODE FOR 10 Gb/s APPLICATION

DESCRIPTION

The NX8349TB is a 1 310 nm Multiple Quantum Well (MQW) structured Distributed Feed-Back (DFB) laser diode TOSA (transmitter optical subassembly) with InGaAs monitor PIN-PD in a receptacle type package designed for SFP+/XFP transceiver.

FEATURES

• Internal optical isolator

• Optical output power

• Low threshold current

• Wide operating temperature range

InGaAs monitor PIN-PD

 $P_f = -2 dBm$

 $I_{th} = 8 \text{ mA TYP.} @ T_C = 25^{\circ}\text{C}$

RENESAS


 $T_{\rm C} = -20 \text{ to } +95^{\circ}{\rm C}$



- 10 G BASE-LW/LR
- 10 G Fibre Channel
- SONET OC-192



PACKAGE DIMENSIONS (UNIT: mm)



ORDERING INFORMATION

Part Number	Receptacle Type	Note
NX8349TB	LC, Electrically isolated	Differential input with flexible PCB, without matching resistor



ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Ratings	Unit
Storage Temperature	T _{stg}	-40 to +95	°C
Operating Case Temperature	T _C	−20 to +95	°C
Forward Current of LD	I _{FLD}	120	mA
Reverse Voltage of LD	V_{RLD}	2	V
Forward Current of PD	I _{FPD}	10	mA
Reverse Voltage of PD	V_{RPD}	15	V
Soldering Temperature (Flexible Printed Circuit)	T_{sld}	350 (10 sec.)	°C
Optical Output Power	P _f	5	mW




ELECTRO-OPTICAL CHARACTERISTICS (Tc = -20 to +95°C, BOL, unless otherwise specified)

Parameter	Symbol	Conditions	MIN.	TYP	MAX.	Unit
Mean Optical Output Power	Pf			-2		dBm
Peak Emission Wavelength	λ_{p}	CW, $P_f = -2 \text{ dBm}$	1 290		1 330	nm
Spectral Width	Δλ	CW, $P_f = -2 \text{ dBm}$, 20 dB down			1	nm
Side Mode Suppression Ratio	SMSR	CW, $P_f = -2 \text{ dBm}$	35			dB
Threshold Current	I _{th}	CW, T _C = 25°C		8	15	mA
		CW	2		30	
Differential Efficiency	η_{d}	CW, $P_f = -2 \text{ dBm}$, $T_C = 25^{\circ}\text{C}$	0.020	0.029	0.040	W/A
		CW, P _f = –2 dBm	0.008		0.060	
Temperature Dependence of Differential Efficiency	$arDelta\eta_{d}$	$\Delta \eta_{\rm d}$ = 10 log $\frac{\eta_{\rm d}}{\eta_{\rm d} (@25^{\circ}\text{C})}$	-3.5		1.5	dB
Operation Voltage	V _{op}	CW, $P_f = -2 \text{ dBm}$	0.5		2.2	V
Monitor Current	I _m	CW, $P_f = -2 \text{ dBm}$	100		1 000	μΑ
Monitor Dark Current	I _D	$V_R = 3.3 \text{ V}, T_C = 25^{\circ}\text{C}$			10	nA
		V _R = 3.3 V			500	
Rise Time	t _r	20-80% *1			50	ps
Fall Time	t _f	20-80% *1			50	ps
Monitor PD Terminal	Ct	V _R = 3.3 V, f = 1 MHz		6	20	pF
Capacitance						
Relative Intensity Noise	RIN	*1)	-128	dB/Hz
Tracking Error*2	γ		-1.0		1.0	dB

Notes: *1. 9.95/10.3/10.5 Gb/s, PRBS 2³¹–1, NRZ, Duty Cycle = 50%





REFERENCE

Document Name	Document No.
Opto-Electronics Devices Pamphlet*1	PX10160E


Notes: *1. Published by the former NEC Electronics Corporation.



SAFETY INFORMATION ON THIS PRODUCT



SEMICONDUCTOR LASER



AVOID EXPOSURE-Invisible Laser Radiation is emitted from this aperture

Worming Lagge Bases	A laser beam is emitted from this diode during operation.
Warning Laser Beam	The laser beam, visible or invisible, directly or indirectly, may cause injury to the eye or loss of
	eyesight.
	Do not look directly into the laser beam.
	Avoid exposure to the laser beam, any reflected or collimated beam.
Caution GaAs Products	This product uses gallium arsenide (GaAs). GaAs vapor and powder are hazardous to human health if inhaled or ingested, so please observe the following points.
	• Follow related laws and ordinances when disposing of the product. If there are no applicable laws and/or ordinances, dispose of the product as recommended below.
	Commission a disposal company able to (with a license to) collect, transport and dispose of materials that contain arsenic and other such industrial waste materials.
	Exclude the product from general industrial waste and household garbage, and ensure that the product is controlled (as industrial waste subject to special control) up until final disposal.
	Do not burn, destroy, cut, crush, or chemically dissolve the product.
	Do not lick the product or in any way allow it to enter the mouth.
Courtiers Courters 5"	A glass-fiber is attached on the product. Handle with care.
Caution Optical Fiber	When the fiber is broken or damaged, handle carefully to avoid injury from the damaged part or fragments.



Revision	History

NX8349TB Data Sheet

		Description	
Rev.	Date	Page	Summary
1.00	Jul 26, 2010	_	First edition issued



Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- 2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronic assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Re depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties an use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and designed for life support.
- Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design or hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate Because the evaluation of microcomputer software alone is very difficult please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Ele tronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries. (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



SALES OFFICES

Renesas Electronics Corporation

http://www.renesas.com

Refer to "http://www.renesas.com/" for the latest and detailed information.

Renesas Electronics America Inc. 2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A. Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited 1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada Tel: +1-905-898-5441, Fax: +1-905-898-3220

Renesas Electronics Europe Limited Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH Arcadiastrasse 10, 40472 Düsseldorf, Tel: +49-211-6503-0, Fax: +49-211-65

Renesas Electronics (China) Co., Ltd.
7th Floor, Quantum Plaza, No.27 Zhi@hunLu Haidian District, Beijing 100083, P.R.China
Tel: +864-0-9235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd., Pudong District, Shanghai 200120, China Tel: #86-21-5877-1818, Fax: +86-21-6887-7858 / -7898

Renesas Electronics Hong Kong Limited

Unit 1601-1613 (16F. 170wer 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong Tel: +852-2886-9318, Fax: +852 2886-9022/9044

Renesas Electronics Taiwan Co., Ltd. 7F, No. 363 Fu Shing North Road Taiwa

F, No. 363 Fu Shing North Road Taipei, Taiwan, R.O.C. el: +886-2-8175-9600, Fax: +886 2-8175-9670

Renease Electronics Singapore Pte. Ltd.
1 harbour Front Avenue, #06-10, keppel Bay Tower, Singapore 098632
Tel: +65-6213-0200, Fax: +65-6278-8001
Renease Electronics Malaysia Sdn.Bhd.
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics Korea Co., Ltd. 11F., Samik Lavied' or Bldg., 720-2 Yeoksam-Dong, Kangnam-Ku, Seoul 135-080, Korea Tel: 482-2-588-3737, Fax: 482-2-588-5141