

PureTouch™* Capacitive Touch Sensor IC Configuration Registers Detailed Register Information and Default Values

Purpose:

The purpose of this document is to provide detail on the registers available for configuration and performance optimization of the LDS6108 and LDS6128 devices

Scope:

This register document covers the LDS6108 (16-channel touch controller) and the LDS6128 (16-channel touch controller with integrated LED drivers). The other members of the LDS61xx family have their own Detailed Register documents as the relevant bit locations vary by device.

The LED-related registers apply to the LDS6128 device only and may be ignored when using the LDS6108.

Required Initialization:

Not all registers need to be initialized under normal usage conditions, as the default conditions may be appropriate and certain functions and features may not be used in the application.

However, the following registers should be initialized in all cases, as their proper configuration is necessary for fundamental operation.

- 0x00A: DCM configuration
 - Pins C6/DCM14 and C7/DCM15 are set as DCM pins by default. They must be reset during initialization if not used as DCM pins
- 0x041 and 0x042: Touch Sensor Enable
 - Only those channels to be used as sensor input should be set to the "1" state. All
 other bits in these registers (including reserved/unused bits) should be set to "0"
- 0x043 and 0x044: Touch Interrupt Enable
 - To enable proper interrupt operation, these registers should be configured identically to the Touch Sensor Enable registers 0x041 and 0x042
- 0x060-0x073 (non-contiguous, memory page 1): Touch Threshold Levels
 - Sets the touch threshold levels which affect the sensitivity of each sensor.
 - Register 0x05F should be set to Memory Page 1 prior to writing to these registers

If using Low Power/Sleep mode, the following registers should be initialized:

- 0x055: Idle Configuration
 - Set value to 24 (dec) to enable sleep period configuration (0x056) in 1ms increments using default 1024 decimation rate
- 0x056: Sleep Period Configuration
 - Sets the sleep period between scan cycles. See the LDS61xx AN1 application note for more information
- 0x003: Sleep Wait
 - Sets the time the device will wait after the last touch before reverting back to Low Power mode

1





PureTouch™* Capacitive Touch Sensor IC Configuration Registers Detailed Register Information and Default Values

Recommended Initialization:

The following registers are recommended to be initialized for optimized operation.

0x04E: SELC_Unit Configuration

• Determines SELC unit steps utilized during calibration process. Use of adaptive SELC algorithm will accelerate calibration process. Recommended register setting: 5000h.

• 0x051: Ambient Calibration

•Determines how quickly ambient calibration occurs when no-touch value drifts above/below the plus/minus noise region. Recommended register setting: 0A1Fh.

• 0x052: Recalibration Configuration

• Sets the delay before a recalibration is initiated when capacitive signal is above the ambient threshold and below the touch threshold. The default IC value (99 decimal) results in a delay of "0.8s x # of active sensor channels". When few sensor channels are utilized, this may result in too short a delay. This delay should be at least 4-5s to avoid calibrating out an approaching finger.

• 0x053: Stuck Touch

• Determines how quickly forced recalibration occurs when touch persists for abnormally long length of time. Optimal setting depends upon usage model.

• 0x060-0x073 (non-contiguous, memory page 0): Initial SELC

 Sets the starting value for SELC for each sensor. Loading initial SELC values for each sensor will result in faster recalibration times. Recommended setting determined during prototype stage.

• 0x075: Touch Hysteresis

• Sets the amount of capacitance value units below Touch Threshold to still be considered a continuation of current/active touch. Recommended register setting: 0005h to 000Ah.

By default, the INTB (Interrupt) pin is configured as an active-low CMOS output, with a fixed duration of 2us when a touch or untouch event occurs. INTB may also be configured as active high (0x008 bit 15 = 1) and as an open drain output requiring a pull-up or pull-down resistor (0x008 bit 3 = 1), depending upon system requirements.

Finally, INTB may also be configured in "Read Reset" mode (0x008 bit 1 = 1), in which case Touch Status Register 0x045 must be read in order to release/reset the INTB pin. Read Reset mode corresponds to the default INTB mode of operation of IDT's LDS60xx family of products.





PureTouch™* Capacitive Touch Sensor IC Configuration Registers Detailed Register Information and Default Values

Functional Groupings

Function	Register	Description
RESET	0x000	Cold Reset
	0x001	Software Reset
POWER	0x002	Normal Operation, Low Power Mode, Shutdown
	0x055	Idle Time - For Low Power Mode
	0x056	Sleep Configuration
	0x003	Sleep Wait
INTERRUPT	0x008	INTERRUPT Configuration
	0x043-0x044	Touch Interupt Enable
GPIO	0x009	GPIO Config
DCM	0x00A	DCM Mode
MANUFACTURER ID	0x01F	Manufacturer/Product Family ID
TOUCH CONFIGURATION	0x040	Touch mode - All touches reported, Strongest Touch, Dual Strongest Touches
	0x041 - 0x042	Touch Sensor Enable
	0x05F	Touch Parameter Memory Page Selection
TOUCH STATUS	0x045 - 0x046	Touch Status
	0x080 - 0x0CD	
	(non-contiguous)	Cap Value (Read Only)
THRESHOLD SETTING	0x05F	Touch Parameter Memory Page Selection - Touch threshold conditions
(SENSITIVITY)	0x060 - 0x073 (non-contiguous)	Touch Threshold Value (Memory Page 1)
	· ·	
LED CONFIGURATION	0x020-0x02F 0x030-0x039	LEDx - Min Current, Max Current, Assignment; Latency; Effect Selection
		LEDx Effect Configuration LED Manual Mode Configuration
	0x03E 0x03F	LED Manual Mode Configuration LED Driver Enable Configuration
BUILT-IN SLIDER/SCROLL	0x04B	Slider/Scroll Position and Direction Reading
BOILT-IN SLIDEN/SCROLL	0x074	Slider/Scroll Fosition and Direction Reading Slider/Scroll Enable
CALIBRATION & SELC	0x04E	SELC Step Size, Ambient Calibration Enable, Calibration Status
OALIBITATION & CLEO	0x050	Calibration Timeout
	0x051	Ambient Calibration
	0x052	Recalibration Configuration
	0x053	Stuck Touch (Forced Recalibration)
	0x05F	Touch Paramater Page Selection
	0x060 - 0x073	
	(non-contiguous)	Calibration Parameters (Memory Pages 0, 2, 3, and 4)
	0x080 - 0x0CD (non-contiguous)	SELC Value (Boad Only)
		SELC Value (Read Only)
STRONGEST TOUCH	0x040	Strongest Touch Enable
CONFIGURATION	0x057 0x075	Strongest Touch Replacement Time Strongest Touch Hysteresis
	0x075	Strongest Fouch Hysteresis
RELATIVE STRONGEST\ TOUCH	0.076	Dolotivo Stronggot Tough Made Enghla
	0x076	Relative Strongest Touch Mode Enable
UNDEBOUNCE	0x076	# of consecutive scan cycles required before untouch is recognized
DEBOUNCE	0x057	Debounce time criteria
HYSERESIS	0x075	Touch Hysteresis Value + Strongest Touch Hysteresis
GUARD/SUPPRESS CHANNEL	0x07C-0x07D 0x07E-0x07F	Guard Channel Enable Guard Channel Mask
NOISE IMMUNITY	0x077	Set to 8001 (hex) for optimal noise filtering.





									Reset								
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x000	W	Cold Reset															
0x001	W	W Software Reset															

Register Name	Position	Description	Function	Remark
COLD RESET		Hardware reset	Any value invokes HW reset (all configuration registers revert to default)	
SOFT RESET		Software reset	Any value invokes SW reset (keeps user settings, but recalibrates)	

								F	OWER								
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x002	R/W							Internal	Internal							LP	SHUTDOWN
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
LP	[1]	power saving mode	0 : Normal mode, 1 : Low Power Mode	
SHUTDOWN	[0]	shutdown mode	0 : Normal mode, 1 : Shutdown mode (only Serial I/F bus active)	

								SLE	EP WAI	Т							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x003	R/W								SLEEF	WAIT							
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
		Full Power to Low Power wait time	Wait time = SLEEP WAIT x Scan Cycle Time	
SLEEP WAIT	[15:0]		(Scan Cycle Time = ~2ms x # of active sensors)	

								INT	B Confi	g							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x008	R/W	INT_POL	Internal										INTB [DRIVE		INTB N	MODE
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
INT_POL	[15]	interrupt polarity	0 : active Low, 1: active High	
INTB DRIVE	[4:3]	interupt drive	0x0 : CMOS output	
		,	0x1 : OPEN-DRAIN output (pull up resistor required)	
INTB MODE	[1:0]	interupt signaling type	00: Fixed Duration Mode (INTB pin drives for 2us Fixed Duration)	
			01: Internal mode	
			1x: Read Reset Mode (INTB pin drives until Register 0x045 is read)	

								GPI	O Confi	g							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x009	R/W												GPI	O Input Co	onfig	GP	1/0
Default Values	0002h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0

Register Name	Position	Description	Function	Remark
GPIO Input Config	[4:2]	GPIO input configuration	0x0 : not used	
			0x1 : negative level-sensitive	
			0x2 : positive level-sensitive	
			0x3 : not used	
			0x4 : not used	
			0x5 : negative edge-triggered	
			0x6 : positive edge-triggered	
			0x7 : both edge-triggered	
GPI/O	[1:0]	GPIO state	0x0 : not used	
			0x1 : input	
			0x2 : active low output	
			0x3 : active high output	



Configuration Register Map and Description

Detailed Register Information and Default Values

								DC	M Config	g							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x00A	R/W							DCM15	DCM14	Inte	rnal	DCM Ena	ble (Bit 5 =	DCM13, E	Bit 4 = DCM	12Bit 0	= DCM8)
Default Values	0300h	0	0	0	0	0	0	1	1	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
DCM Enable	[9:8], [5:0]	DCM Function Enable	0 : disable, 1: enable	

									MID								
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x01F	R				Inte	rnal					Manufa	cturer ID			Devi	ce ID	
Default Values	00F2h	0	0	0	0	0	0	0	0	1	1	1	1	0	0	1	0

Register Name	Position	Description	Function	Remark
Manufacturer ID	[7:4]	IDT PureTouch	IDT PureTouch = 1111	
Device Family ID	[3:0]	LDS61xx Family	LDS61xx Family = 0010	

									LE	D LEDO)							
Re	egister Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
	0x020	R/W		LED	0 Max Cui	rrent			LEC	00 Min Cur	rent				LEC	00 Assignm	ent	
Dε	efault Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

								LE	D LED1								
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x021	R/W		LED	1 Max Cu	rrent			LED	01 Min Cur	rent				LED	01 Assignm	nent	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

								LE	D LED2	2							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x022	R/W		LED	2 Max Cu	rrent			LED	2 Min Cur	rent				LEC	2 Assignm	ent	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

									LE	D LED3	3							
Rec	ister Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
	0x023	R/W		LED	3 Max Cu	rrent			LED	3 Min Cui	rent				LED	03 Assignm	nent	
Def	ault Values	0000h	0	0	0	0	0	0	Λ	0	0	0	0	0	0	0	0	0

								LE	D LED4								
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x024	R/W		LED	4 Max Cui	rrent			LEC	04 Min Cur	rent				LED	4 Assignm	ent	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

								LE	D LEDS								
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x025	R/W		LED	5 Max Cui	rrent			LEC	05 Min Cur	rent				LEC	05 Assignm	ent	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

								LE	D LED6								
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x028	R/W		LED	6 Max Cui	rrent			LEC	6 Min Cur	rent				LEC	6 Assignm	ent	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

								LE	D LED7	•							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x029	R/W		LED	7 Max Cui	rrent			LEC	7 Min Cur	rent				LEC	7 Assignm	ent	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
LED Max Current	[15:11]	LED Maximum Current Drive	Driving Current = Register Value * 0.25 [mA]	
LED Min Current	[10:6]	LED Minimum Current Drive	Driving Current = Register Value * 0.25 [mA]	
LED Assignment	[4:0]	Touch Sensor Association	Touch Sensor Number - SEE LOOKUP TABLE	

LDS6128 Touch Sensor Assignment Lookup Table

Touch Sensor#	Bit [4:0] Assignment	Touch Sensor#	Bit [4:0] Assignment
C0	00000	C8/LED0	01010
C1	00001	C9/LED1	01011
C2	00010	C10/LED2	01100
C3	00011	C11/LED3	01101
C4	00100	C12/LED4	01110
C5	00101	C13/LED5	01111
C6	01000	C14/LED6	10000
C7	01001	C15/LED7	10001



Configuration Register Map and Description

							LE	D Driver	Latence	v Confid							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x02E	R/W											LE	D Driver L	atency Ti	ne		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
LATENCY TIME	[7:0]	Latency time in 5ms increments	LED Driver Delay time = Value * 5 [ms]	

							LED	Effect '	Wavefor	m Confi	q						
Register Address	Direction	Bit 15 Bit 14 Bit 13 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0															
0x02F	R/W	EN_DOFF	EN_DON	Internal								LE	D Active/P	eriod 2 Tir	ner		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
EN_DOFF	[15]	Dimming off enable	0 : disable, 1: enable	
EN_DON	[14]	Dimming on enable	0 : disable, 1: enable	
ACTIVE TIME	[7:0]	LED Active/Period 2 Timer	Time = ACTIVE TIME * 5ms	

							LED0 Eff	ect Con	figuration	on (Perio	od 1/3)						
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x030	R/W	LED0	Effect					LED0 F	Period 1					LED0 F	Period 3		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

							LED1 Eff	fect Cor	nfiguration	on (Perio	od 1/3)						
Register Address	Direction	Bit 15	Bit 14	Bit 13													
0x031	R/W	LED1	Effect					LED1 F	Period 1					LED1 F	Period 3		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

							ED2 Eff	ect Con	figuration	on (Perio	od 1/3)						
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x032	R/W	LED2	Effect					LED2 F	Period 1					LED2 F	Period 3		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

							LED3 Eff	ect Con	figuration	on (Peri	od 1/3)						
Register Address	Direction	Bit 15	Bit 14	Bit 13													
0x033	R/W	LED3	Effect					LED3 F	Period 1					LED3 F	Period 3		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

					_		ED4 Ef	fect Con	figuration	on (Perio	od 1/3)						
Register Address	Direction	Bit 15	Bit 14	Bit 13	3 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0												
0x034	R/W	LED4	Effect					LED4 F	Period 1					LED4 F	Period 3		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

							LED5 Eff	ect Con	figuration	on (Perio	od 1/3)						
Register Address	Direction	Bit 15	it 15 Bit 14 Bit 13 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0														
0x035	R/W	LED5	Effect					LED5 F	Period 1					LED5 F	Period 3		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

							ED6 Eff	ect Con	figuratio	on (Perio	od 1/3)						
Register Address	Direction	Bit 15	Bit 14	Bit 13													
0x038	R/W	LED6	Effect					LED6 F	eriod 1					LED6 F	Period 3		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

							ED7 Eff	ect Con	figuration	on (Perio	od 1/3)						
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x039	R/W	LED7	Effect			LED7 Period 1								LED7 F	Period 3		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
LEDx Effect	[15:14]	LED driver operation mode	0 : Linear (Dimming) mode	
			1 : Pulsate mode	
			2: Flash Mode	
			3 : Reserved	
LEDx Period 1	[11:6]	Period 1 Timer (see LED effect	Timer Value = value * 5ms * # of steps	
		diagram for Period 1 significance)	** # of steps = (max current - min current) / 0.25	
LEDx Period 3	[5:0]	Period 3 Timer (see LED effect	Timer Value = value * 5ms * # of steps	
		diagram for Period 1 significance)	** # of steps = (max current - min current) / 0.25	





							LE	D Manu	al Mode	Config							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x03E	R/W	EN_MAN	Gang					LED7,	LED6	Inte	Internal LED Driver Manual Control Bits (LED5-LE				ED5-LED	0)	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
EN_MAN	[15]	LED manual mode enable	0 : disable, 1: enable manual control, MAN_CTRL controls each LED channel	
GANG	[14]	LED gang mode	0 : normal mode, 1: Single LED event results in all LED turning on	
MAN CTRL	[9:8], [5:0]	Manual LED on/off control for each LED channel	0 : manual LED off, 1 : manual LED on	

			LED Driver Enable Configuration														
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x03F	R/W							LED7,	LED7, LED6		rnal		LED [Driver Enal	ole (LED5-L	ED0)	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
LED_ENABLE	[9:8], [5:0]	LED driver enable	0 : Disable	
			1 : Enable (LED enable bit dominates over Touch Sensor Enable in 0x042)	

					TOUCH CONFIG														
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0		
0x040	R/W	TCH_ENABLE	Internal					BUTTON	_MODE			Inte	rnal	READY		Decimation			
Default Values	8030h	1	0	0	0	0	0	0	0	0	0	1	1	0	0	0	0		

Register Name	Position	Description	Function	Remark
TCH ENABLE	[15]	Touch Function Enable	0 : Touch function in idle state, 1: Touch function in active state	
BUTTON_MODE	[9:8]	Touch Preference Mode	0x0 : Unrestricted mode, All touches reported	
		(Strongest Touch Modes)	0x1 : Strongest Touch Mode	
		,	0x2 : Two Strongest Touches Mode	
			0x3 : reserved	
DEVICE_READY	[3]	Device Ready	0 : Self initialization state, 1: OK for host communication	Read Only Bit
			If DEVICE_READY=0, all bits except DEVICE_READY should be ignored.	
Decimation	[2:0]	CDC decimation	0x0 : 1024 (default)	Consult IDT
			0x1 : 512	representative
			0x2 : 256	if decimation
			0x3 : 128	is changed from
L			0x4 : 2048	1024 default

					Touch Sensor Enable (Channels 0-7)														
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0		
0x041	R/W							C7,	C6	Inte	rnal			ouch Ena	ble (C5-C0)			
Default Values	003Fh	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1		

							Touch S															
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0					
0x042	R/W							C14,	C14	Inte	rnal		To	ouch Enab	le (C13-C8	3)						
Default Values	0300h	0	0	0	0	0	0	1	1	0	0	0	0	0	0	0	0					

Register Name	Position	Description	Function	Remark
TOUCH_ENBL	[9:8], [5:0]	Touch enable for each channel	0 : Channel disabled as touch sensor	
			1 : Channel enabled as touch sensor (may be overridden by LED Enable)	
			DCM register 0x00A has priority over 0x041 in case of dual assignment	

							INTERR	UPT EN	ABLE (C	Channel	s 0-7)						
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x043	R/W							C7,	C6	Inte	rnal		Toucl	n Interrupt	Enable (C	5-C0)	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

							NTERR	JPT EN	ABLE (C	hannels	8-15)						
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x044	R/W							C15, C14 Internal					Touch	Interrupt	Enable (C1	(3-C8)	
Default Values	0300h	0	0	0	0	0	0	1	1	0	0	0	0	0	0	0	0


Register Name	Position	Description	Function	Remark
TOUCH_INT_EN	[9:8], [5:0]	Touch interrupt enable for each channel	0 : disable	
		·	1 : enable	

Configuration Register Map and Description



LED Effect Diagrams

Dimming Effect



Dimming Effect Timers:

Period 1*: Dimming On Time


Period 2**: Active/Hold Time (After Touch is Removed)

Period 3*: Dimming Off Time

*: Individual Timer per LED

**: Universal Timer for All LEDs

Pulsate Effect:



Pulsate Effect Timers:

Period 1*: Dimming On Time


Period 2**: Hold Time at Max Current

Period 3*: Dimming Off Time

*: Individual Timer per LED

**: Universal Timer for All LEDs

Flash Effect:



Flash Effect Timers:

Period 1*: Second Wait Time (Wait B)
Period 2**: Hold Time at Max Current
Period 3*: First Wait Time (Wait A)

*: Individual Timer per LED
**: Universal Timer for All LEDs

Configuration Register Map and Description



							TOU	CH STAT	US (Ch	annels ()-7)						
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x045	R							Status C7, C6		Inte	rnal			Touch Stat	us (C5-C0)		
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

							TOUC	H STAT	US (Cha	nnels 8	-15)						
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x046	R	GPI_INT						Status C15, C14 Internal					Ţ	ouch State	us (C13-C8	3)	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
GPI_INT	[15]	GPI interrupt status	0 : no GPI interrupt, 1 : GPI interrupt	
		•	(Used if GPIO is configured as input via Register 0x009)	
TOUCH_INT_STS	[9:8], [5:0]	Touch interrupt status for each channel	Indicates which touch sensor channel was activated by a touch when	
		•	INTB signal is triggered	

								SCRO	LL STA	TUS							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x04B	R/W	Internal	Internal						SCROLL_INT DIR_ENBL SCROLL_DIR POSITION_ID								
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
SCROLL_INT	[7]	Scroll/Slider Touch Interrupt	0 : Not Touched	Read Only
			1 : Position Interrupt Status	
DIR_ENBL	[6]	Scroll/Slider Touch Direction	0 : Not movement	
		Enable(Active) Status	1 : Direction Enable(Active)	
SCROLL_DIR	[5]	Scroll/Slider Touch Direction Status	0 : Low/Left/CCW Direction	Read Only
			1 : High/Right/CW Direction	
POSITION_ID	[4:0]	Scroll/Slider Touch Position ID	- Value : 0 (Not Used for Scroll/Slider Input Type)	Read Only
			- Value : 1~16 (Scroll/Slider Touch Position ID)	

						SE	LC CON	FIG and	CALIBE	RATION	STATUS							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	
0x04E	R/W	Internal	ACTIVE	AMB_DIS	Internal									SELC_UNIT				
Default Values	0002h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	

Register Name	Position	Description	Function	Remark
ACTIVE	[14]	touch calibration status	0 : in calibration state	Read Only Bit
			1 : calibration finished	
AMB_DIS	[13]	ambient calibration disable	0 : ambient calibration active	Optional disabling
			1 : disable ambient calibration	of ambient cal
SELC_UNIT	[3:0]	SELC change amount during calibration	0 : adaptive SELC tracking algorithm used	Refer to 6100
			others: During tracking, SELC changes its value by the amount of SELC_UNIT	AN2 App Note

							С	ALIBRA	TION TI	MEOUT							
Register Address	Direction	tion Bit 15 Bit 14 Bit 13 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0															
0x050	R/W	Internal	Inte	rnal									CALIB_T	IMEOUT			
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
CALIB_TIMEOUT	[7:0]	calibration timeout limit	0x0 : infinite	
			0x1 : when calibration iteration reaches CALIB_TIMEOUT, tracking is done.	

							Α	MBIENT	CALIBR	RATION							
Register Address	Direction	ection Bit 15 Bit 14 Bit 13 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit													Bit 0		
0x051	R/W	R/W CNT DEC LIMIT											CNT_IN	C_LIMIT			
Default Values	1F1Fh	0	0	0	1	1	1	1	1	0	0	0	1	1	1	1	1

Register Name	Position	Description	Function	Remark
CNT_DEC_LIMIT	[15:8]	Value determines how quickly ambient	0x0 : INVALID	
		calibration is triggered (negative side)	others : count limit	
CNT_INC_LIMIT	[7:0]	Value determines how quickly ambient	0x0 : INVALID	
		calibration is triggered (posative side)	others : count limit	
		,		





							RECAL	IBRATIC	ON CON	FIGURA	TION						
Register Address	Direction	Bit 15 Bit 14 Bit 13 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0															
0x052	R/W	RECAL_DELAY															
Default Values	0063h	0	0	0	0	0	0	0	0	0	1	1	0	0	0	1	1

Register Name	Position	Description	Function	Remark
RECAL_DELAY	[10:0]	Wait time prior to forced recalibration	wait time = (RECAL_DELAY+1) * single round time * 4	Default is 0.8s
		when cap value above ambient threshold	Max time = 16.4s (1 ch) to 262s (16ch)	x # of active ch
		but below touch threshold (i.e. not an		with 1024
		actual touch)		decimation

								STU	CK TOU	CH							
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x053	R/W	CNT_TOUCH_LIMIT															
Default Values	0063h	0	0	0	0	0	0	0	0	0	1	1	0	0	0	1	1

Register Name	Position	Description	Function	Remark
CNT_TOUCH_LIMIT	[10:0]	Wait time prior to forced recalibration	wait time = (CNT_TOUCH_LIMIT+1) * single round period * 4	Default is 0.8s
		when cap value is above threshold level	Max time = 16.4s (1 ch) to 262s (16ch)	x # of active ch
		(stuck touch scenario)		with 1024
				decimation

								IDLI	E CONFI	G							
Register Address	Direction	n Bit 15 Bit 14 Bit 13 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0															
0x055	R/W	/W MAX_DEACT_IDLE															
Default Values	0000h																

Register Name	Position	Description	Function	Remark
MAX_DEACT_IDLE	[15:0]	staying IDLE time during inactive touch	Idle time = (MAX_DEACT_IDLE+1) * OSC period (2us)	Init file must set
		channel selected	All channels treated as inactive during Sleep Period	this to 24(dec)
				to enable 1ms
				increments of
				SLEEP_TIME
				with 1024
				decimation

					_			SLEE	P CON	-IG							
Register Address	Direction	Bit 15	15 Bit 14 Bit 13 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0														
0x056	R/W		SLEEP TIME														
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
SLEEP_TIME	[15:0]	# of ms of desired sleep time	Determines duty cycle between active (full power) and sleep (reduced	Init file must set
			power) that determines average current consumption in low power mode	0x055 to
				24(dec) to
				enable 1ms
				increments of
				SLEEP_TIME
				with 1024
				decimation





	<u> </u>				<u> </u>	- O : G C		1100	<u> </u>								
					DE	BOUNC	E AND	STRONG	SEST TO	UCH C	ONFIGU	RATION					
Register Address	Direction	ction Bit 15 Bit 14 Bit 13 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0															
0x057	R/W		DEBOUNCE REPLACEMENT_TIME														
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
DEBOUNCE	[15:12]		Debounce time criteria required to register first touch Time = DEBOUNCE x scan cycle time, where scan cycle time is	
			equal to 2ms x # of active sensors	
REPLACEMENT_TIME	[11:0]	# of consecutive scan cycles required	Strongest Touch Mode (Absolute or Relative) option to minimize frequent	Set to "0"
		for new touch with strongest signal to	toggling between two touches of comparable strength	for Two
		replace current strongest touch	Time = REPLACEMENT_TIME x scan cycle time, where scan cycle	Strongest
		-	time is equal to 2ms x # of active sensors	Touch

						T	OUCH P	ARAME	TER PAG	SE SELE	CTION						
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x05F	R/W		0:initial SELC, 1: touch threshold, 2:ambient threshold, 3:minus noise level, 4:plus noise level									PAGE					
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
PAGE	[2:0]	indirect memory access address	0 : Initial SELC (May be used to accelerate calibration times)	Refer to 6100
			Please refer to 6100 AN2 app note for detaills	AN2 App Note
			1 : Touch Threshold (# capacitive units above baseline to activate touch) 2 : Ambient Threshold (Defines region, along with touch threshold,	
			within which recalibration is delayed by RECAL_DELAY 0x052)	
			3 : Minus Noise Level (Defines - region within which baseline may vary	
			without triggering an ambient recalibration)	
			4 : Plus Noise Level (Defines + region within which baseline may vary	
			without triggering an ambient recalibration)	

							1	OUCH	PARAME	TERS								
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	
0x060	W										Touc	h0 PARAN	/ [10:0]					
0x061	W										Touc	h1 PARAN	/ [10:0]					
0x062	W										Touc	h2 PARAN	/ [10:0]					
0x063	W										Touc	h3 PARAN	/ [10:0]					
0x064	W										Touc	h4 PARAN	/ [10:0]					
0x065	W										Touc	h5 PARAN	/ [10:0]					
0x068	W										Touc	h6 PARAN	/ [10:0]					
0x069	W										Touc	h7 PARAN	/ [10:0]					
Эх06А	W						Touch8 PARAM[10:0]											
Эх06В	W						Touch9 PARAM[10:0]											
0x06C	W										Touch	10 PARA	M[10:0]					
0x06D	W										Touch	11 PARA	M[10:0]					
Эx06E	W											12 PARA						
0x06F	W										Touch	13 PARA	M[10:0]					
0x072	W										Touch	114 PARA	M[10:0]					
0x073	W										Touch	15 PARA	M[10:0]					
Default Values (PAGE=0)	OODOII	0	0	0	0	0												
Default Values (PAGE=1)		0	0	0	0	0	0	0	0	0	0	1	0	1	0	0	0	
Default Values (PAGE=2)	000/111	0	0	0	0	0	0	0	0	0	0	0	0	1	0	1	0	
Default Values (PAGE=3)	0003h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	
Default Values (PAGE=4)	0003h	0	0	0	0	0	0 0 0 0 0 0 0 0 0 1 1											

Register Name	Position	Description	Function	Remark
Touch PARAM	[10:0]	multiplexed touch parameter	0 : Initial SELC (May be used to accelerate calibration times) Please refer to 6100 AN2 app note for detaills	Refer to 6100 AN2 App Note
			Touch Threshold (# capacitive units above baseline to activate touch) : Ambient Threshold (Defines region, along with touch threshold, within which recalibration is delayed by RECAL_DELAY 0x052)	
			3 : Minus Noise Level (Defines - region within which baseline may vary without triggering an ambient recalibration) 4 : Plus Noise Level (Defines + region within which baseline may vary	
			without triggering an ambient recalibration)	





Detailed Register Information and Default Values

							SCROL	/SLIDE	R CHAN	NEL EN	ABLE						
Register Address	Direction	Bit 15													Bit 0		
0x074	R/W	INT SEL			Internal			SCE C7, C6 Internal				Scroll Channel Enable (C5-C0)					
Default Values	0000h	0	0	0 0 0 0					0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
INT_SEL	[15]	SCROLL/SLIDER Touch channel	0 : disable, 1: enable	
		Interrupt Enable		
SCROLL CH[7]	[9]	channel 7 Scroll/Slider Touch Enable	0 : disable, 1: enable	
SCROLL CH[6]	[8]	channel 6 Scroll/Slider Touch Enable	0 : disable, 1: enable	
SCROLL CH[5]	[5]	channel 5 Scroll/Slider Touch Enable	0 : disable, 1: enable	
SCROLL_CH[4]	[4]	channel 4 Scroll/Slider Touch Enable	0 : disable, 1: enable	
SCROLL_CH[3]	[3]	channel 3 Scroll/Slider Touch Enable	0 : disable, 1: enable	
SCROLL_CH[2]	[2]	channel 2 Scroll/Slider Touch Enable	0 : disable, 1: enable	
SCROLL_CH[1]	[1]	channel 1 Scroll/Slider Touch Enable	0 : disable, 1: enable	
SCROLL CHI01	[0]	channel 0 Scroll/Slider Touch Enable	0 : disable, 1: enable	

					TOUCH HYSTERESIS														
Register Address	Direction	Bit 15	Bit 15 Bit 14 Bit 13 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0																
0x075	R/W			ST	TR_HYSTE	RESIS[15	:8]						HYSTER	ESIS[7:0]					
Default Values	0000h	0	0 0 0 0 0 0 0								0	0	0	0	0	0	0		

Register Name	Position	Description	Function	Remark
STR_HYSTERESIS	[15:8]	Strongest Touch Hysteresis value	Extra/additional capacitance value required for new strongest touch to replace current strongest touch. For example, if STR_HYSTERESIS is set to a value of 15 (decimal), the capacitance value required to displace the current strongest touch must be at least 15 capacitance units higher than the current value of the current strongest touch.	
HYSTERESIS	[7:0]	Touch Hysteresis Value (# of cap value units permitted to decrease below Touch Threshold while still maintaining touch status)	Value range: 0~255 Example: Assuming baseline value of 510 and Touch Threshold setting of 40, capacitive value above 550 triggers an initial touch event. If HYSTERESIS value is set to "15", then the sensor capacitive value may go as low as 535 (550-35) and still be considered as original touch.	

						REL	ATIVE S	TRONG	EST AN	D UNDE	BOUNC	E					
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x076	R/W	RELATIVE_EN	INTERNAL											ĺ	JN_DEBO	JNCE [3:0	
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
RELATIVE_EN	[15]	Relative Strongest Touch Mode	0 : disable, 1: enable	
UN_DEBOUNCE	[3:0]	# of consecutive scan cycles required	Debounce time required for UNtouch event to be recognized	
		before UNtouch is recognized	Time = DEBOUNCE x scan cycle time, where scan cycle time is	
		-	equal to 2ms x # of active sensors	

							NO	ISE IMN	IUNITY	ENABLE							
Register Address	Direction	Bit 15	Bit 15 Bit 14 Bit 13 Bit 12 Bit 11 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0														
0x077	R/W	NI_ENBL		INTERNAL							NI_OI	PTION					
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
Noise Immunity EN	[15]	Enable Noise Immunity	0 : disable, 1: enable. Recommended Value = 1	Set to "1"
Noise Immunity	[11:0]	Noise Immunity Option	Setting Options. Recommended Value = 1	
Option				Set to "1"

© 2010 IDT 12 Doc. No. 6108/6128RM, Rev.



Configuration Register Map and Description

						G	uard Ch	annel Ei	nable Re	gister [(C0-C13]						
Register Address	Direction														Bit 0		
0x07C	R/W	/W GUARD_CH[13:6]										Internal GUARD_CH[5:0]					
Default Values	0000h	0	0 0 0 0 0 0 0								0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
GUARD_CH[13]	[15]	channel 13 guard channel enable	0 : disable, 1: enable	
GUARD_CH[12]	[14]	channel 12 guard channel enable	0 : disable, 1: enable	
GUARD_CH[11]	[13]	channel 11 guard channel enable	0 : disable, 1: enable	
GUARD CH[10]	[12]	channel 10 guard channel enable	0 : disable, 1: enable	
GUARD CH[9]	[11]	channel 9 guard channel enable	0 : disable, 1: enable	
GUARD_CH[8]	[10]	channel 8 guard channel enable	0 : disable, 1: enable	
GUARD_CH[7]	[9]	channel 7 guard channel enable	0 : disable, 1: enable	
GUARD_CH[6]	[8]	channel 6 guard channel enable	0 : disable, 1: enable	
GUARD CH[5]	[5]	channel 5 guard channel enable	0 : disable, 1: enable	
GUARD_CH[4]	[4]	channel 4 guard channel enable	0 : disable, 1: enable	
GUARD_CH[3]	[3]	channel 3 guard channel enable	0 : disable, 1: enable	
GUARD CH[2]	[2]	channel 2 guard channel enable	0 : disable, 1: enable	
GUARD CH[1]	[1]	channel 1 guard channel enable	0 : disable, 1: enable	
GUARD_CH[0]	[0]	channel 0 guard channel enable	0 : disable, 1: enable	

		Guard Channel Enable Register [C13-C14]															
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x07D	R/W													GUARD_	CH[15:14]	Inte	rnal
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Register Name	Position	Description	Function	Remark
GUARD_CH[15]	[3]	channel 15 guard channel enable	0 : disable, 1: enable	
GUARD_CH[14]	[2]	channel 14 guard channel enable	0 : disable, 1: enable	

		Guard Channel Mask Register [C0-C13]																
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	
0x07E	R/W		GUARD MASK[13:6]								Internal GUARD_MASK[5:0]							
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	

Register Name	Position	Description	Function	Remark
GUARD_MASK[13]	[15]	channel 13 guard mask enable	0 : disable, 1: enable	
GUARD_MASK[12]	[14]	channel 12 guard mask enable	0 : disable, 1: enable	
GUARD_MASK[11]	[13]	channel 11 guard mask enable	0 : disable, 1: enable	
GUARD MASK[10]	[12]	channel 10 quard mask enable	0 : disable, 1: enable	
GUARD_MASK[9]	[11]	channel 9 guard mask enable	0 : disable, 1: enable	
GUARD_MASK[8]	[10]	channel 8 guard mask enable	0 : disable, 1: enable	
GUARD MASK[7]	[9]	channel 7 guard mask enable	0 : disable, 1: enable	
GUARD MASK[6]	[8]	channel 6 quard mask enable	0 : disable, 1: enable	
GUARD_MASK[5]	[5]	channel 5 guard mask enable	0 : disable, 1: enable	
GUARD_MASK[4]	[4]	channel 4 guard mask enable	0 : disable, 1: enable	
GUARD_MASK[3]	[3]	channel 3 guard mask enable	0 : disable, 1: enable	
GUARD_MASK[2]	[2]	channel 2 guard mask enable	0 : disable, 1: enable	
GUARD MASK[1]	[1]	channel 1 quard mask enable	0 : disable, 1: enable	
GUARD_MASK[0]	[0]	channel 0 guard mask enable	0 : disable, 1: enable	_

		Guard Channel Mask Register [C14-C15]															
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
0x07F	R/W	INTERNAL	INTERNAL	INTERNAL										GUARD_N	UARD_MSK[15:14]		rnal
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Re	egister Name	Position	Description	Function	Remark
GUA	ARD_MASK[15]	[3]	channel 15 guard mask enable	0 : disable, 1: enable	
GUA	ARD_MASK[14]	[2]	channel 14 guard mask enable	0 : disable, 1: enable	



Configuration Register Map and Description

							Ca	n Value	and SF	LC Value	Δ								
Register Address	Direction	Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	1 Bit 10 Bit 9 Bit 8 Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0												
0x080	R						Touch0 Cap												
0x081	R	Touch() SELP				Touch0 SELC												
0x084	R						Touch1 Cap												
0x085	R	Touch'	1 SELP								T	ouch1 SE	LC						
0x088	R											Touch2 Ca	ар						
0x089	R	Touch2	SELP								T	ouch2 SE	LC						
0x08C	R											Touch3 Ca	ар						
0x08D	R	Touch	3 SELP								Ţ	ouch3 SE	LC						
0x090	R											Touch4 Ca	ар						
0x091	R	Touch4	4 SELP								T	ouch4 SE	LC						
0x094	R											Touch5 Ca	ар						
0x095	R	Touch	SELP								T	ouch5 SE	LC						
0x0A0	R											Touch6 Ca	ар						
0x0A1	R	Touch	SELP								Ţ	ouch6 SE	LC						
0x0A4	R											Touch7 Ca	ар						
0x0A5	R	Touch	7 SELP								T	ouch7 SE	LC						
0x0A8	R											Touch8 Ca	ар						
0x0A9	R	Touch8	SELP								T	ouch8 SE	LC						
0x0AC	R											Touch9 Ca	ар						
0x0AD	R	Touch9	SELP								T	ouch9 SE	LC						
0x0B0	R										1	Touch10 C	Cap						
0x0B1	R	Touch1	0 SELP								To	ouch10 SE	LC						
0x0B4	R											Touch11 C	Сар						
0x0B5	R	Touch1	1 SELP								To	ouch11 SE	LC						
0x0B8	R											Fouch12 C							
0x0B9	R	Touch1	2 SELP								To	ouch12 SE	LC						
0x0BC	R											Fouch13 C							
0x0BD	R	Touch1	3 SELP				Touch13 SELC												
0x0C8	R						Touch14 Cap												
0x0C9	R	Touch1	4 SELP				Touch14 SELC												
0x0CC	R											Touch15 C	Сар						
0x0CD	R	Touch1	5 SELP				Touch15 SELC												
Default Values	0000h	0	0	0	0	0	0	0	0	0	0	0	0	0	0		0	0	





DISCLAIMER Integrated Device Technology, Inc. (IDT) and its subsidiaries reserve the right to modify the products and/or specifications described herein at any time and at IDT's sole discretion. All information in this document, including descriptions of product features and performance, is subject to change without notice. Performance speci fications and the operating parameters of the described products are determined in the independent state and are not guaranteed to perform the same way when installed in customer products. The information contained herein is provided without representation or warranty of any kind, whether express or implied, including, but not limited to, the suitability of IDT's products for any particular purpose, an implied warranty of merchantability, or non -infringement of the intellectual property rights of others. This document is presented only as a guide and does not convey any license under intellectual property rights of IDT or any third parties.

IDT's products are not intended for use in life support systems or similar devices where the failure or malfunction of an IDT product can be reasonably expected to significantly affect the health or safety of users. Anyone using an IDT product in such a manner does so at their own risk, absent an express, written agreement by IDT.

Integrated Device Technology, IDT and the IDT logo are registered trademarks of IDT. Other trademarks and service marks used herein, including protected names, logos and designs, are the property of IDT or their respective third party owners.



6024 Silver Creek Valley Road San Jose, California 95138 http://www.idt.com Document No: 6108/6128RM

Revision: 0.2 Date: 04/01/10