

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

SH7263/SH7203 Groups

10-Bit A/D Converter: Example of Settings for Conversion in Single Mode

Introduction

This application note describes an example of settings for A/D conversion on a single channel as an example of application of the 10-bit A/D converter of the SH7263 and SH7203 Groups.

Target Devices

SH7263/SH7203

Contents

1. Preface.....	2
2. Description of the Sample Application	3
3. Listing of Sample Program.....	8
4. Documents for Reference	11

1. Preface

1.1 Specifications

- A/D conversion on a single channel in single mode by the 10-bit A/D converter
- Three rounds of A/D conversion are performed on analog input channel 0 (AN0), and the converted data are stored in RAM.

1.2 Module Used

- 10-bit A/D converter (10-bit A/D)

1.3 Applicable Conditions

- MCU SH7263/SH7203
- Operating frequency Internal clock: 200 MHz
Bus clock: 66.67 MHz
Peripheral clock: 33.3 MHz
- C compiler SuperH RISC Engine Family C/C++ Compiler Package Ver.9.01
from Renesas Technology
- Compiler options -cpu = sh2afpu -fpu = single -include = "\${WORKSPDIR}\inc"
-object = "\${CONFIGDIR}\\${FILELEAF}.obj" -debug -gbr = auto -chgincpath
-errorpath -global_volatile = 0 -opt_range = all -infinite_loop = 0
-del_vacant_loop = 0 -struct_alloc = 1 -nologo

1.4 Related Application Note

None

2. Description of the Sample Application

The sample program employs the single mode of the 10-bit A/D converter to perform three rounds of A/D conversion on input channel 0 (AN0), and then stores converted data in RAM.

2.1 Operational Overview of Module Used

The 10-bit A/D converter has three operating modes: single mode, multi mode, and scan mode. In single mode, A/D conversion is performed on one channel.

Table 1 gives an overview of the module used in this sample application (i.e. the A/D converter) and figure 1 is a block diagram of the A/D converter. For details on the 10-bit A/D converter, see the section on A/D converter in the *SH7263/SH7203 Group Hardware Manual*.

Table 1 Overview of the Module (A/D converter) Used in the Sample Application

Item	Description
Resolution	10 bits
Minimum conversion time	3.9 μ s per channel (P ϕ = 33 MHz operation)
Number of modules	1
Input channels	8
Operating modes	Single mode Multi mode Scan mode
Sample-and-hold function	Common to all channels: 1 circuit
Sources for activation of A/D conversion	Software: Setting of the ADST bit Timer: TRGAN, TRG0N, TRG4AN, and TRG4BN signals from the MTU2 module External trigger: $\overline{\text{ADTRG}}$




Figure 1 Block Diagram of the 10-Bit A/D Converter

2.2 Procedure for Setting Module Used

Figure 2 shows an example of the initialization sequence for A/D conversion on a single channel. For details on the settings of individual registers, see the *SH7263/SH7203 Group Hardware Manual*.




Figure 2 Example of Initialization Sequence for 10-Bit A/D Conversion

General input pin functions, analog-input pin functions for the A/D converter, analog-output pin functions for the D/A converter (pins PA6 and PA7 only) are multiplexed on the general input pins for port A. These pin functions are changed automatically, so the pin function controller (PFC) does not have a register for settings to control them.

The general input function of the PA7 to PA0 pins is only enabled while the A/D and D/A converters are halted.

When port A data register L (PADRL) is read during operation of the A/D or D/A converter, values of bits corresponding to pins that are in use for conversion become undefined.

2.3 Operation of the Sample Program

In this sample program, A/D conversion in single mode is performed on channel 0. The A/D converter is activated by software, and converted data are stored in RAM. This processing is repeated three times.

Table 2 gives a description of RAM usage in this sample program.

Table 2 Variable Used in the Sample Program

Variable Name	Description	Area	Name of Employing Module
unsigned short AD_data[0-2]	Array for storing A/D-converted data (2 bytes/datum)	On-chip RAM	io_ad_single_scan (void)

2.4 Sequence of Processing by the Sample Program

Table 3 gives settings for a register used in the sample program and figure 3 shows the flow of handling the sample program.

Table 3 Settings for Register Used in the Sample Program

Register Name	Address	Setting	Description
A/D control status register (ADCSR)	H'FFFE5820	H'0000	ADIE = 0: Disables A/D conversion end interrupt ADST = 0: Halts A/D conversion TRGS[3:0] = B'0000: Disables starting of A/D conversion by external trigger CKS[1:0] = B'00: Operating clock = Pφ/4 MDS[2:0] = B'000: Single mode CH[2:0] = B'000: AN0
		H'2000	ADST = 1: Starts A/D conversion




Figure 3 Flow of Handling the Sample Program

3. Listing of Sample Program

1. Sample Program Listing: "main.c" (1)

```

1  /*"FILE COMMENT"*****
2  *
3  *      System Name : SH7203 Sample Program
4  *      File Name   : main.c
5  *      Contents    : Sample program for A/D conversion in single mode
6  *      Version     : 1.00.00
7  *      Model      : M3A-HS30
8  *      CPU        : SH7203
9  *      Compiler   : SHC9.1.1.0
10 *      note       : A/D conversion in single mode is performed by the A/D converter.
11 *                  Three rounds of A/D conversion on channel 0 (AN0) proceed,
12 *                  and the converted data are stored in RAM.
13 *
14 *      The information described here may contain technical inaccuracies or
15 *      typographical errors. Renesas Technology Corporation and Renesas Solutions
16 *      assume no responsibility for any damage, liability, or other loss rising
17 *      from these inaccuracies or errors.
18 *
19 *      Copyright (C) 2008 Renesas Technology Corp. All Rights Reserved
20 *      AND Renesas Solutions Corp. All Rights Reserved
21 *
22 *      history    : 2008.01.09 ver.1.00.00
23 *"FILE COMMENT END"*****/
24 #include <machine.h>
25 #include "iodefine.h" /* SH7203 iodefine */
26
27
28 /* ==== prototype declaration ==== */
29 void main(void);
30 void io_ad_init(void);
31 unsigned short io_ad_single_scan(void);
32
33 /* ==== symbol definition ==== */
34 #define AD_COUNT 3
35
36 /* ==== RAM allocation variable declaration ==== */
37 unsigned short Ad_data[AD_COUNT];
38

```

2. Sample Program Listing: "main.c" (2)

```

39  /*"FUNC COMMENT"*****
40  * Outline          : main
41  *-----
42  * Include          : #include "iodefine.h"
43  *                  : #include <machine.h>
44  *-----
45  * Declaration      : void main(void);
46  *-----
47  * Function         : main
48  *-----
49  * Argument         : void
50  *-----
51  * Return Value     : void
52  *-----
53  * Notice           : non
54  *"FUNC COMMENT END"*****/
55  void main(void)
56  {
57      unsigned char count;
58      count = 0;
59
60      /* ==== Setting of ADC ==== */
61      io_ad_init();
62
63      /* ==== A/D conversion ==== */
64      Ad_data[count] = io_ad_single_scan();
65      count++;
66      Ad_data[count] = io_ad_single_scan();
67      count++;
68      Ad_data[count] = io_ad_single_scan();
69
70      while(1){
71          /* loop */
72      }
73
74 }

```

3. Sample Program Listing: "main.c" (3)

```

75 /*"FUNC COMMENT"*****
76 * Outline      : Setting of ADC
77 * -----
78 * Include      : #include "iodefine.h"
79 * -----
80 * Declaration  : void io_ad_init(void);
81 * -----
82 * Function     : Setting of the A/D converter (ADC)
83 * -----
84 * Argument     : void
85 * -----
86 * Return Value : void
87 * -----
88 * Notice       : non
89 /*"FUNC COMMENT END"*****/
90 void io_ad_init(void)
91 {
92     /* ==== Release of power down mode(ADC) ==== */
93     CPG.STBCR3.BIT.MSTP32 = 0x00;
94
95     /* ==== Setting of ADC ==== */
96     /* ---- A/D Control/Status Register(ADCSR) ---- */
97     ADC.ADCSR.WORD = 0x0000;
98     /* 15 = b'0      : A/D End Flag */
99     /* 14 = b'0      : A/D end interrupt request (ADI) is disabled */
100    /* 13 = b'0      : A/D conversion is stopped */
101    /* 12 = b'0      : reserve */
102    /* 11-8 = b'0000  : Start of A/D conversion by
103                       external trigger input is disabled */
104    /* 7-6 = b'00     : clock = Pφ /4 */
105    /* 5-3 = b'000    : Single mode */
106    /* 2-0 = b'000    : Channel Select AN0 */
107 }
108 /*"FUNC COMMENT"*****
109 * Outline      : A/D conversion
110 * -----
111 * Include      : #include "iodefine.h"
112 * -----
113 * Declaration  : unsigned short io_ad_single_scan(void);
114 * -----
115 * Function     : Clearing of A/D end flag (ADF), and storing of conversion data to RAM
116 * -----
117 * Argument     : void
118 * -----
119 * Return Value: Value from the A/D Data Register A (ADDRA)
120 * -----
121 * Notice       : non
122 /*"FUNC COMMENT END"*****/
123 unsigned short io_ad_single_scan(void)
124 {
125     unsigned short ad_buf;
126
127     ADC.ADCSR.BIT.ADST = 1;          /* A/D conversion start */
128
129     while(ADC.ADCSR.BIT.ADF == 0){  /* A/D conversion completion waiting */
130     }
131
132     ADC.ADCSR.BIT.ADF = 0;          /* ADF clear */
133     ad_buf = ADC.ADDRA.WORD;
134
135     return(ad_buf);
136 }
137
138 /* End of File */

```

4. Documents for Reference

- Software Manual
SH-2A/SH2A-FPU Software Manual
The most up-to-date version of this document is available on the Renesas Technology Website.
- Hardware Manual
SH7203 Group Hardware Manual
SH7263 Group Hardware Manual
The most up-to-date versions of the documents are available on the Renesas Technology Website.

Website and Support

Renesas Technology Website

<http://www.renesas.com/>

Inquiries

<http://www.renesas.com/inquiry>

csc@renesas.com

Revision Record

Rev.	Date	Description	
		Page	Summary
1.00	May.20.08	—	First edition issued
1.01	Dec.17.08	8 to 10	Source file is updated

All trademarks and registered trademarks are the property of their respective owners.

Notes regarding these materials

1. This document is provided for reference purposes only so that Renesas customers may select the appropriate Renesas products for their use. Renesas neither makes warranties or representations with respect to the accuracy or completeness of the information contained in this document nor grants any license to any intellectual property rights or any other rights of Renesas or any third party with respect to the information in this document.
2. Renesas shall have no liability for damages or infringement of any intellectual property or other rights arising out of the use of any information in this document, including, but not limited to, product data, diagrams, charts, programs, algorithms, and application circuit examples.
3. You should not use the products or the technology described in this document for the purpose of military applications such as the development of weapons of mass destruction or for the purpose of any other military use. When exporting the products or technology described herein, you should follow the applicable export control laws and regulations, and procedures required by such laws and regulations.
4. All information included in this document such as product data, diagrams, charts, programs, algorithms, and application circuit examples, is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas products listed in this document, please confirm the latest product information with a Renesas sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas such as that disclosed through our website. (<http://www.renesas.com>)
5. Renesas has used reasonable care in compiling the information included in this document, but Renesas assumes no liability whatsoever for any damages incurred as a result of errors or omissions in the information included in this document.
6. When using or otherwise relying on the information in this document, you should evaluate the information in light of the total system before deciding about the applicability of such information to the intended application. Renesas makes no representations, warranties or guaranties regarding the suitability of its products for any particular application and specifically disclaims any liability arising out of the application and use of the information in this document or Renesas products.
7. With the exception of products specified by Renesas as suitable for automobile applications, Renesas products are not designed, manufactured or tested for applications or otherwise in systems the failure or malfunction of which may cause a direct threat to human life or create a risk of human injury or which require especially high quality and reliability such as safety systems, or equipment or systems for transportation and traffic, healthcare, combustion control, aerospace and aeronautics, nuclear power, or undersea communication transmission. If you are considering the use of our products for such purposes, please contact a Renesas sales office beforehand. Renesas shall have no liability for damages arising out of the uses set forth above.
8. Notwithstanding the preceding paragraph, you should not use Renesas products for the purposes listed below:
 - (1) artificial life support devices or systems
 - (2) surgical implantations
 - (3) healthcare intervention (e.g., excision, administration of medication, etc.)
 - (4) any other purposes that pose a direct threat to human life
 Renesas shall have no liability for damages arising out of the uses set forth in the above and purchasers who elect to use Renesas products in any of the foregoing applications shall indemnify and hold harmless Renesas Technology Corp., its affiliated companies and their officers, directors, and employees against any and all damages arising out of such applications.
9. You should use the products described herein within the range specified by Renesas, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas shall have no liability for malfunctions or damages arising out of the use of Renesas products beyond such specified ranges.
10. Although Renesas endeavors to improve the quality and reliability of its products, IC products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Please be sure to implement safety measures to guard against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other applicable measures. Among others, since the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
11. In case Renesas products listed in this document are detached from the products to which the Renesas products are attached or affixed, the risk of accident such as swallowing by infants and small children is very high. You should implement safety measures so that Renesas products may not be easily detached from your products. Renesas shall have no liability for damages arising out of such detachment.
12. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written approval from Renesas.
13. Please contact a Renesas sales office if you have any questions regarding the information contained in this document, Renesas semiconductor products, or if you have any other inquiries.