

## 8-Channel LED Driver for LCD Panel Backlighting

### 1.0 Features

- Fully integrated power FET with minimum external components
- Patented BroadLED™ adaptive switch mode technology for high current matching at maximum efficiency.
  - » Current matching accuracy  $\pm 2\%$
  - » Enables use of cheaper, loosely binned LED arrays for lower BOM cost
- 8-channel output each at 65V with 9V to 28V input supply voltage range
- Serial Peripheral Interface (SPI) compatible for high bandwidth PWM-based dynamic local dimming
- LED failure (open and short-circuit) detection
- Supports  $V_{\text{SYNC}}$  range 50-480Hz
- Integrated DC-DC boost controller
  - » 10V gate drive voltage
  - » Programmable switching frequency from 100KHz to 200KHz.
  - » Internal soft start to limit the in-rush current
- PWM dimming range from 0% to 99.9% with 12-bit resolution
- PLL locked  $V_{\text{SYNC}}$  and synchronized PWM
- Supports one-pin global direct PWM with phase shift
- Comprehensive protection features
  - » LED open fault detection
  - » Single-pin, resistor programmable LED short level (3V/6V/9V/12V) fault detection
  - » Over-temperature shutdown
  - » Boost controller output OCP, OVP and UV protection
  - » Boost input UVLO (Hys.=110mV) protection
- QFP44 supports 230mA/channel and SOP32 supports 175mA/channel within 50 degree temperature rise on Dialog EVB.
- Packages include: QFP44 with 10mm x 10mm body at 0.8mm pitch, SOP32 with 10.4mm x 20.74mm at 1.27mm pitch
- Pin-out optimized for single-layer PCB layout
- Green & Pb-free (RoHS compliant) BOM

### 2.0 Description

The iW7019 is a high efficiency driver for LEDs. It fully integrates one internal step-up PWM DC-DC converter to drive up to 8 separate strings of multiple series-connected LEDs.

Users can provide versatile configurations of the iW7019 through SPI interface registers.

The iW7019 can maintain very high efficiency even with the existence of LED channel total forward voltage mismatch, with the proprietary digital power management and patent pending adaptive switch (BroadLED™) mode LED current regulation technology.

The iW7019 has multiple features to protect the LED channels from fault conditions, and these protections are LED PWM cycle-by-cycle based to ensure system reliability and provide consistent operation.

### 3.0 Applications

- Direct & segment-edge LED backlit LCD TV
- Edge type global dimming LED backlit LCD TV

## 8-Channel LED Driver for LCD Panel Backlighting




Figure 3.1 : iW7019 Application Diagram

## 8-Channel LED Driver for LCD Panel Backlighting

### 4.0 Pinout Description




Figure 3.2 : Pin Configuration for TQFP44 Package




Figure 3.3 : Pin Configuration for SOP32 Package

## 8-Channel LED Driver for LCD Panel Backlighting

### Pinout Description (continued)

Pin # QFP44	Pin # SOP32	Name	Type	Pin Description
1	X	NC		
2	14	LED6	Analog Output	LED cathode connection for string 6
3	XX	NC		
4	15	LED7	Analog Output	LED cathode connection for string 7
5	17	LEDGND	Ground	Ground for LED driver
6	17	LEDGND	Ground	Ground for LED driver
7	16	LED8	Analog Output	LED cathode connection for string 8
8	X	NC		
9	18	VFB	Analog In	Boost controller feedback pin (settled value is 1.2V)
10	19	DPGND	Digital Ground	Digital Ground and Boost Pre-Driver's ground
11	20	CS	Analog In/Out	Boost pre-driver sense input
12	21	GDRV	Analog Out	Boost gate drive for external MOSFET
13	22	VCOMP	Analog In	Boost controller loop compensation
14	23	RT	Analog In	Programmable boost switching frequency (100K/150K/200K)
15	24	UVLO	Analog In	Boost UVLO comparator input. Voltage level is greater than 1.2V for a healthy boost VIN. Customer has to put resistor divider on
16	25	LDO5_A	Analog Output	Internal LDO output and analog power section supply.
17	17	LEDGND	Ground	Ground for LED driver
18	17	LEDGND	Ground	Ground for LED driver
19	26	LDO5_D	Analog Output	Internal LDO output and digital power section supply.
20	27	RLS	Analog Input	Short Level Threshold voltage setting(3/6/9V/12V, with default at 6V), using different resistor selection.
21	28	VIN	Supply Input	Input voltage to the main supply rail.
22	29	CSB	Digital Input	Slave select input for SPI (Chip Select Bar). Active LOW. Logic high is defined as 5.0V
23	30	SCK	Digital Input	SCK, serial clock input for Serial Peripheral Interface (SPI). Logic high is defined as 5.0V.
24	31	FAULTB	Analog Output	Fault status (Active Low) - Open drain. Pull-up to LDO5A with a 100KOhm +5% resistor.
25	32	EN	Digital Input	Enable Input. Logic high is defined as 5.0V.
26	1	VSYNC/PWM	Digital Input	Vertical SYNC input. [optional direct PWM control] logic high is defined as 5.0V.
27	2	VREF2P5	Analog Output	Analog reference for Analog Dimming.

## 8-Channel LED Driver for LCD Panel Backlighting

### Pinout Description (continued)

Pin # QFP44	Pin # SOP32	Name	Type	Pin Description
28	17	LEDGND	Ground	Ground for LED driver
29	17	LEDGND	Ground	Ground for LED driver
30	3	MOSI	Digital Input	Master output, slave input for SPI.
31	4	MISO	Digital 3 Stat Output	Master input, slave output for SPI. Logic high is defined as 3.3V.
32	5	ADIM/ISET	Analog In	Dedicate Current setting / Analog dimming input
33	6	CPLL	Analog In/Out	PLL compensation output / External Clock In
34	7	AVSS	Ground	Quiet analog ground.
35	8	UNUSE	Analog Input	Set unused channel number.
36	9	LED1	Analog Output	LED cathode connection for string 1
37	10	LED2	Analog Output	LED cathode connection for string 2
38	17	LEDGND	Ground	Ground for LED driver
39	17	LEDGND	Ground	Ground for LED driver
40	11	LED3	Analog Output	LED cathode connection for string 3
41	X	NC		
42	12	LED4	Analog Output	LED cathode connection for string 4
43	X	NC		
44	13	LED5	Analog Output	LED cathode connection for string 5
		EXPGND	Ground	Exposed PAD for LED driver

## 8-Channel LED Driver for LCD Panel Backlighting

### 5.0 Absolute Maximum Ratings

Absolute maximum ratings are the parameter values or ranges which can cause permanent damage if exceeded.

Parameter	Symbol	Value	Units
$V_{IN}$ supply voltage	$V_{IN}$	-0.3 to 40	V
LDO5 output voltage	$V_{LDO5}$	-0.3 to 7	V
AGND / AVSS / GNDn to GND		-0.3 to 0.3	V
LEDn voltage	$V_{LEDn}$	-0.3 to 65	V
Logic I/O pins (SCK, MISO, MOSI, CSB, & VSYNC)		-0.3 to 7	V
Voltage on all other pins except for LEDn pins		-0.3 to 7	V
Power dissipation at $T_A \leq 25^\circ\text{C}$	$P_D$	TBD	mW
Maximum operating junction temperature	$T_{JMAX}$	-40 to 150	$^\circ\text{C}$
Storage temperature	$T_{STG}$	-40 to 150	$^\circ\text{C}$
Lead temperature during IR reflow for $\leq 15$ seconds	$T_{LEAD}$	270	$^\circ\text{C}$
Latch-up current		>100	mA
ESD rating per JEDEC JESD22-A114 - HBM		$\pm 2,000$	V

### 6.0 Recommended Operating Conditions

Parameter	Min	Typ	Max	Units
$V_{IN}$ supply voltage ( $V_{IN}$ )	9		28	V
LEDn voltage	0.5		65	V
Thermal Resistance Junction ( $\theta_{JA}$ ): SOP32		69.2		$^\circ\text{C/W}$
Thermal Resistance Junction ( $\theta_{JA}$ ): TQFP44		41.5		$^\circ\text{C/W}$
Junction Temperature ( $T_J$ )	-40		150	$^\circ\text{C}$
Operate Temperature ( $C_{operate}$ )	-40		85	$^\circ\text{C}$

## 8-Channel LED Driver for LCD Panel Backlighting

### 7.0 Physical Dimensions





Figure 7.1 : Physical Dimensions, TQFP-44 Package

## 8-Channel LED Driver for LCD Panel Backlighting



This product is RoHS compliant and Halide free. Package is IPC/JEDEC Std 020D Moisture Sensitivity Level 3

Figure 7.2 : Physical Dimensions, SOP-32 Package.

## 8.0 Ordering Information

Part Number	Package	Description
iW7019-00-TQ2E	TQFPEP-10mm-44L	Tape & Reel <sup>1</sup>
iW7019-00-SO32	SOP300-32	Tape & Reel <sup>2</sup>

Note 1: Tape & Reel packing quantity is 1,250/reel. Minimum ordering quantity is 1,250.

Note 2: Tape & Reel packing quantity is 1,000/reel. Minimum ordering quantity is 1,000.



## 8-Channel LED Driver for LCD Panel Backlighting

### IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

© 2022 Renesas Electronics Corporation. All rights reserved.

### RoHS Compliance

Dialog Semiconductor's suppliers certify that its products are in compliance with the requirements of Directive 2011/65/EU of the European Parliament on the restriction of the use of certain hazardous substances in electrical and electronic equipment. RoHS certificates from our suppliers are available on request.

(Rev.1.0 Mar 2020)

### Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu  
Koto-ku, Tokyo 135-0061, Japan  
[www.renesas.com](http://www.renesas.com)

### Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:  
[www.renesas.com/contact/](http://www.renesas.com/contact/)

### Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.