Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.



REJ19B0769-0100

RENESAS TECHNOLOGY SINGLE-CHIP 16-BIT MICROCOMPUTER M30623MA-XXXGP MASK ROM CONFIRMATION FORM

Mask ROM number	
-----------------	--

	Date :	
t	Section head signature	Supervisor signature
Receipt		<u> </u>

Note: Please complete all items marked %.

*	Customer	Company	Company name TEL (TFI				Submitted by	Supervisor
				()	uC.	ature		
		Date issued	Date :			Issua	_		

% 1. Check sheet

Name the product you order, and choose which to give in, EPROMs or floppy disks. If you order by means of EPROMs, three sets of EPROMs are required per pattern. If you order by means of floppy disks, one floppy disk is required per pattern.

☐ In the case of EPROMs

Renesas will create the mask using the data on the EPROMs supplied, providing the data is the same on at least two of those sets. Renesas will, therefore, only accept liability if there is any discrepancy between the data on the EPROM sets and the ROM data written to the product. Please carefully check the data on the EPROMs being submitted to Renesas.

Microcomputer type No. :

M30623MA-XXXGP

Checksum code for total EPROM area : (hex)

EPROM type:

☐ 27C201	□ 27C401
Address 0000016 Product : Area containing ASCI 0000106 code for M30823WA 000106 27FFF18 2800018 RØM(96K)	Address 0000016 Product : Area containing A\$CU 0000F16 0001016 67FFF16 6800018 ROM(66K)

- (1) Write "FF16" to the lined area.
- (2) The area from 0000016 to 0000F16 is for storing data on the product type name.

The ASCII code for 'M30623MA-' is shown at right. The data in this table must be written to address 0000016 to 0000F16.

Both address and data are shown in hex.

Address		
0000016	'M '	$=4D_{16}$
0000116	'3'	= 3316
0000216	'0'	= 3016
0000316	'6'	= 3616
0000416	'2'	= 3216
0000516	'3'	= 3316
0000616	'M '	= 4D ₁₆
0000716	'A'	= 4116

Address		
0000816	'—'	= 2D ₁₆
0000916		FF ₁₆
0000A ₁₆		FF ₁₆
0000B ₁₆		FF ₁₆
0000C ₁₆		FF ₁₆
0000D ₁₆		FF ₁₆
0000E ₁₆		FF ₁₆
0000F ₁₆		FF ₁₆



REJ19B0769-0100

RENESAS TECHNOLOGY SINGLE-CHIP 16-BIT MICROCOMPUTER M30623MA-XXXGP MASK ROM CONFIRMATION FORM

Mask ROM number	

The ASCII code for the type No. can be written to EPROM addresses 0000016 to 0000F16 by specifying the pseudo-instructions for the respective EPROM type shown in the following table at the beginning of the assembler source program.

EDDOM type	27C201	27C401
EPROM type		
Code entered in source program	\triangle .SECTION \triangle ASCIICODE, ROM \triangle .ORG \triangle 0C0000H \triangle .BYTE \triangle ' M30623MA- '	M DATA \triangle .SECTION \triangle ASCIICODE, ROM DATA \triangle .ORG \triangle 080000H \triangle .BYTE \triangle ' M30623MA- '
Note: The ROM c in the check		written to the EPROM does not match the type No.
\Box In the case	of floppy disks	
the floppy disks there is any dis products we pr	s you give in to us, and forms them is crepancy between the contents of the oduce. Check thoroughly the contents	ne mask file generation utilities out of those held on into masks. Hence, we assume liability provided that hese mask files and the ROM data to be burned into ints of the mask files you give in. And store only one mask file in a floppy disk.
Microcompu	ter type No. : M30623MA	4-XXXGP
File code :		(hex)
Mask file na	me :	.MSK (alpha-numeric 8-digit)
the separate material for submission	fication differs according to the type ark specification sheet (for each pac	of package. After entering the mark specification on ckage), attach that sheet to this masking check sheet rk specification sheet.
[፠] 3. Usage Conditi	ons	
For our referen the products yo		ase reply to the following questions about the usage o
(1) Which k	ind of XIN-XOUT oscillation circuit is	used?
	Ceramic resonator ☐ Quartze	-crystal oscillator
	external clock input	(
What fre	equency do you use?	



MHz

f(XIN) =

REJ19B0769-0100

RENESAS TECHNOLOGY SINGLE-CHIP 16-BIT MICROCOMPUTER M30623MA-XXXGP MASK ROM CONFIRMATION FORM

Mask ROM number	
Mask ROM number	

(2)	Which kind of XCIN-XCOUT oscilla	ition circuit is used?	
	☐ Ceramic resonator	☐ Quartz-crystal oscillator	
	☐ External clock input	□ Other ()	
	What frequency do you use?		
	f(XCIN) = kHz		
(3)	Which operation mode do you us	se?	
	\square Single-chip mode	☐ Memory expansion mode	Э
	☐ Microprocessor mode		
(4)	Which operating ambient temperating	ature do you use?	
	□-10 °C to 75 °C	\square –20 °C to 75 °C	\square –40 °C to 75 °C
	☐ –10 °C to 85 °C	□–20 °C to 85 °C	☐ –40 °C to 85 °C
(5)	Which operating supply voltage of	do you use?	
	☐ 2.7V to 3.2V	☐ 3.2V to 3.7V	☐ 3.7V to 4.2V
	☐ 4.2V to 4.7V	☐ 4.7V to 5.2V	☐ 5.2V to 5.5V
Thank	you cooperation.		
	al item (Indicate none if there is n	o specified item)	

