

## DA29020 Glow Plug Controller

---

### Description

The DA29020 is a 5-channel driver for external high-side switches with integrated charge-pump. It is intended for PWM operation controlled by an external  $\mu\text{C}$ . The SPI interface provides a variety of configuration options to optimize EMC performance. The built in 10-Bit ADC allows for measurements of channel currents, various interface voltages and the die temperature. The integrated programmable short-circuit protection, over- and under-voltage detection and overtemperature shutdown protect the chip and the load. Operation in harsh environments including ground-shift, ground-loss, strong supply-transients, polarity reversal and a wiring-harness with significant inductance is supported. A programmable high-voltage control-input and a high-voltage diagnosis-output provide connection to the environment. Low-power sleep mode and different selectable wake-up mechanisms help to reduce the system level power consumption.

### Features

- Integrated reverse battery protection
- AEC-Q100 grade 1 qualification
- 10-Bit ADC
- Typ. 14V supply, 30V max
- Over/under voltage detection
- Overtemperature protection
- Integrated gate driver with charge pump
- LDO and SPI interface to external controller
- Integrated gate driver with charge pump
- TQFP48 package with exposed pad


## Benefits

- Diagnosis interface
- Glow plug current measurement with total accuracy 3.5%
- Integrated short circuit protection
- Digital measurement of T<sub>j</sub>

## Applications

- Adaptive glow plug control system for diesel engines
- PTC heater control

## Block Diagram



Rev.5.0-1 October 2020

### Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,  
Koto-ku, Tokyo 135-0061, Japan  
[www.renesas.com](http://www.renesas.com)

### Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

### Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:  
[www.renesas.com/contact/](http://www.renesas.com/contact/).