

RC19024_DVC_REVA


NQQ100





Renesas
6024 Silver Creek Valley Rd.
San Jose, CA 95138


Title:
RC19024_DVC_REVA

Size B	Part Number: <Doc>	Engineer: Lou	Rev. 0.4
	Date: Thursday, August 13, 2020	Sheet: 1 of 7	










Title		
<Title>		
Size	Document Number	Rev
A	SIDE BAND INTERFACE	<RevCode>
Date:	Thursday, August 13, 2020	Sheet 7 of 7



Manufacture	Part Number	Z@100MHz	PkgSz	DC res.	Current(Ma)
muRata	BLM21A601R	600	0805	0.30	600
TDK	MMZ2012S601A	600	0805	0.30	600
STEWART	HZ0805E601R	600	0805	0.30	600
AssocCmpTch	CBG0805-600-50	600	0805	0.30	600

TARGET	VOUT	R75	R77 TYPICAL
1.5 V	4.22 k0	16.9 k0	1.5 V
1.8 V	0.5 k0	21.0 k0	1.8 V
2.0 V	10.0 k0	15.0 k0	2.0 V
2.5 V	6.2 k0	15.0 k0	2.496 V
3.0 V	21.0 k0	14.0 k0	3.0 V
3.3 V	23.2 k0	13.3 k0	3.293 V

Manufacture	Part Number	Z@100MHz	PkgSz	DC res.	Current(Ma)
muRata	BLM21A601R	600	0805	0.30	600
TDK	MMZ2012S601A	600	0805	0.30	600
STEWART	HZ0805E601R	600	0805	0.30	600
AssocCmpTch	CBG0805-600-50	600	0805	0.30	600