

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

H8/38076R

Transition to the Sleep (Medium-Speed) Mode

Introduction

In this example a transition is made from the active (high-speed) mode to the sleep (medium-speed) mode, one of the power-down modes of the H8/38076R.

Target Device

H8/38076R

Contents

1. Specifications	2
2. Description of Functions	2
3. Principles of Operation.....	4
4. Internal Registers Used	5

1. Specifications

After a reset is cleared the H8/38076R can transition to any of seven power-down modes, in which power consumption is reduced substantially, in addition to the normal active (high-speed) mode. In this sample task a transition is made from the active (high-speed) mode to the sleep (medium-speed) mode, one of the power-down modes.

2. Description of Functions

2.1 Functions Used

In this sample task a transition is made from the active (high-speed) mode to the sleep (medium-speed) mode, one of the power-down modes.

The state of the H8/38076R in the sleep (medium-speed) mode is shown in table 1, and the functions used as described below.

1. System Clock (ϕ)

This 10-MHz oscillation clock is a reference clock for operation of the CPU and peripheral functions.

2. Subclock (ϕ_w)

This 32.768-kHz oscillation clock is a reference clock for operation of the CPU and peripheral functions.

3. Power-Down Mode (Sleep (Medium-Speed) Mode) Function

In the sleep (medium-speed) mode CPU operation is halted, but the system clock oscillator, subclock oscillator, and internal peripheral modules continue to function. In the sleep (medium-speed) mode the internal peripheral modules function at the clock frequency set by the MA1 and MA0 bits in SYSCR1. CPU register contents are retained.

The sleep (medium-speed) mode is cleared by an interrupt. When an interrupt is requested, the sleep mode is cleared and interrupt exception handling starts. The sleep mode is not cleared if the I bit in CCR is set to 1 or the requested interrupt is disabled by an interrupt enable bit. After the sleep mode is cleared a transition is made from the sleep (medium-speed) mode to the active (medium-speed) mode. If the $\overline{\text{RES}}$ signal goes low in the sleep (medium-speed) mode, the H8/38076R enters the reset state and the sleep (medium-speed) mode is cleared. Since interrupt request signals are synchronous with the system clock, a maximum delay of $2/\phi$ (s) may occur from the point at which an interrupt request signal occurs until interrupt exception handling starts.

Furthermore, it sometimes operates with half state early timing at the time of transition to the sleep (medium-speed) mode.

- System control register 1 (SYSCR1)

Together with SYSCR2, SYSCR1 controls the power-down modes.

- System control register 2 (SYSCR2)

Together with SYSCR1, SYSCR2 controls the power-down modes.

Table 1 State of the H8/38076R in the Sleep (Medium-Speed) Mode

Function	Sleep (Medium-Speed) Mode	
System clock oscillator		Functioning
Subclock oscillator		Functioning
CPU	Instructions	Halted
	RAM	Retained
	Registers	Retained
	I/O	Retained
External interrupts	IRQ0	Functioning
	IRQ1	Functioning
	IRQ3	Functioning
	IRQ4	Functioning
	IRQAEC	Functioning
	WKP0 to WKP7	Functioning
Peripheral modules	Timer F	Functioning
	Asynchronous event counter	Functioning
	RTC (realtime clock)	Functioning
	TPU (timer pulse unit)	Functioning
	WDT (watchdog timer)	Functioning
	SCI3/IrDA module	Functioning
	I ² C2 module	Functioning
	PWM module	Functioning
	A/D converter	Functioning
	LCD controller/driver	Functioning

2.2 Assignment of Functions

Table 2 shows the assignment of functions in this sample task. A transition is made from the active (high-speed) mode to the sleep (medium-speed) mode, one of the power-down modes, using functions assigned as shown in table 2.

Table 2 Assignment of Functions

Elements	Description
SYSCR1	Together with SYSCR2, controls transition to the sleep (medium-speed) mode
SYSCR2	Together with SYSCR1, controls transition to the sleep (medium-speed) mode

3. Principles of Operation

The principles of operation of this sample task are described below. Using the procedure shown, a transition is made from the active (high-speed) mode to the sleep (medium-speed) mode, one of the power-down modes. The mode transitions in this sample task are illustrated in figure 1.

1. Transition to the sleep (medium-speed) mode
 - a. Clear the SSBY and LSON bits in SYSCR1 to 0.
 - b. Clear the DTON bit to 0 and set the MSON bit to 1 in SYSCR2.
 - c. Execute the SLEEP instruction.
2. Clearing the sleep (medium-speed) mode
 - a. Receive an interrupt request in the sleep (medium-speed) mode.
 - b. Perform interrupt handling. (The recovery destination of the interrupt will be the active (medium-speed) mode.)




Figure 1 Mode Transition Diagram

4. Internal Registers Used

The internal registers used in this sample task are shown below. The set values shown are those used in the sample task and differ from the initial values.

- SYSCR1 System control register 1 Address: H'FFF0

Bit	Bit Name	Set Value	R/W	Description
7	SSBY	0	R/W	Software standby Selects the mode to transition to after execution of the SLEEP instruction. 0: A transition is made to the sleep mode or the subsleep mode. 1: A transition is made to the standby mode or the watch mode.
3	LSON	0	R/W	Selects the system clock (ϕ) or subclock (ϕ_{SUB}) as the CPU operating clock when the watch mode is cleared. 0: The CPU operates on the system clock (ϕ) 1: The CPU operates on the subclock (ϕ_{SUB})
1	MA1	User defined	R/W	Active mode clock selection 1 and 0
0	MA0	User defined	R/W	Selects the operating clock frequency in the active (medium-speed) mode and the sleep (medium-speed) mode. The MA1 and MA0 bits should be written to in the active (high-speed) mode or the subactive mode. 00: $\phi_{OSC}/8$ 01: $\phi_{OSC}/16$ 10: $\phi_{OSC}/32$ 11: $\phi_{OSC}/64$

- SYSCR2 System control register 2 Address: H'FFF1

Bit	Bit Name	Set Value	R/W	Description
3	DTON	0	R/W	Direct transfer on flag Selects the mode to transition to after the SLEEP instruction is executed with bits SSBY, TMA3, and LSON in SYSCR1 and bit MSON in SYSCR2.
2	MSON	1	R/W	Medium speed on flag Selects whether operation continues in the active (high-speed) or the active (medium-speed) mode after the standby mode, the watch mode, or the sleep mode is cleared. 0: Active (high-speed) mode 1: Active (medium-speed) mode

Revision Record

Rev.	Date	Description	
		Page	Summary
1.00	Mar.18.05	—	First edition issued

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.
 Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
 The information described here may contain technical inaccuracies or typographical errors.
 Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
 Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
 Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.