

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

---

## SH7000 Series

### Remainder of 32 Bit ÷ 32 Bit (Unsigned)

---

**Label:** DIVU32R

**Functions Used:** DIV0U Instruction  
DIV1 Instruction

---

#### Contents

1. Function .....	2
2. Arguments.....	2
3. Internal Register Changes and Flag Changes.....	3
4. Programming Specifications .....	4
5. Notes .....	4
6. Description .....	5
7. Flowchart.....	9
8. Program Listing .....	10

## 1. Function

Divides the dividend (unsigned 32 bits) by the divisor (unsigned 32 bits), and determines the remainder (unsigned 32 bits). Also indicates errors (division by 0) in the T bit.

## 2. Arguments

Description	Storage Location	Data Length (Bytes)
Input	Dividend (unsigned 32 bits)	R1
	Divisor (unsigned 32 bits)	R0
Output	Remainder (unsigned 32 bits)	R2
	Error (division by 0) generated/not generated (generated: T = 1, not generated: T = 0)	T bit (SR)

**3. Internal Register Changes and Flag Changes**

	(Before Execution) → (After Execution)
R0	Divisor (unsigned 32 bits) → No change
R1	Dividend (unsigned 32 bits) → Change
R2	Undefined → Remainder (unsigned 32 bits)
R3	
R4	
R5	
R6	
R7	
R8	
R9	
R10	
R11	
R12	
R13	
R14	
R15	(SP)

- T bit  \* — : No change  
 \* : Change  
 0 : Fixed 0  
 1 : Fixed 1

#### 4. Programming Specifications

Program memory (bytes)	148
Data memory (bytes)	0
Stack (bytes)	0
Number of states	74
Reentrant	Yes
Relocation	Yes
Intermediate interrupt	Yes

#### 5. Notes

The number of states indicated in the programming specifications is the value when  $H'FFFFFFF \div H'FFFFFFE$  is calculated.

## 6. Description

### (1) Function

Details of the arguments are as follows.

R0: Set the divisor (unsigned 32 bits) as the input argument.

R1: Set the dividend (unsigned 32 bits) as the input argument.

R2: Holds the remainder (unsigned 32 bits) as the output argument.

T bit (SR): Indicates whether an error (division by 0) has occurred.

T bit = 1: Indicates an error (division by 0) has occurred.

T bit = 0: Indicates no error (division by 0) has occurred.

Figure 1 shows a software DIVU32R execution example.




Figure 1 Software DIVU32R Execution Example

### (2) Usage Notes

The value of R1, which is set to the dividend, is changed when software instruction DIVU32R is executed. If the value for the dividend will be needed after the software DIVU32R instruction is executed, it should be saved beforehand.

### (3) RAM Used

No RAM is used by the software DIVU32R instruction.

### (4) Usage Example


After the dividend and divisor are set in the input arguments, the software instruction DIVU32R is executed by a subroutine call.

```

MOV.L DATA1,R1    ... Sets dividend (unsigned 32 bits) in input argument (R1)
BSR   DIVU32R      ... Subroutine call to software instruction DIVU32R
MOV.L DATA2,R0    ... Sets divisor (unsigned 32 bits) in input argument (R0)
BT    ERROR        ... Branches to error processing subroutine if error (division by 0) occurs
      .
      .
      .
.align 4
DATA1 .data.l H'FFFFFFFF
DATA2 .data.l H'FFFFFFFE
    
```

### (5) Operating Principle

- (a) Before division, the following initial settings are carried out.
  - (i) R2 is used for the upper 32 bits to zero-extend the dividend to 64 bits.  
(Figure 2-(1))
  - (ii) The M, Q, and T bits used in one-step division are set to division values.  
(Figure 2-(2))



**Figure 2 Initial Settings**

(b) As shown in figure 3, the division operation is repeated through the number of divisor bits (32 times) using the ROTCL and DIV1 instructions.




Figure 3 Division

(c) As shown in figure 4, the way of determining the remainder differs depending on the value of the T bit (quotient of 32nd one-step division) at the end of division.





Figure 4 Remainder

7. Flowchart



## 8. Program Listing

```

1          1          ;*****
2          2          ;*
3          3          ;*      NAME ; RESIDUAL OF 32 BIT UNSIGNED DIVISION (DIVU32R) *
4          4          ;*
5          5          ;*****
6          6          ;*
7          7          ;*      ENTRY : R1 (DIVIDEND)
8          8          ;*      R0 (DIVISOR)
9          9          ;*      RETURNS : R2 (RESIDUAL)
10         10         ;*      T BIT (ERROR -> TRUE;T=1,FALSE;T=0
11         11         ;*
12         12         ;*****
13 00001000      13         .SECTION A, CODE, LOCATE=H'1000
14          14         DIVU32R .EQU      $          ; Entry point
15 00001000 2008      15         TST      R0,R0      ; Divisor = 0 ?
16 00001002 8945      16         BT       DIVU32R2    ; Yes
17 00001004 222A      17         XOR     R2,R2      ; R2 <- H'00000000
18 00001006 0019      18         DIVOU    ; Divide as unsigned
19          19         ;
20 00001008 4124      20         ROTCL   R1          ; Divide 1 step
21 0000100A 3204      21         DIV1    R0,R2      ;
22 0000100C 4124      22         ROTCL   R1          ;
23 0000100E 3204      23         DIV1    R0,R2      ;
24 00001010 4124      24         ROTCL   R1          ;
25 00001012 3204      25         DIV1    R0,R2      ;
26 00001014 4124      26         ROTCL   R1          ;
27 00001016 3204      27         DIV1    R0,R2      ;
28 00001018 4124      28         ROTCL   R1          ;
29 0000101A 3204      29         DIV1    R0,R2      ;
30 0000101C 4124      30         ROTCL   R1          ;
31 0000101E 3204      31         DIV1    R0,R2      ;
32 00001020 4124      32         ROTCL   R1          ;
33 00001022 3204      33         DIV1    R0,R2      ;
34 00001024 4124      34         ROTCL   R1          ;
35 00001026 3204      35         DIV1    R0,R2      ;
36          36         ;
37 00001028 4124      37         ROTCL   R1          ;
38 0000102A 3204      38         DIV1    R0,R2      ;
39 0000102C 4124      39         ROTCL   R1          ;
40 0000102E 3204      40         DIV1    R0,R2      ;
41 00001030 4124      41         ROTCL   R1          ;
42 00001032 3204      42         DIV1    R0,R2      ;
43 00001034 4124      43         ROTCL   R1          ;
44 00001036 3204      44         DIV1    R0,R2      ;
45 00001038 4124      45         ROTCL   R1          ;
46 0000103A 3204      46         DIV1    R0,R2      ;
47 0000103C 4124      47         ROTCL   R1          ;
48 0000103E 3204      48         DIV1    R0,R2      ;
49 00001040 4124      49         ROTCL   R1          ;

```

```

50 00001042 3204      50          DIV1   R0,R2   ;
51 00001044 4124      51          ROTCL  R1      ;
52 00001046 3204      52          DIV1   R0,R2   ;
53                    53                    ;
54 00001048 4124      54          ROTCL  R1      ;
55 0000104A 3204      55          DIV1   R0,R2   ;
56 0000104C 4124      56          ROTCL  R1      ;
57 0000104E 3204      57          DIV1   R0,R2   ;
58 00001050 4124      58          ROTCL  R1      ;
59 00001052 3204      59          DIV1   R0,R2   ;
60 00001054 4124      60          ROTCL  R1      ;
61 00001056 3204      61          DIV1   R0,R2   ;
62 00001058 4124      62          ROTCL  R1      ;
63 0000105A 3204      63          DIV1   R0,R2   ;
64 0000105C 4124      64          ROTCL  R1      ;
65 0000105E 3204      65          DIV1   R0,R2   ;
66 00001060 4124      66          ROTCL  R1      ;
67 00001062 3204      67          DIV1   R0,R2   ;
68 00001064 4124      68          ROTCL  R1      ;
69 00001065 3204      69          DIV1   R0,R2   ;
70                    70                    ;
71 00001068 4124      71          ROTCL  R1      ;
72 0000106A 3204      72          DIV1   R0,R2   ;
73 0000106C 4124      73          ROTCL  R1      ;
74 0000106E 3204      74          DIV1   R0,R2   ;
75 00001070 4124      75          ROTCL  R1      ;
76 00001072 3204      76          DIV1   R0,R2   ;
77 00001074 4124      77          ROTCL  R1      ;
78 00001076 3204      78          DIV1   R0,R2   ;
79 00001078 4124      79          ROTCL  R1      ;
80 0000107A 3204      80          DIV1   R0,R2   ;
81 0000107C 4124      81          ROTCL  R1      ;
82 0000107E 3204      82          DIV1   R0,R2   ;
83 00001080 4124      83          ROTCL  R1      ;
84 00001082 3204      84          DIV1   R0,R2   ;
85 00001084 4124      85          ROTCL  R1      ;
86 00001086 3204      86          DIV1   R0,R2   ;
87                    87                    ;
88 00001086 8900      88          BT     DIVU32R1 ; T bit = 1 ?
89 0000108A 320C      89          ADD    R0,R2   ; Clear oversub
90 0000108C                    90          DIVU32R1 ;
91 0000108C 000B      91          RTS     ;
92 0000108E 0008      92          CLRT    ; T bit <- No error
93 00001090                    93          DIVU32R2 ;
94 00001090 000B      94          RTS     ;
95 00001092 0018      95          SETTT   ; T bit <- Error
96                    96          .END

*****TOTAL ERRORS      0
*****TOTAL WARNINGS    0

```

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.  
Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.  
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.  
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.  
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.