


## IOH VS VOH(-40°C/P02)




### IOH VS VOH(-40°C/P10)




## IOH VS VOH(-40°C/P21)




## IOH VS VOH(-40°C/P147)




## IOH VS VOH(-40°C/P200)




# IOH VS VOH(25°C/P02)




## IOH VS VOH(25°C/P10)




# IOH VS VOH(25°C/P21)




# IOH VS VOH(25°C/P147)




# IOH VS VOH(25°C/P200)




# IOH VS VOH(105°C/P02)




## IOH VS VOH(105°C/P10)



## IOH VS VOH(105°C/P21)



# IOH VS VOH(105°C/P147)



# IOH VS VOH(105°C/P200)

