[Notes]

R20TS0571EJ0101 Rev.1.01 May. 16, 2020

CS+ Code Generator for RL78,

e<sup>2</sup> studio Code Generator Plug-in,

Applilet3 Coding Assistance Tool for RL78

# Outline

When using the products in the title, note the following point.

- 1. User option byte (000C1H/010C1H) LVD off setting values
- 1. User Option Byte (000C1H/010C1H) LVD Off Setting Values
- 1.1 Applicable Products
  - CS+ Code Generator for RL78 V2.19.00 (CS+ for CC V8.03.00), (CS+ for CA,CX V4.04.00) or later
  - Code Generator Plug-in V2.15.0 (e<sup>2</sup> studio V7.7.0) or later
  - Applilet3 for RL78 V1.18.00 or later

# 1.2 Applicable Devices

RL78 family: RL78/G13A group

# 1.3 Details


The user option byte (000C1H/010C1H) setting values for LVD off are incorrect. For details, refer to the technical update of the applicable device.

https://www.renesas.com/search/keyword-search.html#genre=document&q=tnrla0097



### 1.4 Workaround


- (1) For CS+ for CC/CS+ for CA,CX
  - Open the build tool property. Then, on the [Link Options] tab, change the user option byte value FF<u>FF</u>E8 to FF<mark>F3</mark>E8.



### (2) e<sup>2</sup> studio


(2-1) For CCRL

Open the properties. Then, from [Settings] - [Device], change the user option byte value FF**FF**E8 to FF**F3**E8.



#### (2-2) For GCC

Open r\_cg\_vector\_table.c, and then change {0xFFU, 0x**FF**U, 0xE8U, 0x04U} to {0xFFU, 0x**F3**U, 0xE8U, 0x04U}.





### (3) For Applilet3 for RL78

The code to be modified differs depending on the type of compiler. Modify the code by referring to the following.

| Compiler | File                | Code to be modified and details |   |
|----------|---------------------|---------------------------------|---|
| CA78K0R  | r_option_cc.txt     | Before<br>modification:         | USER_OPT_BYTE=FF <b>FF</b> E8                 |
|          |                     | After<br>modification:          | USER_OPT_BYTE=FF <mark>F3</mark> E8           |
| CCRL     | r_option_ca.txt     | Before<br>modification:         | gb0FF <u>FF</u> E8h                           |
|          |                     | After<br>modification:          | gb0FF <mark>F3</mark> E8h                     |
| GCC      | r_cg_vector_table.c | Before<br>modification:         | const uint8_t Option_Bytes[]<br>OPTION_SECT = |
|          |                     |                                 | {0xFFU, 0x <b>FF</b> U, 0xE8U, 0x04U};        |
|          |                     | After<br>modification:          | const uint8_t Option_Bytes[]<br>OPTION_SECT = |
|          |                     |                                 | {0xFFU, 0x <b>F3</b> U, 0xE8U, 0x04U};        |
| IAR      | r_main.c            | Before<br>modification:         | <pre>#pragma location = "OPTBYTE"</pre>       |
|          |                     |                                 | root const uint8_t opbyte1 = 0x <b>FF</b> U;  |
|          |                     | After<br>modification:          | #pragma location = "OPTBYTE"                  |
|          |                     |                                 | root const uint8_t opbyte1 = 0xF3U;           |

Note: When code is generated again, generated code returns to the state before modification Therefore, modify the source file each time you generate code.

# 1.5 Schedule for Fixing the Problem

This problem will be fixed in a later version.



# **Revision History**

|      |           | Description |                      |
|------|-----------|-------------|----------------------|
| Rev. | Date      | Page        | Summary              |
| 1.00 | May.16.20 | -           | First edition issued |
| 1.01 | Jun.16.20 | 1           | Correction of errors |
|      |           |             |                      |

Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.

The past news contents have been based on information at the time of publication. Now changed or invalid information may be included.

The URL in the Tool News also may be subject to change or become invalid without prior notice.

# **Corporate Headquarters**

TOYOSU FORESIA, 3- 2- 24 Toyosu, Koto-ku, Tokyo 135- 0061, Japan www.renesas.com

# Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

# **Contact information**

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit: <a href="http://www.renesas.com/contact/">www.renesas.com/contact/</a>

© 2020 Renesas Electronics Corporation. All rights reserved. TS Colophon 4.1

