

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

H8/38602R Group

Voltage Comparison by Comparator (External Voltage Reference)

Introduction

The H8/38602R's comparator function is used to compare the voltage applied to the comparator analog input pin 0 (pin COMP0) with a reference voltage input from the VCref pin.

Target Device

H8/38602R

Contents

1. Specifications	2
2. Description of Functions	3
3. Description of Operation	6
4. Description of Software	7
5. Flowchart.....	10

1. Specifications

- A reference voltage is input from the VCref pin.
- The voltage input to the COMP0 pin is compared with the reference voltage by using the comparator function.
- The result of voltage comparison is stored to RAM. The value 0 indicates that COMP0 pin voltage \leq reference voltage, and 1 indicates that COMP0 pin voltage $>$ reference voltage.

Figure 1 shows the connection for this sample task.




Figure 1 Connection Diagram

2. Description of Functions

2.1 Functions

In this sample task, a reference voltage is provided from the VCref pin. A voltage applied to the COMP0 pin is compared with the reference voltage using the comparator function. Figure 2 shows a block diagram of the comparators, and below is the explanation of the MCU's functions used in this sample task.

2.1.1 Comparator Function

A voltage applied to the VCref pin is specified as the reference voltage, and a voltage input to the COMP0 pin is compared with the reference voltage.

- Compare Control Register 0 (CMCR0)
CMCR0 controls the comparator.
- Compare Data Register (CMDR)
CMDR stores the result of comparing the voltage on the analog input pin with the reference voltage.




Figure 2 Block Diagram of Comparator Function

2.1.2 Watchdog Timer Function

The H8/38602R includes a watchdog timer, which is active after a reset. The timer counter WD (TCWD) counts up, and the H8/38602R is internally reset if the TCWD overflows. This sample task does not use the watchdog timer function, and thus stops this timer.

- Timer Control/Status Register WD1 (TCSRWD1)
TCSRWD1 controls writing to TCSRWD1 and TCWD. TCSRWD1 also controls the watchdog timer operation and indicates the operating status. TCSRWD1 must be rewritten by using the MOV instruction. The setting value cannot be changed by bit manipulation instructions.

2.1.3 I/O Port Function

The function of the port 30 pin is set as the VCref pin.

- Port Mode Register 3 (PMR3)
PMR3 selects the functions for port 3 pins.

2.1.4 Module Standby Function

By the module standby function, the comparators are placed in module standby mode after a reset. Module standby mode of the comparators can be cancelled by setting the COMPCKSTP bit in Clock Halt Register 2 (CKSTPR2) to 1.

- Clock Halt Register 2 (CKSTPR2)
CKSTPR2 controls the standby state of the on-chip peripheral modules in module units.

2.2 Function Assignment

Table 1 lists the function assignment for this sample task. By assigning the functions as shown in table 1, the voltage input to the COMP0 pin is compared with the reference voltage from the VCref pin using the comparator function.

Table 1 Assignment of Functions

Elements	Description
COMP0	Enables the comparator and specifies the voltage input from the VCref pin as a reference voltage.
CMDR	Stores the result of comparing the COMP0 pin voltage with the reference voltage.
PMR3	Sets the P30 pin to function as the VCref pin.
CKSTPR2	Cancels the comparator module standby state.
TCSRWD1	Stops the watchdog timer.

3. Description of Operation

Figure 3 illustrates the operation of this sample task along with the hardware and software processing. The voltage input to the COMP0 is compared with the VCref pin voltage using the comparator function.




Figure 3 Comparison Operation

4. Description of Software

4.1 Module

Table 2 describes the module of this sample task.

Table 2 Description of Module

Function Name	Description
main	Stops the watchdog timer, cancels the comparator module standby state and configures the comparator.

4.2 Arguments

This sample program does not use arguments.

4.3 Internal Registers

The following describes internal registers used in this sample task.

- Compare Control Register 0 (CMCR0) Address H'F0DC

Bit	Bit Name	Setting	R/W	Function
7	CME	1	R/W	Comparator Enable 0: Comparator halted. 1: Comparator operates.
5	CMR	1	R/W	Comparator Reference Voltage Select 0: Selects internal power supply as the reference voltage. 1: Reference voltage is input from the VCref pin. For the combination of the CMR and CMLS bits, see table 3.
4	CMLS	0 (Default)	R/W	Comparator Hysteresis Select 0: Selects no hysteresis 1: Selects hysteresis When CMR = 1, clear this bit to 0. For the combination of the CMR and CMLS bits, see table 3.

Table 3 Combination of CMR and CMLS Bits

CMR	CMLS	Function
0	0	The internal power supply (the voltage, VIH, set by the CRS3 to CRS0 bits in CMCR) and the COMP pin voltage are compared. No hysteresis.
	1	The internal power supply and the COMP pin voltage are compared. With hysteresis. VIH and VIL are set by the CRS3 to CRS0 bits.
1	0	VCref and COMP pin voltages are compared. No hysteresis.
	1	Setting prohibited

- Compare Data Register (CMDR)

Address H'F0DE

Bit	Bit Name	Setting	R/W	Function
4	CMF0	—	R/(W)*	COMP0 Interrupt Flag [Setting condition] When COMP0 interrupt occurs [Clearing condition] 0 is written to CMF0 after reading CMF0 = 1
0	CDR0	—	R	[Setting condition] COMP0 pin > Reference voltage [Clearing condition] COMP0 pin ≤ Reference voltage

Note: Only 0 can be written to clear the flag.

- Port Mode Register 3 (PMR3)

Address H'FFC2

Bit	Bit Name	Setting	R/W	Function
0	VCref	1	R/W	P30/SCK3/VCref Pin Function Switch 0: P30 or SCK3 I/O pin 1: Comparator reference voltage (VCref) pin

- Timer Control/Status Register WD1 (TCSRWD1)

Address H'FFB1

Bit	Bit Name	Setting	R/W	Function
7	B6WI	1	R/W	Bit 6 Write Disable Writing to the TCWE bit is only enabled when 0 is written to the B6WI bit. This bit is always read as 1.
6	TCWE	0	R/W	Timer Counter WD Write Enable Writing to the timer counter WD (TCWD) is enabled when the TCWE bit is set to 1. When writing to this bit, 0 must be written to the B6WI bit.
5	B4WI	1	R/W	Bit 4 Write Disable Writing to the TCSRWE bit is only enabled when 0 is written to the B4WI bit. The B4WI bit is always read as 1.
4	TCSRWE	0	R/W	Timer Control/Status Register WD1 Write Enable Writing to the WDON and WRST bits are enabled when the TCSRWE bit is set to 1. When writing to this bit, 0 must be written to the B4WI bit.
3	B2WI	1	R/W	Bit 2 Write Disable Writing to the WDON is only enabled when 0 is written to the B2WI bit. This bit is always read as 1.

Bit	Bit Name	Setting	R/W	Function
2	WDON	0	R/W	Watchdog Timer On The TDWD starts counting up when the WDON bit is set to 1 and stops counting when the WDON bit is cleared to 0. [Setting condition] <ul style="list-style-type: none"> • If 0 is written to the B2WI bit and 1 to the WDON bit while the TCSRWE bit is 1. • Reset [Clearing condition] <ul style="list-style-type: none"> • If 0 is written to the B2WI and WDON bits while the TCSRWE bit is 1.
1	BOWI	1	R/W	Bit 0 Write Disable Writing to the WRST bit is only enabled when 0 is written to the BOWI bit. This bit is always read as 1.
0	WRST	0	R/W	Watchdog Timer Reset [Setting condition] <ul style="list-style-type: none"> • When the TCWD overflows and an internal reset signal is generated. [Clearing condition] <ul style="list-style-type: none"> • Reset by the $\overline{\text{RES}}$ pin • If 0 is written to both the BOWI and WRST bits while the TCSRWE bit is 1.

- Clock Halt Register 2 (CKSTPR2) Address H'FFFB

Bit	Bit Name	Setting	R/W	Function
1	COMPCKSTP	1	R/W	Comparator Module Standby The comparators enter a standby state when this bit is cleared to 0. 1: Cancels module standby state.

4.4 RAM Usage


Table 4 describes the RAM usage in this sample task.

Table 4 Description of RAM

Label Name	Function	Data Length	Used In
com	Stores the result of comparing the VCref and COMP0 pin voltages.	One byte	main

5. Flowchart

5.1 main



5.2 Link Address Specification

Section Name	Address
CVECT	H'0000
P	H'0100
B	H'FB80

Revision Record

Rev.	Date	Description	
		Page	Summary
1.00	Mar.18.05	—	First edition issued

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.
Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors.
Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.