

Renesas RA and RX Family of MCUs

Document Name

Introduction

AWS dashboard for Renesas CK-RA6M5 and CK-RX65N cloud kits is custom designed to visualize the data of all the sensors on the cloud kits. The dashboard connects to AWS IoT services through [AWS IoT Core](#) and enables users to utilize the cloud services to full potential.

To allow users to experience a hassle-free cloud connectivity, Renesas will credit every cloud kit with \$10 USD AWS credits upon registration.

The dashboard can be accessed at <https://www.renesas.cloud-ra-rx.com/>.

The application projects can be downloaded from www.renesas.com/cloudsolutions/.

Target Device

CK-RA6M5, CK-RX65N

Contents

1. Cloud Kit Registration and Access to Dashboard.....	1
2. Account Quarantine.....	5
3. Next Steps.....	5

1. Cloud Kit Registration and Access to Dashboard

1. Sign up at <https://www.renesas.cloud-ra-rx.com/> with **an email that was not used previously for signing up for an AWS account.**





Figure 1. Dashboard Sign in


2. Enter your first name, last name, email address and password and press on the button **Register**. You are redirected to Confirm your email page.



The screenshot shows the Renesas account registration page. At the top is the Renesas logo. Below it are icons for AWS, Renesas RA, a handshake, and Renesas RX. On the right, there is a link: "Already have an account? [Login](#)". The main heading is "Sign up" with the instruction "Enter your details below.". There are four input fields: "First name", "Last name", "Email address", and "Password" (with a strength indicator). A blue "Register" button is at the bottom.

Figure 2. Account Registration


3. Verification code will be sent to your email. Enter the code and press on the **Send** button. You are redirected to Register Device page.



The screenshot shows the Renesas email verification page. It has the same header as Figure 2. The main heading is "Confirm your email" with the instruction "We sended validation code to your email". There is a "Verification code" input field, a "Resend Code" link, and a blue "Send" button.

Figure 3. Email Verification


4. Enter the UUID of the kit to complete the registration process. UUID is the unique ID of your board. See 'AWS Application Projects' at renesas.com/cloudsolutions for steps to obtain the UUID of the kit.



The screenshot shows the 'Register Device' page on the Renesas AWS dashboard. At the top, there is a blue header with the Renesas logo. Below the header, there is a navigation bar with 'My Devices' on the left and a user profile icon on the right. The main content area features the 'Register Device' title, followed by an 'Email' input field with a placeholder '@.com', a 'UUID' input field, and a blue 'Submit' button at the bottom.

Figure 4. Registering the Device

5. The registration page indicates that the device registration is in progress.



The screenshot shows the 'Device Registration in Progress' page on the Renesas AWS dashboard. At the top, there is a blue header with the Renesas logo. Below the header, there is a navigation bar with 'My Devices' on the left and a user profile icon on the right. The main content area features the 'Device 1' title, followed by the 'Account name' (ra-rx-def00002-98a1556f-bd1e18-eaf7b0e6), 'Email' (placeholder @.com), and 'UUID' (def00002-98a1556f-bd1e18-eaf7b0e6). A blue message box at the bottom states '* Account Registration is in progress'. On the right side, there are two buttons: 'Download Certificate' and 'Go To Dashboard'.

Figure 5. Device Registration in Progress

- Wait for the 'Invitation to join AWS Single sign-on' email to activate the account. It could take up to 10 min to receive this email. Accept the invitation. **Note** that this invitation will expire in 7 days. If your invitation expires, please contact Renesas support.

On accepting the invitation, you will be redirected to the AWS Sign up page.

If you choose to sign into your AWS account (the account indicated in the AWS invitation), enter your new password, and confirm to complete the Sign in process in AWS. You will be redirected to the **Single Sign-On** page.

Proceed to check the status of Renesas dashboard at <https://www.renesas.cloud-ra-rx.com/login>.




Figure 6. AWS Invitation

- Wait for the **Download Certificate** and **Go To Dashboard** buttons to become available on the registration page. It may take up to **1 hour** for the device provisioning process to complete. Click **Download Certificate** button to download the credentials for connecting to the cloud.




Figure 7. Device Active Status and Certificate Download

- Click **go to** Dashboard button to access the dashboard. First time users will access the dashboard with credentials “admin” for both username and password. Then, users will be directed to change the password. Once completed, users can access the dashboard.




Figure 8. AWS Dashboard

2. Account Quarantine

The \$10 AWS credits are valid for one year.

Upon exhaustion or expiration of the credits, the account will be converted to ‘Quarantine’ status.

To activate the account, users can login to the AWS account indicated in the ‘Invitation to join AWS Single sign-on’ email, as shown in the example below, to add their credit card details to activate the account.

3. Next Steps

Visit: www.renesas.com/cloudsolutions for more information and to further explore the cloud solutions

Website and Support

Visit the following vanity URLs to learn about key elements of the RA family, download components and related documentation, and get support.

CK-RA6M5 Kit Information	renesas.com/ra/ck-ra6m5
CK-RX65N Kit Information	renesas.com/rx/ck-rx65n
Renesas RA RX Cloud Solutions	renesas.com/cloudsolutions
RA Product Information	renesas.com/ra
RX Product Information	renesas.com/rx
RA Product Support Forum	renesas.com/ra/forum
RX Product Support Forum	renesas.com/rx/forum
Renesas Support	renesas.com/support

Revision History

Rev.	Date	Description	
		Page	Summary
1.00	Jun.14.22	—	Initial release
1.01	Jul.11.22	—	Minor update

General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Precaution against Electrostatic Discharge (ESD)

A strong electrical field, when exposed to a CMOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop the generation of static electricity as much as possible, and quickly dissipate it when it occurs. Environmental control must be adequate. When it is dry, a humidifier should be used. This is recommended to avoid using insulators that can easily build up static electricity.

Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work benches and floors must be grounded. The operator must also be grounded using a wrist strap. Semiconductor devices must not be touched with bare hands. Similar precautions must be taken for printed circuit boards with mounted semiconductor devices.

2. Processing at power-on

The state of the product is undefined at the time when power is supplied. The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the time when power is supplied. In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the time when power is supplied until the reset process is completed. In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the time when power is supplied until the power reaches the level at which resetting is specified.

3. Input of signal during power-off state

Do not input signals or an I/O pull-up power supply while the device is powered off. The current injection that results from input of such a signal or I/O pull-up power supply may cause malfunction and the abnormal current that passes in the device at this time may cause degradation of internal elements. Follow the guideline for input signal during power-off state as described in your product documentation.

4. Handling of unused pins

Handle unused pins in accordance with the directions given under handling of unused pins in the manual. The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of the LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible.

5. Clock signals

After applying a reset, only release the reset line after the operating clock signal becomes stable. When switching the clock signal during program execution, wait until the target clock signal is stabilized. When the clock signal is generated with an external resonator or from an external oscillator during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Additionally, when switching to a clock signal produced with an external resonator or by an external oscillator while program execution is in progress, wait until the target clock signal is stable.

6. Voltage application waveform at input pin

Waveform distortion due to input noise or a reflected wave may cause malfunction. If the input of the CMOS device stays in the area between V_{IL} (Max.) and V_{IH} (Min.) due to noise, for example, the device may malfunction. Take care to prevent chattering noise from entering the device when the input level is fixed, and also in the transition period when the input level passes through the area between V_{IL} (Max.) and V_{IH} (Min.).

7. Prohibition of access to reserved addresses

Access to reserved addresses is prohibited. The reserved addresses are provided for possible future expansion of functions. Do not access these addresses as the correct operation of the LSI is not guaranteed.

8. Differences between products

Before changing from one product to another, for example to a product with a different part number, confirm that the change will not lead to problems. The characteristics of a microprocessing unit or microcontroller unit products in the same group but having a different part number might differ in terms of internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 October 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan

www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:

www.renesas.com/contact/.