

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

SH7000 Series

32 Bit × 32 Bit = 64 Bit (Signed)

Label: MULS32

Functions Used: MULU Instruction
SWAP Instruction
NEGC Instruction

Contents

1. Function	2
2. Arguments.....	2
3. Internal Register Changes and Flag Changes.....	3
4. Programming Specifications	4
5. Notes.....	4
6. Description	5
7. Flowchart.....	7
8. Program Listing	9

1. Function

Multiplies the multiplicand (signed 32 bits) by the multiplier (signed 32 bits) and determines the product (signed 64 bits).

2. Arguments

Description		Storage Location	Data Length (Bytes)
Input	Multiplicand (signed 32 bits)	R0	4
	Multiplier (signed 32 bits)	R1	4
Output	Upper 32 bits of product (signed 64 bits)	R2	4
	Lower 32 bits of product (signed 64 bits)	R3	4

3. Internal Register Changes and Flag Changes

	(Before Execution) → (After Execution)
R0	Multiplicand (unsigned 32 bits) → No change
R1	Multiplier (unsigned 32 bits) → Change
R2	Undefined → Product (upper 32 bits)
R3	Undefined → Product (lower 32 bits)
R4	Work
R5	Work
R6	Work
R7	
R8	
R9	
R10	
R11	
R12	
R13	
R14	
R15	(SP)

- T bit * — : No change
 * : Change
 0 : Fixed 0
 1 : Fixed 1

4. Programming Specifications

Program memory (bytes)	92
Data memory (bytes)	0
Stack (bytes)	16
Number of states	48
Reentrant	Yes
Relocation	Yes
Intermediate interrupt	Yes

5. Notes

The number of states indicated in the programming specifications is the value when $H'7FFFFFFF \times H'80000000$ is calculated.

6. Description

(1) Function

Details of the arguments are as follows.

R0: Set the multiplicand (signed 32 bits) as the input argument.

R1: Set the multiplier (signed 32 bits) as the input argument.

R2: Holds the upper 32 bits of the product (signed 64 bits) as the output argument.

R3: Holds the lower 32 bits of the product (signed 64 bits) as the output argument.

Figure 1 shows a software MULS32 execution example.




Figure 1 Software MULS32 Execution Example

(2) Usage Notes

The contents of R1, which sets the multiplier, are changed by execution of the software MULS32 instruction. If the value for the multiplier will be needed after the software MULS32 instruction is executed, it should be saved beforehand.

(3) RAM Used

No RAM is used by the software MULS32 instruction.

(4) Usage Example

After the multiplicand and multiplier are set, the software instruction MULS32 is executed by a subroutine call.

```

MOV.L DATA1,R0    . . . . Sets multiplicand in input argument (R0)
BSR   MULU32      . . . . Subroutine call to software instruction MULS32
MOV.L DATA2,R1    . . . . Sets multiplier in input argument (R1)
.
.
.
.align 4
DATA1 .data.l H'7FFFFFFF
DATA2 .data.l H'80000000
    
```

(5) Operating Principle

- As shown in figure 2, multiplication is performed in 16 bit units. Partial products (1–4) are determined, and these are added to get the final 64-bit product. The 16-bit unsigned multiplication instruction (MULU) is used in multiplication of partial products, so if the multiplicand or multiplier are negative, they are converted to positive before multiplication.
- The product is calculated as positive, so the determination of whether it is positive or negative is made using exclusive OR on the multiplicand and multiplier MSB, as shown in table 1.






Figure 2 Multiplication

Table 1 Product Sign Changes

MSB of Multiplicand	MSB of Multiplier	Product Sign Change
Positive	Positive	Positive
Positive	Negative	Negative
Negative	Positive	Negative
Negative	Negative	Positive

7. Flowchart





8. Program Listing

```

1          1          ;*****
2          2          ;*
3          3          ;*          NAME : 32 BIT SINGNED MULTIPLATION (MULS32)          *
4          4          ;*
5          5          ;*****
6          6          ;*
7          7          ;*          ENTRY : R0 (MULTIPLICAND)          *
8          8          ;*          R1 (MULTIPLIER)          *
9          9          ;*          RETURNS : R2 (UPPER 32 BIT PRODUCT)          *
10         10         ;*          R3 (LOWER 32 BIT PRODUCT)          *
11         11         ;*
12         12         ;*****
13 00001000        13          .SECTION A, CODE, LOCATE=H'1000
14          14         MULS32 .EQU $          ; Entry point
15 00001000 4F12    15          STS.L  MACL, @-R15          ; Escape register
16 00001002 2F46    16          MOV.L  R4, @-R15          ;
17 00001004 2F56    17          MOV.L  R5, @-R15          ;
18 00001006 2F66    18          MOV.L  R6, @-R15          ;
19          19          ;
20 00001008 4011    20          CMP/PZ R0          ; Multiplicand >= 0 ?
21 0000100A 8900    21          BT      MULS321          ; Yes
22 0000100C 600B    22          NEG      R0, R0          ; Change plus
23 0000100E        23         MULS321          ;
24 0000100E 4111    24          CMP/PZ R1          ; Multiplier >= 0 ?
25 00001010 8900    25          BT      MULS322          ; Yes
26 00001012 611B    26          NEG      R1, R1          ; Change plus
27 00001014        27         MULS322          ;
28 00001014 201E    28          MULU   R1, R0          ; Lower 16 bit + lower 16 bit -> R3
29 00001016 6009    29          SWAP.W R0, R0          ;
30 00001018 031A    30          STS      MACL, R3          ;
31 0000101A 201E    31          MULU   R1, R0          ; Upper 16 bit + lower 16 bit -> R5
32 0000101C 6119    32          SWAP.W R1, R1          ;
33 0000101E 051A    33          STS      MACL, R5          ;
34 00001020 201E    34          MULU   R1, R0          ; Upper 16 bit + upper 16 bit -> R2
35 00001022 6009    35          SWAP.W R0, R0          ;
36 00001024 021A    36          STS      MACL, R2          ;
37 00001026 201E    37          MULU   R1, R0          ; Lower 16 bit + upper 16 bit -> R4
38 00001028 6119    38          SWAP.W R1, R1          ;
39 0000102A 041A    39          STS      MACL, R4          ;
40          40          ;
41 0000102C 0008    41          CLRT          ;
42 0000102E 345E    42          ADDC   R5, R4          ;
43 00001030 0629    43          MOVT   R6          ; R6 <- Carry
44 00001032 4628    44          SHLL16 R6          ;
45 00001034 326C    45          ADD     R6, R2          ; Carry = 1  R2 <- R2 + H'00010000
46          46          ; Carry = 0  R2 <- R2 + H'00000000
47 00001036 6543    47          MOV     R4, R5          ;
48 00001038 4528    48          SHLL16 R5          ;
49 0000103A 4429    49          SHLR16 R4          ;

```

```

50                                     50                                     ;
51 0000103C 0000                      51          CLRT                          ;
52 0000103E 335E                      52          ADDC      R5,R3          ;
53 00001040 0629                      53          MOVT      R6              ; R6 <- Carry
54 00001042 326C                      54          ADD      R6,R2          ; Carry = 1  R2 <- R2 + H'00000001
55                                     55                                     ; Carry = 0  R2 <- R2 + H'00000000
56 00001044 324C                      56          ADD      R4,R2          ;
57                                     57                                     ;
58 00001046 210A                      58          XOR      R0,R1          ; Product < 0 ?
59 00001048 4100                      59          SHLL     R1              ;
60                                     60                                     ;
61 0000104A 8B02                      61          BF      MULS32_END    ; No
62 0000104C 0008                      62          CLRT                          ; Change minus
63 0000104E 633A                      63          NEGC     R3,R3          ;
64 00001050 622A                      64          NEGC     R2,R2          ;
65 00001052                          65  MULS32_END                    ;
66 00001052 66F6                      66          MOV.L   @R15+,R6        ; Return register
67 00001054 65F6                      67          MOV.L   @R15+,R5        ;
68 00001056 64F6                      68          MOV.L   @R15+,R4        ;
69 00001058 000B                      69          RTS                          ;
70 0000105A 4F16                      70          LDS.L   @R15+,MACL     ;
71                                     71          .END
*****TOTAL ERRORS      0
*****TOTAL WARNINGS    0

```

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.