

Renesas RA Family

EK-RA6M3 Example Project Overview

Introduction

This document describes the contents of the Example Project Bundle for the EK-RA6M3 kit. The Example Projects contained within the bundle show how to write code for the various Renesas Flexible Software Package (FSP) modules supported by the EK-RA6M3 kit.

The Flexible Software Package is an optimized software package designed to provide easy to use, scalable, high quality software for embedded system design. The primary goal is to provide lightweight, efficient drivers that meet common use cases in embedded systems. FSP code quality is enforced by peer reviews, automated requirements-based testing, and automated static analysis. The FSP provides uniform and intuitive APIs that are well documented. Each module is supported with detailed user documentation including example code. FSP modules can be used on any MCU in the RA family, provided the MCU has any peripherals required by the module. FSP modules also have build time configurations that can be used to optimize the size of the module for the feature set required by the application. The e² studio ISDE provides support with intuitive configurators and intelligent code generation to make programming and debugging easier and faster.

Target Device

EK-RA6M3 kit

Required Software Components

FSP v 1.0 or later

Supported Toolchains

- e² studio Integrated Development Environment (IDE), default toolchain is GCC Arm Embedded. Arm Keil MDK
-

Documentation

- Example Project Usage Guide
https://github.com/renesas/ra-fsp-examples/blob/master/example_projects/Example%20Project%20Usage%20Guide.pdf
- e² studio AC6 porting Guide
<https://en-support.renesas.com/knowledgeBase/19375553>

1. Using the Example Projects

To use the EK-RA6M3 Example Projects for e² studio and the GCC compiler, import the entire Example Project Bundle zip file into e² studio using the Project Import capability. After importing the project build, load, and run the project according to the instructions listed in the [FSP Example Project Usage Guide](#).

To use the EK-RA6M3 Example Projects for Keil MDK, download and unzip the contents of the Example Project Bundle. Then navigate to the “Keil MDK” folder and double click the desired project file name with the .UVPROJX file extension to open a specific Keil project. To change between projects, you will need to close the first project and then open the second project.

1.1 List of Example Projects in the Bundle

EK-RA6M3 Example Projects	e² studio/GCC Status	e² studio/AC6 Status	Keil MDK Status
QuickStart	Supported	Supported via port from GCC	
ACMPHS	Supported	Supported via port from GCC	
ADC	Supported	Supported via port from GCC	
AGT	Supported	Supported via port from GCC	Supported
CAC	Supported	Supported via port from GCC	
CAN	Supported	Supported via port from GCC	
CRC	Supported	Supported via port from GCC	
DMAC	Supported	Supported via port from GCC	Supported
DOC	Supported	Supported via port from GCC	
ELC	Supported	Supported via port from GCC	
Ethernet	Supported	Supported via port from GCC	Supported
Flash HP	Supported	Supported via port from GCC	Supported
FreeRTOS	Supported	Supported via port from GCC	Supported
GPT	Supported	Supported via port from GCC	Supported
GPT Input Capture	Supported	Supported via port from GCC	
ICU	Supported	Supported via port from GCC	Supported
IIC Master	Supported	Supported via port from GCC	
IIC Slave	Supported	Supported via port from GCC	Supported
KINT	Supported	Supported via port from GCC	
LPM	Supported	Supported via port from GCC	
LVD	Supported	Supported via port from GCC	
OPAMP	Supported	Supported via port from GCC	
QSPI	Supported	Supported via port from GCC	
RTC	Supported	Supported via port from GCC	Supported
SCI I2C	Supported	Supported via port from GCC	
SCI SPI	Supported	Supported via port from GCC	
SCI UART	Supported	Supported via port from GCC	Supported
SPI	Supported	Supported via port from GCC	Supported
SSI	Supported	Supported via port from GCC	
USB HMSC	Supported	Supported via port from GCC	
WDT	Supported	Supported via port from GCC	Supported
Wi-Fi	Supported	Supported via port from GCC	

Website and Support

Visit the following vanity URLs to learn about key elements of the RA family, download components and related documentation, and get support.

RA Product Information	www.renesas.com/ra
RA Product Support Forum	www.renesas.com/ra/forum
RA Flexible Software Package	www.renesas.com/FSP
Renesas Support	www.renesas.com/support

Revision History

Rev.	Date	Description	
		Page	Summary
1.00	Apr.23.20	—	First release document

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/.