

Renesas Flash Programmer

R20AN0547EJ0100
Rev.1.00
Dec.19.19

Usage from the Command Line

Introduction

This document introduces running the Renesas Flash Programmer from the command line and using this in batch processing. Batch processing enables automated programming.

Target Devices

RA family
RL78 family
RX family
RH850 family
Renesas Synergy™ microcontrollers
RE family
Power management (power-management IC)
Renesas USB Power Delivery family (C30 group)
ICs for driving motors and actuators (ICs for motor control)

Contents

1. Overview	2
2. Basic Procedure before Batch Processing	2
2.1 Connecting a System	2
2.2 Connecting a Target System	2
2.3 Creating a Project File	3
2.4 Setting a Project	5
2.5 Creating a Batch File	8
2.6 Executing the Batch File	8
3. Examples of Batch Processing from the Command Line	9
3.1 Programming Multiple Program Files	9
3.2 Consecutive Programming of Different Specified Projects	9
3.3 Executing the Specified Commands (Erasure, Programming, and Verification)	9
3.4 Programming Sections of the Option Bytes (OPBTs) of MCUs with RH850G4MH Cores	9
3.5 Programming with a Specified Emulator	9
3.6 Simultaneous Programming through Multiple Devices Connected to a PC (Gang Programming)	10
3.7 Output of Descriptions of the Executed Command Lines to the Windows Command Prompt	11

1. Overview

The Renesas Flash Programmer (RFP) can be run from the command line with options prefixed by '/'. This also enables automated programming by using batch files to operate the RFP. For details on the RFP, refer to the user's manual.

<https://www.renesas.com/rfp>

2. Basic Procedure before Batch Processing

This chapter helps you to understand the sequence of the basic procedures to follow before setting up batch processing that runs the RFP from the command line, taking the RL78/G14 as an example of the target MCU.

- The descriptions in this chapter apply under the following conditions.
Target MCU: R5F104LE (RL78/G14)
Tool: E2 emulator Lite
Connection: 1-wire UART (single-wire UART)
Bit rate: 1,000,000 bps
Clock to be supplied: None (on-chip clock oscillator)
Power supply: E2 emulator Lite (3.3 V)
Operations of flash memory: Erasure, programming, and verification
Options for flash memory: None
- This chapter describes the following procedures.
 1. Connecting a system
 2. Connecting a target system
 3. Creating a project file
 4. Setting a project
 5. Creating a batch file
 6. Executing the batch file

2.1 Connecting a System

Connect the USB port of the host PC to the tool to be used via a USB cable.




Figure 2.1 Connecting a Tool

2.2 Connecting a Target System

Connect the target cable of the tool to be used to the target system.



Figure 2.2 Connecting a Target System

2.3 Creating a Project File

Start the RFP GUI to open the main window.

Select [New Project] from the [File] menu to open the [Create New Project] dialog box.




Figure 2.3 [Create New Project] Dialog Box

Select “RL78” for [Microcontroller], enter “sample” for [Project Name], specify “C:\vfp” for [Project Folder], and select “E2 emulator Lite” for [Tool].

Clicking on the [Tool Details] button opens the [Tool Details] dialog box.




Figure 2.4 [Tool Details] Dialog Box

Select “3.3V” and click on the [OK] button.

After returning to the [Create New Project] dialog box, click on the [Connect] button.

The project file is created and the display returns to the main window.




Figure 2.5 Main Window

2.4 Setting a Project

Specify "C:\vfp\sample.mot" for [Program File] on the [Operation] tabbed page.




Figure 2.6 [Operation] Tabbed Page

On the [Operation Settings] tabbed page, select the [Erase], [Program], and [Verify] checkboxes in the [Command] category and confirm this.




Figure 2.7 [Operation Settings] Tabbed Page

Specify “1,000,000 bps” for [Speed] on the [Connect Settings] tabbed page.




Figure 2.8 [Connect Settings] Tabbed Page

Select [Save Project] from the [File] menu to save the project.

Select [Exit] from the [File] menu to close the RFP window.

2.5 Creating a Batch File

Enter the following in a text editor and save it as "C:\rfp\sample.bat".

```
SET PATH=%PATH%;C:\Program Files (x86)\Renesas Electronics\Programming Tools\Renesas Flash  
Programmer V3.06  
RFPV3.exe /silent "C:\rfp\sample\sample.rpj"  
ECHO Result Code: %ErrorLevel%  
PAUSE
```

Figure 2.9 Creating a Batch File

Using the silent option starts the RFP in a silent mode in which the GUI is not displayed.

After the specified project file (sample.rpj) is opened and processing which is equivalent to execution (in this case, erasure, programming, and verification) in response to pressing the [Start] button once is done, the RFP is closed.

If the processing succeeded, result code 0 is returned. Otherwise, 1 is returned.

Specify the folder in which the RFP has been installed as the folder indicated by "SET PATH".

"PAUSE" is added so that the output against the command prompts can be confirmed after the RFP has been closed.

2.6 Executing the Batch File

Execute the sample.bat batch file.

The following lines are displayed in the command prompt window.

```
C:\rfp>SET PATH=%PATH%;C:\Program Files (x86)\Renesas Electronics\Programming Tools\Renesas  
Flash Programmer V3.06  
  
C:\rfp>RFPV3.exe /silent "C:\rfp\sample\sample.rpj"  
  
C:\rfp>ECHO Result Code: 0  
Result Code: 0  
  
C:\rfp>PAUSE  
Press any key to continue...
```

Figure 2.10 Executing the Batch File

3. Examples of Batch Processing from the Command Line

This chapter describes batch processing from the command line for the purpose of efficient automated programming. For details on the command line, refer to the user's manual.

<https://www.renesas.com/rfp>

3.1 Programming Multiple Program Files

Using the file option allows the specification of a program file without using one specified by a project. Multiple program files are also specifiable.

The command in the following example is for the programming of "sample1.mot" and "sample2.mot".

```
RFPV3.exe /silent "C:\rfp\sample\sample.rpj" /file "C:\rfp\sample1.mot" /file "C:\rfp\sample2.mot"
```

3.2 Consecutive Programming of Different Specified Projects

When programming is executed several times from the command line, different projects can be specified and consecutive programming is possible.

The following shows an example of commands for the consecutive programming of "sample1.rpj" and "sample2.rpj".

```
RFPV3.exe /silent "C:\rfp\sample\sample1.rpj"  
RFPV3.exe /silent "C:\rfp\sample\sample2.rpj"
```

3.3 Executing the Specified Commands (Erasure, Programming, and Verification)

The command option can be used to specify a command without using the specification of a command (erasure, programming, or verification) in a project. Multiple commands are also specifiable.

The following shows an example of the specification of three commands (e: erasure, p: programming, and v: verification).

```
RFPV3.exe /silent "C:\rfp\sample\sample.rpj" /command epv
```

3.4 Programming Sections of the Option Bytes (OPBTs) of MCUs with RH850G4MH Cores

The write32 option can be used to program specified values to specified addresses without using the program file specified in the project.

The following shows an example of programming of the value 0x01020304 to OPBT0 (address 0xFF320080) and the value 0x0A0B0C0D to OPBT1 (address 0xFF320084) of an RH850/E2M.

```
RFPV3.exe /silent "C:\rfp\sample\sample.rpj" /write32 FF320080 01020304 0A0B0C0D
```

Since this option also involves reading, it cannot be used with devices that do not support reading or those from which reading is not possible due to security settings.

3.5 Programming with a Specified Emulator

Using the tool option can specify the serial number of an emulator.

The following shows an example of programming through an emulator with the serial number represented by "xxxxxxxx" of the emulator.

```
RFPV3.exe /silent "C:\rfp\sample\sample.rpj" /tool xxxxxxxx
```

3.6 Simultaneous Programming through Multiple Devices Connected to a PC (Gang Programming)

Multiple RFPs can be started on a PC. It can also be used for programming multiple devices by specifying the serial numbers of different emulators. The start command of the Windows command prompt can also be used to set up a batch file that launches multiple batch files which continue running at the same time.

The following shows an example where two RFPs are started at the same time to program the devices connected to two emulators in the sample.rpj project.

This example is the sample1.bat batch file to handle programming through the first emulator (serial number: xxxxxxxxx).

```
RFPV3.exe /silent "C:\rfp\sample\sample.rpj" /tool xxxxxxxxx
echo off
if errorlevel 1 goto NG
:OK
echo OK Result Code: %ErrorLevel%
goto END
:NG
echo NG Result Code: %ErrorLevel%
:END
PAUSE
exit
```

This example is the sample2.bat batch file to handle programming through the second emulator (serial number: yyyyyyyyy).

```
RFPV3.exe /silent "C:\rfp\sample\sample.rpj" /tool yyyyyyyyy
echo off
if errorlevel 1 goto NG
:OK
echo OK Result Code: %ErrorLevel%
goto END
:NG
echo NG Result Code: %ErrorLevel%
:END
PAUSE
exit
```

This example is the sample.bat batch file, which executes calls of both "sample1.bat" and "sample2.bat".

```
:LOOP
start sample1.bat
start sample2.bat
PAUSE
goto LOOP
```

3.7 Output of Descriptions of the Executed Command Lines to the Windows Command Prompt

The file RFPV3.Console.exe in the folder where the RFP is installed produces descriptions of the executed command lines in the command prompt window.

The following shows an example of the execution of RFPV3.Console.exe for programming from the sample.rpj project.

```
RFPV3.Console.exe "C:\rfp\sample\sample.rpj"
```

The following is output to the command prompt.

```
C:\rfp>RFPV3.Console.exe "C:\rfp\sample\sample.rpj"
Renesas Flash Programmer V3.06.01 [1 Oct 2019] (Commercial Edition)
Load a project (C:\rfp\sample\sample.rpj).
Load a file (C:\rfp\sample.mot). CRC-32 : A96368C2

Connected device: R5F104LE

Connecting the RFP to the tool.
: (Omitted.)
Disconnecting the RFP from the tool.
The operation succeeded.
```

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/.