

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

M16C/26

Using the A-D Converter In Repeat Sweep Mode 0

1.0 Abstract

The following document outlines the steps necessary to setup and perform analog to digital conversions of the M16C/26 using repeat sweep mode 0. The ADC is useful in measuring output voltages of sensors such as accelerometers or other analog instrumentation and converting them to digital values.

2.0 Introduction

The Renesas M30262 is a 16-bit MCU based on the M16C/60 series CPU core. The MCU features include up to 64K bytes of Flash ROM, 2K bytes of RAM and 4K bytes of Virtual EEPROM. The peripheral set includes 10-bit A/D, UARTS, Timers, DMA, and GPIO. The M16C/26 features an onboard analog to digital converter (ADC). The ADC consists of one 10-bit successive approximation circuit, eight analog input pins, selectable conversion clock speeds, sample and hold function, and several conversion modes. Table 1 shows the performance of the ADC and Figure 1 shows a diagram of the ADC block.

Table 1 ADC Performance

Item	Performance
Method of A-D Conversion	Successive approximation (capacitive coupling amplifier)
Analog input voltage	0V to AVcc (Vcc)
Operating clock f_{AD}	f_{AD} , f_{AD2} , f_{AD3} , f_{AD4} , f_{AD6} , or f_{AD6} or f_{AD12} where $f_{AD}=f(Xin)$
Resolution	8-bit or 10-bit (selectable)
Operating modes	One-shot mode, repeat, single sweep mode, repeat mode, repeat sweep mode 0 and repeat sweep mode 1.
Analog input pins	8 pins AN ₀ to AN ₇
A-D conversion start condition	Software trigger: A-D conversion starts when the A-D conversion start flag changes to "1" External trigger (can be retriggered): A-D conversion starts when the A-D conversion start flag is "1" and the AD _{TRG} /P15 input (shared with INT3) changes from "H" to "L"
Conversion speed per pin	Without sample and hold function 8-bit resolution: 49 f_{AD} cycles, 10-bit resolution: 59 f_{AD} cycles. With sample and hold function 8-bit resolution: 28 f_{AD} cycles, 10-bit resolution: 33 f_{AD} cycles.




Figure 1 ADC Block Diagram

3.0 Repeat Sweep Mode 0 Description

In repeat sweep mode 0, several pins of the ADC can be selected as input sources. Once triggered, a conversion takes place on the selected pins and the result is stored in the ADC result registers corresponding to the selected channels. This is repeated until the ADC conversion start flag is disabled. No interrupt is generated on the completed conversions, but rather the ADC output registers are read anytime to determine the converted values. Below is an overview of the registers that will be used in this example. These registers are detailed in the included sample code. For specific details, consult the MCU datasheet. Figure 2 and Figure 3 show the control registers for ADC setup in Repeat Sweep Mode 0.




Figure 2 ADC control registers in Repeat Sweep Mode 0




Figure 3 ADC Control Registers

4.0 Example Program

The following example program demonstrates how to perform a conversion using the ADC with the following configuration.

- Repeat sweep mode 0 conversions
- 10 bit mode
- Analog inputs 0-3 used
- Sample and hold enabled
- Internal Vref
- Conversion clock used will be $f_{AD}/4$ (When $f(X_{in})$ is greater than 10 MHz, f_{AD} must be divided)
- Software conversion start

5.0 Reference

Renesas Technology Corporation Semiconductor Home Page

<http://www.renesas.com>

E-mail Support

support_apl@renesas.com

Data Sheets

- M16C/26 datasheets, M30262eds.pdf

User's Manual

- M16C/20/60 C Language Programming Manual, 6020c.pdf
- M16C/20/60 Software Manual, 6020software.pdf
- MSV30262-SKP or MSV-Mini26-SKP Quick start guide
- MSV30262-SKP or MSV-Mini26-SKP Users Manual
- MDECE30262 or MSV-Mini26-SKP Schematic

6.0 Software Code

The sample software provided was compiled using the KNC30 compiler. The program sets up the ADC to continuously perform conversions on channels 0 to 3. The code then repeatedly reads the results of those conversions. The example program was written to run on the MSV30262 Starter Kit but could be modified for a user application.

```
/*
*****
*      DESCRIPTION: repeat_sweep_mode_0.c
*
*      PURPOSE: Outlines how to use the M16C/26 ADC in repeat sweep
*      mode0. On reset, program repeatedly stores the result
*      of the conversion in a variable that can be examined
*      using KD30 or similar tool.
*****
#include "sfr26.h"
int TempStore0 = 0x0000;          // Location where ADC result is stored
int TempStore1 = 0x0000;          // Location where ADC result is stored

int TempStore2 = 0x0000;          // Location where ADC result is stored
int TempStore3 = 0x0000;          // Location where ADC result is stored

/*
```



```
_asm (" fset i" ) ;          // globally enable interrupts

adst = 1;                    // Start a conversion here

while (1){
    TempStore0= ad0 & 0x03ff;    // Mask off the upper 6 bits of the
                                // variable leaving only the result
                                // in the variable itself

    TempStore1= ad1 & 0x03ff;    // Mask off the upper 6 bits of the
                                // variable leaving only the result
                                // in the variable itself

    TempStore2= ad2 & 0x03ff;    // Mask off the upper 6 bits of the
                                // variable leaving only the result
                                // in the variable itself

    TempStore3= ad3 & 0x03ff;    // Mask off the upper 6 bits of the
                                // variable leaving only the result
                                // in the variable itself
}
}
```

Keep safety first in your circuit designs!

- Renesas Technology Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corporation product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corporation or a third party.
- Renesas Technology Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corporation by various means, including the Renesas Technology Corporation Semiconductor home page (<http://www.renesas.com>).
- When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- Renesas Technology Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- The prior written approval of Renesas Technology Corporation is necessary to reprint or reproduce in whole or in part these materials.
- If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- Please contact Renesas Technology Corporation for further details on these materials or the products contained therein.