

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

H8SX Series

Enhanced Addressing Mode (for Arrays)

Introduction

As well as having an architecture that is upward-compatible with each CPU of the H8/300, H8/300H, and H8S series, so as to inherit a full complement of peripheral functions, the H8SX microcomputer series has a maximum operating frequency of 50 MHz and uses a 32-bit H8SX core CPU as well as an on-chip multiplier/divider to improve performance.

This H8SX series Application Note provides information you may need during software and hardware design. This is a basic edition that provides operation examples that each use a single H8SX series on-chip peripheral function.

Although the operation of each program, circuit, and other aspects covered by this application note has been checked, make sure that you conduct your own operation checks before actually using the H8SX series.

Contents

1. Overview	2
2. Configuration.....	2
3. Sample Program	4

1. Overview

The H8SX series has an architecture that is upward-compatible with each CPU of the H8/300, H8/300H, and H8S series. Furthermore, in addition its instruction set has been enhanced to improve CPU performance. This enhancement of the instruction set has greatly improved code efficiency relative to the conventional series. This code efficiency leads to benefits such as a reduction in the ROM capacity required for storing programs and a reduction in each instruction fetch cycle. This application note describes the index register indirect with displacement, which is a new addressing mode that has been added as an enhanced instruction set item and which is particularly effective for array data processing.

2. Configuration

As an addressing mode similar to the index register indirect addressing mode with displacement, the H8SX series supports the register indirect addressing mode with displacement. The conventional H8S series also supports the register indirect addressing mode with displacement. The index register indirect addressing mode with displacement is a new addressing mode that is newly supported by the H8SX series. The following describes the difference between these two addressing modes. In the register indirect addressing mode with displacement, the value obtained by adding the displacement to the contents of the specified register (ERn only) is used as the effective address. In the index register indirect addressing mode with displacement, any of 8-, 16-, 32-bit registers (that is, RnL, Rn, and ERn) can be specified and the value obtained by adding the displacement to the contents of the specified registers that are zero-extended to 32 bits is used as the effective address. For this reason, the latter addressing mode allows more flexible addressing than the former and is better suited to a wider range of applications. Table 1 lists methods for calculating the effective address in each addressing mode. Figure 1 shows an example of accessing array data.

In the following description, a typical sort program that accesses array data is used as a sample to compare the H8SX series with the H8S series. The sample program is written in C. The results of comparing the aspects shown below are listed: Code generated by a compiler (assembler code), the instruction code length, and other items in the generated code.

Table 1 Method of Calculating the Effective Address in Each Addressing Mode

Addressing mode	Method of calculating the effective address	Effective address
Register indirect with displacement @(disp:16,ERn)		
Index register indirect with displacement @(disp:16,Rn.L.B)		
Index register indirect with displacement @(disp:16,Rn.W)		
Index register indirect with displacement @(disp:16,ERn.L)		

For a displacement of 16 bits





Figure 1 Example of Accessing Array Data

3. Sample Program

3.1 Flowchart

The sample program shown below is a very simple sort program, that will allow you to understand the descriptions of the index register indirect addressing mode with displacement, an enhanced instruction set item. For comparison with the H8S series, the results of compilation are shown. These results are only intended to be an example, because the instruction code length generated in the compilation of an application-level program greatly depends on the source program and the compile conditions. The flowchart that is shown below is for a sample program that performs a bubble sort.



3.2 Program Listing

A source program that is written in C is shown below.

```

/*****
/* include file
/*****
#include <machine.h>

/*****
/* function prototype
/*****
void bubble_sort( void );

/*****
/* array variable
/*****
#define N 100
signed short wArray[N];           // Assume that data to be
                                   // sorted is set here.

/*****
/* function definition
/*****
void bubble_sort( void )
{
    signed char  i, j;
    signed short temp;

    for(i=0; i<(N-1); i++)
    {
        for(j=(i+1); j<N; j++)
        {
            if(wArray[i]<wArray[j])
            {
                // Compares and swaps array elements.
                temp      = wArray[i];
                wArray[i] = wArray[j];
                wArray[j] = temp;
            }
        }
    }
}

```

3.3 Comparison of the H8S Series with the H8SX Series

The result of compilation (assembly code) with the H8S series is shown below.

SCT	OFFSET	LABEL	INSTRUCTION	OPERAND	COMMENT
P					; section
00000000		_bubble_sort:			; function
	00000000		STM.L	(ER4-ER6),@-SP	
	00000004		MOV.L	#_wArray,ER6	
	0000000A		SUB.B	R4H,R4H	
	0000000C	L71:			
	0000000C		MOV.B	R4H,R4L	
	0000000E		ADD.B	#1,R4L	
	00000010		MOV.B	R4H,R1L	
	00000012		EXTS.W	R1	
	00000014		EXTS.L	ER1	
	00000016		SHLL.L	ER1	
	00000018		ADD.L	ER6,ER1	
	0000001A		BRA	L73:8	
	0000001C	L72:			
	0000001C		MOV.B	R4L,R5L	
	0000001E		EXTS.W	R5	
	00000020		EXTS.L	ER5	
	00000022		SHLL.L	ER5	
	00000024		ADD.L	ER6,ER5	
	00000026		MOV.W	@ER1,R0	
	00000028		MOV.W	@ER5,E0	
	0000002A		CMP.W	E0,R0	
	0000002C		BGE	L74:8	
	0000002E		MOV.W	R0,E0	
	00000030		MOV.W	@ER5,R0	
	00000032		MOV.W	R0,@ER1	
	00000034		MOV.W	E0,@ER5	
	00000036	L74:			
	00000036		INC.B	R4L	
	00000038	L73:			
	00000038		CMP.B	#100,R4L	
	0000003A		BLT	L72:8	
	0000003C		INC.B	R4H	
	0000003E		CMP.B	#99,R4H	
	00000040		BLT	L71:8	
	00000042		LDM.L	@SP+,(ER4-ER6)	
	00000046		RTS		
B					; section
00000000		_wArray:			; static: wArray
00000000		.RES.W		100	

The result of compilation (assembly code) with the H8SX series is shown below.

SCT	OFFSET	LABEL	INSTRUCTION	OPERAND	COMMENT
P					; section
00000000		_bubble_sort:			; function
00000000			PUSH.L	ER2	

```

00000004      BRA/S      L8:8
00000006      MOV.B      #0:8,R0H
00000008 L9:
00000008      MOV.B      R0H,R0L
0000000A      INC.B      R0L
0000000C      MOV.B      R0H,R1L
0000000E      EXTS.L     #2,ER1
00000010      BRA/S      L10:8
00000012      MOV.L      ER1,ER2
00000014 L11:
00000014      MOV.W      @(_wArray:32,ER2.L),R1
0000001C      MOV.W      @(_wArray:32,R0L.B),E0
00000024      CMP.W      E0,R1
00000026      BGE      L13:8
00000028      MOV.W      E0,@(_wArray:32,ER2.L)
00000030      MOV.W      R1,@(_wArray:32,R0L.B)
00000038 L13:
00000038      INC.B      R0L
0000003A L10:
0000003A      CMP.B      #100:8,R0L
0000003C      BLT      L11:8
0000003E      INC.B      R0H
00000040 L8:
00000040      CMP.B      #99:8,R0H
00000042      BLT      L9:8
00000044      RTS/L      ER2
B
00000000      _wArray:      ; section
00000000      .RES.W      100      ; static: wArray

```

The following source code section performs comparison and swapping of array elements.

```

    if (wArray[i]<wArray[j])
    {
        // Compares and swaps array elements.
        temp      = wArray[i];
        wArray[i] = wArray[j];
        wArray[j] = temp;
    }

```

Table 2 lists the results of comparison of the H8S series and H8SX series about the assembly code in this section.

Table 2 Comparing the Results of Compilation

CPU	Assemble code	Instruction length		Execution time		
		In bytes	Total	In states	Total	
H8S series	L72:					
	MOV.B	R4L,R5L	2		1	
	EXTS.W	R5	2		1	
	EXTS.L	ER5	2		1	
	SHLL.L	ER5	2		1	
	ADD.L	ER6,ER5	2	26	1	18
	MOV.W	@ER1,R0	2		2	
	MOV.W	@ER5,E0	2		2	
	CMP.W	E0,R0	2		1	
	BGE	L74:8	2		2	
	MOV.W	R0,E0	2		1	
	MOV.W	@ER5,R0	2		1	
	MOV.W	R0,@ER1	2		2	
	MOV.W	E0,@ER5	2		2	
H8SX series	MOV.L	ER1,ER2	2		1	
	L11:					
	MOV.W	@(_wArray:32,ER2.L),R1	8		3	
	MOV.W	@(_wArray:32,R0L.B),E0	8	38	3	16
	CMP.W	E0,R1	2		1	
	BGE	L13:8	2		2	
	MOV.W	E0,@(_wArray:32,ER2.L)	8		3	
	MOV.W	R1,@(_wArray:32,R0L.B)	8		3	

Revision Record

Rev.	Date	Description	
		Page	Summary
1.00	Sept.19.03	—	First edition issued

Keep safety first in your circuit designs!

1. Renesas Technology Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corporation product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corporation or a third party.
2. Renesas Technology Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corporation by various means, including the Renesas Technology Corporation Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corporation is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corporation for further details on these materials or the products contained therein.