
JEDEC TRAY

Tray Code	RENESAS Code	Previous Code
L196-112A	PTLG0100KA-A	100F0M

Unit:mm



The pin1 is located in the hatching portion

Note: Numbers in parentheses are the numbers of Ics contained in five trays per inner box, and those without parentheses are the numbers of Ics contained in eight trays per inner box.

those without parentheses are the numbers of les contained in eight trays per limer box.				
Position dimension of cells (mm)	Z_{W}	8.825		
	Z_{L}	9.9		
	e _w	10.75		
	e_L	12.3		
Thickness (mm)	H ₁	7.62		
Number of cells	N _W	12		
	N _L	25		
Maximum storage No. IC/Tray		300		
Maximum storage No. IC/Inner box (Note)		2700(1500)		
Material		Carbon PPE		
Surface resistance		Less than $1x10^{11}\Omega/\Box$		
Heat resistant temperature		125°C24h		
Packing form		Dry pack		