

# RA4M1 Group

## Notes on RA4M1 Group High-Temperature Operation

### Introduction

Renesas provides RA4M1 Group microcontrollers that operate in high-temperature environments. These products are guaranteed to operate within the stipulated range. However, the reliability of a semiconductor device is influenced greatly by the environment in which it is used. That is, even for products with the same quality level, if one is operated in a more severe environment, its reliability will be reduced. Conversely, if one is used in a less severe environment, its reliability will increase. For example, a device used under extremely severe conditions, such as those used for lifetime testing, may exhibit wear-out failures, even if the environment is within the maximum ratings.

This application note presents notes on operating environments under which RA4M1 Group microcontrollers are used in high-temperature applications.

### Target Device

RA4M1 Group

### Contents

<b>1. Relationship between Actual Usage Environments for Renesas Synergy Microcontrollers and Reliability .....</b>	<b>2</b>
<b>1.1 Approaches to Microcontroller Reliability.....</b>	<b>2</b>
<b>1.2 Derating.....</b>	<b>2</b>
<b>2. Thermal Characteristics Term Definitions.....</b>	<b>3</b>
<b>3. Thermal Characteristics.....</b>	<b>5</b>
<b>3.1 RA4M1 Group thermal resistances .....</b>	<b>5</b>
<b>4. Derating Examples for Representative High-Temperature Applications.....</b>	<b>6</b>
<b>5. Reference Documents.....</b>	<b>エラー! ブックマークが定義されていません。</b>

## 1. Relationship between Actual Usage Environments for RA4M1 Group Microcontrollers and Reliability

### 1.1 Approaches to microcontroller reliability

We strongly recommend that customers follow the items described in this document to assure device reliability when using RA4M1 Group microcontrollers.

Semiconductor device reliability is indicated by the failure rate curve (bathtub curve). This curve is divided into three regions:

- The early failure region, in which failures occur at a relatively early time after device use (operation) is first started.
- The random failure period, during which, after the early failure period, failures occur randomly across the relatively long period during which the device is used,
- The wear-out failure period (end of service life), during which failures increase with the elapsing of the time that is inherent life of the device. (See the Reliability Handbook, Revision 2.50 (R51ZZ0001EJ0250) for further details on the bathtub curve.)

Of these regions, it is the wear-out failure region that is most strongly influenced by the thermal environment in which the semiconductor device is used. The concept of derating is critical to assuring that RA4M1 Group microcontrollers do not reach the wear-out failure region.

### 1.2 Derating

Derating is defined under JIS Z 8115 as the systematic reduction of load for the sake of improved reliability.


Derating is commonly applied to product groups, such as discreet components and power ICs, where concern is required regarding the junction temperature due to the relationship between the generated power, ambient temperature, and heat sink characteristics. Concern is required even if, in addition to the usage conditions having wide ranges, operation is within those usage conditions (for example, voltage) from the standpoint of the problem of heat generation, and, furthermore, adjustment is required between usage conditions such as ambient temperature, junction temperature, current, and power, which have mutual relationships.

See section 5.2.3, Derating, in the Reliability Handbook, Revision 2.50 (R51ZZ0001EJ0250) for further details on derating.


This application note presents temperature profiles expected for representative high-temperature applications and derating examples that RA4M1 Group microcontrollers can support.

**2. Thermal Characteristics Term Definitions**

- Ta (ambient temperature): Ta is the temperature at a place that is not affected by heat sources and is based on measurement methods stipulated by JEDEC (figure 2-1 and figure 2-2). See the EIA/JEDEC Standard 51-2 for details. Also see the product and package information that Renesas provides on its website.



**Figure 2-1 Ta measurement position (from the EIA/JEDEC 51-2 Standard)**



**Figure 2-2 Ta measurement position - bird's Eye View (no chassis)  
(from the EIA/JEDEC 51-2 Standard)**

The mounting board is a 76.2 x 114.3 x 1.6 mm 4-layer board. See the EIA/JEDEC Standard 51-7 for details.

### 3. Thermal Characteristics

#### 3.1 RA4M1 Group thermal resistances

RA4M1 Group supports T<sub>jmax</sub> as 112°C. Enclosure environment and printed wiring board (PWB) environment are as described in

Table 3.1.

For additional details, refer to the following URL:

<https://www.renesas.com/us/en/support/technical-resources/packaging/characteristic/heat-dissipation.html>

**Table 3.1 RA4M1 Group thermal resistances**

Package	Enclosure Environment	PWB Environment	$\theta_{ja}$ [°C/W]
100-pin LQFP PLQP0100KB-B	304.8*304.8*304.8mm (JE5D51-2 compliant)	4 layers (JE5D 51-7 compliant)	45.2
64-pin LQFP PLQP0064KB-C	304.8*304.8*304.8mm (JE5D51-2 compliant)	4 layers (JE5D 51-7 compliant)	44.6
48-pin LQFP PLQP0048KB-B	304.8*304.8*304.8mm (JE5D51-2 compliant)	4 layers (JE5D 51-7 compliant)	52.2
64-pin QFN PWQN0064LA-A	304.8*304.8*304.8mm (JE5D51-2 compliant)	4 layers (JE5D 51-7 compliant)	26.1
48-pin QFN PWQN0048KB-A	304.8*304.8*304.8mm (JE5D51-2 compliant)	4 layers (JE5D 51-7 compliant)	28.0
40-pin QFN PWQN0040KC-A	304.8*304.8*304.8mm (JE5D51-2 compliant)	4 layers (JE5D 51-7 compliant)	30.7

#### 4. Derating Examples for Representative High-Temperature Applications

Table 4.1 lists temperature profiles expected for representative high-temperature applications and recommended temperature profiles for derating.

The corresponding packages are the LQFP 100, 64, 48-pin packages, HWQFN 64,48,40-pin packages. And the package codes are PLQP0100KB-A, PLQP0064KB-C, PLQP0048KB-B, PWQN0064LA-A, PWQN0048KB-A, and PWQN0040KC-A/. Table 4.2 lists the specific corresponding products.

The customer should select the example that is the most similar to the intended application. Contact your Renesas representative if none of these examples are applicable. Except for No.5, derating assumes a 10-year life time.

The recommended temperature profile is calculated based on the total power dissipation and the thermal resistance ( $\Theta_{ja}$ ) determined from the thermal characteristics definitions assumed for the environment described in section 2 and section 3. For example, if  $T_j=112^\circ\text{C}$  in No.1, then the total power dissipation for LQFP 48-pin devices will be around 130 mW or lower, users should use these products while maintaining either the thermal resistance assumed in section 3, section 4 or environment with an even lower thermal resistance.

Table 4.1 Representative High-Temperature Applications

No.	Main Applications	Assumed Temperature Profile	Recommended Temperature Profile for Derating
1	Cooking equipment (kitchen stoves, IH heaters)	An operating time of 3 hours/day in a high-temperature environment. Standby or stopped at other times.	$T_j \leq 112^\circ\text{C}$ for 3 hours/day. At other times, standby or stopped at $T_j \leq 97^\circ\text{C}$
2	Appliance motors, power tools	Used for 3 hours/day in a high-temperature environment. Used for 3 hours/day in a non-high-temperature environment. Standby or stopped at other times.	$102^\circ\text{C} < T_j \leq 112^\circ\text{C}$ for 3 hours/day. $T_j \leq 102^\circ\text{C}$ for 3 hours/day. At other times, standby or stopped at $T_j \leq 97^\circ\text{C}$
3	EV chargers	Used for 8 hours/day in a high-temperature environment. Standby or stopped at other times.	$102^\circ\text{C} < T_j \leq 112^\circ\text{C}$ for 4 hours/day. $T_j \leq 102^\circ\text{C}$ for 4 hours/day. At other times, standby or stopped at $T_j \leq 92^\circ\text{C}$
4	Smart meters, power converters, and equipment that may be installed outdoors (24-hour operation)	Used for 4 hours/day in a high-temperature environment. Used for 4 hours/day in a non-high-temperature environment. Also operating at other times.	$102^\circ\text{C} < T_j \leq 112^\circ\text{C}$ for 4 hours/day. $\leq T_j \leq 102^\circ\text{C}$ for 4 hours/day. At other times, operating at $T_j \leq 87^\circ\text{C}$
5	PC and server power supplies (24-hour operation)	Used continuously for 5 years in an environment that includes high-temperature periods.	$102^\circ\text{C} < T_j \leq 112^\circ\text{C}$ 15,000 hours $T_j \leq 102^\circ\text{C}$ 30,000 hours
6	Industrial motors (24-hour operation: example 1)	Used continuously in a high-temperature environment.	$89^\circ\text{C} < T_j \leq 99^\circ\text{C}$ 80% $T_j \leq 89^\circ\text{C}$ 20%
7	Industrial motors (24-hour operation: example 2)	Used continuously in an environment that includes extreme high-temperature periods.	$97^\circ\text{C} < T_j \leq 112^\circ\text{C}$ 5% $92^\circ\text{C} < T_j \leq 97^\circ\text{C}$ 75% $T_j \leq 92^\circ\text{C}$ 20%

Note: The ambient temperature ( $T_a$ ) should be between  $-40^\circ\text{C}$  and  $105^\circ\text{C}$ .

**Table 4.2 Corresponding Products**

Product	Package	Code flash	Data flash	SRAM
R7FA4M1AB3CFP	PLQP0100KB-B	256KB	8KB	32KB
R7FA4M1AB3CFM	PLQP0064KB-C			
R7FA4M1AB3CNB	PWQN0064LA-A			
R7FA4M1AB3CFL	PLQP0048KB-B			
R7FA4M1AB3CNE	PWQN0048KB-A			
R7FA4M1AB3CNF	PWQN0040KC-A			

## 5. Reference Documents

Semiconductor Reliability Handbook Rev. 2.50 (R51ZZ0001EJ0250), January 2017

## Revision History

Rev.	Date	Description	
		Page	Summary
1.00	Jul.10.23	All	First edition issued.



## General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

### 1. Handling of Unused Pins

Handle unused pins in accordance with the directions given under Handling of Unused Pins in the manual.

- The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.

### 2. Processing at Power-on

The state of the product is undefined at the moment when power is supplied.

- The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.

In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed.

In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.

### 3. Prohibition of Access to Reserved Addresses

Access to reserved addresses is prohibited.

- The reserved addresses are provided for the possible future expansion of functions. Do not access these addresses; the correct operation of LSI is not guaranteed if they are accessed.

### 4. Clock Signals

After applying a reset, only release the reset line after the operating clock signal has become stable. When switching the clock signal during program execution, wait until the target clock signal has stabilized.

- When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.

### 5. Differences between Products

Before changing from one product to another, i.e. to a product with a different part number, confirm that the change will not lead to problems.

- The characteristics of Microprocessing unit or Microcontroller unit products in the same group but having a different part number may differ in terms of the internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

## Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.  
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.  
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.  
Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.
6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



### SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

#### **Renesas Electronics America Inc.**

2801 Scott Boulevard Santa Clara, CA 95050-2549, U.S.A.  
Tel: +1-408-588-6000, Fax: +1-408-588-6130

#### **Renesas Electronics Canada Limited**

9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3  
Tel: +1-905-237-2004

#### **Renesas Electronics Europe Limited**

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.  
Tel: +44-1628-585-100, Fax: +44-1628-585-900

#### **Renesas Electronics Europe GmbH**

Arcadiastrasse 10, 40472 Düsseldorf, Germany  
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

#### **Renesas Electronics (China) Co., Ltd.**

Room 1709, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100191, P.R.China  
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

#### **Renesas Electronics (Shanghai) Co., Ltd.**

Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, P. R. China 200333  
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

#### **Renesas Electronics Hong Kong Limited**

Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong  
Tel: +852-2265-6688, Fax: +852 2886-9022

#### **Renesas Electronics Taiwan Co., Ltd.**

13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan  
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

#### **Renesas Electronics Singapore Pte. Ltd.**

80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949  
Tel: +65-6213-0200, Fax: +65-6213-0300

#### **Renesas Electronics Malaysia Sdn.Bhd.**

Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia  
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

#### **Renesas Electronics India Pvt. Ltd.**

No.777C, 100 Feet Road, HALII Stage, Indiranagar, Bangalore, India  
Tel: +91-80-67208700, Fax: +91-80-67208777

#### **Renesas Electronics Korea Co., Ltd.**

12F., 234 Teheran-ro, Gangnam-Gu, Seoul, 135-080, Korea  
Tel: +82-2-558-3737, Fax: +82-2-558-5141