Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)
Send any inquiries to http://www.renesas.com/inquiry.





Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights
 of third parties by or arising from the use of Renesas Electronics products or technical information described in this document.
 No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights
 of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.

"Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.

- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



SILICON TRANSISTOR 2SC4569

UHF TV TUNER OSC/MIXER NPN SILICON EPITAXIAL TRANSISTOR

DESCRIPTION


The 2SC4569 is an NPN silicon epitaxial transistro intended for use as UHF oscillator and UHF mixer in a tuner of TV receiver.

FEATURES

- · High gain bandwidty product $f_T = 5.0 \text{ GHz TYP}.$
- · Low output capacitance $C_{ob} = 0.9 pF TYP.$
- · Surface mount package EIAJ: SC-59

ABSOLUTE MAXIMUM RATINGS (TA = 25 °C)

Maximum Voltages and Current Collector to Base Voltage **V**сво 20 12 Collector to Emitter Voltage VCEO Emitter to Base Voltage VFRO 3.0 Collector Current 60 lс mΑ PT **Total Power Dissipation** 150 mW °C Junction Temperature Ŧj 125 -55 to +125 Storage Temperature Tstg °C



ELECTRICAL CHARACTERISTICS (TA = 25 °C)

CHARACTERISTIC	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITIONS		
Collector Cutoff Current	Ісво			0.1	μΑ	V _{CB} = 15 V, I _E = 0		
Emitter Cutoff Current	ІЕВО			0.1	μΑ	V _{EB} = 1 V, I _C = 0		
Collector Saturation Voltage	V _{CE(sat)}			0.5	V	her = 10, Ic = 5 mA		
DC Current Gain	hfe	40	100	200		VcE = 5 V, Ic = 5 mA *1		
Gain Bandwidth Product	f⊤		5.0		GHz	V _{CE} = 5 V, I _C = 5 mA f = 1.0 GHz		
Output Capacitance	Cob		0.9	1.2	pF	V _{CB} = 5 V, I _E = 0, f = 1.0 MHz		
Insertion Gain	S _{21e} ²	5.0			dB	V _{CE} = 5 V, I _C = 5 mA, f = 1.0 MHz		

^{*1} Pulsd: PW \leq 35 μ S, Dyty Cycle \leq 2 %

hre Classification

Class	T75/EB *	T76/FB *	T77/GB *
Marking	T75	T76	T77
hfE	40 to 80	60 to 120	100 to 200


^{*} Old Specification / New Specification


The information in this document is subject to change without notice. Before using this document, please confirm that


this is the latest version.

Not all devices/types available in every country. Please check with local NEC Compound Semiconductor Devices representative for availability and additional information.

TYPICAL CHARACTERISTICS (TA = 25 °C)









S-PARAMETER

Vce = 5 V, Ic = 1	I mA							
FREQUENCY		S ₁₁	9	S ₂₁	S	12		S ₂₂
MHz	MAG	ANG	MAG	ANG	MAG	ANG	MAG	ANG
100.00	0.958	-18.7	3.299	164.6	0.038	77.8	0.973	-7.8
200.00	0.917	-36.4	3.151	150.4	0.072	68.2	0.944	-14.5
300.00	0.855	-53.0	2.926	137.5	0.100	59.7	0.899	-20.6
400.00	0.799	-67.5	2.685	126.2	0.118	51.7	0.850	-25.9
500.00	0.739	-81.5	2.462	116.1	0.134	45.8	0.806	-29.7
600.00	0.693	-93.5	2.256	107.3	0.142	41.1	0.778	-33.0
700.00	0.647	-104.2	2.072	99.9	0.148	37.6	0.743	-35.9
800.00	0.607	-113.9	1.889	92.4	0.152	35.2	0.716	-39.0
900.00	0.583	-123.7	1.760	86.5	0.154	33.4	0.702	-40.6
1000.00	0.559	-132.5	1.615	79.8	0.155	31.7	0.688	-43.4
VcE = 5 V, Ic = 3	3 mA							
FREQUENCY		S ₁₁	Ş	S ₂₁	S	12		S ₂₂
MHz	MAG	ANG	MAG	ANG	MAG	ANG	MAG	ANG
100.00	0.860	-29.5	9.203	156.2	0.035	74.7	0.932	-14.9
200.00	0.754	-55.1	7.982	137.3	0.062	61.5	0.826	-25.6
300.00	0.648	-75.6	6.693	122.6	0.078	55.1	0.723	-32.3
400.00	0.562	-91.9	5.623	111.9	0.090	51.0	0.641	-36.7
500.00	0.506	-106.5	4.796	103.1	0.099	48.9	0.583	-39.1
600.00	0.462	-118.1	4.188	95.9	0.106	48.2	0.547	-41.0
700.00	0.429	-127.8	3.695	90.3	0.112	48.7	0.514	-42.2
800.00	0.400	-137.4	3.278	84.5	0.119	48.1	0.492	-44.3
900.00	0.390	-144.7	2.984	79.9	0.127	49.2	0.478	-45.2
1000.00	0.378	-153.3	2.711	75.0	0.133	49.8	0.467	-47.2
VcE = 5 V, Ic = 5	5 mA							
FREQUENCY		S ₁₁		S ₂₁	S	12		S ₂₂
MHz	MAG	ANG	MAG	ANG	MAG	ANG	MAG	ANG
100.00	0.769	-38.2	13.666	149.3	0.032	70.4	0.885	-20.1
200.00	0.630	-68.1	10.889	128.6	0.054	60.9	0.728	-32.1
300.00	0.513	-89.7	8.545	114.5	0.067	55.6	0.606	-37.7
400.00	0.442	-106.3	6.888	104.9	0.076	54.2	0.528	-40.6
500.00	0.399	-120.6	5.752	97.1	0.086	54.8	0.495	-42.0
600.00	0.368	-131.7	4.940	91.0	0.094	54.5	0.446	-42.9
700.00	0.345	-140.4	4.300	86.2	0.104	55.8	0.420	-43.9
800.00	0.329	-149.4	3.801	81.3	0.113	56.3	0.401	-45.3
900.00	0.323	-156.7	3.434	77.3	0.123	56.7	0.390	-45.8
1000.00	0.316	-163.7	3.112	72.8	0.133	56.8	0.384	-47.4
	0.0.0						0.001	

V _{CE} = 5 V, I _C = 7 mA								
FREQUENCY	;	S ₁₁	(S ₂₁	S	12	S	S22
MHz	MAG	ANG	MAG	ANG	MAG	ANG	MAG	ANG
100.00	0.698	-45.4	17.070	144.7	0.031	68.1	0.839	-24.3
200.00	0.540	-45.4 -77.6	12.682	122.8	0.031	58.9	0.655	-24.3 -35.9
300.00		-77.0 -99.9	9.583	109.5		58.2	0.533	
	0.435				0.061			-40.4
400.00	0.372	-116.7	7.566	100.8	0.071	58.1	0.461	-43.1
500.00	0.343	-129.7	6.238	93.8	0.080	59.3	0.415	-42.9
600.00	0.321	-139.8	5.324	88.4	0.090	59.9	0.390	-43.1
700.00	0.306	-148.4	4.613	84.0	0.100	60.7	0.370	-44.0
800.00	0.297	-157.5	4.066	79.4	0.113	60.7	0.354	-45.3
900.00	0.291	-162.9	3.669	75.7	0.124	61.2	0.344	-45.7
1000.00	0.286	-170.4	3.319	71.6	0.135	61.0	0.340	-47.6
Vce = 5 V, Ic = 9 mA								
FREQUENCY	;	S ₁₁	(S ₂₁	S	12	S	S ₂₂
MHz	MAG	ANG	MAG	ANG	MAG	ANG	MAG	ANG
100.00	0.629	-51.3	19.656	140.7	0.029	66.7	0.800	-27.2
200.00	0.474	-85.3	13.850	118.7	0.045	61.4	0.598	-38.3
300.00	0.381	-107.7	10.219	106.2	0.056	59.8	0.481	-41.5
400.00	0.334	-123.4	7.978	98.1	0.067	61.1	0.170	-42.4
500.00	0.310	-137.2	6.530	91.8	0.079	61.8	0.375	-43.0
600.00	0.295	-146.9	5.550	86.7	0.089	63.4	0.356	-43.0
700.00	0.286	-154.5	4.805	82.5	0.101	63.6	0.339	-43.4
800.00	0.274	-162.4	4.228	78.3	0.112	63.5	0.325	-44.8
900.00	0.275	-168.2	3.793	74.8	0.125	63.7	0.317	-45.5
1000.00	0.274	-175.1	3.442	71.0	0.136	63.2	0.310	-47.2

- The information in this document is current as of October, 2001. The information is subject to
 change without notice. For actual design-in, refer to the latest publications of NEC's data sheets or
 data books, etc., for the most up-to-date specifications of NEC semiconductor products. Not all
 products and/or types are available in every country. Please check with an NEC sales representative
 for availability and additional information.
- No part of this document may be copied or reproduced in any form or by any means without prior written consent of NEC. NEC assumes no responsibility for any errors that may appear in this document.
- NEC does not assume any liability for infringement of patents, copyrights or other intellectual property rights of
 third parties by or arising from the use of NEC semiconductor products listed in this document or any other
 liability arising from the use of such products. No license, express, implied or otherwise, is granted under any
 patents, copyrights or other intellectual property rights of NEC or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of customer's equipment shall be done under the full responsibility of customer. NEC assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC endeavours to enhance the quality, reliability and safety of NEC semiconductor products, customers
 agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize
 risks of damage to property or injury (including death) to persons arising from defects in NEC
 semiconductor products, customers must incorporate sufficient safety measures in their design, such as
 redundancy, fire-containment, and anti-failure features.
- NEC semiconductor products are classified into the following three quality grades:
 - "Standard", "Special" and "Specific". The "Specific" quality grade applies only to semiconductor products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of a semiconductor product depend on its quality grade, as indicated below. Customers must check the quality grade of each semiconductor product before using it in a particular application.
 - "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots
 - "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)
 - "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC semiconductor products is "Standard" unless otherwise expressly specified in NEC's data sheets or data books, etc. If customers wish to use NEC semiconductor products in applications not intended by NEC, they must contact an NEC sales representative in advance to determine NEC's willingness to support a given application.

(Note)

- (1) "NEC" as used in this statement means NEC Corporation, NEC Compound Semiconductor Devices, Ltd. and also includes its majority-owned subsidiaries.
- (2) "NEC semiconductor products" means any semiconductor product developed or manufactured by or for NEC (as defined above).

M8E 00.4-0110



▶Business issue

NEC Compound Semiconductor Devices, Ltd.

5th Sales Group, Sales Division TEL: +81-3-3798-6372 FAX: +81-3-3798-6783 E-mail: salesinfo@csd-nec.com

NEC Compound Semiconductor Devices Hong Kong Limited

Hong Kong Head Office TEL: +852-3107-7303 FAX: +852-3107-7309
Taipei Branch Office TEL: +886-2-8712-0478 FAX: +886-2-2545-3859
Korea Branch Office TEL: +82-2-528-0301 FAX: +82-2-528-0302

NEC Electron Devices European Operations http://www.nec.de/

TEL: +49-211-6503-101 FAX: +49-211-6503-487

California Eastern Laboratories, Inc. http://www.cel.com/

TEL: +1-408-988-3500 FAX: +1-408-988-0279

▶ Technical issue

NEC Compound Semiconductor Devices, Ltd. http://www.csd-nec.com/

Sales Engineering Group, Sales Division

E-mail: techinfo@csd-nec.com FAX: +81-44-435-1918