

PTX100R/105R antenna matching simulations for IoT applications using QucsStudio

Panthronics AG

Exported on 05/15/2023



Table of Contents

No headings included in this document

QucsStudio is a free and powerful circuit simulator and can be used to simulate and optimize the matching network for the PTX100R/PTX105R.

This is the link <http://dd6um.darc.de/QucsStudio/download.html> to download the SW.

After the SW installation double click on the icon qucs.exe

Organise	New	Open	Select
Simulations > QUCSStudio > QucsStudio-2.5.7 > QucsStudio > bin			
Search bi			
Name	Date modified	Type	Size
admsXml.exe	16/09/2016 11:49	Application	542 KB
ghdl.exe	09/03/2016 18:30	Application	2,272 KB
history5.dll	12/11/2006 16:51	Application exten...	21 KB
iverilog.exe	13/12/2007 21:54	Application	37 KB
msvc100.dll	11/06/2011 03:58	Application exten...	412 KB
msvcr100.dll	11/06/2011 03:58	Application exten...	756 KB
QtCore4.dll	25/07/2015 12:38	Application exten...	2,539 KB
QtGui4.dll	20/04/2014 03:43	Application exten...	8,386 KB
QtNetwork4.dll	20/04/2014 03:38	Application exten...	1,029 KB
qucs.exe	31/05/2018 20:18	Application	2,932 KB
qucs_de.qm	31/05/2018 20:12	QM File	593 KB
qucsattenuator.exe	31/05/2018 20:18	Application	113 KB
qucscomp.exe	31/05/2018 20:18	Application	249 KB
qucsconv.exe	31/05/2018 20:09	Application	445 KB
qucsdev.exe	31/05/2018 20:18	Application	82 KB
qucsfilter.exe	31/05/2018 20:19	Application	339 KB
qucs-help.exe	31/05/2018 20:11	Application	106 KB
qucssim.exe	31/05/2018 20:11	Application	433 KB


Download the file corresponding to the device you are using, save it and open it.

PTX100R Simulation file.


[PTX100R_Eval_1v4_SP.sch](#)


PTX105R Simulation file.

[PTX105R_Eval_1v0_SP.sch](#)



Hit the button simulate and the result should be like in the picture below





The simulation performed is an S-parameter simulation where the port is applied to the driver input. The driver resistance and the internal series capacitors are fixed the antenna electrical characteristics are measured as described in the [PTX100R/105R antenna matching guidelines for IoT applications](#). In order to match the antenna, the serial and parallel capacitors (Cs, Cp) need to be tuned, and an Optimizer has been set to quickly find the correct values for the components. The optimized value is related to the desired matching impedance selected that is dependent on the system. The example proposed reflects the matching from the PTX100R, PTX105R, and the PTX130R Eval Board.

In the two tables is displayed info on the antenna matching impedance (Z) and the optimized values for Cp and Cs (Cp_opt Cs_opt).

number	L_ANT	RP_ANT	ANT_SR	CP_ANT	Q_ANT
1	6.304e-07	3.47e+03	7.77e+07	6.66e-12	64.6

number	Z	Zreal	Zimag	Cp.opt	Cs.opt
1	7.2-j1.71e-11	7.2	-1.71e-11	1.18e-10	5.67e-10



The target matching impedance can be set by entering a value in the field **Z_goal_R**. The imaginary part and the target frequency can stay the same.

```
equation
Antenna_values
RS_ANT=0.832
XS_ANT=53.71
ANT_SR=77.7e6
Rp=1320
Export=yes
```

The equation containing the antenna electrical characteristics is the one filled with the value measured with a VNA, in this page [PTX10xR Eval-Board antenna and matching](#) an extract of the antenna of the Eval Board.

Every time new data is entered in this field a new simulation needs to be performed. The values for Cp and Cs simulated to represent a starting point for the matching network, a fine-tuning could be required in the real device. The q-factor measurement performed with the Config Tool can guide in the fine-tuning. An accurate antenna measurement will help to speed up the matching process.

```
equation
Goal
Z_goal_R=7.2
Z_goal_I=0
Target_Freq=13.56e6
```

The material herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner. Devices sold by Panthronics AG are covered by the warranty and patent indemnification provisions appearing in its General Terms of Trade. Panthronics AG makes no warranty, express, statutory, implied, or by description regarding the information set forth herein. Panthronics AG reserves the right to change specifications and prices at any time and without notice. Therefore, prior to designing this product into a system, it is necessary to check with Panthronics AG for the most up to date information. Applications requiring extended temperature range, unusual environmental requirements, or high reliability applications, such as military, medical life-support or life-sustaining equipment are not recommended. This product is provided by Panthronics AG “AS IS” and any express or implied warranties, including, but not limited to the implied warranties of merchantability and fitness for a particular purpose are disclaimed. Panthronics AG shall not be liable to recipient or any third party for any damages, including but not limited to personal injury, property damage, loss of profits, loss of use, interruption of business or indirect, special, incidental or consequential damages, of any kind, in connection with or arising out of the furnishing, performance or use of the technical data herein.

Legal Notice - Purchase of Panthronics ICs with MIFARE Classic® compatibility:

PTX100R IC offers modes to be compatible with MIFARE Classic® RFID tags, allowing to build MIFARE Classic® compatible reader systems. MIFARE® and MIFARE Classic® are trademarks of NXP B.V., High Tech Campus 60 NL-5656 AG EINDHOVEN, NL. Purchase of Panthronics' MIFARE Classic® compatible products does not provide a license of any NXP rights, in particular does not provide the right to use MIFARE® or MIFARE Classic® as a trademark to brand such systems.

Copyright Panthronics AG, Sternäckerweg 16, 8041, Graz

Ordering and Contact Information



Headquarters

Panthronics AG
Sternaeckerweg 16
A-8041, GRAZ
AUSTRIA

office@panthronics.com

Phone: +43 316 269 259

www.panthronics.com