

Description

The 5PB1104 is a high-performance LVCMOS clock buffer. It has an additive phase jitter of 50fs RMS.

The 5PB1104 also supports a synchronous glitch-free output enable (OE) function to eliminate any potential intermediate incorrect output clock cycles when enabling or disabling outputs. It can operate from a 1.8V to 3.3V supply.


Typical Applications

- Automotive applications

Features

- High-performance 1:4 LVCMOS clock buffer
- Very low pin-to-pin skew: < 50ps
- Very low additive jitter: < 50fs
- Supply voltage: 1.8V to 3.3V
- 3.3V tolerant input clock
- $f_{MAX} = 200\text{MHz}$
- Integrated serial termination for 50Ω channel
- 2.0 × 2.0 mm 8-VFQFN package
- AEC-Q100 Grade 1 (-40°C to +125°C) and Grade 2 (-40°C to +105°C)

Block Diagram



Pin Assignments

Figure 1. Pin Assignments for 2.0 × 2.0 mm 8-VFQFN Package – Top View

CLKIN	1	8	Y1
1G	2	7	Y3
Y0	3	6	VDD
GND	4	5	Y2

5PB1104

Pin Descriptions

Table 1. Pin Descriptions

Number	Name	Type	Description
1	CLKIN	Input	LVC MOS clock input.
2	1G	Input	Clock output enable.
3	Y0	Output	LVC MOS clock output.
4	GND	Power	Connect to ground.
5	Y2	Output	LVC MOS clock output.
6	V _{DD}	Power	1.8V to 3.3V power supply.
7	Y3	Output	LVC MOS clock output.
8	Y1	Output	LVC MOS clock output.

Output Logic Table

Inputs		Output
CLKIN	1G	Yn
X	L	L
L	H	L
H	H	H

After at least three cycles of input clock toggling, Output Enable function is asynchronous to eliminate any intermediate incorrect output clock cycles during transition which may cause frequency peaking to the downstream device.

Absolute Maximum Ratings

The absolute maximum ratings are stress ratings only. Stresses greater than those listed below can cause permanent damage to the device. Functional operation of the 5PB1104 at absolute maximum ratings is not implied. Exposure to absolute maximum rating conditions may affect device reliability.

Table 2. Absolute Maximum Ratings

Item	Rating
Supply Voltage, V_{DD}	3.8V
Output Enable and All Outputs	-0.4 V to $V_{DD} + 0.5$ V
Input Voltage, CLKIN	-0.4 V to 3.465V
Ambient Operating Temperature (Grade 1)	-40 to +125°C
Ambient Operating Temperature (Grade 2)	-40 to +105°C
Storage Temperature	-65 to +150°C
Junction Temperature	125°C
Soldering Temperature	260°C

Thermal Characteristics

Table 3. Thermal Characteristics

Symbol	Parameter	Value	Units
θ_{JA}	Still air.	120.2	°C/W
θ_{JB}	Still air.	63.3	°C/W
θ_{JC}	Still air.	99.4	°C/W

Recommended Operating Conditions

Table 4. Recommended Operating Conditions

Parameter	Minimum	Typical	Maximum	Units
Ambient Operating Temperature (Grade 1)	-40		+125	°C
Ambient Operating Temperature (Grade 2)	-40		+105	°C
Power Supply Voltage (measured in respect to GND)	+1.71		+3.465	V

DC Electrical Characteristics

$V_{DD} = 1.8V, 2.5V, \text{ or } 3.3V$ (see tables below). $T_A = -40^\circ\text{C to } 125^\circ\text{C}$ unless stated otherwise.

Table 5. DC Electrical Characteristics – $V_{DD} = 1.8V \pm 5\%$

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
V_{DD}	Operating Voltage		1.71	1.8	1.89	V
V_{IH}	Input High Voltage, CLKIN ^[1]		$0.7 \times V_{DD}$			V
V_{IL}	Input Low Voltage, CLKIN ^[1]				$0.3 \times V_{DD}$	V
V_{IH}	Input High Voltage, 1G		1.6		V_{DD}	V
V_{IL}	Input Low Voltage, 1G				0.6	V
V_{OH}	Output High Voltage	$I_{OH} = -5\text{mA}$.	1.2			V
V_{OL}	Output Low Voltage	$I_{OL} = 5\text{mA}$.			0.45	V
Z_O	Nominal Output Impedance			50		Ω
C_{IN}	Input Capacitance	CLKIN, 1G pin.		5		pF
I_{DD}	Operating Supply Current	0.001MHz, $C_L = 5\text{pF}$.		0.7	1	mA
		0.008MHz, $C_L = 5\text{pF}$.		0.7	1	mA
		40MHz, $C_L = 5\text{pF}$.		11	13	mA
		100MHz, $C_L = 5\text{pF}$.		25	30	mA
		156.25MHz, $C_L = 5\text{pF}$.		37	47	mA
		200MHz, $C_L = 5\text{pF}$.		39	57	mA

¹ Nominal switching threshold is $V_{DD}/2$.

Table 6. DC Electrical Characteristics – $V_{DD} = 2.5V \pm 5\%$

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
V_{DD}	Operating Voltage		2.375	2.5	2.625	V
V_{IH}	Input High Voltage, CLKIN ^[1]		$0.7 \times V_{DD}$			V
V_{IL}	Input Low Voltage, CLKIN ^[1]				$0.3 \times V_{DD}$	V
V_{IH}	Input High Voltage, 1G		1.8		V_{DD}	V
V_{IL}	Input Low Voltage, 1G				0.7	V
V_{OH}	Output High Voltage	$I_{OH} = -8\text{mA}$.	1.6			V
V_{OL}	Output Low Voltage	$I_{OL} = 8\text{mA}$.			0.625	V
Z_O	Nominal Output Impedance			50		Ω
C_{IN}	Input Capacitance	CLKIN, 1G pin.		5		pF

Table 6. DC Electrical Characteristics – $V_{DD} = 2.5V \pm 5\%$ (Cont.)

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
I_{DD}	Operating Supply Current	0.001MHz, $C_L = 5pF$.		0.9	1.3	mA
		0.008MHz, $C_L = 5pF$.		0.9	1.3	mA
		40MHz, $C_L = 5pF$.		15	17	mA
		100MHz, $C_L = 5pF$.		35	42	mA
		156.25MHz, $C_L = 5pF$.		52	67	mA
		200MHz, $C_L = 5pF$.		56	80	mA

¹ Nominal switching threshold is $V_{DD}/2$.

 Table 7. DC Electrical Characteristics – $V_{DD} = 3.3V \pm 5\%$

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
V_{DD}	Operating Voltage		3.135	3.3	3.465	V
V_{IH}	Input High Voltage, CLKIN ^[1]		$0.7 \times V_{DD}$			V
V_{IL}	Input Low Voltage, CLKIN ^[1]				$0.3 \times V_{DD}$	V
V_{IH}	Input High Voltage, 1G		2		V_{DD}	V
V_{IL}	Input Low Voltage, 1G				0.8	V
V_{OH}	Output High Voltage	$I_{OH} = -12mA$.	2.1			V
V_{OL}	Output Low Voltage	$I_{OL} = 12mA$.			0.825	V
Z_O	Nominal Output Impedance			50		Ω
C_{IN}	Input Capacitance	CLKIN, 1G pin.		5		pF
I_{DD}	Operating Supply Current	0.001MHz, $C_L = 5pF$.		1.2	1.7	mA
		0.008MHz, $C_L = 5pF$.		1.2	1.7	mA
		40MHz, $C_L = 5pF$.		19	22	mA
		100MHz, $C_L = 5pF$.		45	54	mA
		156.25MHz, $C_L = 5pF$.		67	87	mA
		200MHz, $C_L = 5pF$.		75	107	mA

¹ Nominal switching threshold is $V_{DD}/2$.

AC Electrical Characteristics

$V_{DD} = 1.8V, 2.5V, \text{ or } 3.3V$ (see tables below). $T_A = -40^\circ C$ to $125^\circ C$ unless stated otherwise.

Table 8. AC Electrical Characteristics – $V_{DD} = 1.8V \pm 5\%$

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
	Input Frequency		0		200	MHz
t_{OR}	Output Rise Time (5pF load)	0.36V to 1.44V, $C_L = 5pF$.		0.65	1.2	ns
t_{OF}	Output Fall Time (5pF load)	1.44V to 0.36V, $C_L = 5pF$.		0.65	1.2	ns
$t_{START-UP}$	Start-up Time	Part start-up time for valid outputs after V_{DD} ramp-up.			3	ms
	Propagation Delay ^[1]		1.6	2.3	3.4	ns
	Buffer Additive Phase Jitter, RMS	156.25MHz, Integration Range: 12kHz–20MHz.			0.06	ps
	Output to Output Skew	Rising edges at $V_{DD}/2$ ^[2]		35	50	ps
	Device to Device Skew	Rising edges at $V_{DD}/2$.			200	ps
t_{EN}	Output Enable Time	$C_L \leq 5pF$.			3	cycles
t_{DIS}	Output Disable Time	$C_L \leq 5pF$.			3	cycles
t_{DC}	Duty Cycle ^[3]			50		%

Table 9. AC Electrical Characteristics – $V_{DD} = 2.5V \pm 5\%$

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
	Input Frequency		0		200	MHz
t_{OR}	Output Rise Time (5pF load)	0.5V to 2.0V, $C_L = 5pF$.		0.63	1.2	ns
t_{OF}	Output Fall Time (5pF load)	2.0V to 0.5V, $C_L = 5pF$.		0.63	1.2	ns
$t_{START-UP}$	Start-up Time	Part start-up time for valid outputs after V_{DD} ramp-up.			3	ms
	Propagation Delay ^[1]		2.0	2.9	4.5	ns
	Buffer Additive Phase Jitter, RMS	156.25MHz, Integration Range: 12kHz–20MHz.			0.06	ps
	Output to Output Skew	Rising edges at $V_{DD}/2$ ^[2]		35	50	ps
	Device to Device Skew	Rising edges at $V_{DD}/2$.			200	ps
t_{EN}	Output Enable Time	$C_L \leq 5pF$.			3	cycles
t_{DIS}	Output Disable Time	$C_L \leq 5pF$.			3	cycles
t_{DC}	Duty Cycle ^[3]			50		%

Table 10. AC Electrical Characteristics – $V_{DD} = 3.3V \pm 5\%$

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
	Input Frequency		0		200	MHz
t_{OR}	Output Rise Time (5pF load)	0.66V to 2.64V, $C_L = 5pF$.		0.61	1.2	ns
t_{OF}	Output Fall Time (5pF load)	2.64V to 0.66V, $C_L = 5pF$.		0.61	1.2	ns
$t_{START-UP}$	Start-up Time	Part start-up time for valid outputs after V_{DD} ramp-up.			3	ms
	Propagation Delay ^[1]		1.7	2.3	3.4	ns
	Buffer Additive Phase Jitter, RMS	156.25MHz, Integration Range: 12kHz–20MHz.			0.05	ps
	Output to Output Skew	Rising edges at $V_{DD}/2$ ^[2]		35	50	ps
	Device to Device Skew	Rising edges at $V_{DD}/2$.			200	ps
t_{EN}	Output Enable Time	$C_L \leq 5pF$.			3	cycles
t_{DIS}	Output Disable Time	$C_L \leq 5pF$.			3	cycles
t_{DC}	Duty Cycle ^[3]			50		%


¹ With rail-to-rail input clock.

² Between any 2 outputs with equal loading.


³ Duty cycle on outputs will match incoming clock duty cycle when V_{IH} on CLKIN pin equals V_{DD} power supply voltage. Consult IDT for tight duty cycle clock generators.

Phase Noise Plots

The phase noise plots show the low additive jitter of the 5PB1104 high-performance buffer. With an integration range of 12kHz to 20MHz, the reference input has about 58.9fs of RMS phase jitter while the output of 5PB1104 has about 70.9fs of RMS phase jitter. This results in a low additive phase jitter of only 39fs.




Reference Phase Noise 58.9fs (12kHz to 20MHz)



Output Phase Noise 70.9fs (12kHz to 20MHz)

Test Load and Circuit




Package Outline Drawings


The package outline drawings are appended at the end of this document and are accessible from the link below. The package information is the most current data available.

www.idt.com/document/psc/cm8-package-outline-drawing-20-x-20-x-05-mm-body-05mm-pitch-dfn

Marking Diagrams



- Line 1: truncated part number; last number is the temperature grade: 1 = Grade 1; 2 = Grade 2.
- "YW" is the last digit of the year and work week that the part was assembled.
- "***" denotes the lot sequence number.



Ordering Information

Orderable Part Number	Package	Carrier Type	Temperature
5PB1104CMG1	2.0 × 2.0 mm, 0.5mm pitch 8-VFQFN	Tubes	-40° to +125°C
5PB1104CMG18	2.0 × 2.0 mm, 0.5mm pitch 8-VFQFN	Reel	-40° to +125°C
5PB1104CMG2	2.0 × 2.0 mm, 0.5mm pitch 8-VFQFN	Tubes	-40° to +105°C
5PB1104CMG28	2.0 × 2.0 mm, 0.5mm pitch 8-VFQFN	Reel	-40° to +105°C

Revision History

Revision Date	Description of Change
October 15, 2018	Initial release.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.

9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev. 4.0-2 April 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.