

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

SH7000 Series

32 Bit × 32 Bit = 64 Bit (Unsigned)

Label: MULU32

Functions Used: MULU Instruction
SWAP Instruction

Contents

1. Function	2
2. Arguments.....	2
3. Internal Register Changes and Flag Changes.....	3
4. Programming Specifications	4
5. Notes	4
6. Description	5
7. Flowchart.....	7
8. Program Listing	8

1. Function

Multiplies the multiplicand (unsigned 32 bits) by the multiplier (unsigned 32 bits) and determines the product (unsigned 64 bits).

2. Arguments

Description		Storage Location	Data Length (Bytes)
Input	Multiplicand (unsigned 32 bits)	R0	4
	Multiplier (unsigned 32 bits)	R1	4
Output	Upper 32 bits of product (unsigned 64 bits)	R2	4
	Lower 32 bits of product (unsigned 64 bits)	R3	4

3. Internal Register Changes and Flag Changes

	(Before Execution)	→	(After Execution)
R0	Multiplicand (unsigned 32 bits)	→	No change
R1	Multiplier (unsigned 32 bits)	→	No change
R2	Undefined	→	Product (upper 32 bits)
R3	Undefined	→	Product (lower 32 bits)
R4			Work
R5			Work
R6			Work
R7			
R8			
R9			
R10			
R11			
R12			
R13			
R14			
R15			(SP)

- T bit * — : No change
 * : Change
 0 : Fixed 0
 1 : Fixed 1

4. Programming Specifications

Program memory (bytes)
76
Data memory (bytes)
0
Stack (bytes)
24
Number of states
35
Reentrant
Yes
Relocation
Yes
Intermediate interrupt
Yes

5. Notes

The number of states indicated in the programming specifications is the value when $H'FFFFFFF \times H'FFFFFFF$ is calculated.

6. Description

(1) Function

Details of the arguments are as follows.

R0: Set the multiplicand (unsigned 32 bits) as the input argument.

R1: Set the multiplier (unsigned 32 bits) as the input argument.

R2: Holds the upper 32 bits of the product (unsigned 64 bits) as the output argument.

R3: Holds the lower 32 bits of the product (unsigned 64 bits) as the output argument.

Figure 1 shows a software MULU32 execution example.




Figure 1 Software MULU32 Execution Example

(2) Usage Notes

There are no particular precautions for the software MULU32 instruction.

(3) RAM Used

No RAM is used by the software MULU32 instruction.

(4) Usage Example

After the multiplicand and multiplier are set, the software instruction MULU32 is executed by a subroutine call.

```

MOV.L DATA1,R0    . . . . Sets multiplicand in input argument (R0)
BSR  MULU32        . . . . Subroutine call to software instruction MULU32
MOV.L DATA2,R1    . . . . Sets multiplier in input argument (R1)
.
.
.
.align 4
DATA1 .data.l H'FFFFFFFF
DATA2 .data.l H'FFFFFFFF
    
```

(5) Operating Principle

As shown in figure 2, multiplication is performed in 16 bit units. Partial products (1–4) are determined, and these are added to get the final product (64 bits). The 16-bit unsigned multiplication instruction (MULU) is used to multiply the partial products.





Figure 2 Multiplication

7. Flowchart



8. Program Listing

```

1          1          ;*****
2          2          ;*
3          3          ;*      NAME ; 32 BIT UNSIGNED MULTIPLICATION (MULU32)
4          4          ;*
5          5          ;*****
6          6          ;*
7          7          ;*      ENTRY : R0 (MULTIPLICAND)
8          8          ;*      R1 (MULTIPLIER)
9          9          ;*      RETURNS : R2 (UPPER 32 BIT PRODUCT)
10         10         ;*      R3 (LOWER 32 BIT PRODUCT)
11        11         ;*
12        12         ;*****
13 00001000        13          .SECTION A, CODE, LOCATE=H'1000
14          14         MULU32 .EQU    $          ; Entry point
15 00001000 4F12        15          STS.L   MACL, @-R15 ; Escape register
16 00001002 2F46        16          MOV.L   R4, @-R15 ;
17 00001004 2F56        17          MOV.L   R5, @-R15 ;
18 00001006 2F66        18          MOV.L   R6, @-R15 ;
19          19          ;
20 00001008 201E        20          MULU   R1, R0 ; Lower 16 bit + lower 16 bit -> R3
21 0000100A 6009        21          SWAP.W R0, R0 ;
22 0000100C 031A        22          STS    MACL, R3 ;
23 0000100E 201E        23          MULU   R1, R0 ; Upper 16 bit + lower 16 bit -> R5
24 00001010 6119        24          SWAP.W R1, R1 ;
25 00001012 051A        25          STS    MACL, R5 ;
26 00001014 201E        26          MULU   R1, R0 ; Upper 16 bit + upper 16 bit -> R2
27 00001016 6009        27          SWAP.W R0, R0 ;
28 00001018 021A        28          STS    MACL, R2 ;
29 0000101A 201E        29          MULU   R1, R0 ; Lower 16 bit + upper 16 bit -> R4
30 0000101C 6119        30          SWAP.W R1, R1 ;
31 0000101E 041A        31          STS    MACL, R4 ;
32          32          ;
33 00001020 0008        33          CLRT          ;
34 00001022 345E        34          ADDC   R5, R4 ;
35 00001024 0629        35          MOVT   R6          ; R6 <- Carry
36 00001026 4628        36          SHLL16 R6          ;
37 00001028 326C        37          ADD    R6, R2 ; Carry = 1  R2 <- R2 + H'0001000
38          38          ; Carry = 0  R2 <- R2 + H'0000000
39 0000102A 6543        39          MOV    R4, R5 ;
40 0000102C 4528        40          SHLL16 R5          ;
41 0000102E 4429        41          SHLR16 R4          ;
42          42          ;
43 00001030 0008        43          CLRT          ;
44 00001032 335E        44          ADDC   R5, R3 ;
45 00001034 0629        45          MOVT   R6          ; R6 <- Carry
46 00001036 326C        46          ADD    R6, R2 ; Carry = 1  R2 <- R2 + H'00000001
47          47          ; Carry = 0  R2 <- R2 + H'00000000
48 00001038 324C        48          ADD    R4, R2 ;
49          49          ;

```

```
50 0000103A 66F6      50      MOV.L  @R15+,R6      ; Return register
51 0000103C 65F6      51      MOV.L  @R15+,R5      ;
52 0000103E 64F6      52      MOV.L  @R15+,R4      ;
53 00001040 000B      53      RTS                ;
54 00001042 4F16      54      LDS.L  @R15+,MACL   ;
55                                55      .END

*****TOTAL ERRORS      0
*****TOTAL WARNINGS    0
```

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.
Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.