

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.



Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

SH7000 Series

64 Bit + 64 Bit = 64 Bit (Signed)

Label: ADDS64

Functions Used: ADDV Instruction

Contents

1. Function	2
2. Arguments.....	2
3. Internal Register Changes and Flag Changes.....	3
4. Programming Specifications	4
5. Description	5
6. Flowchart.....	8
7. Program Listing	9

1. Function

Adds the augend (signed 64 bits) and addend (signed 64 bits), and determines the sum (signed 64 bits). At this time, whether or not an overflow or underflow is present is set in the T bit. Overflow and underflow discrimination is not performed.

2. Arguments

Description		Storage Location	Data Length (Bytes)
Input	Upper 32 bits of augend (signed 64 bits)	R0	4
	Lower 32 bits of augend (signed 64 bits)	R1	4
	Upper 32 bits of addend (signed 64 bits)	R2	4
	Lower 32 bits of addend (signed 64 bits)	R3	4
Output	Upper 32 bits of sum (signed 64 bits)	R0	4
	Lower 32 bits of sum (signed 64 bits)	R1	4
	With/without overflow or underflow (with: T = 1, without: T = 0)	T bit (SR)	4

3. Internal Register Changes and Flag Changes

	(Before Execution) → (After Execution)
R0	Upper 32 bits of augend → Upper 32 bits of sum
R1	Lower 32 bits of augend → Lower 32 bits of sum
R2	Upper 32 bits of addend → No change
R3	Lower 32 bits of addend → No change
R4	Work
R5	Work
R6	
R7	
R8	
R9	
R10	
R11	
R12	
R13	
R14	
R15	(SP)

T bit * — : No change

* : Change

0 : Fixed 0

1 : Fixed 1

4. Programming Specifications

Program memory (bytes)
28
Data memory (bytes)
0
Stack (bytes)
8
Number of states
15
Reentrant
Yes
Relocation
Yes
Intermediate interrupt
Yes

5. Description

(1) Function

Details of the arguments are as follows.

- R0: Set the upper 32 bits of the augend (signed 64 bits) as the input argument.
Holds the upper 32 bits of the sum (signed 64 bits) as the output argument.
- R1: Sets the lower 32 bits of the augend (signed 64 bits) as the input argument.
Holds the lower 32 bits of the sum (signed 64 bits) as the output argument.
- R2: Set the upper 32 bits of the addend (signed 64 bits) as the input argument.
- R3: Set the lower 32 bits of the addend (signed 64 bits) as the input argument.
- T bit (SR): Indicates the presence or absence of an overflow or underflow after execution of the software instruction ADDS64.
T bit = 1: Indicates an overflow or underflow was generated.
T bit = 0: Indicates no overflow or underflow was generated.

Figure 1 shows a software ADDS64 execution example.




Figure 1 Software ADDS64 Execution Example

(2) Usage Notes

Since the sum is set in R1 and R2, which contained the augend settings, the augend data is destroyed. If the value for the augend will be needed after the software ADDS64 instruction is executed, it should be saved beforehand.

(3) RAM Used

No RAM is used by the software ADDS64 instruction.


(4) Usage Example

After the augend and addend are set in input arguments, the software ADDS64 instruction is executed by a subroutine call.


```
MOV.L DATA1,R0    . . . Sets augend (upper 32 bits) in input argument
MOV.L DATA2,R1    . . . Sets augend (lower 32 bits) in input argument
MOV.L DATA3,R2    . . . Sets addend (upper 32 bits) in input argument
BSR   ADDS64      . . . Subroutine call to ADDS64
MOV.L DATA4,R3    . . . Sets addend (lower 32 bits) in input argument
BT    ERROR        . . . Branches to error-processing subroutine if overflow or underflow occurs
.
.
.
.align 4
DATA1 .data.1 H'7FFFFFFF
DATA2 .data.1 H'FFFFFFFF
DATA3 .data.1 H'10000000
DATA4 .data.1 H'10000000
```

(5) Operating Principle

- (a) The lower 32 bits of the augend and addend are added using the add with carry instruction (ADDC). If a carry occurs after addition, it is indicated in the T bit (figure 2-(1)).
- (b) If a carry occurs, it is added to the upper 32 bits of the augend. The content of the T bit from (a) is stored in R4 and then added to the upper 32 bits of the augend using the binary addition with overflow check instruction (ADDV). If a carry occurs, 1 is added to the upper 32 bits of the augend. If there is no carry, 0 is added to the upper 32 bits of the augend. Whether an overflow or underflow has occurred is indicated in the T bit after addition (figure 2-(2)).
- (c) The sum from (b) is added to the upper 32 bits of the addend by binary addition using the overflow check instruction (ADDV). Whether an overflow or underflow has occurred is indicated in the T bit after addition (figure 2-(3)).
- (d) The contents of the T bits from (b) and (c) are logically ORed and the result is stored in the T bit. If the value of the T bit is 1, an overflow or underflow has occurred. If the value of the T bit is 0, no overflow or underflow has occurred.

**Figure 2 Signed Addition**

6. Flowchart



7. Program Listing

```
1      ;*****
2      ;*
3      ;*      NAME : 64 BIT SIGNED BINARY ADDITION (ADDS64) *
4      ;*
5      ;*****
6      ;*
7      ;*      ENTRY : R0 (UPPER 32 BIT AUGEND) *
8      ;*          R1 (LOWER 32 BIT AUGEND) *
9      ;*          R2 (UPPER 32 BIT ADDEND) *
10     ;*         R3 (LOWER 32 BIT ADDEND) *
11     ;*      RETURNS : R0 (UPPER 32 BIT SUM) *
12     ;*          R1 (LOWER 32 BIT SUM) *
13     ;*          T BIT (OVERFLOW/UNDERFLOW -> TRUE;T=1,FALSE;T=0) *
14     ;*
15     ;*****
16 00001000 16 .SECTION A,CODE,LOCATE=H'1000
17      00001000 17 ADDS64 .EQU   $           ; Entry point
18 00001000 2F46 18 MOV.L   R4,@-R15       ; Escape register
19 00001002 2F56 19 MOV.L   R5,@-R15       ;
20 00001004 0008 20 CLRT                ; Clear T bit
21 00001006 313E 21 ADDC    R3,R1        ; Lower 32 bit augend + Lower 32
                                         ; bit addend
22 00001008 0429 22 MOVT    R4           ; R4 <- Carry
23 0000100A 304F 23 ADDV    R4,R0        ; Upper 32 bit augend + Carry
24 0000100C 0429 24 MOVT    R4           ; R4 <- Overflow / Underflow
25 0000100E 302F 25 ADDV    R2,R0        ; Upper 32 bit augend + Upper 32
                                         ; bit addend
26 00001010 0529 26 MOVT    R5           ; R5 <- Overflow / Underflow
27 00001012 245B 27 OR     R5,R4        ; R4 <- R5 or R4
28 00001014 4401 28 SHLR    R4           ; T bit <- Overflow / Underflow
29 00001016 65F6 29 MOV.L   @R15+,R5       ; Return register
30 00001018 000B 30 RTS                 ;
31 0000101A 64F6 31 MOV.L   @R15+,R4       ;
32                         32 .END

*****TOTAL ERRORS    0
*****TOTAL WARNINGS  0
```

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.
Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors.
Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.