



Tsi148™ VMEbus Test and Set Application Note

Formal Status
September 6, 2012



Tsi148 VMEbus Test and Set Application Note

This document details both the traditional mechanisms for implementing a VMEbus Test and Set (TAS) function, as well as additional Tsi148-specific solutions. Topics discussed include the following:

- [Overview](#)
- [Tsi148-specific Wrap-around RMW Solution](#)

Revision History

September 6, 2012, Formal

This version includes several minor fixes. No technical changes were made.

October 2009, Formal

This version of the document was rebranded as IDT. No technical changes were made.

October 2008, Formal

General content update.

Overview

The traditional methods for implementing a VMEbus test-and-set (TAS) function include the following:

1. A VME RMW cycle

The standard way to implement a TAS is to use the PCI- to-VME bridge device's RMW cycle to set the semaphore. This method is used by a board that does not host the semaphore in its own memory but needs to access the semaphore over the VMEbus. In order to guarantee indivisibility, both the processor host bridge as well as the PCI-to-VME bridge should support the PCI Lock feature.

2. Using bus locking capabilities in the PCI-to-VME bridge device

Locking of the VMEbus by using the bus locking capability of the PCI-to-VME bridge device can be used to complete the TAS function. When the VMEbus is locked, the semaphore can be read, tested, and, optionally, written. The same method is used by the board that hosted the semaphore and boards that must cross the VMEbus to access the semaphore.

3. Software TAS

The software TAS option continuously re-reads the address to obtain the semaphore. The number of times the address must be read is a configurable value which must be large enough to ensure that no other agent trying to acquire the semaphore could have written its own node-unique locking value to the semaphore. The number of times the address must be read is very system dependent and it is difficult to guarantee the desired locked condition in all circumstances and environments.



IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.