

CAN Configuration with PLL

V850E2/Fx4

32-bit Microcontroller

32

All information contained in these materials, including products and product specifications, represents information on the product at the time of publication and is subject to change by Renesas Electronics Corp. without notice. Please review the latest information published by Renesas Electronics Corp. through various means, including the Renesas Electronics Corp. website (<http://www.renesas.com>).

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics.

The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.

- “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
- “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
- “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.

8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

General Precautions in the Handling of MPU/MCU Products

The following usage notes are applicable to all MPU/MCU products from Renesas. For detailed usage notes on the products covered by this manual, refer to the relevant sections of the manual. If the descriptions under General Precautions in the Handling of MPU/MCU Products and in the body of the manual differ from each other, the description in the body of the manual takes precedence.

1. Handling of unused Pins

Handle unused pins in accord with the directions given under Handling of Unused Pins in the manual.

- The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.

2. Processing at power-on

The state of the product is undefined at the moment when power is supplied.

- The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.

In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed.

In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.

3. Prohibition of access to reserved addresses

Access to reserved addresses is prohibited.

- The reserved addresses are provided for the possible future expansion of functions. Do not access these addresses; the correct operation of LSI is not guaranteed if they are accessed.

4. Clock signals

After applying a reset, only release the reset line after the operating clock signal has become stable. When switching the clock signal during program execution, wait until the target clock signal has stabilized.

- When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.

5. Differences between products

Before changing from one product to another, i.e. to one with a different part number, confirm that the change will not lead to problems.

- The characteristics of MPU/MCU in the same group but having different part numbers may differ because of the differences in internal memory capacity and layout pattern. When changing to products of different part numbers, implement a system-evaluation test for each of the products.

Table of Contents

Notice	2
General Precautions in the Handling of MPU/MCU Products	4
Table of Contents	5
Chapter 1 Methods to define the CAN Jitter	6
1.1 The protocol oriented jitter definition	6
1.2 The OEM jitter definition	6
Chapter 2 Maximum Deviation for V850E2/Fx4	7
2.1 Involved parts	7
2.2 Properties of V850E2/Fx4	7
2.3 Properties of the quartz	7
2.4 Calculation results	8
2.4.1 Protocol oriented jitter at baud rate $b = 500$ kbit/s	8
2.4.2 OEM jitter 0.4% at baud rate $b = 500$ kbit/s	8
Chapter 3 Final Conclusion	9
Revision History	10

Chapter 1 Methods to define the CAN Jitter

Currently, two different methods are known how to define a maximum allowed jitter of a CAN protocol engine (transfer layer). Both methods have different targets and calculations.

While the “protocol oriented” method defines a maximum jitter, which is below a resynchronisation threshold in worst case, the “OEM” method is related to a single bit timing directly.

1.1 The protocol oriented jitter definition

Definition The jitter must be less than 1 time quanta (TQ) within 10 bits of the given baud rate of the CAN bus.

Thus, the *reference time interval* is 10 CAN bus bits.

Note 10 bits are corresponding with the maximum distance between subsequent resynchronisation phases within a CAN frame. The *time quanta* is the elementary resolution of the CAN bus protocol. If the jitter is below 1 TQ , any participant on the CAN bus will not see the jitter at all, because no resynchronisation takes place, which would have been caused by the jitter. In worst case, a bit consists of 25 TQ , which is TQ_{max} .

Values for this calculation must be taken with peak-to-peak values, because in worst case the jitter may accumulate in the same direction along with the whole time of 10 bits.

1.2 The OEM jitter definition

Definition The jitter must be less than $x_{OEM}\%$ of the length one CAN bus bit.

Thus, the *reference time interval* is one CAN bus bit.

This method is easily verifiable, which is its main advantage. On the other hand, this method typically defines the limit in such a way, that it is harder to fulfill. In addition, the method is not related to the CAN protocol itself, so that a violation of this limit does not have a consequent impact on the CAN bus function.

Values for this calculation must be taken with peak-to-peak values, because in worst case the jitter may accumulate in the same direction along with the whole time of one bit.

Chapter 2 Maximum Deviation for V850E2/Fx4

2.1 Involved parts

To calculate a worst case deviation of a node on the CAN bus, the following values have to be added:

- the jitter peak-to-peak values of the oscillator during the *reference time interval*.
- the jitter peak-to-peak values of the (optionally) used PLL during the *reference time interval*.
- the aging, voltage and temperature effects on clock deviation for quartz and oscillator.

2.2 Properties of V850E2/Fx4¹

- Oscillator deviation: 0 ppm $= d_{OSC}$
No voltage dependency,
No temperature dependency,
No aging dependency.
- Oscillator jitter: 0 (no jitter) $= j_{OSC}$
- PLL jitter: 1.275 ns / μ s $= j_{PLL}$

2.3 Properties of the quartz²

- Initial tolerance: 50 ppm $= d_{QI}$
- Temperature dependency: 150 ppm $= d_{QT}$
- Aging deviation: 100 ppm $= d_{QA}$

¹⁾ According to data sheet

²⁾ Typical example values

2.4 Calculation results

For both jitter definition cases, the peak-to-peak worst case is considered by a multiplication factor of 2 for the V850E2/Fx4 deviation.

2.4.1 Protocol oriented jitter at baud rate $b = 500$ kbit/s

The maximum *allowed* deviation caused by deviations and jitter is:

$$\begin{aligned} 1 / b / TQ_{max} &= \\ 1 / (500 \text{ kbit/s}) / (25 / \text{bit}) &= \underline{\underline{80 \text{ ns}}} \end{aligned}$$

The deviation of V850E2/Fx4 including the quartz is:

$$\begin{aligned} 2 * ((d_{QI} + d_{QT} + d_{QA} + d_{OSC}) / b + ((j_{PLL} + j_{OSC}) * 10 / b)) &= \\ 2 * ((300 \text{ ppm}) / 500 \text{ kbit/s} + ((1.275 \text{ ns} / \mu\text{s}) * 10 / 500 \text{ kbit/s})) &= \underline{\underline{25.5 \text{ ns}}} \end{aligned}$$

Conclusion The deviation of V850E2/Fx4 including quartz is within the limit.

2.4.2 OEM jitter 0.4% at baud rate $b = 500$ kbit/s

Note The limit of 0.4% applies for the baud rate of 500 kbit/s, if the bit resolution is equal or higher than 10 TQ/bit.

The maximum *allowed* deviation caused by deviations and jitter is:

$$\begin{aligned} 1 / b * x_{OEM}\% &= \\ 1 / (500 \text{ kbit/s}) * 0.4\% &= \underline{\underline{8 \text{ ns}}} \end{aligned}$$

The deviation of V850E2/Fx4 including the quartz is:

$$\begin{aligned} 2 * ((d_{QI} + d_{QT} + d_{QA} + d_{OSC}) / b + ((j_{PLL} + j_{OSC}) / b)) &= \\ 2 * ((300 \text{ ppm}) / 500 \text{ kbit/s} + ((1.275 \text{ ns} / \mu\text{s}) / 500 \text{ kbit/s})) &= \underline{\underline{6.3 \text{ ns}}} \end{aligned}$$

Conclusion The deviation of V850E2/Fx4 including quartz is within the limit.

Chapter 3 Final Conclusion

The clock deviation of V850E2/Fx4 does not exceed the limits for CAN usage, even if the PLL is used as a clock source for the CAN controller. This deviation includes tolerances of the oscillator, an external quartz (with assumed 300 ppm in total), voltage and temperature drift within the allowed operating range, aging, and the jitter of oscillator and PLL in worst case.

For this reason the usage of the V850E2/Fx4 PLL as a clock source for the CAN controller is allowed.

Regarding the OEM jitter definition criteria, the current definition values have to be considered. In this document, a baud rate of 500 kbit/s and a bit resolution of at least 10 TQ/bit has been assumed to be checked with an actual OEM requirements definition.

Revision History

Version	Date	Document number	Description
1.0	May 30, 2012	R01AN1191ED0100	Initial document

V850E2/Fx4 Application Note

Publication Date:

Rev. 1.00 May 30, 2012

Published by: Renesas Electronics Corporation



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "http://www.renesas.com/" for the latest and detailed information.

Renesas Electronics America Inc.

2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A.
Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited

1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada
Tel: +1-905-898-5441, Fax: +1-905-898-3220

Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-65030, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.

7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.

Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd., Pudong District, Shanghai 200120, China
Tel: +86-21-5877-1818, Fax: +86-21-6887-7858 / -7898

Renesas Electronics Hong Kong Limited

Unit 1601-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2886-9318, Fax: +852 2886-9022/9044

Renesas Electronics Taiwan Co., Ltd.

7F, No. 363 Fu Shing North Road Taipei, Taiwan
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd.

1 harbourFront Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: +65-6213-0200, Fax: +65-6278-8001

Renesas Electronics Malaysia Sdn.Bhd.

Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics Korea Co., Ltd.

11F., Samik Laved'or Bldg., 720-2 Yeoksam-Dong, Kangnam-Ku, Seoul 135-080, Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5141

V850E2/Fx4