# RENESAS

Continuous Conduction Mode Interleaving PFC Control IC

R03DS0008EJ0301 Rev.3.01 Jan 08, 2016

### Description

R2A20104/114 series is a boost converter control IC with PFC (Power Factor Correction). Employing continuous conduction mode interleaving PFC, it performs higher efficiency and lower switching noise even for high power use. The control of continuous conduction mode is carried out by detecting the current in power MOSFET. The R2A20114 series supports two types of current detection methods; current detection by current transformers (R2A20104SP/FP), and that by shunt resisters (R2A20114SP/FP). So that, it can be applicable for a variety of applications. Interleaving control of the boost converters, namely, producing 180 degrees phase shift between the output signals (GD1,2) driving the boost converters, enables the system to perform high conversion efficiency and low switching noises and, at the same time, to reduces ripple currents in input and output current and then this allows use of smaller components such as boost inductors, input filters and output capacitors. R2A20114 series integrates a various kinds of protection circuits, such as the detection circuit of breaking of wire in feedback loop, two modes of over voltage protection circuits, over current protection circuit and error output circuit (\*<sup>1</sup>), which improve the reliability of the power supply system and reduce the number of component parts on the system.

#### Features

- Maximum Ratings
  - Supply voltage Vcc: 24 V
  - Junction temperature Tj: from -40 to +150 degrees centigrade
- Electrical characteristics
  - VFB feedback voltage VREF: 2.5 V  $\pm$  1.5%
  - UVLO (Undervoltage Lockout) operation start voltage VH: 10.4 V  $\pm$  0.7 V
  - UVLO operation shutdown voltage VL: 8.9 V  $\pm$  0.5 V
  - UVLO hysteresis voltage Hysuvl : 1.5 V  $\pm$  0.5 V
- Functions
  - Boost converter control with continuous conduction mode
  - Interleaving control
  - Frequency modulation (\*<sup>2</sup>)
  - Brownout
  - Phase drop  $(*^1)$
  - External clock synchronization input
  - External clock synchronization output (\*1)
  - Two modes of over voltage protections
     Mode 1: Dynamic OVP preventing over voltage after sudden variation of load.
     Mode 2: Static OVP preventing over voltage in the period of normal operation.
  - Feedback loop wire breaking/open detector
  - Dual over voltage protection circuits (\*1): FB and OVP2 terminals
  - Current balance control
  - Phase 1 and Phase 2 independent over current protection
  - Package line-up
    - Pb-free LQFP-40 (R2A20104FP, R2A20114FP)
    - Pb-free SOP-20 (R2A20104SP, R2A20114SP)
- Notes: \*1 Supported only by R2A20104FP and R2A20114FP
  - \*2 Frequency modulation periods (dfm) of R2A20104SP and R2A20114SP are fixed.



#### The Function List of R2A20104/114 Series

| lte                    | m  | R2A20104SP  | R2A20104FP | R2A20114SP  | R2A20114FP |  |  |  |
|------------------------|--|---|------------|---|------------|--|--|--|
| PFC control            |  | Continuous conduction mode interleaving   |            |   |            |  |  |  |
| Current detection meth | nod  | Current transformer   |            | Shunt resistor  |            |  |  |  |
| Package                |  | SOP-20  | LQFP-40    | SOP-20  | LQFP-40    |  |  |  |
| Protection circuits    | Brownout detection                             | Supported   | Supported  | Supported   | Supported  |  |  |  |
|                        | 2nd OVP  | Not supported   | Supported  | Not supported   | Supported  |  |  |  |
|                        | Phase error                                    | Not supported   | Supported  | Not supported   | Supported  |  |  |  |
| Noise reduction        | Jitter generation<br>(Frequency<br>modulation) | Supported<br>(But, frequency<br>modulation period<br>(dfm)(* <sup>1</sup> ) is fixed) | Supported  | Supported<br>(But, frequency<br>modulation period<br>(dfm)(* <sup>1</sup> ) is fixed) | Supported  |  |  |  |
| Synchronization with   | Input  | Supported   | Supported  | Supported   | Supported  |  |  |  |
| external signal        | Output   | Not supported   | Supported  | Not supported   | Supported  |  |  |  |
| Efficiency improvement | Phase drop                                     | Not supported   | Supported  | Not supported   | Supported  |  |  |  |

Note: \*1 Refer to the figure depicted below:



### **Ordering Information**

| Part No.     | Package Name | Package Code | Package<br>Abbreviation | Taping Abbreviation<br>(Quantity) | Remarks |
|--------------|--------------|--------------|-------------------------|-----------------------------------|---------|
| R2A20104FPW0 | FP-40EV      | PLQP0040JB-C | FP                      | W (2000 pcs/reel)                 | non-HF  |
| R2A20104FPW5 |              |              |                         |                                   | HF      |
| R2A20114FPW0 |              |              |                         |                                   | non-HF  |
| R2A20114FPW5 |              |              |                         |                                   | HF      |
| R2A20104SPW0 | FP-20DAV     | PRSP0020DD-B | SP                      | W (2000 pcs/reel)                 | non-HF  |
| R2A20104SPW5 |              |              |                         |                                   | HF      |
| R2A20114SPW0 |              |              |                         |                                   | non-HF  |
| R2A20114SPW5 |              |              |                         |                                   | HF      |

Note: HF: Halogen-Free



#### Pin Arrangement of R2A20104FP and R2A20114FP



#### Pin Functions of R2A20104FP and R2A20114FP

| Pin No. | Pin Name | Input/Output | Function   |  |  |  |
|---------|----------|--------------|--|--|--|--|
| 1       | FMR      | Input        | Frequency modulation setting resistor connecting terminal                    |  |  |  |
| 2       | FMC      | Input        | Frequency modulation setting capacitor connecting terminal                   |  |  |  |
| 3       | VREF     | Output       | Reference voltage output terminal  |  |  |  |
| 4       | BO       | Input        | Brownout input terminal  |  |  |  |
| 5       | VAC      | Input        | AC voltage input terminal  |  |  |  |
| 6       | PD       | Input        | Phase drop input terminal  |  |  |  |
| 7       | AGND     | —            | Analog ground  |  |  |  |
| 8       | E-DELAY  | Input        | Delay of the Error signal setting terminal                                   |  |  |  |
| 9, 10   | N.C.     | —            | Open   |  |  |  |
| 11      | ERROR    | Output       | Error output terminal  |  |  |  |
| 12      | OFF      | Input        | Shutdown terminal (VCC Reset)  |  |  |  |
| 13      | RS       | Input        | Current correction setting resistor connecting terminal                      |  |  |  |
| 14      | SS       | Input        | Soft start setting capacitor connecting terminal                             |  |  |  |
| 15      | COMP     | Output       | Error amplifier output terminal (to be phase-compensated)                    |  |  |  |
| 16      | N.C.     | —            | Open   |  |  |  |
| 17      | FB       | Input        | Error amplifier input terminal (feedback voltage input terminal)             |  |  |  |
| 18      | QVP2     | Input        | OVP2 input terminal  |  |  |  |
| 19-21   | N.C.     | —            | Open   |  |  |  |
| 22      | IRAMP    | Input        | Ramp waveform setting resistor connecting terminal                           |  |  |  |
| 23      | CSO2     | Output       | Current sense amplifier 2 output terminal (to be phase-compensated)          |  |  |  |
| 24      | CSO1     | Output       | Current sense amplifier 1 output terminal (to be phase-compensated)          |  |  |  |
| 25      | CS2      | Input        | Current sense 2 input terminal   |  |  |  |
| 26      | CS1      | Input        | Current sense 1 input terminal   |  |  |  |
| 27      | N.C.     | —            | Open   |  |  |  |
| 28      | VCC      | Input        | Supply voltage terminal  |  |  |  |
| 29-31   | N.C.     | —            | Open   |  |  |  |
| 32      | GD2      | Output       | Converter 2 Power MOSFET drive terminal                                      |  |  |  |
| 33      | PGND     | —            | Power ground   |  |  |  |
| 34      | GD1      | Output       | Converter 1 Power MOSFET drive terminal                                      |  |  |  |
| 35      | N.C.     | —            | Open   |  |  |  |
| 36      | SYNC-O   | Output       | Synchronization signal output terminal                                       |  |  |  |
| 37      | RT/SYNC  | Input        | Frequency setting resistor connecting terminal / Sync. Signal input terminal |  |  |  |
| 38      | CT       | Input        | Frequency setting capacitor connecting terminal                              |  |  |  |
| 39, 40  | N.C.     | —            | Open   |  |  |  |



#### Pin Arrangement of R2A20104SP and R2A20114SP



#### Pin Functions of R2A20104SP and R2A20114SP

| Pin No. | Pin Name | Input/Output | Function  |
|---------|----------|--------------|---|
| 1       | RT/SYNC  | Input        | Frequency setting timing resistor connecting terminal / Sync. signal input terminal |
| 2       | СТ       | Input        | Frequency setting timing capacitor connecting terminal                              |
| 3       | FM       | Input        | Frequency modulation setting timing capacitor connecting terminal                   |
| 4       | VREF     | Output       | Reference voltage output terminal   |
| 5       | BO       | Input        | Brownout input terminal   |
| 6       | VAC      | Input        | AC voltage input terminal   |
| 7       | AGND     | —            | Analog ground   |
| 8       | RS       | Input        | Current correction setting resistor connecting terminal                             |
| 9       | SS       | Input        | Soft start setting capacitor connecting terminal                                    |
| 10      | COMP     | Output       | Error amplifier output terminal (to be phase-compensated)                           |
| 11      | FB       | Input        | Error amplifier input terminal (feedback voltage input terminal)                    |
| 12      | IRAMP    | Input        | Ramp waveform setting resistor connecting terminal                                  |
| 13      | CSO2     | Output       | Current sense amplifier 2 output terminal (to be phase-compensated)                 |
| 14      | CSO1     | Output       | Current sense amplifier Output 1 output terminal (to be phase-compensated)          |
| 15      | CS2      | Input        | Current sense 2 input terminal  |
| 16      | CS1      | Input        | Current sense 1 input terminal  |
| 17      | VCC      | Input        | Supply voltage terminal   |
| 18      | GD2      | Output       | Converter 2 Power MOSFET drive terminal   |
| 19      | PGND     | —            | Power ground  |
| 20      | GD1      | Output       | Converter 1 Power MOSFET drive terminal   |











#### Absolute Maximum Ratings

| Item                          |              | Symbol           | Value            | Unit | Note |
|-------------------------------|--------------|------------------|------------------|------|------|
| Supply voltage                |              | VCC              | -0.3 to +24      | V    | 3    |
| GD1 and 2                     | Peak current | lpk-gd1, lpk-gd2 | ±1               | A    | 3, 4 |
|                               | DC current   | ldc-gd1, ldc-gd2 | ±0.1             | A    | 3    |
| Vref terminal current         |              | Iref             | -5               | mA   | 3    |
| Terminal current              |              | lt-group         | ±1               | mA   | 3, 5 |
| RS terminal current           |              | Irs              | -500             | μA   | 3    |
| RT terminal current           |              | Irt              | -200             | μA   | 3    |
| RAMP terminal current         |              | Iramp            | -200             | μA   | 3    |
| BO clamp current              |              | lbo              | 300              | μA   | 3    |
| Terminal voltage              |              | Vt-group         | –0.3 to Vref     | V    | 3, 6 |
| Vref terminal voltage         |              | Vt-ref           | -0.3 to Vref+0.3 | V    | 3    |
| SS terminal voltage           |              | Vt-ss            | -0.3 to Vref+1   | V    | 3    |
| Power dissipation             |              | Pt               | 1                | W    | 3, 7 |
| Operating ambient temperature |              | Ta-opr           | -40 to +125      | °C   |      |
| Junction temperature          |              | Tj               | -40 to +150      | °C   | 8    |
| Storage temperature           |              | Tstg             | -55 to +150      | °C   |      |

Notes: 1. Rated voltages are with reference to the AGND and PGND terminal.

2. For the direction of Rated currents, (+) denotes the current flowing into the IC, and (–) denotes the current flowing out of the IC.

- 3. Ambience temperature, Ta is 25 degrees centigrade.
- 4. Transient current when driving a capacitive load.
- 5. Rated currents of the terminals listed below: COMP, CSO1, CSO2
- 6. Rated voltages of the terminals listed below: in the case of R2A20104FP/R2A20114FP: CS1, CS2, VAC, RS, FB, PD, BO, ERROR, E-DLAY, OFF, OVP2, FMC, FMR, RT/SYNC, IRAMP, SYNC-O, CT, COMP, CS01, CS02
  in the case of R2A20104SP/R2A20114SP: CS1 CS2 VAC, RS, FB, BO, IRAMP, FM, RT/SYNC, CT

in the case of R2A20104SP/R2A20114SP: CS1, CS2, VAC, RS, FB, BO, IRAMP, FM, RT/SYNC, CT, COMP, CSO1, CSO2

7. Thermal resistor

in the case of R2A20104FP/R2A20114FP: θja = 85.3 degrees centigrade/W

in the case of R2A20104SP/R2A20114SP:  $\theta$ ja = 120 degrees centigrade/W

These values are obtained under the condition that the IC is mounted on the glass epoxy board, of which size is  $50 \times 50 \times 1.6$  [mm] and wiring density is 10%.

 Stresses exceeding the absolute maximum ratings may damage the device. These are stress ratings only. Functional operation above the recommended operating ambient temperature range is not implied.

Extended exposure to stresses above the absolute maximum ratings may affect device reliability.



Electrical Characteristics

| $(Ta = 25^{\circ}C, VCC = 12 V, CT = 1000 pF, RT = 27 k\Omega, CS1, CS2 = GND, IRAMP = 10 k\Omega, BO = 1 V, VAC = 0 V, CT = 1000 pF, RT = 27 k\Omega, CS1, CS2 = GND, IRAMP = 10 k\Omega, BO = 1 V, VAC = 0 V, CT = 1000 pF, RT = 27 k\Omega, CS1, CS2 = GND, IRAMP = 10 k\Omega, BO = 1 V, VAC = 0 V, CT = 1000 pF, RT = 27 k\Omega, CS1, CS2 = GND, IRAMP = 10 k\Omega, BO = 1 V, VAC = 0 V, CS1, CS2 = CS1, CS1, CS2 = CS1, CS1, CS2 = CS1, CS2 = CS1, CS1, CS2 = CS1, CS2 = CS1, CS1, CS1, CS1, CS1, CS1, CS1, CS1,$ |
|--|
| $RS = 220 \text{ k}\Omega$ , $FMC = GND (*^1)$ , $FM = GND (*^2)$ , $FB = COMP$ )  |

|            | Item                       | Symbol         | Min   | Тур   | Max   | Unit   | Test Conditions                               |
|------------|----------------------------|----------------|-------|-------|-------|--------|---|
| Supply     | UVLO turn-on threshold     | Vuvlh          | 9.7   | 10.4  | 11.1  | V      |   |
|            | UVLO turn-off threshold    | Vuvll          | 8.4   | 8.9   | 9.4   | V      |   |
|            | UVLO hysteresis            | Hysuvl         | 1.0   | 1.5   | 2.0   | V      |   |
|            | Standby current            | Istby          |       | 100   | 160   | μΑ     | VCC = 8.9 V                                   |
|            | Operating current          | lcc            | _     | 5     | 7.5   | mA     |   |
| VREF       | Output voltage             | Vref           | 4.85  | 5.00  | 5.15  | V      | Isource = -1 mA                               |
|            | Line regulation            | Vref-line      |       | 5     | 20    | mV     | Isource = -1 mA,                              |
|            |                            |                |       |       |       |        | VCC = 10 V to 24 V                            |
|            | Load regulation            | Vref-load      | —     | 5     | 20    | mV     | Isource = -1 mA to -5 mA                      |
|            | Temperature stability      | dVref          | —     | ±80   | —     | ppm/°C | Ta = -40 to 125°C (* <sup>3</sup> )           |
| Error      | Feedback voltage           | Vfb            | 2.462 | 2.500 | 2.538 | V      | FB-COMP Short                                 |
| amplifier  | Input bias current         | lfb            | -0.8  | -0.5  | -0.2  | μA     | Measured pin: FB                              |
|            | Open loop gain             | Av             | _     | 40    | _     | dB     | (* <sup>3</sup> )                             |
|            | Upper clamp voltage        | Vclamp-comp    | 3.8   | 4.0   | 4.3   | V      | FB = 2.0 V, COMP: Open                        |
|            | Low voltage                | VI-comp        | 0.0   | 0.1   | 0.3   | V      | FB = 3.0 V, COMP: Open                        |
|            | Source current             | Isrc-comp      | -190  | -135  | -80   | μA     | FB = 1.5 V, COMP = 2.5 V                      |
|            | Sink current 1             | Isnk-comp1     | _     | 120   | _     | μΑ     | (* <sup>3</sup> )                             |
|            | Sink current 2             | Isnk-comp2     | 220   | 320   | 420   | μΑ     | FB =3.5 V, COMP = 2.5 V                       |
|            | Transconductance           | gm             | 120   | 200   | 290   | μs     | FB = 2.45 V ↔ 2.55 V,                         |
|            |                            |                |       |       |       |        | COMP = 2.5 V                                  |
| Brownout   | PFC enable voltage         | Von-pfc        | 0.74  | 0.82  | 0.9   | V      | Input pin: BO                                 |
|            | PFC disable voltage        | Voff-pfc       | 0.73  | 0.81  | 0.89  | V      | Input pin: BO                                 |
| Oscillator | Initial accuracy           | fout           | 70    | 78    | 86    | kHz    | Measured pin: OUT,<br>FMC = 0 V               |
|            | fout temperature stability | dfout/dTa      | _     | ±0.1  | _     | %/°C   | Ta = -40 to 125°C (*3)                        |
|            | fout voltage stability     | fout-line      | -1.5  | 0.5   | 1.5   | %      | VCC = 12 V to 18 V                            |
|            | CT top voltage             | Vct-H          | _     | 3.6   | 4.0   | V      | (* <sup>3</sup> )                             |
|            | RT voltage                 | Vrt            | 1.15  | 1.25  | 1.35  | V      |   |
|            | FMC sink current (*1)/     | lsnk-fmc (*1)/ | 6     | 11    | 16    | μA     | FMC = 1 V (*1)/                               |
|            | FM sink current (*2)       | Isnk-fm (*2)   |       |       |       |        | FM = 1 V (* <sup>2</sup> )                    |
|            | FMC source current (*1)/   | lso-fmc (*1)/  | -16.5 | -11.5 | -6.5  | μΑ     | FMC = 1 V (* <sup>1</sup> )/                  |
|            | FM source current (*2)     | Iso-fm (*2)    |       |       |       |        | FM = 1 V (* <sup>2</sup> )                    |
|            | FM magnitude change        | dfm            | 19    | 24    | 29    | kHz    | FMC = 5 V (*1)/FM = 5 V (*2)<br>(*3, *4)      |
|            | FM frequency 1 (*1)        | ffm1           | 0.25  | 0.38  | 0.5   | kHz    | FMC = 6.8 nF, FMR = 4 V<br>(* <sup>4</sup> )  |
|            | FM frequency 2 (*1)        | ffm2           | 14    | 25    | 35    | kHz    | FM = 220 pF, FMR = 1.2 V<br>(* <sup>4</sup> ) |
|            | FM frequency (*2)          | ffm            | 6     | 10    | 14    | kHz    | FMC = 220 pF (* <sup>4</sup> )                |

Notes: \*1 Applied to R2A20104FP, R2A20114FP

\*2 Applied to R2A20104SP, R2A20114SP

- \*3 Design Specification (Reference data)
- \*4 Refer to the figure shown below:





#### Electrical Characteristics (cont.)

 $(Ta = 25^{\circ}C, VCC = 12 V, CT = 1000 \text{ pF}, RT = 27 \text{ k}\Omega, CS1, CS2 = GND, IRAMP = 10 \text{ k}\Omega, BO = 1 V, VAC = 0 V, RS = 220 \text{ k}\Omega, FMC = GND (*1), FM = GND (*2), FB = COMP$ 

|                      | Item                              | Symbol   | Min           | Тур           | Max           | Unit | Test Conditions  |
|----------------------|-----------------------------------|----------|---------------|---------------|---------------|------|--|
| Synchroni-<br>zation | SYNC threshold voltage (rising)   | Vsync    | 2.0           | 2.5           | 3.0           | V    |  |
|                      | SYNC Min. pulse                   | Psync    | 2             |               | _             | μs   |  |
|                      | SYNC-OUT shunt current (*1)       | lsync-s  | 5.0           | _             | _             | mA   |  |
|                      | SYNC-OUT leakage current (*1)     | lsync-l  | —             | _             | 1.0           | μA   |  |
| Current              | RS output voltage 1               | Vrs1     | 0.56          | 0.65          | 0.74          | V    | VAC = 0 V, VFB = 2.5 V   |
| slope                | RS output voltage 2               | Vrs2     | 0.04          | 0.14          | 0.26          | V    | VAC = 2.5 V, VFB = 0 V   |
|                      | VAC bias current                  | lvac     | -0.4          | -0.2          | -0.05         | μA   | Measured pin: VAC  |
| Soft start           | Source current                    | lss      | -40           | -28           | -16           | μA   | SS = 2 V   |
| Phase drop           | Phase drop threshold voltage (*1) | Vpd      | 2.4           | 2.5           | 2.6           | V    |  |
|                      | Phase drop hysteresis (*1)        | Hya-pd   | 150           | 200           | 250           | mV   |  |
|                      | PD bias current (*1)              | lpd      | 0.05          | 0.2           | 0.5           | μA   | Measured pin: PD   |
| AMP1, 2              | CSO offset voltage1 (*5)          | Voffset  | 0.68          | 0.88          | 1.0           | V    | Vcs = 0 V  |
|                      | CSO offset voltage1 (*6)          | Voffset  | 0.54          | 0.74          | 0.86          | V    | Vcs = 0 V  |
|                      | CSO offset voltage2               | Vcaoh    | 2.83          | 3             | 3.17          | V    | Vcs = 0.24 V (* <sup>5</sup> ),<br>Vcs = 2.3 V (* <sup>6</sup> ) |
|                      | CS Bias current (*5)              | lcs-r    | -0.4          | -0.2          | -0.05         | μA   | Measured pin: CS1, 2   |
|                      | CS Bias current (*6)              | lcs-ct   | -1.1          | -0.8          | -0.5          | μA   | Measured pin: CS1, 2   |
| Gate drive           | Gate drive rise time              | tr-gd    | —             | 30            | 100           | ns   | CL = 500 pF  |
| 1, 2                 | Gate drive fall time              | tf-gd    | —             | 30            | 100           | ns   | CL = 500 pF  |
|                      | Gate drive low voltage            | Vol1-gd  | —             | 0.05          | 0.2           | V    | lsink = 10 mA  |
|                      |                                   | Vol2-gd  | —             | 1             | 1.25          | V    | Isink = 0.25 mA, VCC = 5 V                                       |
|                      | Gate drive high voltage           | Voh-gd   | 11.5          | 11.9          | —             | V    | Isource = -10 mA   |
|                      | Minimum duty cycle                | Dmin-out | —             | _             | 0             | %    |  |
|                      | Maximum duty cycle                | Dmax-out | 90            | 95            | 98            | %    |  |
| Over                 | Dynamic OVP Threshold             | Vdovp    | VFB×          | VFB×          | VFB×          | V    |  |
| voltage              | voltage                           |          | 1.025         | 1.040         | 1.055         |      |  |
| protection           | Static OVP Threshold              | Vsovp    | VFB×          | VFB×          | VFB×          | V    | COMP = OPEN  |
|                      | voltage                           |          | 1.065         | 1.080         | 1.095         | .,   |  |
|                      | Static OVP Hysteresis             | Hys-sovp | 30            | 80            | 130           | mV   | COMP = OPEN  |
|                      | OVP2 Threshold voltage (*1)       | Vovp2    | VFB×<br>1.065 | VFB×<br>1.080 | VFB×<br>1.095 | μA   |  |
|                      | OVP2 Hysteresis (*1)              | Hys-ovp2 | 30            | 80            | 130           | mV   | COMP = OPEN  |
|                      | OVP2 Bias current (*1)            | lovp2    | -0.5          | -0.3          | -0.05         | μA   | Measured pin: OVP2   |
|                      | FB Open Detect Threshold voltage  | Vfbopen  | 0.45          | 0.5           | 0.55          | V    |  |
|                      | FB Open Detect hysteresis         | Vfbopen  | 0.16          | 0.2           | 0.24          | V    |  |
| Over                 | OCP Threshold voltage (*5)        | VCL      | 0.28          | 0.31          | 0.34          | V    |  |
| current              | OCP Threshold voltage (*6)        | VCL      | 2.9           | 3             | 3.1           | V    |  |
| protection           | Delay to output                   | td-CL    | _             | 100           | 250           | ns   |  |

Notes: \*1 Applied to R2A20104FP, R2A20114FP

\*2 Applied to R2A20104SP, R2A20114SP

\*5 Applied to R2A20114FP, R2A20114SP

\*6 Applied to R2A20104FP, R2A20104SP

#### Electrical Characteristics (cont.)

 $(Ta = 25^{\circ}C, VCC = 12 V, CT = 1000 \text{ pF}, RT = 27 \text{ k}\Omega, CS1, CS2 = GND, IRAMP = 10 \text{ k}\Omega, BO = 1 V, VAC = 0 V, RS = 220 \text{ k}\Omega, FMC = GND (*1), FM = GND (*2), FB = COMP$ 

| Item         |                                | Symbol   | Min  | Тур  | Max  | Unit | Test Conditions  |
|--------------|--------------------------------|----------|------|------|------|------|--|
| Error signal | ERROR shunt current (*1)       | lerror-s | 5.0  | _    | _    | mA   |  |
|              | ERROR leakage current (*1)     | lerror-l | _    | _    | 1.0  | μA   |  |
|              | Phase error detect point       | Perror   | 1.1  | 1.35 | 1.6  | —    | Vcso1 or 2 = 2.5 V,<br>Vcso2 or 1: sweep (* <sup>7</sup> ) |
|              | OFF threshold voltage (*1)     | Voff     | 3.3  | 4.0  | 4.7  | V    |  |
|              | E-DELAY charge current (*1)    | led-c    | -55  | -36  | -20  | μA   |  |
|              | E-DELAY discharge current (*1) | led-d    | 20   | 36   | 55   | μA   |  |
|              | E-DELAY threshold voltage (*1) | Vdelay   | 2.35 | 2.45 | 2.55 | V    |  |

Notes: \*1 Applied to R2A20104FP, R2A20114FP

- \*2 Applied to R2A20104SP, R2A20114SP
- \*7 Refer to the figure shown below:

V'cso1(or 2) -----Vcso2(or 1) -Ñ CSO1(or 2) CSO2(or 1) ERROR -

 $Perror = \frac{V'cso1(or \ 2)[V] - 0.55[V]}{Vcso2(or \ 1)[V] - 0.55[V]}$ 



#### **Package Dimensions**





#### • R2A20104SP and R2A20114SP





#### Notice 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits software or information 2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product. 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc. "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc. Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics. 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, lease evaluate the safety of the final products or systems manufactured by you 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations. 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics

products.

#### 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.

- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

Refer to "http://www.renesas.com/" for the latest and detailed information.

## RENESAS

#### SALES OFFICES

### Renesas Electronics Corporation

http://www.renesas.com

Renesas Electronics America Inc. 2801 Scott Boulevard Santa Clara, CA 95050-2549, U.S.A. Tel: +1-408-588-6000, Fax: +1-408-588-6130 Renesas Electronics Canada Limited 9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3 Tel: +1-905-237-2004 **Renesas Electronics Europe Limited** Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K Tel: +44-1628-585-100, Fax: +44-1628-585-900 Renesas Electronics Europe GmbH Arcadiastrasse 10, 40472 Düsseldorf, German Tel: +49-211-6503-0, Fax: +49-211-6503-1327 Renesas Electronics (China) Co., Ltd. Room 1709, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100191, P.R.China Tel: +88-10-8235-1155, Fax: +88-10-8235-7679 Renesas Electronics (Shanghai) Co., Ltd. Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, P. R. China 200333 Tei: +86-21-2226-0888, Fax: +86-21-2226-0999 Renesas Electronics Hong Kong Limited Non-sease Lectronics nong round Limited Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong Tel: +852-2265-6688, Fax: +852 2886-9022 Renesas Electronics Taiwan Co., Ltd. 13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan Tel: +886-2-8175-9600, Fax: +886 2-8175-9670 Renesas Electronics Singapore Pte. Ltd. 80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949 Tel: +55-631-30200, Fax: +65-6213-0300 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia +60-3-7955-9390, Fax: +60-3-7955-9510 Renesas Electronics Malaysia Sdn.Bhd. Unit 1207. Block B. Menara Amcorp. Amco Renesas Electronics India Pvt. Ltd. No.777C, 100 Feet Road, HAL II Stage, Indiranagar, Bangalore, India Tel: +91-80-67208700, Fax: +91-80-67208777 Renesas Electronics Korea Co., Ltd. 12F., 234 Teheran-ro, Gangnam-Gu, Seoul, 135-080, Korea Tel: +82-2-558-3737, Fax: +82-2-558-5141